



Type Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 355LKA 4																																																																																												
				Product Code: 3GJM352810-_DG																																																																																												
				Protection type: Ex d I Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3089 X / IECEx LCI 04.0008X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>500</td> <td>1490</td> <td>501</td> <td>0,86</td> <td>S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>500</td> <td>1490</td> <td>865</td> <td>0,86</td> <td>S1</td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>500</td> <td>1491</td> <td>843</td> <td>0,85</td> <td>S1</td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty	3-Motor	690	Y 50	500	1490	501	0,86	S1	Insul.cl.F	400	D 50	500	1490	865	0,86	S1	IP66	415	D 50	500	1491	843	0,85	S1																																																						
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	500	1490	501	0,86	S1																																																																																									
Insul.cl.F	400	D 50	500	1490	865	0,86	S1																																																																																									
IP66	415	D 50	500	1491	843	0,85	S1																																																																																									
Cold resistance				Insulation resistance at 57 °C			Overload																																																																																									
Line Ambient: 22 °C				4200 MΩ 1000 V			Torque 160% 15s																																																																																									
U ₁ - V ₁ 0,00248 Ω																																																																																																
U ₁ - W ₁ 0,00248 Ω																																																																																																
V ₁ - W ₁ 0,00248 Ω																																																																																																
				High-voltage test winding 2400 V			60 s																																																																																									
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>400,0</td> <td>D 50</td> <td>266,4</td> <td>6,60</td> <td></td> <td>1500</td> <td>0,04</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>67,2</td> <td>D 50</td> <td>865,3</td> <td>31,1</td> <td></td> <td>0</td> <td>0,31</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>3205</td> <td>400,2</td> <td>D 50</td> <td>865,2</td> <td>515,6</td> <td>500,0</td> <td>1491</td> <td>0,86</td> <td>97,0</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>2406</td> <td>400,4</td> <td>D 50</td> <td>671,4</td> <td>368,5</td> <td>375,0</td> <td>1494</td> <td>0,83</td> <td>97,0</td> </tr> <tr> <td>~50% load</td> <td>1602</td> <td>400,6</td> <td>D 50</td> <td>494,4</td> <td>258,8</td> <td>250,0</td> <td>1496</td> <td>0,76</td> <td>96,6</td> </tr> <tr> <td>~25% load</td> <td>807,7</td> <td>400,9</td> <td>D 50</td> <td>348,1</td> <td>132,2</td> <td>125,0</td> <td>1498</td> <td>0,55</td> <td>94,6</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		400,0	D 50	266,4	6,60		1500	0,04		Locked rotor test		67,2	D 50	865,3	31,1		0	0,31		Thermal test (100% load)	3205	400,2	D 50	865,2	515,6	500,0	1491	0,86	97,0	Partial load points:										~75% load	2406	400,4	D 50	671,4	368,5	375,0	1494	0,83	97,0	~50% load	1602	400,6	D 50	494,4	258,8	250,0	1496	0,76	96,6	~25% load	807,7	400,9	D 50	348,1	132,2	125,0	1498	0,55	94,6
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		400,0	D 50	266,4	6,60		1500	0,04																																																																																								
Locked rotor test		67,2	D 50	865,3	31,1		0	0,31																																																																																								
Thermal test (100% load)	3205	400,2	D 50	865,2	515,6	500,0	1491	0,86	97,0																																																																																							
Partial load points:																																																																																																
~75% load	2406	400,4	D 50	671,4	368,5	375,0	1494	0,83	97,0																																																																																							
~50% load	1602	400,6	D 50	494,4	258,8	250,0	1496	0,76	96,6																																																																																							
~25% load	807,7	400,9	D 50	348,1	132,2	125,0	1498	0,55	94,6																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>61</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>32</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>42</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		61	1	1 Resistance	Frame :		32	2	2 Thermocouples	Bearing D-end :		42	2	3 Thermometer	Ambient Temperature :	25		2																																																														
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		61	1	1 Resistance																																																																																												
Frame :		32	2	2 Thermocouples																																																																																												
Bearing D-end :		42	2	3 Thermometer																																																																																												
Ambient Temperature :	25		2																																																																																													
<p style="text-align: right;">Starting current (I_S / I_N) : 7,39 Locked rotor torque (T_L / T_N) : 2,77</p> <p>These tests have been carried out on motor no. 3G1F1535281418, on date 2015-09-30, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p style="text-align: right;">Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.