

TYPE APPROVAL CERTIFICATE

Certificate No:
TAA00000YB
Revision No:
3

This is to certify:

That the DC Power Supply

with type designation(s)

CP-C.1-24/5.0(-L), CP-C.1-24/10.0(-L), CP-C.1-24/20.0(-L), CP-C.1-24/5.0-C, CP-C.1-24/10.0-C, CP-C.1-24/20.0-C

Issued to

ABB Stotz-Kontakt GmbH
Heidelberg, Germany

is found to comply with

DNV rules for classification – Ships, offshore units, and high speed and light craft

Application :

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.

Location classes:

Temperature B
Humidity B
Vibration A
EMC A, B (limitation to be observed)
Enclosure A

Issued at **Hamburg** on **2022-05-17**

This Certificate is valid until **2027-05-16**.

DNV local station: **Augsburg**

Approval Engineer: **Dariusz Lesniewski**

for **DNV**

.....
Joannis Papanuskas
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Product description

Primary switched mode power supply.

For all models:

Rated output voltage: 24 V DC

Adjustment range of the output voltage: 22.5-28.5 V DC

Mounting: DIN Rail (EN 60715)

Degree of protection: IP20

DC OK – signaling output (relay)

Power reserve signaling output (transistor)

Model related:	CP-C.1-24/5.0	CP-C.1-24/10.0	CP-C.1-24/20.0
	CP-C.1-24/5.0-L	CP-C.1-24/10.0-L	CP-C.1-24/20.0-L
	CP-C.1-24/5.0-C	CP-C.1-24/10.0-C	CP-C.1-24/20.0-C
Rated input voltage AC (50-60 Hz)	100-240 V	100-240 V	100-240 V
Rated input voltage DC (see limitation)	90-300 V	90-300 V	90-300 V
Rated output current ($\leq 60^{\circ}\text{C}$)	5.0 A	10 A	20 A
Derating of the output current ($60^{\circ}\text{C} < T_a \leq 70^{\circ}\text{C}$)	2.5 %/ $^{\circ}\text{C}$	2.5 %/ $^{\circ}\text{C}$	2.5 %/ $^{\circ}\text{C}$
Reserve output current ($\leq 40^{\circ}\text{C}$)	7.6 A	15.0 A	26.0 A
Rated output power	120 W	240 W	480 W

*(-C): with coated PCB

*(-L): light grey cover colour (RAL7035)

Place of manufacture

Dongguan Teamwise Electronic Co., Ltd.

No.1, Ao Bei Road, Cross Xiang Xin West Road

Yantian, Fenggang, Dongguan, Guangdong, China

Application/Limitation

DC supply is only allowed on stabilized, controlled secondary circuits.

Location class EMC-B: only for models with 10A & 20A rated output current and only at rated input voltage of 230V AC.

Approval conditions

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNV, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV rules for classification of ships Pt.4 Ch.9 Control and monitoring systems.

Type Approval documentation

Tests carried out

Applicable tests according to class guideline DNV-CG-0339, August 2021.

Marking of product

The products to be marked with:

- manufacturer name
- model name
- serial number
- power supply ratings

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications



Job Id: **262.1-023464-4**
Certificate No: **TAA00000YB**
Revision No: **3**

- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE