



$S = \begin{cases} \text{Ø11 - Special IM 2001/*11} \\ \text{M8 - Special IM 2101/*11} \end{cases}$ 
**M2AA 080**

**Additional information:**

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador  
 VC226: Flange ring FF 130 / Aro brida FF 130 // VC227: Flange ring FT 130 / Aro brida FT 130

<b>Motor Dimension Print</b>		Motor Type : M2AA 080	Document Nº : 3GZE 500 080-941.005
Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11			
Unit : Discret Automation & Motion - Fábrica Motores	Issued by : ERM/ A. Caubera	Replaces :	
Date : 2012-11-29	Approved by : ERM/ G. Blanes	Replaced by :	
<b>Asea Brown Boveri, S.A.</b>	Customer Reference :		<b>ABB</b>