

## TECHNICAL DATA SHEET

**PMA Accessories - SGB - Tube clamp**

Steel, galvanized

**PMA**

CE

**Applications:**

- In wide range of applications in all industries

**Features & Benefits:**

- For the mounting of static conduits
- Elastomer profile, free from halogens
- Smooth connection to PMAFLEX corrugated conduits
- Good resistance to ozone and ageing

**Materials:**

- Clamp: galvanized steel (stainless steel available on request)
- Profile: elastomer (EPDM)

**Compatible with:**

- PMAFLEX Pro Conduits
- PMAFLEX Multilayer Conduits
- PMAFLEX Conduits
- PMA Smart Line Conduits

**Conforms to:**

- DIN 3016

**Chemical properties:**

- Resistant to alcohols, acids and alkalies  
Please refer to [www.pma.ch](http://www.pma.ch)  
(Technical Information / Chemical Resistance)

**Environmental properties:**

- Free from halogens and cadmium
- RoHS and REACH compliant


**Product selection:**

Part no.	Conduit size	Dimensions in mm (nom.)					Weight	Packing unit
		d1	A	B	C	M		
	NW	d1	A	B	C	M	kg/100 pcs	pcs/PU
SGB-07	7	10.0	24.0	12.5	11.0	M4	0.4	100
SGB-07-6.4	7	10.0	33.0	18.5	16.5	M6	1.0	100
SGB-09	10	12.0	26.0	12.5	12.0	M4	0.5	100
SGB-09-6.4	10	12.0	35.0	18.5	17.5	M6	1.1	100
SGB-09-8.4	10	12.0	41.5	25.0	20.5	M8	2.0	100
SGB-11	12	15.0	29.0	12.5	13.5	M4	0.5	100
SGB-11-6.4	12	15.0	38.0	18.5	19.0	M6	1.3	100
SGB-11-8.4	12	15.0	44.5	25.0	22.0	M8	2.0	100
SGB-16	17	21.0	38.0	15.0	16.5	M5	0.9	100
SGB-16-6.4	17	21.0	44.0	18.5	22.0	M6	1.5	100
SGB-16-8.4	17	21.0	45.5	25.0	25.0	M8	1.5	100
SGB-21	23	28.0	45.0	15.0	20.0	M5	1.1	50
SGB-21-6.4	23	28.0	51.0	18.5	25.5	M6	1.9	50
SGB-21-8.4	23	28.0	57.5	25.0	28.5	M8	3.7	50
SGB-29	29	34.0	57.0	18.5	28.5	M6	2.2	30
SGB-36	36	41.0	64.0	18.5	32.0	M6	2.5	20
SGB-36-8.4	36	41.0	70.5	25.0	35.0	M8	4.8	20
SGB-48	48	53.0	76.0	18.5	38.0	M6	3.4	20

For bigger sizes please see SGS product range data sheet No. 60021

For all-polyamide products please see GL/GH product range data sheets No. 60024 / No. 60025

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	- 50 ... + 105 °C		PMA DO 9.21-4510
	+ 120 °C		
	+ 160 °C		

ABB Switzerland Ltd,  
PMA Cable Protection  
Aathalstrasse 90  
8610 Uster, Switzerland  
Phone: +41 58 585 00 11  
pma-info@ch.abb.com  
www.pma.ch

Let's write the future.  
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

