


MULTIPLES OF CURRENT RATING (In)



**Time Current Curve**

Available Ratings (Amperes)

| Type  | Model | Trip Unit | Frame Amps | Current Rating (In) |
|-------|-------|-----------|------------|---------------------|
| Power | E6.2  | Ekip DIP  | 6000       | 4000 6000<br>5000   |

Voltage Rating: 635 Vac, 50 to 60 hz systems

electrification.us.abb.com

**Power Circuit Breaker**

**Type Emax E6.2 with Ekip DIP LSI/LSIG Short Time I2T OFF**

**Operating Conditions:** Curves apply at 50 to 60 Hertz and ambient temperature from -25°C to +70°C up to an altitude of 2000 meters. Electronic trip units do not undergo any variations in performance as the temperature varies, but, in the case of temperatures exceeding +40°C, the maximum setting for protection L (protection against overloads) must be reduced, as indicated in the UL Catalog.

**Interrupting Ratings:** The pickup setting for each interrupting rating is listed below. Tolerance is in parentheses.  
**H-A:** 100,000 (minus 10% or plus 0%)  
**V-A:** 100,000 (minus 10% or plus 0%)

**Ground Fault:** Refer to TCC 9AKK108468A2269 for ground fault curve