


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,  
16 positions, linear switching.  
Min. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 9,  
the preceding pos. was 8.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,  
16 linjär koppling.  
Min antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 9,  
föregående läge var 8.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	

The tap-changer is shown in pos. 9,  
the preceding pos. was 8.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 9,  
föregående läge var 8.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
tap-changer. Dashed lines show leads belonging  
to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
lindningskopplaren. Streckade linjer visar  
ledare som tillhör anslutningsdonet.

Sheet	Cont									
	Year	Week								
Form No.	Dept									
	Rev Ind	Revision	Appd	Year	Week					
Drawn by	Accepted by qual control	Accepted for prod by		Description (English)		DATA ORIGINAL				
	L.Oberg	M.Haggmar		CONNECTION DIAGRAM						
	Design checked by	Drawn by	Description (own language)		File name					
Design checked by	H.Sundberg	A.Wang	KOPPLINGSSHEMA							
	Drawing checked by	Issued by Dept	Year	Week			Lang	Sheet		
ABB	N.Gustavsson	CO/TK	14	02			1	Cont		
					1ZSC004308-AAM		-			