

KM26 Magnetic level gauge

Helping to keep worldwide infrastructure at a safe level, day-in and day-out

Key features



Engineered to Order



No electric power



Integrate transmitters, switches & accessories



Adaptable solution



Non-invasive magnetic indicator

Installation and service – fast & easy



No field calibration



5 Year warranty



Easy start-up and low maintenance



Fully factory assembled with all quality reports

Industrial design and world class manufacturing



NDE, PMI, NACE tests



ASME U, UM, S stamping



Wide range of applications: Oil & Gas, Petrochem, chemical, Power etc.

Wide environmental and process conditions



RoHS 2.0




ATEX




PED



EAC Ex




IP 68



-195°C to 537°C



Upto 344 bar / 5000 psi



Advantages



Full fabrication, assembly and accessories installed, tested and calibrated and shipped from factory results in lower cost of ownership



No piping modifications or process interruptions to add transmitters and switches to a KM26 results in lower cost of ownership



Superior float design results in increased accuracy of level measurement increasing the energy efficiency and throughput.



Easy blow down or flush of chamber, no disassembly required; minimum spare parts requirements resulting in increase in productivity



Fewer potential leak points, no hazardous liquids in the indicator; no glass under high pressure or temperature