



Test Report				Date of issue: 4.6.2014					
				Serial No.: 3GF10021467					
				Type: M3JP 315SMB 4 IMB3/IM1001					
				Product Code: 3GJP312220-ADG					
				Protection type: Ex d IIB T4 Gb					
				Cert. No.: LCIE 11 ATEX 3090X / IECEX LCI 04.0007X					
Rating:									
	V	Hz	kW	r/min	A	cos φ	Duty		
3~Motor	690	Y 50	132	1487	132	0,86	S1		
Insul.cl.F	400	D 50	132	1487	233	0,86	S1		
IP55	415	D 50	132	1488	227	0,85	S1		
Ambient temp. +50°C									
Resistance				Insulation resistance at 60,0 °C		Overload			
Line	Ambient: 21,0 °C			15000 MΩ 1000 V		Torque 160 % 15s			
U <sub>1</sub> - V <sub>1</sub>	0,01680 Ω								
U <sub>1</sub> - W <sub>1</sub>	0,01679 Ω								
V <sub>1</sub> - W <sub>1</sub>	0,01678 Ω								
				High-voltage test winding 2400 V		60 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]
No load test		400,0 D	50	72,1	2,19		1500	0,04	
Locked rotor test		73,9 D	50	232,0	9,42		0	0,32	
Thermal test (100% load)	847,7	400,0 D	50	234,8	138,3	132,0	1487	0,85	95,4
Partial load points:									
~75% load	631,0	400,1 D	50	181,5	103,5	99,0	1491	0,82	95,7
~50% load	427,5	400,1 D	50	133,5	69,2	66,0	1494	0,75	95,4
~25% load	215,0	400,1 D	50	93,9	35,5	33,0	1497	0,55	93,1
Temperature rise at rated load.				[°C]	[K]	Method		Measurement method	
Stator winding :				61,7	1	1 Resistance			
Frame :				27,0	2	2 Thermometer			
Bearing D-end :				46,3	2	3 Thermocouples			
Ambient Temperature :				25,0	2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer			Date of test		20.4.2010				
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211		Telefax +358 10 22 47372	

Computer print-out valid without signature.