


TECHNICAL DATA SHEET - INTERACTIVE PDF

Couplings, flexible, explosion-proof

XP Flex stainless steel

T&B® Fittings



Used to make flexible connections in hazardous locations

Certifications / Standards:



3-Part Specification : 26 05 33.56

End User Tools

Features & Benefits:

- Corrosion resistant design, ideal for wash down areas
- Flexible construction with arc-resistant inner sleeve
- Terminated with two threaded male fittings
- NPT threads

Applications:

- Used to achieve tight bends in conduit systems in confined spaces
- Can be used to connect stationary equipment to equipment that vibrates

Conforms to:

- cULus listed- UL1203
- Class I Div 1 Groups A,B,C,D : ½" - ¾"
- Class I Div 1 Groups C,D : 1" - 2"
- Class II Div 1 Groups E,F,G : ½" - 2"
- IP69 Rated for wet locations

Material

- Body: Flexible stainless steel 316
- Fitting: Stainless steel 316


Explosion-proof flexible couplings

Product selection					
Part no.	Hub Size	Flexible length	A	B	
			inches	inches	
XPLFL14S	½"	4"	1.73	1.34	
XPLFL16S	½"	6"	1.73	1.34	
XPLFL18S	½"	8"	1.73	1.34	
XPLFL110S	½"	10"	1.73	1.34	
XPLFL112S	½"	12"	1.73	1.34	
XPLFL115S	½"	15"	1.73	1.34	
XPLFL118S	½"	18"	1.73	1.34	
XPLFL121S	½"	21"	1.73	1.34	
XPLFL124S	½"	24"	1.73	1.34	
XPLFL127S	½"	27"	1.73	1.34	
XPLFL130S	½"	30"	1.73	1.34	
XPLFL133S	½"	33"	1.73	1.34	
XPLFL136S	½"	36"	1.73	1.34	
XPLFL24S	¾"	4"	1.73	1.77	
XPLFL26S	¾"	6"	1.73	1.77	
XPLFL28S	¾"	8"	1.73	1.77	
XPLFL210S	¾"	10"	1.73	1.77	
XPLFL212S	¾"	12"	1.73	1.77	
XPLFL215S	¾"	15"	1.73	1.77	
XPLFL218S	¾"	18"	1.73	1.77	
XPLFL221S	¾"	21"	1.73	1.77	
XPLFL224S	¾"	24"	1.73	1.77	
XPLFL227S	¾"	27"	1.73	1.77	
XPLFL230S	¾"	30"	1.73	1.77	
XPLFL233S	¾"	33"	1.73	1.77	
XPLFL236S	¾"	36"	1.73	1.77	
XPLFL36S	1"	6"	2.13	2.05	
XPLFL38S	1"	8"	2.13	2.05	
XPLFL310S	1"	10"	2.13	2.05	
XPLFL312S	1"	12"	2.13	2.05	
XPLFL315S	1"	15"	2.13	2.05	
XPLFL318S	1"	18"	2.13	2.05	
XPLFL321S	1"	21"	2.13	2.05	

Note: Product must be installed in accordance with applicable national and local electrical codes.

Product selection					
Part no.	Hub Size	Flexible length	A	B	
			inches	inches	
XPLFL324S	1"	24"	2.13	2.05	
XPLFL327S	1"	27"	2.13	2.05	
XPLFL330S	1"	30"	2.13	2.05	
XPLFL333S	1"	33"	2.13	2.05	
XPLFL336S	1"	36"	2.13	2.05	
XPLFL412S	1 ¼"	12"	2.13	2.56	
XPLFL415S	1 ¼"	15"	2.13	2.56	
XPLFL418S	1 ¼"	18"	2.13	2.56	
XPLFL421S	1 ¼"	21"	2.13	2.56	
XPLFL424S	1 ¼"	24"	2.13	2.56	
XPLFL427S	1 ¼"	27"	2.13	2.56	
XPLFL430S	1 ¼"	30"	2.13	2.56	
XPLFL433S	1 ¼"	33"	2.13	2.56	
XPLFL436S	1 ¼"	36"	2.13	2.56	
XPLFL512S	1 ½"	12"	2.56	3.19	
XPLFL515S	1 ½"	15"	2.56	3.19	
XPLFL518S	1 ½"	18"	2.56	3.19	
XPLFL521S	1 ½"	21"	2.56	3.19	
XPLFL524S	1 ½"	24"	2.56	3.19	
XPLFL527S	1 ½"	27"	2.56	3.19	
XPLFL530S	1 ½"	30"	2.56	3.19	
XPLFL533S	1 ½"	33"	2.56	3.19	
XPLFL536S	1 ½"	36"	2.56	3.19	
XPLFL612S	2"	12"	2.6	3.19	
XPLFL615S	2"	15"	2.6	3.19	
XPLFL618S	2"	18"	2.6	3.19	
XPLFL621S	2"	21"	2.6	3.19	
XPLFL624S	2"	24"	2.6	3.19	
XPLFL627S	2"	27"	2.6	3.19	
XPLFL630S	2"	30"	2.6	3.19	
XPLFL633S	2"	33"	2.6	3.19	
XPLFL636S	2"	36"	2.6	3.19	

Note: Product must be installed in accordance with applicable national and local electrical codes.



tnb.abb.com (US/Latin America)
tnb.ca.abb.com (Canada)
abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. © 2021 ABB Installation Products Inc. and/or its related companies. All Rights Reserved.