

# ABB | ReliaGear® XFMR - Transformer




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T11C1458G03**


**300.0 KVA    60 HZ    3 PH    3.6 % IMP**  
**40 C AMB.    150 C RISE    220 C SYSTEM IS-19C**

**JUMPER CONNECTION**  
**TAP VOLTS**  
 1-2 224  
 2-3 216  
 3-4 208

**PRIMARY (H)    208 VOLTS (LINE-LINE)**  
**SECONDARY (X)    208 VOLTS (LINE-LINE)**  
                           **120 VOLTS (LINE-NEUTRAL)**



**COIL TAP ARRANGEMENT**



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
3720 LB	
1687.4 Kg	<b>NOG</b>
93387	<b>N438!</b>
DX79C	<b>091724</b>



ELECTROSTATIC GROUND SHIELD IN EACH PHASE

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1079G06  
**SUITABLE FOR NONSINUSOIDAL CURRENT LOAD WITH K-FACTOR NOT TO EXCEED 13**

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001

**COPPER CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL**  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

**NEMA CLASS AA DRY TYPE TRANSFORMER**

Meets DOE 2016 efficiency


ASSEMBLED IN MEXICO

Note:

Outline: 303B112GEDXP79C



\*2M000000\*



\*3M000000\*