



# EC DECLARATION OF CONFORMITY

(supplier's name) We ABB SACE S.p.A

(address) VIALE VICENZA, 61

36063 - MAROSTICA (VI)

declare under our sole responsibility that the product : \_\_\_\_\_

CABLE LADDERS H100

(name,type or model,lot,batch or serial number,possibly sources and numbers of items)

ARTICLES : IN ATTACHED

to which this declaration relates is in conformity with the following standard(s) or other  
normative/documents EN 61537

(title and/or number and date of issue of the standard(s) or other normative document(s))

following the provisions of the Directive(s) 73/23 CEE MODIFIED BY 93/68 CEE

MAROSTICA, 11/03/2002

(Place and date of issue)

02

(last two digits of the year in which the mark was affixed)

ABB SACE S.p.A  
TECHNICAL MANAGER  
ENZO RIZZI


(seal, name and signature of authorized person)

Mod. 379 - 12/94 - 900

1SLT000017D00

# Industrial metal trunkings

## Cable ladders H 100



Article	For cable ladder base (mm)	Length (mm)	Unit/pack-metres
---------	----------------------------	-------------	------------------

### Cable ladder

09 410	100	3000	3
09 411	200	3000	3
09 412	300	3000	3
09 413	400	3000	3
09 414	500	3000	3
09 415	600	3000	3

### Snap-on cover

09 430	100	3000	3
09 431	200	3000	3
09 432	300	3000	3
09 433	400	3000	3
09 434	500	3000	3
09 435	600	3000	3


Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

### 90° flat corner

Base		
09 450	100	1
09 451	200	1
09 452	300	1
09 453	400	1
09 454	500	1
09 455	600	1
Cover		
09 470	100	1
09 471	200	1
09 472	300	1
09 473	400	1
09 474	500	1
09 475	600	1

# Industrial metal trunkings

## Cable ladders H 100



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

### 45° flat corner

Base		
09 490	100	1
09 491	200	1
09 492	300	1
09 493	400	1
09 494	500	1
09 495	600	1
Cover		
09 510	100	1
09 511	200	1
09 512	300	1
09 513	400	1
09 514	500	1
09 515	600	1

### Flat tee


Base		
09 530	100	1
09 531	200	1
09 532	300	1
09 533	400	1
09 534	500	1
09 535	600	1
Cover		
09 550	100	1
09 551	200	1
09 552	300	1
09 553	400	1
09 554	500	1
09 555	600	1

### Flat cross

Base		
09 570	100	1
09 571	200	1
09 572	300	1
09 573	400	1
09 574	500	1
09 575	600	1
Cover		
09 590	100	1
09 591	200	1
09 592	300	1
09 593	400	1
09 594	500	1
09 595	600	1

# Industrial metal trunkings

## Cable ladders H 100



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

### Vertical inside and outside riser adjustable from 0° to 90°

09 610	100	1
09 611	200	1
09 612	300	1
09 613	400	1
09 614	500	1
09 615	600	1

Use straight covers for covering

### 90° vertical inside riser

Base		
09 968	100	1
09 969	200	1
09 970	300	1
09 971	400	1
09 972	500	1
09 973	600	1

Cover		
09 927	100	1
09 928	200	1
09 929	300	1
09 930	400	1
09 931	500	1
09 932	600	1


### 90° vertical outside riser

Base		
09 986	100	1
09 987	200	1
09 988	300	1
09 989	400	1
09 990	500	1
09 991	600	1

Cover		
09 948	100	1
09 949	200	1
09 950	300	1
09 951	400	1
09 952	500	1
09 953	600	1

# Industrial metal trunkings

## Cable ladders H 100



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------

### Concentric reducer

#### Base

09 650	200/100	1
09 651	300/100	1
09 652	300/200	1
09 653	400/200	1
09 654	400/300	1
09 655	500/300	1
09 656	500/400	1
09 657	600/400	1
09 658	600/500	1

#### Cover

09 670	200/100	1
09 671	300/100	1
09 672	300/200	1
09 673	400/200	1
09 674	400/300	1
09 675	500/300	1
09 676	500/400	1
09 677	600/400	1
09 678	600/500	1

### Left reducer

#### Base


09 690	200/100	1
09 691	300/100	1
09 692	300/200	1
09 693	400/200	1
09 694	400/300	1
09 695	500/300	1
09 696	500/400	1
09 697	600/400	1
09 698	600/500	1

#### Cover

09 710	200/100	1
09 711	300/100	1
09 712	300/200	1
09 713	400/200	1
09 714	400/300	1
09 715	500/300	1
09 716	500/400	1
09 717	600/400	1
09 718	600/500	1

# Industrial metal trunkings

## Cable ladders H 100



Article	For cable ladder base (mm)	Unit/pack-pieces
---------	----------------------------	------------------


### Right reducer

Base		
09 730	200/100	1
09 731	300/100	1
09 732	300/200	1
09 733	400/200	1
09 734	400/300	1
09 735	500/300	1
09 736	500/400	1
09 737	600/400	1
09 738	600/500	1

Cover		
09 750	200/100	1
09 751	300/100	1
09 752	300/200	1
09 753	400/200	1
09 754	400/300	1
09 755	500/300	1
09 756	500/400	1
09 757	600/400	1
09 758	600/500	1

# Industrial metal trunkings

## Cable ladders H 100



Article	Description	Unit/pack-pieces
---------	-------------	------------------

### Mechanical joint

Includes 2 plates complete with screws and nuts.

09 763	Straight joint	1/20
09 764	Horizontal adjustable joint	1/20
09 765	Vertical adjustable joint	1/10

Article	For reductions of (mm)	Unit/pack-pieces
---------	------------------------	------------------

### Couplers for left and right reduction

09 803	50	1
09 804	100	1
09 805	200	1


Article	Length (mm)	Unit/pack-metres
---------	-------------	------------------

### Metal divider

09 901	2000	2/10
--------	------	------

# Industrial metal trunkings

## Cable ladders H 100



Article	Description	Unit/pack-pieces
---------	-------------	------------------

### Square and cover spacer

09 903	Spacer for cover H 50 mm	1/20
09 904	Square for fastening brackets – inner	1/50
09 905	Square for fastening brackets – outer	1/50

### Fastening components

07 848	Round-headed M6x10 screw with nut	100
07 818	Hexagonal-headed M8x16 screw with nut	100
07 819	Hexagonal-headed M10x20 screw with nut	100

For fastening squares and spacers and for earth connections

Article	Length (mm)	Unit/pack-metres
---------	-------------	------------------

### Earth cable

09 906	Cable with 4mm <sup>2</sup> section	20
--------	-------------------------------------	----