


---

# VanLien/ABB Noodverlichting


## Spacingtabellen



## Spacingtabellen





### SER-(C/D)SI - 5 LUX

Middelpunt object - plafond (C)	Armatuur tot muur (L)
0.5	0.8
1.0	1.2
1.5	1.7
2.0	2.0







## DIB 325/140B/1

### DIB B - 0.5 LUX





Hoogte (m)				
2.8	4.1	10.5	3.3	8.2
3.0	4.2	10.7	3.4	8.4
3.5	4.4	11.2	3.5	8.9
4.0	4.4	11.7	3.6	9.4
6.0	4.2	12.6	2.9	10.2
8.0	-	12.4	-	8.8
10.0	-	6.8	-	4.7

### DIB B - 1 LUX





Hoogte (m)				
2.8	3.1	8.3	2.6	6.6
3.0	3.2	8.5	2.6	6.8
3.5	3.3	8.7	2.5	7.1
4.0	3.1	8.8	2.2	7.3
6.0	-	8.3	-	5.7

## DIB 325/140A/1

### DIB A - 0.5 LUX





Hoogte (m)				
2.8	3.7	9.8	3.3	8.4
3.0	3.8	9.9	3.4	8.6
3.5	3.9	10.2	3.6	9.0
4.0	4.0	10.5	3.7	9.5
6.0	3.4	11.3	3.1	10.6
8.0	0.4	10.2	0.4	9.4
10.0	-	6.3	-	6.4

### DIB A - 1 LUX





Hoogte (m)				
2.8	2.8	7.4	2.6	6.7
3.0	2.8	7.5	2.6	6.9
3.5	2.8	7.8	2.6	7.2
4.0	2.5	8.0	2.4	7.4
6.0	-	6.8	-	6.2
8.0	-	0.8	-	0.8

## CIB-TL 325/140/HF

### CIB 325/140/HF - 0.5 LUX

Hoogte (m)				
2.8	4.2	10.7	3.4	8.3
3.0	4.3	10.9	3.5	8.5
3.5	4.5	11.4	3.6	9.0
4.0	4.5	12.0	3.7	9.5
6.0	4.4	12.9	3.1	10.6
8.0	-	13.0	-	9.3
10.0	-	7.9	-	5.5

### CIB 325/140/HF - 1 LUX

Hoogte (m)				
2.8	3.2	8.4	2.6	6.7
3.0	3.2	8.6	2.6	6.9
3.5	3.3	8.9	2.6	7.2
4.0	3.2	9.1	2.3	7.4
6.0	-	8.9	-	6.1

## Spacingtabellen

### CIB-TL 325/140/24

CIB 325/140/24 - 0.5 LUX

Hoogte (m)				
2.8	4.3	11.1	3.4	8.6
3.0	4.4	11.3	3.5	8.8
3.5	4.6	11.8	3.7	9.3
4.0	4.7	12.3	3.8	9.8
6.0	4.8	13.4	3.4	11.0
8.0	2.1	13.9	0.8	10.1
10.0	-	9.9	-	6.7

CIB 325/140/24 - 1 LUX

Hoogte (m)				
2.8	3.3	8.7	2.7	6.9
3.0	3.4	8.9	2.8	7.1
3.5	3.4	9.3	2.7	7.5
4.0	3.5	9.4	2.5	7.7
6.0	-	9.5	-	6.8
8.0	-	4.1	-	1.5

### NBN

NBN - 0.5 LUX

Hoogte (m)				
2.5	3.9	10.9	3.1	7.8
3.0	3.8	11.2	3.4	8.4
3.5	3.9	11.2	3.5	8.9
4.0	4.0	10.7	3.7	9.3
4.5	4.1	10.8	3.7	9.8
5.0	3.9	11.0	3.6	10.0
5.5	3.7	11.1	3.5	10.3

NBN - 1 LUX

Hoogte (m)				
2.5	2.7	7.8	2.5	6.3
3.0	2.8	7.6	2.6	6.8
3.5	2.8	7.7	2.6	7.1
4.0	2.6	7.9	2.4	7.4
4.5	2.3	8.1	2.1	7.4
5.0	1.7	7.8	1.7	7.3
5.5	1.2	7.5	1.2	6.9

### NB

NB - 0.5 LUX





Hoogte (m)				
2.5	4.7	12.5	3.1	7.6
3.0	4.6	13.0	3.3	8.1
3.5	4.3	13.4	3.5	8.6
4.0	4.2	13.6	3.6	9.2
4.5	4.3	12.4	3.5	9.6
5.0	4.4	12.0	3.4	9.9
5.5	4.3	11.9	3.2	10.1

NB - 1 LUX





Hoogte (m)				
2.5	3.0	9.5	2.5	6.1
2.5	3.0	9.5	2.5	6.1
3.5	3.1	8.5	2.4	6.9
4.0	3.0	8.4	2.2	7.2
4.5	2.6	8.6	1.7	7.1
5.0	1.6	8.7	1.2	6.8

## NB 08/24

### NB 08/24 - 0.5 LUX





Hoogte (m)				
2.5	4.3	11.5	3.3	8.1
3.0	4.0	11.9	3.5	8.7
3.5	4.1	12.3	3.7	9.3
4.0	4.2	11.6	3.9	9.7
4.5	4.3	11.5	4.0	10.2
5.0	4.3	11.7	3.9	10.6
5.5	4.2	11.8	3.9	10.9

### NB 08/24 - 1 LUX





Hoogte (m)				
2.5	2.9	8.7	2.6	6.6
3.0	3.0	8.1	2.8	6.1
3.5	3.1	8.2	2.8	7.5
4.0	2.9	8.4	2.7	7.7
4.5	2.7	8.6	2.5	8.0
5.0	2.3	8.6	2.1	7.9
5.5	1.7	8.4	1.7	7.7

## NB 08/HF

### NB 08/HF - 0.5 LUX

Hoogte (m)				
2.5	5.1	11.2	3.2	7.9
3.0	4.9	11.5	3.4	8.5
3.5	4.0	11.6	3.6	9.0
4.0	4.1	10.9	3.8	9.5
4.5	4.1	11.1	3.8	10.0
5.0	4.1	11.2	3.8	10.2
5.5	3.9	11.4	3.6	10.5

### NB 08/HF - 1 LUX

Hoogte (m)				
2.5	2.8	8.2	2.6	6.4
3.0	2.9	7.8	2.7	6.9
3.5	2.9	7.9	2.7	7.2
4.0	2.7	8.1	2.5	7.5
4.5	2.4	8.3	2.2	7.6
5.0	1.9	8.1	1.9	7.5
5.5	1.4	7.8	1.4	7.2

## Spacingtabellen

### (I/O)LN

(I/O)LN-1 - 0.5 LUX

Hoogte (m)				
2.5	6.4	16.3	2.9	7.2
3.0	6.7	17.4	3.1	7.8
3.5	6.7	18.0	3.3	8.3
4.0	6.7	18.6	3.3	8.8
4.5	6.5	18.9	3.2	9.0
5.0	6.2	19.0	3.1	9.3
5.5	5.8	19.0	2.8	9.3

(I/O)LN - 1 LUX

Hoogte (m)				
2.5	4.7	12.7	2.3	5.9
3.0	4.7	13.3	2.3	6.3
3.5	4.4	13.4	2.2	6.5
4.0	4.0	13.4	1.9	6.6
4.5	1.6	13.1	1.4	6.5
5.0	0.3	12.4	0.1	6.1
5.5	-	11.5	-	5.6

(I/O)LN-1 + PPL - 0.5 LUX

Hoogte (m)				
2.5	6.2	15.5	2.2	5.9
3.0	6.5	16.6	2.2	6.1
3.5	6.7	17.5	2.2	6.2
4.0	6.7	18.2	1.9	6.2
4.5	6.7	18.6	1.5	6.1
5.0	6.6	19.0	0.7	5.9
5.5	6.4	19.2	-	5.5

(I/O)LN-1 + PPL - 1 LUX

Hoogte (m)				
2.5	4.8	12.4	1.5	4.4
3.0	4.7	13.0	1.2	4.4
3.5	4.7	13.5	0.6	4.2
4.0	4.5	13.5	-	3.8
4.5	-	13.3	-	3.0

### (I/O)LN






(I/O)L - 0.5 LUX

Hoogte (m)				
2.5	6.5	16.6	3.0	7.3
3.0	6.8	17.8	3.2	7.9
3.5	6.9	18.4	3.3	8.4
4.0	6.9	19.0	3.4	8.9
4.5	6.8	19.4	3.4	9.2
5.0	6.5	19.5	3.2	9.5
5.5	6.1	19.6	3.0	9.6






(I/O)L - 1 LUX

Hoogte (m)				
2.5	4.9	13.0	2.4	6.0
3.0	4.8	13.6	2.4	6.4
3.5	4.6	13.8	2.3	6.7
4.0	4.2	13.9	2.0	6.8
4.5	2.2	13.5	1.6	6.7
5.0	0.9	13.1	0.7	6.4
5.5	-	12.2	-	6.0






**(I/O)L-230HF****(I/O)L-230HF - 0.5 LUX**

Hoogte (m)					
2.5	6.7	16.8	3.0	7.5	
3.0	7.0	18.2	3.3	8.1	
3.5	7.1	18.8	3.4	8.6	
4.0	7.1	19.4	3.5	9.1	
4.5	7.0	19.9	3.5	9.4	
5.0	6.8	20.0	3.4	9.7	
5.5	6.4	20.1	3.2	9.9	






**(I/O)L-230HF - 1 LUX**

Hoogte (m)					
2.5	5.0	13.3	2.4	6.1	
3.0	5.0	13.9	2.5	6.6	
3.5	4.8	14.2	2.4	6.8	
4.0	4.4	14.2	2.2	7.0	
4.5	2.8	14.0	1.8	6.9	
5.0	1.2	13.7	1.1	6.7	
5.5	-	12.8	-	6.3	

**(I/O)L-230HF + PPL-0.5**

Hoogte (m)					
2.5	6.5	16.0	2.3	6.1	
3.0	6.8	17.2	2.3	6.4	
3.5	7.0	18.2	2.3	6.5	
4.0	7.2	19.0	2.1	6.6	
4.5	7.1	19.5	1.8	6.6	
5.0	7.0	20.0	1.3	6.4	

**(I/O)LN-1 + PPL - 1 LUX**

Hoogte (m)					
2.5	5.0	12.9	1.6	4.6	
3.0	5.1	13.6	1.4	4.8	
3.5	5.0	14.1	1.0	4.6	
4.0	4.9	14.3	-	4.2	
4.5	4.6	14.2	-	3.6	
5.0	-	14.0	-	2.6	

## Spacingtabellen

### (I/O)L-24

(I/O)L-24 - 0.5 LUX

Hoogte (m)				
2.5	6.9	17.2	3.1	7.7
3.0	7.2	18.7	3.4	8.3
3.5	7.4	19.4	3.5	8.8
4.0	7.4	20.0	3.6	9.3
4.5	7.4	20.7	3.6	9.7
5.0	7.2	20.9	3.6	10.0
5.5	6.9	21.0	3.4	10.2

(I/O)L-24 - 1 LUX

Hoogte (m)				
2.5	5.2	14.1	2.6	6.6
3.0	5.3	14.4	2.6	6.8
3.5	5.1	14.8	2.5	7.0
4.0	4.8	14.8	2.4	7.3
4.5	4.3	14.8	2.0	7.3
5.0	1.7	14.4	1.5	7.2
5.5	0.6	13.8	0.4	6.8

(I/O)L-24 + PPL - 0.5 LUX

Hoogte (m)				
2.5	6.6	16.4	2.4	6.3
3.0	7.0	17.6	2.4	6.6
3.5	7.3	18.7	2.4	6.8
4.0	7.5	19.6	2.3	6.9
4.5	7.5	20.2	2.0	6.9
5.0	7.4	20.7	1.6	6.8
5.5	7.3	21.0	0.8	6.5

(I/O)L-24 + PPL - 1 LUX

Hoogte (m)				
2.5	5.2	13.3	1.7	4.8
3.0	5.3	14.1	1.5	4.9
3.5	5.2	14.6	1.2	4.8
4.0	5.1	14.9	0.2	4.6
4.5	4.9	14.9	-	4.1
5.0	-	14.7	-	3.3

### FM-1

FM - 0.5 LUX

Hoogte (m)				
2.8	4.1	10.5	3.3	8.2
3.0	4.2	10.7	3.4	8.4
3.5	4.4	11.2	3.5	8.9
4.0	4.4	11.7	3.6	9.4
6.0	4.2	12.6	2.9	10.2
8.0	-	12.4	-	8.8
10.0	-	6.8	-	4.7





FM - 1 LUX

Hoogte (m)				
2.8	3.1	8.3	2.6	6.6
3.0	3.2	8.5	2.6	6.8
3.5	3.3	8.7	2.5	7.1
4.0	3.1	8.8	2.2	7.3
6.0	-	8.3	-	5.7







## FMN-1

### FMN - 0.5 LUX





Hoogte (m)				
2.8	3.7	9.8	3.3	8.4
3.0	3.8	9.9	3.4	8.6
3.5	3.9	10.2	3.6	9.0
4.0	4.0	10.5	3.7	9.5
6.0	3.4	11.3	3.1	10.6
8.0	0.4	10.2	0.4	9.4
10.0	-	6.3	-	6.4

### FMN - 1 LUX





Hoogte (m)				
2.8	2.8	7.4	2.6	6.7
3.0	2.8	7.5	2.6	6.9
3.5	2.8	7.8	2.6	7.2
4.0	2.5	8.0	2.4	7.4
6.0	-	6.8	-	6.2
8.0	-	0.8	-	0.8

## FM 08/HF

### FM 08/HF - 0.5 LUX





Hoogte (m)				
2.8	4.2	10.7	3.4	8.3
3.0	4.3	10.9	3.5	8.5
3.5	4.5	11.4	3.6	9.0
4.0	4.5	12.0	3.7	9.5
6.0	4.4	12.9	3.1	10.6
8.0	-	13.0	-	9.3
10.0	-	7.9	-	5.5

### FM 08/HF - 1 LUX





Hoogte (m)				
2.8	3.2	8.4	2.6	6.7
3.0	3.2	8.6	2.6	6.9
3.5	3.3	8.9	2.6	7.2
4.0	3.2	9.1	2.3	7.4
6.0	-	8.9	-	6.1

## FM 08/24

### FM 08/24 - 0.5 LUX

Hoogte (m)				
2.8	4.3	11.1	3.4	8.6
3.0	4.4	11.3	3.5	8.8
3.5	4.6	11.8	3.7	9.3
4.0	4.7	12.3	3.8	9.8
6.0	4.8	13.4	3.4	11.0
8.0	2.1	13.9	0.8	10.1
10.0	-	9.9	-	6.7

### FM 08/24 - 1 LUX

Hoogte (m)				
2.8	3.3	8.7	2.7	6.9
3.0	3.4	8.9	2.8	7.1
3.5	3.4	9.3	2.7	7.5
4.0	3.5	9.4	2.5	7.7
6.0	-	9.5	-	6.8
8.0	-	4.1	-	1.5

## Spacingtabellen

### FIX FOX FCX

F(I/O/C)X - 0.5 LUX

Hoogte (m)				
2.0	2.2	5.2	2.2	4.9
2.5	2.6	5.9	2.6	5.7
3.0	2.8	6.6	2.9	6.5
3.5	3.0	7.2	3.1	7.3
4.0	3.1	7.7	3.1	8.1
4.5	3.1	8.1	2.8	8.5
5.0	2.9	8.5	2.4	8.8

F(I/O/C)X - 1 LUX

Hoogte (m)				
2.0	1.9	4.5	2.0	4.4
2.5	2.1	5.1	2.2	5.2
3.0	2.2	5.6	2.1	5.9
3.5	2.1	6.0	1.7	6.2
4.0	0.4	6.2	0.4	6.1

### SER-(C/D)LI

SER-(C/D)LI - 0.5 LUX

Hoogte (m)				
2.0	4.5	10.2	1.3	3.8
2.5	5.2	11.8	1.3	3.7
3.0	5.9	13.3	1.3	3.7
3.5	6.5	14.7	1.3	3.6
4.0	7.0	16.0	1.3	3.6
4.5	7.5	17.3	1.3	3.6
5.0	8.0	18.4	1.2	3.6

SER-(C/D)LI - 1 LUX

Hoogte (m)				
2.0	4.0	9.0	0.9	2.6
2.5	4.6	10.5	0.9	2.6
3.0	5.2	11.8	0.9	2.6
3.5	5.6	12.9	0.9	2.6
4.0	6.0	14.1	0.8	2.6
4.5	6.4	15.1	0.7	2.5
5.0	6.7	16.0	0.5	2.5

### SER-(C/W)WI

SER-(C/D)WI - 0.5 LUX

Hoogte (m)				
2.0	3.6	8.9	3.7	9.2
2.5	3.9	9.7	4.1	10.1
3.0	4.1	10.4	4.3	10.8
3.5	4.3	11.0	4.5	11.4
4.0	4.5	11.5	4.6	12.0
4.5	4.5	11.9	4.6	12.4
5.0	4.6	12.2	4.5	12.7

SER-(C/D)WI - 1 LUX

Hoogte (m)				
2.0	2.9	7.2	3.0	7.5
2.5	3.1	7.8	3.2	8.1
3.0	3.2	8.2	3.3	8.6
3.5	3.2	8.6	3.2	9.0
4.0	3.1	8.9	3.0	9.2
4.5	2.9	9.1	2.8	9.2
5.0	2.4	9.1	2.2	9.0

## SER-CLO

SER-CLO(/24) - 0.5 LUX

Hoogte (m)				
2.5	5.0	10.7	1.4	3.3
3.0	5.9	12.4	1.6	3.6
3.5	6.7	14.1	1.7	4.0
4.0	7.4	15.8	1.8	4.3
4.5	8.1	17.5	1.9	4.6
5.0	8.9	19.1	2.0	4.9
5.5	9.6	20.5	2.1	5.1

SER-CLO(/24) - 1 LUX

Hoogte (m)				
2.5	4.8	10.0	1.2	2.8
3.0	5.5	11.7	1.3	3.1
3.5	6.2	13.4	1.4	3.4
4.0	6.9	14.8	1.5	3.7
4.5	7.5	16.3	1.5	3.9
5.0	8.1	17.7	1.5	4.1
5.5	8.8	19.1	1.4	4.2

## SER-DLO

SER-DLO - 0.5 LUX

Hoogte (m)				
2.5	5.0	10.7	1.4	3.3
3.0	5.9	12.4	1.6	3.6
3.5	6.7	14.1	1.7	3.9
4.0	7.4	15.8	1.8	4.3
4.5	8.1	17.4	1.9	4.6
5.0	8.8	19.1	2.0	4.8
5.5	9.6	20.5	2.1	5.1

SER-DLO - 1 LUX

Hoogte (m)				
2.5	4.8	10.0	1.2	2.8
3.0	5.5	11.7	1.3	3.1
3.5	6.2	13.4	1.4	3.4
4.0	6.9	14.8	1.5	3.7
4.5	7.5	16.2	1.5	3.9
5.0	8.1	17.7	1.5	4.1
5.5	8.8	19.1	1.4	4.2

## SER-CWO

SER-CWO(/24) - 0.5 LUX

Hoogte (m)				
2.5	3.7	7.9	3.7	7.9
3.0	4.2	9.2	4.2	9.2
3.5	4.7	10.4	4.6	10.4
4.0	5.0	11.5	4.9	11.5
4.5	4.9	12.4	4.2	12.4
5.0	4.0	13.2	3.6	13.2
5.5	3.7	13.9	3.3	13.8

SER-CWO(/24) - 1 LUX

Hoogte (m)				
2.5	3.3	7.4	3.3	7.4
3.0	3.6	8.5	3.5	8.5
3.5	2.8	9.3	2.6	9.3
4.0	2.6	9.9	2.2	9.9
4.5	-	9.8	-	8.4

## Spacingtabellen

### SER-DWO

SER-DWO - 0.5 LUX

Hoogte (m)				
2.5	3.7	7.9	3.7	7.9
3.0	4.2	9.2	4.2	9.2
3.5	4.6	10.3	4.6	10.3
4.0	4.9	11.5	4.9	11.5
4.5	4.7	12.4	4.1	12.4
5.0	3.9	13.2	3.5	13.2
5.5	3.7	13.8	3.2	13.7

SER-DWO - 1 LUX

Hoogte (m)				
2.5	3.3	7.4	3.3	7.4
3.0	3.5	8.4	3.5	8.4
3.5	2.8	9.3	2.5	9.3
4.0	2.5	9.9	2.1	9.8
4.5	-	9.4	-	8.1

### AQL 08/HF

AQL 08/HF - 0.5 LUX

Hoogte (m)				
2.5	5.6	13.9	3.5	8.6
3.0	6.1	14.2	3.7	9.2
3.5	6.5	15.3	3.9	9.8
4.0	7.0	16.5	4.1	10.3
4.5	7.3	17.4	4.1	10.9
5.0	7.5	18.2	4.2	11.2
5.5	7.8	19.8	4.1	11.4

AQL 08/HF - 1 LUX

Hoogte (m)				
2.5	4.6	11.3	2.8	7.0
3.0	5.0	12.2	2.9	7.5
3.5	5.3	13.1	3.0	7.9
4.0	5.5	13.9	2.9	8.1
4.5	5.6	14.5	2.7	8.2
5.0	5.5	15.1	2.4	8.4
5.5	5.3	15.6	2.1	8.2

### AQL 08/24

AQL 08/24 - 0.5 LUX






Hoogte (m)				
2.5	5.5	13.3	3.4	8.3
3.0	5.9	14.4	3.6	8.9
3.5	6.4	15.5	3.8	9.5
4.0	6.8	16.4	3.9	10.1
4.5	7.0	17.3	4.0	10.5
5.0	7.3	18.1	4.0	10.8
5.5	7.5	19.0	3.9	11.0

AQL 08/24 - 1 LUX






Hoogte (m)				
2.5	4.5	11.0	2.7	6.8
3.0	4.9	11.9	2.8	7.3
3.5	5.1	12.8	2.8	7.6
4.0	5.3	13.5	2.7	7.8
4.5	5.4	14.1	2.5	7.9
5.0	5.2	14.6	2.2	7.9
5.5	4.8	14.9	1.7	7.8

## AQL 08/1

### AQL 08/1 - 0.5 LUX






Hoogte (m)					
2.5	5.1	12.3	3.1	7.7	
3.0	5.5	13.4	3.3	8.3	
3.5	5.9	14.4	3.4	8.8	
4.0	6.2	15.2	3.5	9.2	
4.5	6.5	16.1	3.4	9.5	
5.0	6.6	16.8	3.3	9.7	
5.5	6.7	17.3	3.1	9.8	

### AQL 08/1 - 1 LUX






Hoogte (m)					
2.5	4.2	10.2	2.4	6.3	
3.0	4.5	11.1	2.5	6.6	
3.5	4.6	11.8	2.4	6.8	
4.0	4.7	12.4	2.1	6.9	
4.5	4.5	12.9	1.8	6.9	
5.0	4.1	13.1	1.2	6.7	
5.5	3.8	13.3	-	6.2	

## AQL 08/3

### AQL 08/3 - 0.5 LUX






Hoogte (m)					
2.5	4.7	11.3	2.8	7.0	
3.0	5.1	12.3	2.9	7.6	
3.5	5.4	13.2	3.0	8.0	
4.0	5.6	14.0	2.9	8.2	
4.5	5.7	14.7	2.8	8.3	
5.0	5.7	15.2	2.5	8.5	
5.5	5.4	15.7	2.2	8.4	

### AQL 08/3 - 1 LUX






Hoogte (m)					
2.5	3.8	9.4	2.1	5.7	
3.0	4.0	10.2	2.0	5.9	
3.5	4.0	10.7	1.8	6.0	
4.0	3.7	11.2	1.4	5.9	
4.5	3.4	11.4	0.5	5.6	
5.0	2.6	11.3	-	5.0	

## AQL 02/LED

### AQL 02 - 0.5 LUX

Hoogte (m)					
2.5	3.2	8.2	3.2	8.6	
3.0	3.3	8.6	3.2	8.8	
3.5	3.3	9.0	3.2	8.9	
4.0	3.2	9.2	3.0	9.0	
4.5	3.1	9.3	2.8	9.0	
5.0	2.8	9.3	2.5	8.9	
5.5	2.4	9.2	2.0	8.7	

### AQL 02 - 1 LUX

Hoogte (m)					
2.5	2.3	6.4	2.2	6.3	
3.0	2.3	6.6	2.1	6.4	
3.5	2.0	6.6	1.8	6.3	
4.0	1.6	6.5	1.3	6.1	

## Spacingtabellen

### AQL 03/HF

AQL 03/HF - 0.5 LUX

Hoogte (m)				
2.5	5.3	12.6	2.7	7.1
3.0	5.9	13.8	2.7	7.5
3.5	6.3	14.9	2.6	7.6
4.0	6.5	16.0	2.4	7.6
4.5	6.3	17.1	2.2	7.5
5.0	5.9	17.8	1.9	7.3
5.5	5.7	18.4	1.4	7.0

AQL 03/HF - 1 LUX

Hoogte (m)				
2.5	4.5	10.6	1.8	5.4
3.0	4.6	11.7	1.6	5.3
3.5	4.2	12.6	1.3	5.2
4.0	4.0	13.1	0.8	4.8

### AQL 03/1

AQL 03/1 - 0.5 LUX





Hoogte (m)				
2.5	5.0	11.8	2.4	6.5
3.0	5.5	13.0	2.3	6.7
3.5	5.8	14.1	2.1	6.7
4.0	5.5	15.1	1.9	6.6
4.5	5.1	15.9	1.6	6.4
5.0	5.0	16.3	1.0	6.0
5.5	4.9	16.0	-	5.6

AQL 03/1 - 1 LUX





Hoogte (m)				
2.5	4.1	10.0	1.5	4.7
3.0	3.7	10.9	1.2	4.6
3.5	3.6	11.5	0.8	4.3
4.0	3.4	11.1	-	3.8

## AQL 11/24





### AQL 11/24 - 0.5 LUX

Hoogte (m)				
2.5	6.2	14.9	4.6	10.8
3.0	6.8	16.3	5.0	11.9
3.5	7.3	17.4	5.4	12.9
4.0	7.7	18.6	5.7	13.9
4.5	8.1	19.7	5.9	14.6
5.0	8.5	20.7	6.0	15.2
5.5	8.8	21.6	6.2	15.9





### AQL 11/24 - 1 LUX

Hoogte (m)				
2.5	5.2	12.4	3.8	9.2
3.0	5.6	13.5	4.1	10.1
3.5	6.0	14.6	4.3	10.7
4.0	6.3	15.4	4.4	11.3
4.5	6.6	16.3	4.5	11.7
5.0	6.8	17.0	4.5	12.1
5.5	6.9	17.6	4.5	12.4

### AQL 11/24 - 1 LUX

Hoogte (m)				
6.0	6.9	18.2	4.4	12.6
6.5	6.6	18.8	4.3	12.8
7.0	6.1	19.2	4.0	12.9
7.5	5.7	19.4	3.7	12.9
8.0	5.1	19.6	3.3	12.7
8.5	4.4	19.4	2.6	12.6
9.0	3.4	18.8	1.6	12.3

### AQL 11/24 - 5 LUX

Hoogte (m)				
2.5	3.1	7.9	2.0	5.6
3.0	2.9	8.5	1.9	5.7
3.5	2.4	8.7	1.5	5.7
4.0	1.6	8.5	0.8	5.5

## Spacingtabellen

### AQL 11/HF

#### AQL 11/HF - 0.5 LUX

Hoogte (m)				
2.5	6.6	15.8	4.8	11.2
3.0	7.2	17.2	5.3	12.5
3.5	7.7	18.6	5.7	13.6
4.0	8.2	19.7	6.0	14.6
4.5	8.6	20.9	6.4	15.6
5.0	9.1	22.0	6.5	16.2
5.5	9.5	23.0	6.7	16.9

#### AQL 11/HF - 1 LUX

Hoogte (m)				
2.5	5.5	13.2	4.1	9.6
3.0	6.0	14.3	4.4	10.7
3.5	6.4	15.5	4.6	11.4
4.0	6.8	16.5	4.8	12.1
4.5	7.1	17.3	4.9	12.7
5.0	7.4	18.1	5.1	13.1
5.5	7.6	18.9	5.1	13.5

#### AQL 11/HF - 1 LUX

Hoogte (m)				
7.0	7.5	20.7	4.9	14.3
7.5	7.2	21.3	4.6	14.4
8.0	6.7	21.5	4.4	14.4
8.5	6.2	21.7	4.1	14.4
9.0	5.6	21.9	3.6	14.2
9.5	4.9	21.7	2.9	14.1
10.0	4.0	21.1	1.9	13.8

#### AQL 11/HF - 5 LUX

Hoogte (m)				
2.5	3.4	8.5	2.3	6.0
3.0	3.4	9.1	2.2	6.3
3.5	3.1	9.6	2.0	6.4
4.0	2.6	9.8	1.6	6.4
4.5	1.7	9.4	0.8	6.2



## AQL 11/1

### AQL 11/1 - 1 LUX

Hoogte (m)				
2.5	5.7	13.8	4.3	10.0
3.0	6.3	14.9	4.6	11.0
3.5	6.7	16.1	4.9	12.0
4.0	7.1	17.2	5.1	12.7
4.5	7.4	18.1	5.2	13.3
5.0	7.7	18.9	5.4	13.9
5.5	8.0	19.8	5.5	14.2

### AQL 11/1 - 1 LUX

Hoogte (m)				
8.0	8.4	21.8	5.4	15.2
8.5	7.9	23.0	5.1	15.6
9.0	7.0	23.4	4.5	15.6
9.5	6.4	23.6	4.2	15.5
10.0	5.8	23.8	3.6	15.3
10.5	5.1	23.3	2.8	15.2
11.0	3.8	22.7	1.5	14.8

### AQL 11/1 - 5 LUX

Hoogte (m)				
2.5	3.6	8.9	2.5	6.0
3.0	3.7	9.6	2.5	6.3
3.5	3.6	10.2	2.3	6.4
4.0	3.1	10.5	2.0	6.4
4.5	2.5	10.6	1.6	6.2
5.0	1.3	10.1	0.3	6.5

### AQL 11/1 - 10 LUX

Hoogte (m)				
2.5	2.5	7.2	1.6	4.9
3.0	2.0	7.5	1.3	4.9
3.5	1.1	7.2	0.4	4.7

## AQL 11/3

### AQL 11/3 - 0.5 LUX

Hoogte (m)				
2.5	5.1	12.2	3.7	9.0
3.0	5.5	13.3	4.0	9.9
3.5	5.9	14.3	4.2	10.5
4.0	6.2	15.1	4.3	11.1
4.5	6.5	16.0	4.4	11.4
5.0	6.6	16.7	4.4	11.8
5.5	6.7	17.3	4.3	12.1





### AQL 11/3 - 1 LUX

Hoogte (m)				
2.5	4.2	10.2	2.9	7.5
3.0	4.5	11.0	3.1	8.0
3.5	4.7	11.7	3.1	8.3
4.0	4.8	12.3	3.1	8.6
4.5	4.5	12.9	2.9	8.8
4.5	4.5	12.9	2.9	8.8
5.5	3.4	13.4	2.2	8.7





## Spacingtabellen

### DECO 2D28





#### DECO 2D28 - 0.5 LUX

Hoogte (m)				
2.5	6.3	15.3	6.3	15.3
3.0	6.9	16.5	6.9	16.5
3.5	7.3	17.7	7.3	17.7
4.0	7.7	18.9	7.7	18.9
4.5	8.1	20.1	8.1	20.1
5.0	8.4	20.8	8.4	20.8
5.5	8.7	21.6	8.7	21.6





#### DECO 2D28 - 1 LUX

Hoogte (m)				
2.5	5.2	12.6	5.2	12.6
3.0	5.6	13.8	5.6	13.8
3.5	5.9	14.7	5.9	14.7
4.0	6.2	15.4	6.2	15.4
4.5	6.4	16.2	6.4	16.2
5.0	6.6	16.8	6.6	16.8
5.5	6.8	17.3	6.8	17.3

#### DECO 2D28 - 5 LUX

Hoogte (m)				
2.5	3.0	7.8	3.0	7.8
3.0	3.1	8.3	3.1	8.3
3.5	3.1	8.6	3.1	8.6
4.0	3.1	8.9	3.1	8.9
4.5	2.9	8.9	2.9	8.9
5.0	2.7	8.8	2.7	8.8
5.5	2.3	8.7	2.3	8.7

#### DECO 2D28 - 15 LUX

Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9

## DECO 230

### DECO 230 - 0.5 LUX

Hoogte (m)				
2.5	8.3	20.0	8.3	20.0
3.0	9.1	21.7	9.1	21.7
3.5	9.7	23.4	9.7	23.4
4.0	10.3	25.0	10.3	25.0
4.5	10.9	26.4	10.9	26.4
5.0	11.5	27.6	11.5	27.6
5.5	12.0	28.8	12.0	28.8

### DECO 230 - 1 LUX

Hoogte (m)				
2.5	6.9	16.6	6.9	16.6
3.0	7.5	18.2	7.5	18.2
3.5	8.1	19.4	8.1	19.4
4.0	8.6	20.6	8.6	20.6
4.5	8.9	21.8	8.9	21.8
5.0	9.3	23.0	9.3	23.0
5.5	9.7	24.0	9.7	24.0

### DECO 230 - 5 LUX

Hoogte (m)				
2.5	4.4	10.8	4.4	10.8
3.0	4.6	11.5	4.6	11.5
3.5	4.8	12.3	4.8	12.3
4.0	5.0	12.8	5.0	12.8
4.5	5.2	13.3	5.2	13.3
5.0	5.2	13.8	5.2	13.8
5.5	5.2	14.1	5.2	14.1

### DECO 230 - 15 LUX

Hoogte (m)				
2.5	2.9	7.6	2.9	7.6
3.0	3.0	8.6	3.0	8.0
3.5	3.0	8.3	3.0	8.3
4.0	2.9	8.5	2.9	8.5
4.5	2.8	8.5	2.8	8.5
5.0	2.5	8.5	2.5	8.5
5.5	2.0	8.3	2.0	8.3

## Spacingtabellen

### FMN-1/11

#### FMN-1/11 - 0.5 LUX

Hoogte (m)				
2.5	5.6	14.1	4.8	11.8
3.0	5.9	15.0	5.1	12.7
3.5	6.3	15.7	5.4	13.5
4.0	6.7	16.4	5.7	14.2
4.5	7.0	17.2	5.9	14.9
5.0	7.2	18.0	6.0	15.4
5.5	7.4	18.7	6.2	15.9

#### FMN-1/11 - 1 LUX

Hoogte (m)				
2.5	4.5	11.2	3.9	9.6
3.0	4.9	11.9	4.1	10.3
3.5	5.1	12.6	4.3	10.9
3.5	5.1	12.6	4.3	10.9
4.5	5.3	14.1	4.6	11.8
5.0	5.4	14.5	4.7	12.1
5.5	5.4	14.7	4.8	12.4

#### FMN-1/11 - 5 LUX





Hoogte (m)				
2.5	2.4	6.6	2.1	5.6
3.0	2.5	6.7	2.1	5.8
3.5	2.4	6.9	2.0	6.0
4.0	1.8	7.0	1.6	6.1
4.5	1.0	7.0	0.9	6.0

#### FMN-1/11 - 10 LUX





Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9

## FM 11/24





### FM 11/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.4	4.6	11.3
3.0	5.7	14.2	4.9	12.1
3.5	6.1	14.9	5.2	12.9
4.0	6.4	15.6	5.4	13.6
4.5	6.6	16.4	5.6	14.1
5.0	6.8	17.2	5.7	14.
5.5	6.9	17.9	5.9	15.1





### FM 11/24 - 1 LUX

Hoogte (m)				
2.5	4.3	10.6	3.7	9.1
3.0	4.6	11.3	3.9	9.8
3.5	4.8	12.1	4.0	10.3
4.0	4.9	12.8	4.2	10.8
4.5	4.9	13.3	4.3	11.1
5.0	5.0	13.6	4.4	11.4
5.5	5.1	13.8	4.5	11.7

### FM 11/24 - 5 LUX

Hoogte (m)				
2.5	2.3	6.2	2.0	5.3
3.0	2.3	6.3	1.9	5.5
3.5	2.0	6.4	1.6	5.6
4.0	1.2	6.5	1.1	5.6

### FM 11/24 - 10 LUX

Hoogte (m)				
2.5	1.4	4.6	1.1	4.0
3.0	0.6	4.6	0.5	3.9

## Spacingtabellen

### FM 11/HF

FM 11/HF - 0.5 LUX

Hoogte (m)				
2.5	5.7	14.4	4.9	12.0
3.0	6.1	15.4	5.3	13.0
3.5	6.4	16.1	5.6	13.8
4.0	6.8	16.8	5.8	14.5
4.5	7.2	17.5	6.0	15.2
5.0	7.4	18.3	6.2	15.8
5.5	7.6	19.1	6.4	16.3

FM 11/HF - 0.5 LUX

Hoogte (m)				
2.5	4.6	11.4	3.9	9.8
3.0	4.9	12.1	4.2	10.5
3.5	5.2	12.9	4.4	11.1
4.0	5.4	13.7	4.5	11.6
4.5	5.5	14.4	4.7	12.1
5.0	5.5	14.8	4.8	12.4
5.5	5.6	15.2	4.9	12.7

FM 11/HF - 5 LUX

Hoogte (m)				
2.5	2.5	6.8	2.2	5.7
3.0	2.6	6.9	2.2	6.0
3.5	2.5	7.1	2.1	6.2
4.0	2.1	7.2	1.8	6.3
4.5	1.3	7.3	1.2	6.3

FM 11/HF - 10 LUX

Hoogte (m)				
2.5	1.8	5.0	1.5	4.4
3.0	1.2	5.1	1.1	4.5
3.5	0.4	5.0	-	4.2

## DIB 325/140A/CL11

### DIB 11 - 0.5 LUX

Hoogte (m)				
2.5	5.6	14.1	4.8	11.8
3.0	5.9	15.0	5.1	12.7
3.5	6.3	15.7	5.4	13.5
4.0	6.7	16.4	5.7	14.2
4.5	7.0	17.2	5.9	14.9
5.0	7.2	18.0	6.0	15.4
5.5	7.4	18.7	6.2	15.9

### DIB 11 - 1 LUX

Hoogte (m)				
2.5	4.5	11.2	3.9	9.6
3.0	4.9	11.9	4.1	10.3
3.5	5.1	12.6	4.3	10.9
4.0	5.2	13.4	4.4	11.4
4.5	5.3	14.1	4.6	11.8
5.0	5.4	14.5	4.7	12.1
5.5	5.4	14.7	4.8	12.4

### DIB 11 - 5 LUX

Hoogte (m)				
2.5	2.4	6.6	2.1	5.6
3.0	2.5	6.7	2.1	5.8
3.5	2.4	6.9	2.0	6.0
4.0	1.8	7.0	1.6	6.1
4.5	1.0	7.0	0.9	6.0

### DIB 11 - 10 LUX

Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9

## Spacingtabellen

### CIB-TL 325/140/24/CL11

CIB 11/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.4	4.6	11.3
3.0	5.7	14.2	4.9	12.1
3.5	6.1	14.9	5.2	12.9
4.0	6.4	15.6	5.4	13.6
4.5	6.6	16.4	5.6	14.1
5.0	6.8	17.2	5.7	14.7
5.5	6.9	17.9	5.9	15.1

CIB 11/24 - 1 LUX

Hoogte (m)				
2.5	4.3	10.6	3.7	9.1
3.0	4.6	11.3	3.9	9.8
3.5	4.8	12.1	4.0	10.3
4.0	4.9	12.8	4.2	10.8
4.5	4.9	13.3	4.3	11.1
5.0	5.0	13.6	4.4	11.4
5.5	5.1	13.8	4.5	11.7

CIB 11/24 - 5 LUX

Hoogte (m)				
2.5	2.3	6.2	2.0	5.3
3.0	2.3	6.3	1.9	5.5
3.5	2.0	6.4	1.6	5.6
4.0	1.2	6.5	1.1	5.6





CIB 11/24 - 10 LUX

Hoogte (m)				
2.5	1.4	4.6	1.1	4.0
3.0	0.6	4.6	0.5	3.9







## CIB-TL 325/140/HF/CL11





### CIB 11/HF - 0.5 LUX

Hoogte (m)				
2.5	5.7	14.4	4.9	12.0
3.0	6.1	15.4	5.3	13.0
3.5	6.4	16.1	5.6	13.8
4.0	6.8	16.8	5.8	14.5
4.5	7.2	17.5	6.0	15.2
5.0	7.4	18.3	6.2	15.8
5.5	7.6	19.1	6.4	16.3





### CIB 11/HF - 1 LUX

Hoogte (m)				
2.5	4.6	11.4	3.9	9.8
3.0	4.9	12.1	4.2	10.5
3.5	5.2	12.9	4.4	11.1
4.0	5.4	13.7	4.5	11.6
4.5	5.5	14.4	4.7	12.1
5.0	5.5	14.8	4.8	12.4
5.5	5.6	15.2	4.9	12.7

### CIB 11/HF - 5 LUX

Hoogte (m)				
2.5	2.5	6.8	2.2	5.7
3.0	2.6	6.9	2.2	6.0
3.5	2.5	7.1	2.1	6.2
4.0	2.1	7.2	1.8	6.3
4.5	1.3	7.3	1.2	6.3

### CIB 11/HF - 10 LUX

Hoogte (m)				
2.5	1.8	5.0	1.5	4.4
3.0	1.2	5.1	1.1	4.5
3.5	0.4	5.0	-	4.2

## Spacingtabellen

### DVA 360A/1

DVA 360A/1 - 0.5 LUX

Hoogte (m)				
2.5	3.9	10.9	3.1	7.8
3.0	3.8	11.2	3.4	8.4
3.5	3.9	11.2	3.5	8.9
4.0	4.0	10.7	3.7	9.3
4.5	4.1	10.8	3.7	9.8
5.0	3.9	11.0	3.6	10.0
5.5	3.7	11.1	3.5	10.3

DVA 360A/1 - 1 LUX

Hoogte (m)				
2.5	2.7	7.8	2.5	6.3
3.0	2.8	7.6	2.6	6.8
3.5	2.8	7.7	2.6	7.1
4.0	2.6	7.9	2.4	7.4
4.5	2.3	8.1	2.1	7.4
5.0	1.7	7.8	1.7	7.3
5.5	1.2	7.5	1.2	6.9

### DVA 360B/1

DVA 360B/1 - 0.5 LUX

Hoogte (m)				
2.5	4.7	12.5	3.1	7.6
3.0	4.6	13.0	3.3	8.1
3.5	4.3	13.4	3.5	8.6
4.0	4.2	13.6	3.6	9.2
4.5	4.3	12.4	3.5	9.6
5.0	4.4	12.0	3.4	9.9
5.5	4.3	11.9	3.2	10.1

DVA 360B/1 - 1 LUX

Hoogte (m)				
2.5	3.0	9.5	2.5	6.1
3.0	3.0	9.2	2.5	6.7
3.5	3.1	8.5	2.4	6.9
4.0	3.0	8.4	2.2	7.2
4.5	2.6	8.6	1.7	7.1
5.0	1.6	8.7	1.2	6.8

### VA-TL 360/24

VA-TL 360/24 - 0.5 LUX

Hoogte (m)				
2.5	4.3	11.5	3.3	8.1
3.0	4.0	11.9	3.5	8.7
3.5	4.1	12.3	3.7	9.3
4.0	4.2	11.6	3.9	9.7
4.5	4.3	11.5	4.0	10.2
5.0	4.3	11.7	3.9	10.6
5.5	4.2	11.8	3.9	10.9

VA-TL 360/24 - 1 LUX

Hoogte (m)				
2.5	2.9	8.7	2.6	6.6
3.0	3.0	8.1	2.8	6.1
3.5	3.1	8.2	2.8	7.5
4.0	2.9	8.4	2.7	7.7
4.5	2.7	8.6	2.5	8.0
5.0	2.3	8.6	2.1	7.9
5.5	1.7	8.4	1.7	7.7

## VA-TL 360/HF

VA-TL 360/HF - 0.5 LUX

Hoogte (m)				
2.5	5.1	11.2	3.2	7.9
3.0	4.9	11.5	3.4	8.5
3.5	4.0	11.6	3.6	9.0
4.0	4.1	10.9	3.8	9.5
4.5	4.1	11.1	3.8	10.0
5.0	4.1	11.2	3.8	10.2
5.5	3.9	11.4	3.6	10.5

VA-TL 360/HF - 1 LUX

Hoogte (m)				
2.5	2.8	8.2	2.6	6.4
3.0	2.9	7.8	2.7	6.9
3.5	2.9	7.9	2.7	7.2
4.0	2.7	8.1	2.5	7.5
4.5	2.4	8.3	2.2	7.6
5.0	1.9	8.1	1.9	7.5
5.5	1.4	7.8	1.4	7.2

## PRE-1

PRE-1 - 0.5 LUX

Hoogte (m)				
2.5	4.7	11.7	2.7	7.0
3.0	4.9	12.5	2.7	7.3
3.5	5.0	13.2	2.6	7.6
4.0	4.9	13.7	2.4	7.6
4.5	4.2	14.1	2.1	7.6
5.0	2.2	14.2	1.5	7.4

PRE-1 - 1 LUX

Hoogte (m)				
2.5	3.6	9.3	1.8	5.3
3.0	3.3	9.8	1.6	5.4
3.5	1.7	10.1	1.1	5.2

## PRE-24

PRE-24 - 0.5 LUX

Hoogte (m)				
2.5	5.5	13.6	3.2	8.1
3.0	5.8	14.6	3.4	8.7
3.5	6.1	15.5	3.4	9.1
4.0	6.3	16.2	3.4	9.4
4.5	6.4	16.8	3.3	9.6
5.0	6.2	17.4	3.1	9.7
5.5	5.8	17.8	2.9	9.7


PRE-24 - 1 LUX

Hoogte (m)				
2.5	4.3	11.0	2.4	6.5
3.0	4.5	11.7	2.4	6.8
3.5	4.4	12.2	2.2	6.9
4.0	3.9	12.7	1.9	6.8
4.5	2.0	12.8	1.4	6.6

# Spacingtabellen


## PRE-HF

PRE-HF - 0.5 LUX



Hoogte (m)	5.8	14.4	3.5	8.6
2.5	5.8	14.4	3.5	8.6
3.0	6.2	15.5	3.6	9.2
3.5	6.6	16.5	3.8	9.8
4.0	6.8	17.3	3.8	10.2
4.5	7.0	18.0	3.8	10.4
5.0	7.1	18.6	3.6	10.6
5.5	6.9	19.1	3.5	10.7


PRE-HF - 1 LUX



Hoogte (m)	4.7	11.7	2.7	6.9
2.5	4.7	11.7	2.7	6.9
3.0	4.9	12.5	2.7	7.3
3.5	5.0	13.1	2.6	7.5
4.0	4.8	13.6	2.4	7.6
4.5	3.1	14.0	2.0	7.5
5.0	2.1	14.1	1.4	7.3


## PRE-V

PRE-V - 0.5 LUX



Hoogte (m)	5.9	12.9	2.7	6.4
2.5	5.9	12.9	2.7	6.4
3.0	6.6	14.8	2.9	7.1
3.5	7.0	16.6	3.0	7.6
4.0	6.9	18.0	2.8	8.1
4.5	6.5	19.3	2.4	8.4
5.0	6.3	19.8	2.1	8.4
5.5	4.9	19.6	1.8	8.1


PRE-V - 1 LUX



Hoogte (m)	4.9	11.8	2.1	5.4
2.5	4.9	11.8	2.1	5.4
3.0	4.7	13.2	1.8	5.8
3.5	4.5	14.0	1.5	6.0
4.0	3.3	13.7	1.2	5.5
4.5	2.9	13.1	1.0	4.7
5.0	2.5	12.7	0.7	4.1
5.5	2.0	9.9	0.5	3.5


## PRE-1/R

PRE-1/R - 0.5 LUX



Hoogte (m)	4.3	10.0	2.6	6.7
2.5	4.3	10.0	2.6	6.7
3.0	4.7	11.2	2.6	7.1
3.5	4.9	12.2	2.5	7.2
4.0	4.9	13.0	2.3	7.3
4.5	4.2	13.5	1.9	7.2
5.0	4.0	13.9	1.2	7.0

PRE-1/R - 1 LUX



Hoogte (m)	3.5	8.7	1.7	5.1
2.5	3.5	8.7	1.7	5.1
3.0	3.3	9.4	1.5	5.1
3.5	2.8	9.8	0.9	5.0

## PRE-24/R

### PRE-24/R - 0.5 LUX

Hoogte (m)				
2.5	5.0	11.3	3.3	8.4
3.0	5.6	12.7	3.5	9.0
3.5	6.1	14.0	3.6	9.4
4.0	6.4	15.2	3.6	9.8
4.5	6.7	16.2	3.5	10.0
5.0	6.8	17.2	3.4	10.1
5.5	6.8	18.0	3.2	10.2

### PRE-24/R - 1 LUX

Hoogte (m)				
2.5	4.3	10.0	2.5	6.7
3.0	4.7	11.1	2.5	7.0
3.5	4.8	12.1	2.4	7.2
4.0	4.8	12.9	2.2	7.2
4.5	4.1	13.4	1.8	7.1
5.0	3.9	13.7	1.1	6.8

## PRE-HF/R

### PRE-HF/R - 0.5 LUX

Hoogte (m)				
2.5	5.2	11.8	3.6	9.0
3.0	5.8	13.3	3.8	9.7
3.5	6.4	14.6	4.0	10.2
4.0	6.9	15.9	4.0	10.6
4.5	7.2	17.1	4.0	11.0
5.0	7.5	18.1	4.0	11.2
5.5	7.7	19.2	3.9	11.4

### PRE-HF/R - 1 LUX

Hoogte (m)				
2.5	4.5	10.4	2.8	7.2
3.0	5.0	11.7	2.9	7.6
3.5	5.3	12.7	2.8	7.9
4.0	5.4	13.7	2.7	8.1
4.5	5.4	14.5	2.5	8.1
5.0	4.7	15.0	2.1	8.0
5.5	4.4	15.4	1.4	7.8

## PRE R/LED

### PRE R/LED - 0.5 LUX

Hoogte (m)				
2.5	6.4	13.9	2.8	6.6
3.0	7.3	16.0	3.1	7.3
3.5	8.0	17.9	3.2	7.9
4.0	8.6	19.8	3.2	8.4
4.5	8.3	21.7	2.9	8.8
5.0	7.7	22.9	2.5	9.1
5.5	7.5	24.0	2.3	9.2


### PRE R/LED - 1 LUX

Hoogte (m)				
2.5	5.7	12.8	2.3	5.6
3.0	6.0	14.7	2.2	6.1
3.5	5.5	16.1	1.8	6.4
4.0	5.2	17.2	1.5	6.4
4.5	3.8	16.6	1.3	5.8
5.0	3.4	15.4	1.1	5.0
5.5	3.0	15.0	0.9	4.5

# Spacingtabellen


## 8860-EX-(A/B)

8860-EX-(A/B) - 0.5 LUX




Hoogte (m)	4.6	11.8	3.6	9.7
2.5	4.6	11.8	3.6	9.7
3.0	4.9	12.5	3.9	9.4
3.5	5.0	13.1	4.0	10.1
4.0	5.1	13.6	4.2	10.7
4.5	5.1	13.9	4.2	11.1
5.0	5.1	14.2	4.2	11.5
5.5	5.0	14.4	4.2	11.8

8860-EX- A/B) - 1 LUX




Hoogte (m)	3.5	9.3	2.9	7.2
2.5	3.5	9.3	2.9	7.2
3.0	3.6	9.7	3.0	7.7
3.5	3.6	10.0	3.0	8.1
4.0	3.5	10.2	2.9	8.3
4.5	3.3	10.3	2.8	8.5
5.0	3.0	10.2	2.5	8.5
5.5	2.5	10.0	2.0	8.3

8860-EX-24 - 0.5 LUX



Hoogte (m)	4.9	12.3	3.7	9.0
2.5	4.9	12.3	3.7	9.0
3.0	5.2	13.2	4.1	9.8
3.5	5.3	13.8	4.2	10.5
4.0	5.4	14.3	4.4	11.2
4.5	5.5	14.7	4.5	11.7
5.0	5.5	15.0	4.6	12.1
5.5	5.4	15.3	4.5	12.4


8860-EX-24 - 1 LUX



Hoogte (m)	3.8	9.8	3.0	7.5
2.5	3.8	9.8	3.0	7.5
3.0	3.9	10.3	3.2	8.1
3.5	3.9	10.6	3.2	8.5
4.0	3.8	10.9	3.2	8.9
4.5	3.7	11.0	3.1	9.0
5.0	3.4	11.0	2.9	9.2
5.5	3.1	10.9	2.6	9.1


## 8860-EX-HF

8860-EX-HF - 0.5 LUX



Hoogte (m)	4.7	12.0	3.6	8.8
2.5	4.7	12.0	3.6	8.8
3.0	5.0	12.8	3.9	9.6
3.5	5.1	13.3	4.1	10.3
4.0	5.2	13.9	4.3	10.9
4.5	5.3	14.2	4.3	11.3
5.0	5.2	14.5	4.4	11.7
5.5	5.2	14.7	4.3	12.0





8860-EX-HF - 1 LUX







Hoogte (m)	3.6	9.5	2.9	7.3
2.5	3.6	9.5	2.9	7.3
3.0	3.7	9.9	3.0	7.9
3.5	3.7	10.2	3.1	8.2
4.0	3.6	10.4	3.0	8.5
4.5	3.4	10.5	3.9	8.7
5.0	3.2	10.5	2.6	8.8
5.5	2.7	10.3	2.2	8.8

## DVA-TL 360A

### DVA 360A/3 - 0.5 LUX





Hoogte (m)				
2.5	3.1	9.1	2.8	6.9
3.0	3.2	8.8	2.9	7.3
3.5	3.3	8.7	3.0	7.8
4.0	3.2	8.8	2.9	8.1
4.5	3.0	9.0	2.8	8.4
5.0	2.7	9.2	2.5	8.5
5.5	2.2	9.1	2.1	8.4

### DVA 360A/3 - 1 LUX





Hoogte (m)				
2.5	2.3	6.2	2.1	5.5
3.0	2.2	6.3	2.0	5.8
3.5	1.9	6.5	1.8	6.0
4.0	1.4	6.4	1.4	5.9
4.5	0.8	6.0	0.8	5.5

## DVA-TL 360B

### DVA 360B/3 - 0.5 LUX

Hoogte (m)				
2.5	3.6	10.6	2.7	6.6
3.0	3.4	10.9	2.9	7.2
3.5	3.5	10.4	2.9	7.7
4.0	3.5	9.8	2.8	7.9
4.5	3.5	9.6	2.5	8.2
5.0	3.2	9.8	2.1	8.2
5.5	2.4	10.0	1.6	8.0





### DVA 360B/3 - 1 LUX

Hoogte (m)				
2.5	2.5	7.3	2.0	5.4
3.0	2.5	6.8	1.9	5.7
3.0	2.5	6.8	1.9	5.7
3.5	2.3	6.9	1.5	5.8
4.0	1.4	7.1	1.0	5.5





## Spacingtabellen

### NRO 11/HF(/W)





#### NRO 11/HF - 0.5 LUX

Hoogte (m)				
2.5	6.8	16.3	4.9	11.8
3.0	7.2	17.7	5.3	13.0
3.5	7.7	19.1	5.6	13.8
4.0	8.0	20.0	6.9	14.6
4.5	8.3	20.9	6.1	15.4
5.0	8.5	21.8	6.3	16.0
5.5	8.7	22.4	6.4	16.6

#### NRO 11/HF - 1 LUX

Hoogte (m)				
2.5	5.4	13.5	4.0	9.8
3.0	5.7	14.4	4.3	10.6
3.5	6.0	15.3	4.4	11.3
4.0	6.2	16.0	4.6	11.9
4.5	6.4	16.5	4.7	12.3
5.0	6.5	17.1	4.7	12.6
5.5	6.7	17.5	4.6	12.9

#### NRO 11/HF - 5 LUX

Hoogte (m)				
2.5	3.0	7.9	2.1	5.8
3.0	3.0	8.2	1.9	5.9
3.5	2.8	8.4	1.7	5.9
4.0	2.4	8.5	1.1	5.7



## NRO 11/24(/W)

### NRO 11/24 - 0.5 LUX

Hoogte (m)				
2.5	6.3	15.3	4.6	11.2
3.0	6.7	16.7	5.0	12.2
3.5	7.1	17.7	5.3	13.0
4.0	7.4	18.6	5.5	13.8
4.5	7.7	19.5	5.6	14.3
5.0	7.9	20.1	5.8	14.9
5.5	8.1	20.7	5.9	15.4

### NRO 11/24 - 1 LUX

Hoogte (m)				
2.5	5.0	12.6	3.7	9.2
3.0	5.3	13.5	3.9	9.9
3.5	5.5	14.2	4.1	10.5
4.0	5.7	14.8	4.2	11.0
4.5	5.9	15.3	4.2	11.3
5.0	6.0	15.7	4.1	11.5
5.5	6.0	16.1	4.0	11.7

### NRO 11/24 - 5 LUX

Hoogte (m)				
2.5	2.7	7.2	1.8	5.3
3.0	2.6	7.5	1.6	5.3
3.5	2.2	7.6	1.1	5.1

## Spacingtabellen

### NRO 11(A/B)/1(/W)

NRO 11/1- 0.5 LUX

Hoogte (m)				
2.5	7.1	17.0	5.2	12.3
3.0	7.6	18.5	5.6	13.5
3.5	8.0	19.9	5.9	14.5
4.0	8.5	21.1	6.2	15.3
4.5	8.7	21.9	6.5	16.1
5.0	9.0	22.8	6.7	16.8
5.5	9.3	23.7	6.9	17.4

NRO 11/1- 1 LUX

Hoogte (m)				
2.5	5.7	14.1	4.2	10.3
3.0	6.1	15.2	4.5	11.1
3.5	6.4	16.1	4.7	11.9
4.0	6.6	16.9	4.9	12.5
4.5	6.8	17.5	5.0	13.0
5.0	7.0	18.1	5.1	13.4
5.5	7.1	18.6	5.1	13.7

NRO 11/1- 1 LUX






Hoogte (m)				
6.0	7.2	19.0	5.0	14.0
6.5	7.2	19.4	4.9	14.1
7.0	7.3	19.7	4.8	14.3
7.5	7.2	20.0	4.6	14.3
8.0	7.0	20.2	4.3	14.3
8.5	6.8	20.4	4.0	14.2
9.0	6.5	20.5	4.5	14.0

NRO 11/1- 5 LUX






Hoogte (m)				
2.5	3.2	8.3	2.3	6.2
3.0	3.2	8.7	2.2	6.4
3.5	2.2	9.0	2.0	6.4
4.0	2.9	9.2	1.6	6.3
4.5	2.3	9.2	0.8	6.0

## NRO 11(A/B)/3(/W)

### NRO 11/3 - 0.5 LUX






Hoogte (m)					
2.5	4.9	12.3	3.7	9.0	
3.0	5.2	13.2	3.8	9.7	
3.5	5.4	13.9	4.0	10.3	
4.0	5.6	14.4	4.0	10.7	
4.5	5.7	14.9	4.0	11.0	
5.0	5.8	15.3	4.0	11.2	
5.5	5.8	15.7	3.9	11.4	

### NRO 11/3 - 1 LUX






Hoogte (m)					
2.5	3.8	9.8	2.8	7.3	
3.0	4.0	10.4	2.9	7.7	
3.5	4.1	10.8	2.8	7.9	
4.0	4.1	11.2	2.7	8.1	
4.5	4.0	11.4	2.4	8.1	
5.0	3.7	11.5	2.1	7.9	
5.5	3.2	11.6	1.4	7.7	

## NB-1/WD

### NB-1/WD - 0.5 LUX

Hoogte (m)					
2.5	4.3	13.0	3.6	8.9	
3.0	4.4	13.1	3.8	9.6	
3.5	4.5	12.1	3.9	10.2	
4.0	4.5	12.4	3.9	10.6	
4.5	4.5	12.6	3.9	10.9	
5.0	4.5	12.8	3.9	11.1	
5.5	4.4	12.8	3.9	11.1	






### NB-1/WD - 1 LUX

Hoogte (m)					
2.5	3.2	8.6	2.8	7.2	
3.0	3.2	8.8	2.8	7.6	
3.5	3.2	9.0	2.8	7.9	
4.0	3.1	9.1	2.7	7.9	
4.5	2.9	9.1	2.6	7.8	
5.0	2.6	9.0	2.3	7.8	
5.5	2.1	8.8	1.9	7.8	






## Spacingtabellen

### NBN-1/WD

NBN-1/WD - 0.5 LUX





Hoogte (m)					
2.5	4.1	10.0	3.6	9.0	
3.0	4.4	10.8	3.8	9.6	
3.5	4.5	11.5	4.0	10.2	
4.0	4.5	12.1	4.0	10.7	
4.5	4.5	12.6	4.0	11.0	
5.0	4.5	12.8	4.0	11.3	
5.5	4.4	12.8	4.0	11.4	

NBN-1/WD - 1 LUX





Hoogte (m)					
2.5	3.2	8.2	2.8	7.2	
3.0	3.2	8.7	2.8	7.7	
3.5	3.2	9.1	2.8	8.0	
4.0	3.1	9.1	2.8	8.0	
4.5	2.9	9.1	2.7	8.0	
5.0	2.7	9.0	2.4	8.0	
5.5	2.2	8.8	2.0	7.9	

### IND 08/24

IND 08/24 - 0.5 LUX





Hoogte (m)				
2.5	4.6	12.0	3.3	8.2
3.0	4.8	12.6	3.5	8.9
3.5	4.8	13.0	3.7	9.4
4.0	4.8	13.4	3.7	9.8
4.5	4.7	13.5	3.7	10.1
5.0	4.5	13.6	3.7	10.4
5.5	4.3	13.6	3.5	10.5

IND 08/24 - 1 LUX





Hoogte (m)				
2.5	3.4	9.2	2.6	6.7
3.0	3.4	9.5	2.6	7.1
3.5	3.2	9.6	2.6	7.3
4.0	3.0	9.6	2.4	7.4
4.5	2.6	9.4	2.2	7.5
5.0	2.1	9.1	1.7	7.3
5.5	1.1	8.7	1.0	7.0

## IND 08/HF

### IND 08/HF - 0.5 LUX





Hoogte (m)				
2.5	4.5	11.7	3.2	8.0
3.0	4.6	12.2	3.4	8.7
3.5	4.6	12.6	3.5	9.1
4.0	4.6	12.9	3.6	9.6
4.5	4.4	13.0	3.5	9.8
5.0	4.3	13.0	3.5	10.0
5.5	4.0	13.0	3.3	10.1

### IND 08/HF - 1 LUX





Hoogte (m)				
2.5	3.3	8.9	2.5	6.5
3.0	3.2	9.2	2.5	6.8
3.5	3.0	9.2	2.5	7.1
4.0	2.8	9.1	2.3	7.1
4.5	2.3	8.9	1.9	7.1
5.0	1.7	8.6	1.4	6.9

## IND 08(A/B)1

### IND 08/1- 0.5 LUX

Hoogte (m)				
2.5	4.1	10.9	3.1	7.6
3.0	4.2	11.4	3.2	8.2
3.5	4.2	11.7	3.3	8.6
4.0	4.1	11.9	3.3	8.9
4.5	3.9	11.9	3.2	9.1
5.0	3.7	11.9	3.0	9.2
5.5	3.3	11.7	2.7	9.3





### IND 08/1 - 1 LUX

Hoogte (m)				
2.5	3.0	8.3	2.3	6.1
3.0	2.8	8.4	2.3	6.4
3.5	2.6	8.4	2.1	6.5
4.0	2.3	8.2	1.9	6.5
4.5	1.7	7.9	1.4	6.4





## Spacingtabellen

### IND 18/24





#### IND 18/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.8	4.7	9.0
3.0	5.6	14.4	4.0	9.8
3.5	5.7	15.0	4.2	10.5
4.0	5.8	15.5	4.3	11.0
4.5	5.8	15.9	4.4	11.5
5.0	5.8	16.1	4.4	11.9
5.5	5.7	16.3	4.4	12.1

#### IND 18/24 - 1 LUX






Hoogte (m)				
2.5	4.0	10.7	3.0	7.4
3.0	4.1	11.1	3.1	8.0
3.5	4.1	11.4	3.1	8.4
4.0	4.0	11.6	3.1	8.6
4.5	3.8	11.6	3.0	8.8
5.0	3.6	11.6	2.8	8.8
5.5	3.1	11.5	2.5	8.7

#### IND 18/24 - 5 LUX






Hoogte (m)				
2.5	1.4	5.1	1.1	3.9
3.0	0.1	4.7	0.1	3.6

## IND 18/HF






### IND 18/HF - 0.5 LUX

Hoogte (m)					
2.5		10.5	26.0	6.3	14.7
3.0		11.5	27.8	7.0	16.5
3.5		12.1	29.7	7.6	17.8
4.0		12.7	31.5	8.2	19.1
4.5		13.2	33.2	8.6	20.4
5.0		13.8	34.4	9.0	21.8
5.5		14.1	35.5	9.5	22.8






### IND 18/HF - 1 LUX

Hoogte (m)					
2.5		8.6	21.1	5.4	12.7
3.0		9.2	22.9	5.9	14.0
3.5		9.7	24.2	6.4	15.3
4.0		10.1	25.4	6.8	16.3
4.5		10.4	26.5	7.1	17.2
5.0		10.7	27.6	7.4	18.1
5.5		10.9	28.3	7.7	18.9

### IND 18/HF - 5 LUX

Hoogte (m)					
2.5		4.9	12.7	3.5	8.5
3.0		5.1	13.3	3.7	9.2
3.5		5.2	13.8	3.8	9.8
4.0		5.2	14.2	3.9	10.2
4.5		5.2	14.5	3.9	10.6
5.0		5.1	14.6	3.9	10.9
5.5		5.9	14.7	3.8	11.1





### IND 18/HF - 15 LUX

Hoogte (m)					
2.5		3.0	8.3	2.3	6.1
3.0		2.9	8.5	2.2	6.3
3.5		2.7	8.5	2.1	6.4
4.0		2.3	8.4	1.8	6.4
4.5		1.7	8.1	1.3	6.2





## Spacingtabellen

### IND 18/(A/B)/1

#### IND 18/1 - 0.5 LUX

Hoogte (m)				
2.5	5.4	14.0	3.8	9.1
3.0	5.6	14.7	4.0	9.9
3.5	5.8	15.3	4.2	10.6
4.0	5.9	15.7	4.4	11.2
4.5	5.9	16.2	4.5	11.6
5.0	5.9	16.4	4.5	12.0
5.5	5.9	16.6	4.5	12.3





#### IND 18/1 - 1 LUX

Hoogte (m)				
2.5	4.1	10.8	3.0	7.5
3.0	4.2	11.3	3.1	8.1
3.5	4.2	11.5	3.2	8.5
4.0	4.1	11.8	3.1	8.7
4.5	4.0	11.8	3.0	9.0
5.0	3.7	11.9	2.9	9.0
5.5	3.3	11.7	2.6	8.9







## IND 36/HF





### IND 36/HF - 0.5 LUX

Hoogte (m)				
2.5	13.5	31.5	7.7	18.1
3.0	14.4	35.6	8.6	19.9
3.5	15.3	38.1	9.4	21.7
4.0	16.2	39.9	10.1	23.5
4.5	17.1	41.7	10.7	25.3
5.0	17.8	43.6	11.4	26.8
5.5	18.4	45.4	12.0	28.1





### IND 36/HF - 1 LUX

Hoogte (m)				
2.5	10.9	27.0	6.7	15.4
3.0	11.8	28.9	7.4	17.2
3.5	12.6	30.7	8.0	18.9
4.0	13.1	32.5	8.7	20.2
4.5	13.7	34.3	9.1	21.5
5.0	14.2	35.7	9.6	22.8
5.5	14.7	36.8	10.0	24.1

### IND 36/HF - 5 LUX

Hoogte (m)				
2.5	6.6	16.5	4.5	10.9
3.0	6.9	17.6	4.9	11.8
3.5	7.2	18.6	5.2	12.7
4.0	7.4	19.2	5.5	13.5
4.5	7.5	19.8	5.7	14.2
5.0	7.7	20.3	5.8	14.8
5.5	7.8	20.7	5.9	15.4





### IND 36/HF - 15 LUX

Hoogte (m)				
2.5	4.3	11.3	3.2	8.1
3.0	4.4	11.8	3.4	8.7
3.5	4.5	12.2	3.5	9.2
4.0	4.5	12.5	3.5	9.5
4.5	4.4	12.7	3.4	9.7
5.0	4.2	12.7	3.3	9.9
5.5	3.9	12.7	3.1	9.9





## Spacingtabellen

### IND 36/(A/B)1





#### IND 36/1 - 0.5 LUX

Hoogte (m)				
2.5	6.7	16.8	4.6	11.0
3.0	7.0	17.9	5.0	12.0
3.5	7.3	18.9	5.3	12.9
4.0	7.5	19.6	5.6	13.7
4.5	7.7	20.2	5.8	14.4
5.0	7.8	20.7	6.0	15.1
5.5	7.9	21.1	6.1	15.7

#### IND 36/1 - 1 LUX

Hoogte (m)				
2.5	5.2	13.4	3.8	9.2
3.0	5.4	14.0	4.0	9.9
3.5	5.5	14.6	4.2	10.6
4.0	5.6	15.0	4.3	11.2
4.5	5.6	15.4	4.4	11.6
5.0	5.6	15.6	4.4	11.9
5.5	5.5	15.9	4.3	12.1

#### IND 36/1 - 5 LUX

Hoogte (m)				
2.5	2.5	7.1	1.9	5.4
3.0	2.2	7.1	1.8	5.5
3.5	1.8	7.0	1.4	5.5
4.0	0.8	6.6	0.7	5.2

## TNAT 1x8W

TNAT 1x8W - 0.5 LUX

Hoogte (m)				
2.5	4.3	13.0	3.6	8.9
3.0	4.4	13.1	3.8	9.6
3.5	4.5	12.1	3.9	10.2
4.0	4.5	12.4	3.9	10.6
4.5	4.5	12.6	3.9	10.9
5.0	4.5	12.8	3.9	11.1
5.5	4.4	12.8	3.9	11.1

TNAT 1x8W - 1 LUX

Hoogte (m)				
2.5	3.2	8.6	2.8	7.2
3.0	3.2	8.8	2.8	7.6
3.5	3.2	9.0	2.8	7.9
4.0	3.1	9.1	2.7	7.9
4.5	2.9	9.1	2.6	7.8
5.0	2.6	9.0	2.3	7.8
5.5	2.1	8.8	1.9	7.8

## TNAT 2x8W

TNAT 2x8W - 0.5 LUX

Hoogte (m)				
2.5	4.1	10.0	3.6	9.0
3.0	4.4	10.8	3.8	9.6
3.5	4.5	11.5	4.0	10.2
4.0	4.5	12.1	4.0	10.7
4.5	4.5	12.6	4.0	11.0
5.0	4.5	12.8	4.0	11.3
5.5	4.4	12.8	4.0	11.4


TNAT 2x8W - 1 LUX

Hoogte (m)				
2.5	3.2	8.2	2.8	7.2
3.0	3.2	8.7	2.8	7.7
3.5	3.2	9.1	2.8	8.0
4.0	3.1	9.1	2.8	8.0
4.5	2.9	9.1	2.7	8.0
5.0	2.7	9.0	2.4	8.0
5.5	2.2	8.8	2.0	7.9

# Spacingtabellen


## TNT/24

TNT/24 - 0.5 LUX



Hoogte (m)	4.8	13.8	3.8	9.2
2.5	4.8	13.8	3.8	9.2
3.0	4.7	14.1	4.0	10.0
3.5	4.8	13.6	4.2	10.6
4.0	4.9	13.2	4.2	11.2
4.5	4.9	13.4	4.2	11.5
5.0	4.9	13.7	4.2	11.8
5.5	4.8	13.7	4.2	12.0


TNT/24 - 1 LUX



Hoogte (m)	3.4	9.5	2.9	7.5
2.5	3.4	9.5	2.9	7.5
3.0	3.5	9.4	3.0	8.1
3.5	3.4	9.6	3.0	8.3
4.0	3.4	9.7	3.0	8.5
4.5	3.3	9.8	2.9	8.4
5.0	3.1	9.7	2.7	8.4
5.5	2.7	9.6	2.4	8.4


## TNT/HF

TNT/HF - 0.5 LUX



Hoogte (m)	4.5	13.3	3.7	9.0
2.5	4.5	13.3	3.7	9.0
3.0	4.5	13.6	3.9	9.7
3.5	4.6	12.7	4.0	10.3
4.0	4.7	12.7	4.0	10.9
4.5	4.7	12.9	4.0	11.1
5.0	4.6	13.1	4.0	11.4
5.5	4.6	13.2	4.0	11.4

TNT/HF - 1 LUX



Hoogte (m)	3.3	8.9	2.8	7.3
2.5	3.3	8.9	2.8	7.3
3.0	3.3	9.1	2.9	7.8
3.5	3.3	9.3	2.8	8.0
4.0	3.2	9.3	2.8	8.1
4.5	3.1	9.3	2.7	8.1
5.0	2.8	9.3	2.5	8.1
5.5	2.4	9.1	2.1	8.1

## XION

—  
XN-EX-1/ZT - 1 LUX

Hoogte (m)				
2.0	3.9	9.5	3.8	8.9
2.5	4.3	10.6	4.2	10.0
3.0	4.6	11.4	4.5	11.0
3.5	4.9	12.2	4.8	11.8
4.0	5.1	12.8	5.0	12.5
4.5	5.2	13.4	5.1	13.1
5.0	5.3	13.8	5.2	13.6

—  
XN-EX-1/ZT - 1 LUX

Hoogte (m)				
5.5	5.3	14.2	5.3	14.0
6.0	5.3	14.5	5.3	14.4
6.5	5.2	14.7	5.2	14.6
7.0	5.1	14.9	5.1	14.8
7.5	4.9	15.0	4.9	14.9
8.0	4.6	15.0	4.7	15.0
8.5	4.3	14.9	4.4	14.9

—  
XN-EX-1/ZT - 5 LUX

Hoogte (m)				
1.5	2.2	5.4	2.1	5.2
2.0	2.3	6.0	2.3	5.8
2.5	2.4	6.4	2.4	6.3
3.0	2.3	6.6	2.3	6.6
3.5	2.1	6.7	2.1	6.7
4.0	1.8	6.6	1.8	6.6
4.5	1.1	6.4	1.1	6.4





—  
XN-EX-1/ZT - 10 LUX

Hoogte (m)				
1.0	1.5	3.7	1.5	3.6
1.5	1.7	4.3	1.6	4.2
2.0	1.7	4.6	1.7	4.6
2.5	1.5	4.7	1.5	4.7
3.0	1.1	4.6	1.1	4.6





## Spacingtabellen

### EVA-.-.L.





#### EVA-.L. - 1 LUX

Hoogte (m)				
2.0	8.0	21.2	2.2	5.6
2.5	7.7	22.9	2.2	6.1
3.0	7.8	23.2	1.5	6.4
3.5	4.8	21.9	1.2	6.0
4.0	4.4	21.5	1.2	5.0
4.5	3.6	18.8	1.1	4.1
5.0	2.8	13.7	1.0	3.6

#### EVA-.L.-X - 1 LUX

Hoogte (m)				
5.0	8.3	19.9	1.9	4.9
5.5	8.4	21.1	1.9	5.1
6.0	8.5	22.0	1.9	5.3
6.5	8.6	22.8	1.9	5.4
7.0	8.6	23.5	1.9	5.5
7.5	8.6	24.1	1.9	5.6
8.0	8.5	24.5	1.7	5.6

#### EVA-.L.-X<sup>2</sup> - 1 LUX

Hoogte (m)				
9.0	8.1	18.8	2.4	6.7
9.5	8.5	19.5	2.4	6.8
10.0	8.7	20.2	2.5	6.9
10.5	8.8	20.8	2.4	6.9
11.0	8.9	21.5	2.1	7.0
11.5	9.0	22.1	1.8	7.0
12.0	9.0	22.7	1.5	7.1

## EVA-.-.W

### EVA-.-.W. - 1 LUX

Hoogte (m)				
2.0	3.8	8.1	3.8	8.1
2.5	4.6	9.8	4.6	9.8
3.0	5.3	11.4	5.3	11.4
3.5	5.8	13.0	5.8	13.0
4.0	5.8	14.4	5.8	14.4
4.5	3.3	13.4	3.3	13.4
5.0	2.9	13.1	2.9	13.1

### EVA-.-.W.-X - 1 LUX

Hoogte (m)				
4.5	4.7	10.7	4.7	10.7
5.0	4.9	11.5	4.9	11.5
5.5	4.8	12.2	4.8	12.2
6.0	3.5	12.0	3.5	12.0
6.5	3.0	11.9	3.0	11.9
7.0	2.6	12.0	2.6	12.0
7.5	2.2	11.9	2.2	11.9



### EVA-.-.W.-X<sup>2</sup> - 1 LUX

Hoogte (m)				
6.0	3.7	8.7	3.7	8.7
6.5	3.9	9.1	3.9	9.1
7.0	4.0	9.5	4.0	9.5
7.5	4.1	9.9	4.1	9.9
8.0	4.2	10.2	4.2	10.2
8.5	4.3	10.5	4.3	10.5
9.0	4.4	10.8	4.4	10.8
9.5	4.5	11.1	4.5	11.1
10.0	4.6	11.3	4.6	11.3
10.5	4.6	11.6	4.6	11.6
11.0	4.6	11.8	4.6	11.8



## Spacingtabellen

### EVA-.SO



EVA-.SO - 1 LUX - 2m breed

Hoogte (m)		
1.5	2.8	6.7
2.0	3.1	7.5
2.5	3.2	8.4
3.0	1.9	8.6
3.5	1.5	8.0
4.0	1.2	4.4
4.5	1.0	3.6
5.0	0.5	3.3

EVA-.SO - 1 LUX - 3m breed

Hoogte (m)		
1.5	3.1	7.1
2.0	3.4	7.5
2.5	3.6	8.4
3.0	3.6	8.9
3.5	3.6	9.2
4.0	3.0	9.2
4.5	1.6	8.5
5.0	1.4	5.8

EVA-.SO - 1 LUX - 4m breed

Hoogte (m)		
1.5	3.5	7.7
2.0	3.7	8.5
2.5	4.0	9.0
3.0	4.1	9.5
3.5	4.1	9.8
4.0	4.1	10.0
4.5	3.7	10.2
5.0	1.3	9.9



## KOMPAS

### EKN - 1 LUX

Hoogte (m)				
2.5	3.3	8.7	2.5	6.6
3.0	3.3	9.0	2.6	7.0
3.5	3.2	9.2	2.5	7.2
4.0	2.9	9.4	2.4	7.3
4.5	2.5	9.2	2.1	7.3
5.0	2.4	9.0	1.7	7.1
5.5	1.2	8.5	1.0	6.9

### EK-HF - 1 LUX

Hoogte (m)				
2.5	3.5	9.3	2.7	7.0
3.0	3.6	9.7	2.8	7.4
3.5	3.6	10.0	2.8	7.7
4.0	3.4	10.2	2.7	7.9
4.5	3.1	10.2	2.6	8.0
5.0	2.7	10.1	1.3	7.9
5.5	2.2	9.8	1.9	7.8

### EK-24 - 1 LUX

Hoogte (m)				
2.5	3.7	9.6	2.8	7.2
3.0	3.8	10.1	2.9	7.7
3.5	3.7	10.4	3.0	8.0
4.0	3.6	10.6	2.9	8.2
4.5	3.4	10.7	2.8	8.3
5.0	3.0	10.6	2.5	8.4
5.5	2.6	10.4	2.2	8.2

## Spacingtabellen

### NP

NP 8(N/H) - 1 LUX

Hoogte (m)				
2.5	3.1	7.6	2.9	7.2
3.0	3.2	8.3	3.0	7.7
3.5	3.1	8.7	2.9	8.1
4.0	3.0	8.9	2.8	8.3
4.5	2.7	9.0	2.5	8.3
5.0	2.4	8.9	2.2	8.2
5.5	2.2	8.6	2.0	7.9

NP 230 - 1 LUX





Hoogte (m)				
2.5	3.1	7.7	2.9	7.3
3.0	3.2	8.5	3.0	7.8
3.5	3.2	8.8	3.0	8.3
4.0	3.1	9.1	2.9	8.5
4.5	2.9	9.2	2.6	8.6
5.0	2.5	9.1	2.4	8.5
5.5	2.3	9.0	2.2	8.3

NP 24 - 1 LUX





Hoogte (m)				
2.5	3.2	7.9	3.0	7.4
3.0	3.4	8.7	3.1	8.0
3.5	3.4	9.1	3.2	8.5
4.0	3.3	9.5	3.1	8.8
4.5	3.2	9.6	2.9	9.0
5.0	2.8	9.6	2.6	8.9
5.5	2.5	9.5	2.4	8.8

## NPW





NPW-8N - 1 LUX

Hoogte (m)				
2.5	3.2	8.2	2.8	7.2
3.0	3.2	8.7	2.8	7.7
3.5	3.2	9.1	2.8	8.0
4.0	3.1	9.1	2.8	8.0
4.5	2.9	9.1	2.7	8.0
5.0	2.7	9.0	2.4	8.0
5.5	2.2	8.8	2.0	7.9





NPW-8H - 1 LUX

Hoogte (m)				
2.5	3.2	8.6	2.8	7.2
3.0	3.2	8.8	2.8	7.6
3.5	3.2	9.0	2.8	7.9
4.0	3.1	9.1	2.7	7.9
4.5	2.9	9.1	2.6	7.8
5.0	2.6	9.0	2.3	7.8
5.5	2.1	8.8	1.9	7.8

NPW-HF - 1 LUX

Hoogte (m)				
2.5	3.3	8.9	2.8	7.3
3.0	3.3	9.1	2.9	7.8
3.5	3.3	9.3	2.8	8.0
4.0	3.2	9.3	2.8	8.1
4.5	3.1	9.3	2.7	8.1
5.0	2.8	9.3	2.5	8.1
5.5	2.4	9.1	2.1	8.1





NPW-24 - 1 LUX

Hoogte (m)				
2.5	3.4	9.5	2.9	7.5
3.0	3.5	9.4	3.0	8.1
3.5	3.4	9.6	3.0	8.3
4.0	3.4	9.7	3.0	8.5
4.5	3.3	9.8	2.9	8.4
5.0	3.1	9.7	2.7	8.4
5.5	2.7	9.6	2.4	8.4





## Spacingtabellen

### KLI





#### KLI - 1 LUX

Hoogte (m)				
2.5	2.9	7.7	2.8	7.0
3.0	3.1	8.0	3.0	7.5
3.5	3.1	8.3	3.0	7.9
4.0	3.1	8.6	3.0	8.2
4.5	3.0	8.8	2.8	8.4
5.0	2.7	8.9	2.6	8.5
5.5	2.2	8.8	2.2	8.4

#### KLI 230 - 1 LUX





Hoogte (m)				
2.5	3.0	7.9	2.9	7.2
3.0	3.1	8.2	3.0	7.6
3.5	3.2	8.5	3.1	8.0
4.0	3.2	8.8	3.1	8.4
4.5	3.1	9.1	2.9	8.6
5.0	2.9	9.1	2.7	8.7
5.5	2.5	9.1	2.4	8.7

#### KLI 24 - 1 LUX





Hoogte (m)				
2.5	3.1	8.2	2.9	7.3
3.0	3.2	8.5	3.1	7.8
3.5	3.4	8.7	3.2	8.3
4.0	3.4	9.0	3.2	8.6
4.5	3.3	9.3	3.1	9.0
5.0	3.1	9.5	2.9	9.1
5.5	2.8	9.5	2.7	9.2

## HILED





HIL-.LO - 1 LUX

Hoogte (m)				
2.0	4.0	8.6	2.0	5.7
2.5	5.0	10.8	2.4	7.1
3.0	6.0	12.9	2.9	8.5
3.5	6.9	14.9	3.2	9.4
4.0	7.6	16.6	3.1	9.2
4.5	8.4	18.1	3.1	9.1
5.0	9.2	19.6	3.1	8.9





HIL-.LO - 1 LUX

Hoogte (m)				
5.5	9.9	21.0	3.2	8.7
6.0	10.6	22.7	3.3	8.5
6.5	11.3	24.2	3.4	8.4
7.0	12.0	25.8	3.6	8.7
7.5	12.8	27.2	3.7	8.8
8.0	13.5	28.7	3.9	9.1
8.5	14.2	30.1	4.0	9.3

HIL-.LO - 1 LUX

Hoogte (m)				
9.0	14.9	31.4	4.2	9.6
9.5	15.6	32.8	4.3	9.9
10.0	16.3	34.3	4.4	10.2
10.5	16.9	35.8	4.6	10.5
11.0	17.5	37.3	4.7	10.8
12.0	18.8	40.2	4.8	11.4
13.0	19.9	43.0	4.9	11.9





HIL-.LO - 1 LUX

Hoogte (m)				
14.0	21.0	45.6	5.0	12.5
15.0	22.1	48.2	4.0	12.9
16.0	23.1	50.7	4.8	13.3
17.0	23.9	53.2	4.6	13.7
18.0	24.4	55.5	4.1	13.9
19.0	24.9	57.8	3.4	14.1
20.0	24.3	59.9	2.1	14.0





## Spacingtabellen

### HILED





HIL-WO - 1 LUX

Hoogte (m)				
2.0	4.0	8.5	4.0	8.5
2.5	4.3	10.1	4.3	10.1
3.0	5.0	11.6	5.0	11.6
3.5	5.6	13.0	5.6	13.0
4.0	6.2	14.2	6.2	14.2
4.5	6.7	15.5	6.7	15.5
5.0	7.0	16.7	7.0	16.7





HIL-WO - 1 LUX

Hoogte (m)				
5.5	7.2	17.8	7.2	17.8
6.0	7.5	18.7	7.5	18.7
6.5	7.7	19.6	7.7	19.6
7.0	7.8	20.4	7.8	20.4
7.5	8.1	21.1	8.1	21.1
8.0	8.2	21.7	8.2	21.7
8.5	8.2	22.4	8.2	22.4

HIL-WO - 1 LUX





Hoogte (m)				
9.0	8.4	22.9	8.4	22.9
9.5	8.6	23.5	8.6	23.5
10.0	8.7	24.1	8.7	24.1
10.5	8.7	24.6	8.7	24.6
11.0	8.7	25.0	8.7	25.0
11.5	8.7	25.5	8.7	25.5
12.0	8.7	25.9	8.7	25.9

HIL-WO - 1 LUX





Hoogte (m)				
12.5	8.6	26.3	8.6	26.3
13.0	8.4	26.6	8.4	26.6
13.5	8.0	26.9	8.0	26.9
14.0	7.3	27.1	7.3	27.1
14.5	3.8	27.4	3.8	27.4
15.0	0.1	28.1	0.1	28.1
15.5	0.3	28.6	0.3	28.6

## HILED





### HIL-WO - 5 LUX

Hoogte (m)				
1.0	1.8	4.0	1.8	4.0
1.5	2.5	5.5	2.5	5.5
2.0	3.0	6.9	3.0	6.9
2.5	3.4	8.0	3.4	8.0
3.0	3.7	8.9	3.7	8.9
3.5	3.9	9.6	3.9	9.6
4.0	4.1	10.2	4.1	10.2





### HIL-WO - 5 LUX

Hoogte (m)				
4.5	4.2	10.7	4.2	10.7
5.0	4.2	11.2	4.2	11.2
5.5	4.1	11.6	4.1	11.6
6.0	3.7	11.9	3.7	11.9
6.5	1.5	12.1	1.5	12.1

### HIL-WO - 10 LUX

Hoogte (m)				
1.0	1.7	3.7	1.7	3.7
1.5	2.2	5.1	2.2	5.1
2.0	2.5	6.1	2.5	6.1
2.5	2.8	6.8	2.8	6.8
3.0	2.9	7.4	2.9	7.4
3.5	3.0	7.9	3.0	7.9
4.0	2.8	8.3	2.8	8.3
4.5	1.8	8.5	1.8	8.5

### HIL-WO - 15 LUX

Hoogte (m)				
1.0	1.6	3.6	1.6	3.6
1.5	2.0	4.7	2.0	4.7
2.0	2.2	5.5	2.2	5.5
2.5	2.4	6.1	2.4	6.1
3.0	2.4	6.6	2.4	6.6
3.5	2.0	6.9	2.0	6.9

## Spacingtabellen

### HILED

#### HIL-.LO - 5 LUX

Hoogte (m)				
1.0	1.9	4.3	0.9	2.8
1.5	2.9	6.4	1.4	4.1
2.0	3.7	8.0	1.3	4.0
2.5	4.4	9.5	1.4	3.8
3.0	5.1	11.1	1.5	3.8
3.5	5.9	12.6	1.7	4.0
4.0	6.6	13.9	1.8	4.2

#### HIL-.LO - 5 LUX

Hoogte (m)				
4.5	7.3	15.4	1.9	4.5
5.0	7.9	16.9	2.0	4.9
5.5	8.5	18.3	2.1	5.1
6.0	9.1	19.7	2.2	5.4
6.5	9.6	21.0	2.2	5.6
7.0	10.1	22.3	2.1	5.9
7.5	10.6	23.5	2.0	6.0





#### HIL-.LO - 5 LUX

Hoogte (m)				
8.0	10.8	24.7	1.8	6.2
8.5	11.1	25.8	1.5	6.2
9.0	10.7	26.9	0.8	6.2







## HILED





### HIL-.LO - 10 LUX

Hoogte (m)				
1.0	1.9	4.3	0.9	2.8
1.5	2.7	5.9	0.9	2.8
2.0	3.4	7.4	1.0	2.7
2.5	4.2	8.9	1.2	2.8
3.0	4.9	10.3	1.3	3.1
3.0	5.5	11.8	1.4	3.4
4.0	6.1	13.2	1.5	3.7

### HIL-.LO - 10 LUX

Hoogte (m)				
4.5	6.7	14.6	1.5	3.9
5.0	7.2	15.8	1.5	4.1
5.5	7.6	17.1	1.3	4.3
6.0	7.8	18.2	1.0	4.4
6.5	1.0	16.7	0.2	4.3





### HIL-.LO - 15 LUX

Hoogte (m)				
1.0	1.9	4.1	0.7	2.3
1.5	2.6	5.6	0.8	2.2
2.0	3.3	7.2	0.9	2.2
2.5	4.0	8.6	1.1	2.5
3.0	4.7	10.0	1.2	2.8
3.0	5.3	11.4	1.2	3.1
4.0	5.8	12.7	1.2	3.3
4.5	6.2	13.9	1.1	3.5
5.0	6.4	15.1	0.7	3.6





## Spacingtabellen

### EVA-.LO-X





#### EVA-.LO-X - 5 LUX

Hoogte (m)				
1.0	2.2	4.9	0.7	2.2
1.5	3.0	6.7	0.7	2.0
2.0	3.5	8.3	0.8	2.1
2.5	3.8	9.5	0.8	2.2
3.0	3.9	10.3	0.8	2.4
3.5	3.8	10.9	0.8	2.5
4.0	3.7	11.0	0.7	2.5





#### EVA-.LO-X - 5 LUX

Hoogte (m)				
4.5	3.4	11.0	0.6	2.4
5.0	2.6	10.9	0.5	2.3

#### EVA-.LO-X - 10 LUX





Hoogte (m)				
1.0	2.0	4.5	0.5	1.4
1.5	2.5	6.1	0.6	1.5
2.0	2.7	7.1	0.6	1.6
2.5	2.7	7.7	0.5	1.7
3.0	2.5	7.8	0.4	1.7
3.5	1.9	7.7	0.3	1.6

#### EVA-.LO-X - 15 LUX





Hoogte (m)				
1.0	1.9	4.3	0.4	1.1
1.5	2.2	5.6	0.5	1.3
2.0	2.2	6.2	0.4	1.4
2.5	2.0	6.3	0.3	1.4
3.0	1.1	6.2	0.2	1.3

## EVA-.LO-X2





### EVA-.LO-X<sup>2</sup> - 5 LUX

Hoogte (m)				
1.0	1.2	2.8	0.9	2.9
1.5	1.8	3.8	0.9	2.7
2.0	2.2	4.9	0.9	2.7
2.5	2.7	5.8	1.0	2.7
3.0	3.0	6.7	1.0	2.7
3.5	3.4	7.6	1.1	2.8
4.0	3.7	8.3	1.1	2.9





### EVA-.LO-X<sup>2</sup> - 5 LUX

Hoogte (m)				
4.5	3.9	9.0	1.1	3.0
5.0	4.0	9.7	0.9	3.1
5.5	0.5	10.3	0.1	3.1

### EVA-.LO-X<sup>2</sup> - 10 LUX

Hoogte (m)				
1.0	1.1	2.5	0.6	1.9
1.5	1.6	3.6	0.6	1.9
2.0	2.0	4.5	0.7	1.8
2.5	2.4	5.4	0.7	2.0
3.0	2.6	6.1	0.7	2.1
3.5	2.8	6.8	0.6	2.2





### EVA-.LO-X<sup>2</sup> - 15 LUX

Hoogte (m)				
1.0	1.0	2.4	0.5	1.6
1.5	1.6	3.4	0.5	1.5
2.0	1.9	4.3	0.6	1.6
2.5	2.2	5.1	0.6	1.7
3.0	2.3	5.7	0.4	1.8





## Spacingtabellen

### EVA-.WO-X





#### EVA-.WO-X - 5 LUX

Hoogte (m)				
1.0	1.2	2.7	1.2	2.7
1.5	1.7	3.7	1.7	3.7
2.0	2.0	4.7	2.0	4.7
2.5	1.9	5.5	1.9	5.5
3.0	1.2	5.3	1.2	5.3
3.5	0.8	5.3	0.8	5.3

#### EVA-.WO-X - 10 LUX





Hoogte (m)				
1.0	1.1	2.5	1.1	2.5
1.5	1.5	3.5	1.5	3.5
2.0	1.0	3.7	1.0	3.7
2.5	0.5	3.7	0.5	3.7

#### EVA-.WO-X - 15 LUX





Hoogte (m)				
1.0	1.1	2.4	1.1	2.4
1.5	0.9	3.2	0.9	3.2
2.0	0.5	3.0	0.5	3.0

## EVA-.WO-X2





### EVA-.WO-X<sup>2</sup> - 5 LUX

Hoogte (m)				
1.0	1.0	2.6	1.0	2.6
1.5	1.2	3.0	1.2	3.0
2.0	1.4	3.3	2.4	3.3
2.5	1.6	3.7	1.6	3.7
3.0	1.7	4.1	1.7	4.1
3.5	1.8	4.5	1.8	4.5
4.0	1.9	4.8	1.9	4.8
4.5	2.0	5.0	2.0	5.0

### EVA-.WO-X<sup>2</sup> - 10 LUX

Hoogte (m)				
1.0	0.8	2.1	0.8	2.1
1.5	1.0	2.4	1.0	2.4
2.0	1.2	2.8	1.2	2.8
2.5	1.3	3.2	1.3	3.2
3.0	1.4	3.4	1.4	3.4
3.5	1.4	3.7	1.4	3.7





### EVA-.WO-X<sup>2</sup> - 15 LUX

Hoogte (m)				
1.0	0.7	1.8	0.7	1.8
1.5	0.9	2.2	0.9	2.2
2.0	1.0	2.5	1.0	2.5
2.5	1.1	2.8	1.1	2.8





## Spacingtabellen

### EVA-.L.-X





#### EVA-.L.-X - 5 LUX

Hoogte (m)				
1.0	2.2	4.9	0.7	2.2
1.5	3.0	6.7	0.7	2.0
2.0	3.5	8.3	0.8	2.1
2.5	3.8	9.5	0.8	2.2
3.0	3.9	10.3	0.8	2.4
3.5	3.8	10.9	0.8	2.5
4.0	3.7	11.0	0.7	2.5





#### EVA-.L.-X - 5 LUX

Hoogte (m)				
4.5	3.4	11.0	0.6	2.4
5.0	2.6	10.9	0.5	2.3

#### EVA-.L.-X - 10 LUX

Hoogte (m)				
1.0	2.0	4.5	0.5	1.4
1.5	2.5	6.1	0.6	1.5
2.0	2.7	7.1	0.6	1.6
2.5	2.7	7.7	0.5	1.7
3.0	2.5	7.8	0.4	1.7
3.5	1.9	7.7	0.3	1.6

#### EVA-.L.-X - 15 LUX

Hoogte (m)				
1.0	1.9	4.3	0.4	1.1
1.5	2.2	5.6	0.5	1.3
2.0	2.2	6.2	0.4	1.4
2.5	2.0	6.3	0.3	1.4
3.0	1.1	6.2	0.2	1.3

## EVA-.L.-X2

### EVA-.L.-X<sup>2</sup> - 5 LUX

Hoogte (m)				
1.0	1.2	2.8	0.9	2.9
1.5	1.8	3.8	0.9	2.7
2.0	2.2	4.9	0.9	2.7
2.5	2.7	5.8	1.0	2.7
3.0	3.0	6.7	1.0	2.7
3.5	3.4	7.6	1.1	2.8
4.0	3.7	8.3	1.1	2.9

### EVA-.L.-X<sup>2</sup> - 5 LUX

Hoogte (m)				
4.5	3.9	9.0	1.1	3.0
5.0	4.0	9.7	0.9	3.1
5.5	0.5	10.3	0.1	3.1

### EVA-.L.-X<sup>2</sup> - 10 LUX

Hoogte (m)				
1.0	1.1	2.5	0.6	1.9
1.5	1.6	3.6	0.6	1.9
2.0	2.0	4.5	0.7	1.8
2.5	2.4	5.4	0.7	2.0
3.0	2.6	6.1	0.7	2.1
3.5	2.8	6.8	0.6	2.2





### EVA-.L.-X<sup>2</sup> - 15 LUX

Hoogte (m)				
1.0	1.0	2.4	0.5	1.6
1.5	1.6	3.4	0.5	1.5
2.0	1.9	4.3	0.6	1.6
2.5	2.2	5.1	0.6	1.7
3.0	2.3	5.7	0.4	1.8





## Spacingtabellen

### EVA-.W.-X





#### EVA-.W.-X - 5 LUX

Hoogte (m)				
1.0	1.3	2.7	1.3	2.7
1.5	1.8	3.8	1.8	3.8
2.0	2.1	4.7	2.1	4.7
2.5	1.9	5.5	1.9	5.5
3.0	1.3	5.3	1.3	5.3
3.5	0.9	5.3	0.9	5.3

#### EVA-.W.-X - 10 LUX

Hoogte (m)				
1.0	1.2	2.5	1.2	2.5
1.5	1.5	3.5	1.5	3.5
2.0	1.0	3.8	1.0	3.8
2.5	0.6	3.8	0.6	3.8





#### EVA-.W.-X - 15 LUX

Hoogte (m)				
1.0	1.1	2.5	1.1	2.5
1.5	1.0	3.2	1.0	3.2
2.0	0.5	3.1	0.5	3.1







## EVA-.W.-X2





### EVA-.W.-X<sup>2</sup> - 5 LUX

Hoogte (m)				
1.0	0.7	1.7	0.7	1.7
1.5	0.9	2.1	0.9	2.1
2.0	1.0	2.4	1.0	2.4
2.5	1.0	2.7	1.0	2.7

### EVA-.W.-X<sup>2</sup> - 10 LUX

Hoogte (m)				
1.0	0.6	1.4	0.6	1.4
1.5	0.7	1.8	0.7	1.8





### EVA-.W.-X<sup>2</sup> - 15 LUX

Hoogte (m)				
1.0	0.5	1.3	0.5	1.3





## Spacingtabellen

### INDULUX





IND 1X4A/3 - 1 LUX

Hoogte (m)				
2.0	3.7	9.4	3.0	7.5
2.5	3.9	10.0	3.3	8.3
3.0	4.0	10.5	3.4	8.8
3.5	4.0	10.9	3.5	9.3
4.0	4.0	11.1	3.5	9.6
4.5	3.8	11.3	3.4	9.8
5.0	3.6	11.3	3.3	9.9





IND 1X4A/3 - 1 LUX

Hoogte (m)				
5.5	3.4	11.2	3.1	10.0
6.0	3.0	11.1	2.8	9.9
6.5	2.5	10.8	2.3	9.7
7.0	1.7	10.4	1.6	9.4

IND 1X4A/3 - 5 LUX

Hoogte (m)				
1.0	1.7	4.3	1.4	3.6
1.5	1.8	4.8	1.6	4.1
2.0	1.7	5.0	1.5	4.7
2.5	1.5	5.0	1.4	4.7
3.0	1.0	4.8	0.9	4.5

IND 1X4A/3 - 10 LUX

Hoogte (m)				
1.0	1.3	3.4	1.1	2.9
1.5	1.2	3.6	1.1	3.1
2.0	0.8	3.4	0.8	3.1

## INDULUX

### IND 1X4HF - 1 LUX

Hoogte (m)				
2.0	4.7	11.8	3.7	9.0
2.5	5.0	12.7	4.1	10.1
3.0	5.3	13.5	4.4	10.9
3.5	5.4	14.2	4.6	11.6
4.0	5.6	14.7	4.8	12.2
4.5	5.6	15.1	4.9	12.7
5.0	5.6	15.4	4.9	13.2

### IND 1X4HF - 1 LUX

Hoogte (m)				
5.5	5.6	15.7	5.0	13.5
6.0	5.5	15.8	4.9	13.7
6.5	5.4	15.9	4.8	13.9
7.0	5.2	16.0	4.7	14.0
7.5	4.9	15.9	4.5	14.1
8.0	4.6	15.8	4.2	14.1
8.5	4.2	15.6	3.9	14.0

### IND 1X4HF - 1 LUX

Hoogte (m)				
9.0	3.7	15.4	3.5	13.8
9.5	3.0	15.0	2.9	13.6
10.0	2.1	14.6	2.1	13.3

### IND 1X4HF - 5 LUX

Hoogte (m)				
1.5	2.4	6.2	2.0	5.1
2.0	2.5	6.7	2.2	5.7
2.5	2.5	7.0	2.2	6.1
3.0	2.4	7.1	2.1	6.3
3.5	2.1	7.1	1.9	6.3
4.0	1.7	6.9	1.6	6.2
4.5	0.8	6.5	0.9	5.9

## Spacingtabellen

### INDULUX

IND 1X4HF - 10 LUX

Hoogte (m)				
1.0	1.7	4.3	1.4	3.6
1.5	1.8	4.8	1.6	4.1
2.0	1.7	5.0	1.5	4.4
2.5	1.5	5.0	1.4	4.5
3.0	1.0	4.8	0.9	4.3

IND 1X4HF - 15 LUX

Hoogte (m)				
1.0	1.4	3.7	1.2	3.1
1.5	1.4	4.1	1.3	3.5
2.0	1.2	4.1	1.1	3.6
2.5	0.7	3.8	0.7	3.5

IND 1X4/24 - 1 LUX






Hoogte (m)				
2.0	4.5	11.3	3.6	8.7
2.5	4.8	12.2	3.9	9.7
3.0	5.0	12.9	4.2	10.5
3.5	5.1	13.5	4.4	11.2
4.0	5.2	14.0	4.5	11.7
4.5	5.3	14.3	4.6	12.2
5.0	5.3	14.6	4.6	12.5

IND 1X4/24 - 1 LUX






Hoogte (m)				
5.5	5.2	14.8	4.6	12.8
6.0	5.1	14.9	4.5	13.0
6.5	4.9	14.9	4.4	13.1
7.0	4.6	14.9	4.2	13.2
7.5	4.3	14.8	4.0	13.2
8.0	3.9	14.6	3.6	13.1
8.5	3.4	14.3	3.2	12.9

## INDULUX






### IND 1X4/24 - 1 LUX

Hoogte (m)					
9.0	2.7	14.0	2.6	12.7	
9.5	1.5	13.5	1.6	12.3	






### IND 1X4/24 - 5 LUX

Hoogte (m)					
1.0	2.1	5.2	1.7	4.1	
1.5	2.3	6.0	2.0	4.9	
2.0	2.4	6.4	2.1	5.4	
2.5	2.3	6.6	2.1	5.7	
3.0	2.1	6.7	1.9	5.9	
3.5	1.8	6.6	1.7	5.9	
4.0	1.2	6.3	1.2	5.7	

### IND 1X4/24 - 10 LUX

Hoogte (m)					
1.0	1.6	4.1	1.4	3.4	
1.5	1.7	4.6	1.5	3.9	
2.0	1.6	4.7	1.4	4.1	
2.5	1.3	4.6	1.2	4.1	
3.0	0.5	4.3	0.5	3.9	





### IND 1X4/24 - 15 LUX

Hoogte (m)					
1.0	1.3	3.6	1.2	3.0	
1.5	1.3	3.8	1.2	3.4	
2.0	1.1	3.8	1.0	3.4	
2.5	0.2	3.5	0.3	3.1	





## Spacingtabellen

### LUTIA





LTA-DLO - 1 LUX

Hoogte (m)				
2.0	4.0	8.8	1.2	3.6
2.5	4.6	10.3	1.2	3.5
3.0	5.3	11.7	1.1	3.4
3.5	5.8	13.0	1.2	3.3
4.0	6.1	14.5	1.2	3.2
4.5	6.5	15.5	1.2	3.3
5.0	6.4	16.3	1.2	3.3





LTA-DLO - 1 LUX

Hoogte (m)				
5.5	6.4	17.3	1.1	3.4
6.0	6.4	17.8	1.0	3.4
6.5	6.1	18.2	0.9	3.4
7.0	5.5	18.1	0.8	3.3
7.5	3.4	18.2	0.6	3.2

LTA-CLO - 1 LUX

Hoogte (m)				
2.0	4.5	10.1	1.8	5.0
2.5	5.2	11.6	1.8	5.2
3.0	5.9	13.1	1.7	5.3
3.5	6.6	14.6	1.7	5.1
4.0	7.2	16.0	1.7	5.0
4.5	7.8	17.3	1.7	4.9
5.0	8.3	18.7	1.7	4.9

LTA-CLO - 1 LUX

Hoogte (m)				
5.5	8.8	20.0	1.7	4.7
6.0	9.1	21.3	1.7	4.7
6.5	9.4	22.4	1.7	4.7
7.0	9.4	23.4	1.7	4.8
7.5	9.4	24.4	1.7	4.9
8.0	9.4	25.8	1.6	4.9
8.5	9.3	25.8	1.5	4.9

## LUTIA

—  
LTA-CLO - 1 LUX

Hoogte (m)					
9.0	9.1	26.2	1.4	4.9	
9.5	8.8	26.5	1.3	4.9	
10.0	8.2	26.5	1.2	4.8	
10.5	6.1	26.5	1.0	4.7	
11.0	4.7	26.5	0.8	4.6	

—  
LTA-DLO - 5 LUX

Hoogte (m)					
1.0	1.9	4.2	0.5	1.6	
1.5	2.5	5.7	0.5	1.5	
2.0	2.9	6.9	0.5	1.5	
2.5	2.9	7.8	0.5	1.5	
3.0	2.6	8.1	0.4	1.5	
3.5	0.9	8.1	0.2	1.4	

—  
LTA-CLO - 5 LUX

Hoogte (m)					
1.0	2.1	4.8	0.8	2.3	
1.5	2.8	6.3	0.8	2.3	
2.0	3.5	7.7	0.7	2.2	
2.5	4.0	9.1	0.8	2.1	
3.0	4.2	10.2	0.8	2.1	
3.5	4.2	11.2	0.7	2.2	
4.0	4.1	11.7	0.6	2.2	


—  
LTA-CLO - 5 LUX

Hoogte (m)					
4.5	3.7	11.8	0.5	2.2	
5.0	1.8	11.8	0.3	2.0	


## Spacingtabellen

### LUTIA - MUUR / WALL


LTA-DLO - 1 LUX - 1m

Hoogte (m)		
2.0	3.7	8.2
2.5	4.3	9.6
3.0	4.8	11.0
3.5	5.2	12.0
4.0	5.6	12.8
5.0	5.8	15.2
6.0	5.6	16.0
7.0	2.7	16.0


LTA-DLO - 1 LUX - 2m

Hoogte (m)		
4.0	4.4	13.0
5.0	5.2	15.4
6.0	5.1	16.6
7.0	3.2	17.0

LTA-CLO - 1 LUX - 1m

Hoogte (m)		
2.0	4.1	9.2
3.0	5.5	12.4
4.0	6.7	15.2
5.0	7.7	17.6
6.0	8.2	19.8
7.0	8.2	21.6
8.0	8.1	22.8
9.0	7.4	22.8

LTA-CLO - 1 LUX - 2m

Hoogte (m)		
3.0	5.0	12.0
4.0	6.7	15.4
5.0	7.8	18.0
6.0	8.5	20.4
7.0	8.7	22.4
8.0	8.9	23.6
9.0	8.6	24.0
10.0	7.7	24.2



## EVA-.L.-X

### EVA-.L. - 0,5 LUX

Hoogte (m)				
2.0	10.6	25.8	2.8	7.0
2.5	11.5	28.9	3.0	7.6
3.0	11.6	30.6	3.2	8.1
3.5	10.9	32.3	3.2	8.5
4.0	11.1	32.9	2.5	8.9
4.5	11.5	32.3	2.0	8.9
5.0	6.8	30.9	1.8	8.4

### EVA-.L.-X - 0,5 LUX

Hoogte (m)				
5.0	9.0	22.3	2.5	6.4
5.5	10.6	23.9	2.5	6.5
6.0	11.0	25.4	2.6	6.6
6.5	11.4	26.8	2.7	6.7
7.0	11.8	28.0	2.8	6.8
7.5	12.0	29.2	2.8	7.8
8.0	12.2	30.3	2.8	7.8

### EVA-.L.-X<sup>2</sup> - 0,5 LUX

Hoogte (m)				
9.0	9.4	20.6	3.3	8.4
9.5	9.8	21.5	3.3	8.6
10.0	10.1	22.3	3.4	8.7
10.5	10.4	23.2	3.5	8.8
11.0	10.8	24.0	3.5	8.0
11.5	11.1	24.8	3.5	9.1
12.0	11.4	25.6	3.6	9.3

## Spacingtabellen

### DECOLED

DECO 20/DEC - 0,5 LUX

Hoogte (m)				
2.0	4.2	10.3	4.1	10.3
2.5	4.6	11.3	4.5	11.3
3.0	4.9	12.1	4.8	12.1
3.5	5.1	12.8	5.0	12.8
4.0	5.3	13.5	5.2	13.5
4.5	5.4	14.0	5.3	14.0
5.0	5.5	14.4	5.4	14.4

DECO 20/DEC - 0,5 LUX

Hoogte (m)				
5.5	5.6	14.8	5.4	14.8
6.0	5.6	15.1	5.5	15.1
6.5	5.5	15.3	5.4	15.3
7.0	5.4	15.5	5.3	15.5
7.5	5.3	15.6	5.2	15.6
8.0	5.1	15.6	5.0	15.6
8.5	4.9	15.6	4.8	15.6

DECO 20/DEC - 0,5 LUX

Hoogte (m)				
9.0	4.6	15.6	4.5	15.6
9.5	4.2	15.5	4.1	15.5
10.0	3.7	15.3	3.6	15.3
10.5	3.0	15.0	2.9	15.0
11.0	2.0	14.7	1.9	14.7

DECO 20/DEC - 1 LUX

Hoogte (m)				
2.0	3.4	8.4	3.3	8.4
2.5	3.6	9.1	3.6	9.1
3.0	3.8	9.7	3.7	9.7
3.5	3.9	10.2	3.8	10.2
4.0	3.9	10.6	3.9	10.6
4.5	3.9	10.8	3.8	10.8
5.0	3.8	11.0	3.8	11.0

## DECOLED

### DECO 20/DEC - 1 LUX

Hoogte (m)				
5.5	3.7	11.0	3.6	11.0
6.0	3.5	11.0	3.4	11.1
6.5	3.1	10.0	3.1	10.0
7.0	2.7	10.8	2.6	10.8
7.5	2.0	10.6	1.9	10.6
8.0	0.2	10.2	0.2	10.2

### DECO 20/DEC - 5 LUX

Hoogte (m)				
1.0	1.6	3.9	1.5	3.1
1.5	1.7	4.5	1.7	3.5
2.0	1.8	4.8	1.7	4.8
2.5	1.6	4.9	1.6	4.9
3.0	1.3	4.9	1.3	4.9
3.5	0.6	4.6	0.6	4.6

### DECO 20/DEC - 10 LUX

Hoogte (m)				
1.0	1.2	3.1	1.2	2.5
1.5	1.2	3.5	1.2	2.6
2.0	1.0	3.5	1.0	3.5
2.5	0.3	3.2	0.3	3.2

### DECO 20/HF - 0.5 LUX

Hoogte (m)				
2.0	4.1	10.3	4.4	10.3
3.0	6.1	15.5	6.5	15.4
4.0	8.1	20.6	8.7	20.6
5.0	10.2	25.8	10.9	25.7
6.0	11.8	29.4	12.5	29.9
7.0	12.8	31.5	13.0	31.9
8.0	13.7	33.0	13.6	33.4

## Spacingtabellen

### DECOLED

DECO 20/HF - 0.5 LUX

Hoogte (m)				
9.0	14.3	34.9	14.2	35.2
10.0	14.9	36.6	15.0	36.7
12.0	15.6	39.0	15.6	39.3
14.0	16.2	41.5	16.6	41.9
16.0	16.6	43.4	16.5	43.9
18.0	16.4	45.1	16.9	45.1
20.0	17.1	46.5	17.3	45.9

DECO 20/HF - 0.5 LUX

Hoogte (m)				
22.0	16.5	47.1	16.8	46.1
24.0	16.0	46.9	16.6	46.8
26.0	16.0	47.1	15.9	47.7
28.0	16.3	47.8	14.4	48.1
30.0	12.8	47.5	14.8	46.4
32.0	10.7	46.5	11.5	46.4
34.0	7.6	46.0	8.0	45.6

DECO 20/HF - 1 LUX

Hoogte (m)				
2.0	4.1	10.3	4.4	10.3
3.0	6.1	15.5	6.5	15.4
4.0	8.1	20.5	8.7	20.5
5.0	9.1	22.3	9.3	22.6
6.0	9.9	24.0	9.8	24.3
7.0	10.5	25.8	10.5	25.8
8.0	10.9	27.1	11.1	27.1

DECO 20/HF - 1 LUX

Hoogte (m)				
9.0	11.2	28.1	11.3	28.4
10.0	11.5	29.5	11.7	29.8
12.0	11.8	31.1	11.8	39.3
14.0	12.1	32.7	12.2	41.9
16.0	11.5	33.2	11.8	43.9
18.0	11.3	33.1	11.6	45.1
20.0	9.3	33.7	10.1	45.9

## DECOLED

DECO 20/HF - 5 LUX

Hoogte (m)				
1.0	2.0	4.2	2.2	4.4
1.5	3.1	6.3	3.3	6.7
2.0	3.8	9.5	4.0	9.7
2.5	4.3	10.4	4.3	10.5
3.0	4.6	11.3	4.6	11.4
3.5	4.9	12.1	5.0	12.0
4.0	5.0	12.5	5.1	12.7

DECO 20/HF - 5 LUX

Hoogte (m)				
4.5	5.1	13.2	5.2	13.3
5.0	5.2	13.7	5.2	13.8
6.0	5.3	14.4	5.4	14.5
7.0	5.2	14.9	5.3	14.6
8.0	5.0	14.8	5.2	15.0
9.0	4.1	15.1	4.5	15.2
10.0	3.6	14.8	3.9	14.7

DECO 20/HF - 10 LUX

Hoogte (m)				
1.0	2.0	4.2	2.2	4.4
1.5	2.8	6.3	2.9	5.8
2.0	3.2	7.8	3.2	7.9
2.5	3.5	8.6	3.5	8.5
3.0	3.6	9.1	3.7	9.2
3.5	3.7	9.7	3.7	9.8
4.0	3.7	10.1	3.8	10.1

DECO 20/HF - 10 LUX

Hoogte (m)				
4.5	3.8	10.4	3.9	10.3
5.0	3.7	10.5	3.7	10.3
5.5	3.6	10.5	3.7	10.5
6.0	3.6	10.6	3.4	10.8
6.5	2.9	10.6	3.1	10.8
7.0	2.7	10.5	2.9	10.4
7.5	1.8	10.3	1.9	10.2

## Spacingtabellen

### EVA-.W

EVA-.W. - 0,5 LUX

Hoogte (m)				
2.0	4.1	8.4	4.1	8.4
2.5	4.9	10.3	4.9	10.3
3.0	5.7	12.1	5.7	12.1
3.5	6.5	13.8	6.5	13.8
4.0	7.2	15.4	7.2	15.4
4.5	7.9	17.0	7.9	17.0
5.0	8.3	18.5	8.3	18.5

EVA-.W.-X - 0,5 LUX

Hoogte (m)				
5.5	6.1	13.5	6.1	13.5
6.0	6.4	14.4	6.4	14.4
6.5	6.7	15.3	6.7	15.3
7.0	6.9	16.1	6.9	16.1
7.5	6.9	16.9	6.9	16.9
8.0	5.6	17.6	5.6	17.6
8.5	4.9	16.9	4.9	16.9

EVA-.W.-X<sup>2</sup> - 0,5 LUX





Hoogte (m)				
9.0	5.4	12.8	5.4	12.8
9.5	5.5	13.2	5.5	13.2
10.0	5.7	13.6	5.7	13.6
10.5	5.8	13.9	5.8	13.9
11.0	5.9	14.2	5.9	14.2
11.5	6.0	14.5	6.0	14.5
12.0	6.1	14.9	6.1	14.9

EVA-.W.-X<sup>2</sup> - 0,5 LUX





Hoogte (m)				
12.5	6.2	15.2	6.2	15.2
13.0	6.3	15.4	6.3	15.4
13.5	6.4	15.7	6.4	15.7
14.0	6.4	16.0	6.4	16.0
14.5	6.5	16.2	6.5	16.2
15.0	6.5	16.5	6.5	16.5
15.5	6.6	16.7	6.6	16.7

## XION





XN-EX-(24/HF) - 1 LUX

Hoogte (m)				
2.0	3.6	8.8	3.5	8.2
2.5	3.9	9.7	3.8	9.3
3.0	4.2	10.4	4.1	10.1
3.5	4.3	11.0	4.3	10.8
4.0	4.5	11.6	4.4	11.3
4.5	4.5	12.0	4.5	11.8
5.0	4.5	12.3	4.5	12.2





XN-EX-(24/HF) - 1 LUX

Hoogte (m)				
5.5	4.4	12.5	4.5	12.4
6.0	4.3	12.7	4.4	12.6
6.5	4.1	12.8	4.2	12.7
7.0	3.9	12.7	3.9	12.8
7.5	3.5	12.7	3.5	12.7
8.0	2.0	12.5	3.0	12.5
8.5	2.3	12.2	2.3	12.3

XN-EX-(24/HF) - 5 LUX

Hoogte (m)				
1.0	1.7	4.1	1.6	3.9
1.5	1.9	4.9	1.9	4.7
2.0	2.0	5.3	2.0	5.3
2.5	1.0	5.6	2.0	5.6
3.0	1.8	5.7	1.8	5.7
3.5	1.4	5.6	1.4	5.6
4.0	0.5	5.3	0.5	5.4





XN-EX-(24/HF) - 10 LUX

Hoogte (m)				
1.0	1.3	3.4	1.3	3.3
1.5	1.4	3.8	1.4	3.8
2.0	1.3	4.0	1.3	4.0
2.5	1.0	4.0	1.0	4.0





## Spacingtabellen

### EVA-.W.-3





EVA-.W.-3 - 0,5 LUX

Hoogte (m)				
2.0	3.5	8.4	3.5	78.4
2.5	4.2	10.2	4.2	10.2
3.0	4.8	11.7	4.8	11.7
3.5	5.2	13.2	5.2	13.2
4.0	5.6	14.6	5.6	4.6
4.5	6.0	16.0	6.0	16.0
5.0	6.2	17.4	6.2	17.4

EVA-.W.-X-3 - 0,5 LUX

Hoogte (m)				
5.5	5.9	13.1	5.9	13.1
6.0	6.1	14.0	6.1	14.0
6.5	6.3	14.8	6.3	14.8
7.0	6.4	15.5	6.4	15.5
7.5	5.6	16.2	5.6	16.2
8.0	4.7	16.0	4.7	16.0
8.5	4.2	15.9	4.2	15.9





EVA-.W.-X<sup>2</sup>-3 - 0,5 LUX

Hoogte (m)				
9.0	3.7	12.0	3.0	12.0
9.5	4.0	12.3	4.5	12.3
10.0	4.0	12.7	4.0	12.7
10.5	4.2	13.0	4.5	13.0
11.0	4.4	13.3	4.0	13.3
11.5	4.4	13.7	4.5	13.7
12.0	4.5	14.0	4.0	14.0







## EVA-.W.-3





### EVA-.W.-3 - 1 LUX

Hoogte (m)				
2.0	3.2	7.9	3.2	7.9
2.5	3.8	9.4	3.8	9.4
3.0	4.1	10.8	4.1	10.8
3.5	4.4	12.2	4.4	12.2
4.0	2.5	13.4	2.5	13.4
4.5	1.2	12.1	1.2	12.1
5.0	1.0	12.5	1.0	12.5

### EVA-.W.-X-3 - 1 LUX

Hoogte (m)				
4.0	4.2	9.5	4.2	9.5
4.5	4.4	10.3	4.4	10.3
5.0	4.4	11.1	4.4	11.1
5.5	3.5	11.7	3.5	11.7
6.0	3.0	11.2	3.0	11.2
6.5	2.6	11.2	2.6	11.2
7.0	2.2	11.3	2.2	11.3





### EVA-.W.-X<sup>2</sup>-3 - 1 LUX

Hoogte (m)				
9.0	3.2	10.2	3.2	10.2
9.5	3.3	10.5	3.3	10.5
10.0	3.3	10.8	3.3	10.8
10.5	3.3	11.1	3.3	11.1
11.0	3.3	11.4	3.3	11.4
11.5	4.0	9.4	4.0	9.4
12.0	4.0	8.8	4.0	8.8





## Spacingtabellen

### EVA-.L.-3





#### EVA-.L.-3 - 1 LUX

Hoogte (m)				
2.0	2.0	5.3	7.3	20.2
2.5	1.9	5.8	7.2	21.4
3.0	1.3	5.9	7.3	21.4
3.5	1.3	5.4	4.3	20.5
4.0	1.1	4.2	3.8	18.2
4.5	1.0	3.5	2.7	13.8
5.0	1.0	3.2	2.4	12.3

#### EVA-.L.-X-3 - 1 LUX




Hoogte (m)				
5.0	1.8	4.7	8.0	19.3
5.5	1.8	4.9	8.1	20.3
6.0	1.8	5.0	7.9	21.2
6.5	1.7	5.2	8.0	21.9
7.0	1.7	5.2	8.0	22.4
7.5	1.6	5.3	8.0	22.8
8.0	1.6	5.3	7.7	23.0

#### EVA-.L.-X<sup>2</sup>-3 - 1 LUX




Hoogte (m)				
8.0	2.3	6.1	7.4	16.9
8.5	2.3	6.2	7.6	17.7
9.0	2.2	6.3	7.8	18.4
9.5	2.2	6.4	7.9	19.1
10.0	2.1	6.5	8.4	19.7
10.5	1.9	6.5	8.2	20.3
11.0	1.5	6.6	8.3	20.9

## EVA-.SO-3




EVA-.S.-3 - 1 LUX – 2m breed

Hoogte (m)			
1.5	2.7	6.4	
2.0	3.0	7.3	
2.5	3.1	8.0	
3.0	1.5	8.0	
3.5	1.4	7.0	
4.0	1.3	4.4	
4.5	0.8	3.6	

EVA-.S.-3 - 1 LUX – 3m breed

Hoogte (m)			
1.5	3.1	7.0	
2.0	3.2	7.4	
2.5	3.5	8.0	
3.0	3.6	8.6	
3.5	3.5	8.8	
4.0	2.3	8.7	
4.5	1.3	7.6	
5.0	1.2	4.9	





EVA-.S.-3 - 1 LUX – 4m breed

Hoogte (m)			
1.5	3.3	7.6	
2.0	3.7	8.2	
2.5	3.8	8.7	
3.0	4.0	9.2	
3.5	4.1	9.5	
4.0	4.0	9.7	
4.5	1.1	9.8	
5.0	1.0	8.6	





## Spacingtabellen

### LUTIA





LTA-DLO - 0.5 LUX

Hoogte (m)				
2.0	4.4	10.0	1.8	4.8
2.5	5.1	11.5	1.7	5.0
3.0	5.8	12.9	1.7	5.1
3.5	6.5	14.4	1.6	4.9
4.0	7.2	15.8	1.6	4.8
4.5	7.7	17.2	1.6	4.8
5.0	8.2	18.6	1.6	4.6





LTA-DLO - 0.5 LUX

Hoogte (m)				
5.5	8.7	22.2	1.7	4.5
6.0	9.0	23.1	1.7	4.6
6.5	9.1	24.0	1.7	4.6
7.0	9.1	24.8	1.6	4.7
7.5	9.1	25.2	1.6	4.7
8.0	9.1	18.2	1.5	4.8
8.5	9.0	18.2	1.4	4.8

LTA-DLO - 0.5 LUX

Hoogte (m)				
9.0	8.7	25.6	1.3	4.8
9.5	8.2	25.7	1.2	4.7
10.0	7.7	25.6	1.1	4.6
10.5	5.1	25.7	0.9	4.5
11.0	3.3	25.7	0.6	4.4

LTA-CLO - 0.5 LUX

Hoogte (m)				
2.0	4.6	10.4	2.0	5.5
2.5	5.7	13.0	2.5	6.8
3.0	6.5	14.8	2.6	7.1
3.5	7.3	16.3	2.6	7.3
4.0	8.0	17.8	2.5	7.4
4.5	8.7	19.2	2.5	7.4
5.0	9.4	20.7	2.4	7.2

## LUTIA

### LTA-CLO - 0.5

Hoogte (m)				
5.5	10.0	22.2	2.4	7.1
6.0	10.6	23.6	2.4	7.0
6.5	11.2	24.9	2.4	7.0
7.0	11.7	26.3	2.4	6.9
7.5	12.2	27.6	2.4	6.7
8.0	12.6	28.9	2.5	6.6
8.5	12.9	30.1	2.5	6.7

### LTA-CLO - 0.5 LUX

Hoogte (m)				
9.0	13.2	31.3	2.5	6.7
9.5	13.3	32.4	2.5	6.7
10.0	13.2	33.3	2.4	6.8
10.5	13.2	34.3	2.4	6.9
11.0	13.2	35.2	2.3	6.9
11.5	13.3	36.0	2.2	7.0
12.0	13.2	36.4	2.1	7.0

### LTA-CLO - 0.5 LUX

Hoogte (m)				
12.5	13.0	36.8	2.0	7.0
13.0	12.7	37.3	1.9	7.0
13.5	12.4	37.6	1.8	6.9
14.0	11.8	37.5	1.7	6.9
14.5	11.3	37.4	1.6	6.8
15.0	8.3	37.4	1.4	6.6
15.5	6.8	37.5	1.2	6.5

## Spacingtabellen

### HILED

#### HIL-.LO - 0.5 LUX

Hoogte (m)				
2.0	4.0	8.6	2.0	5.7
2.5	5.0	10.8	2.4	7.1
3.0	6.0	12.9	2.9	8.5
3.5	7.0	15.1	3.4	10.0
4.0	8.0	17.2	3.9	11.4
4.5	8.9	19.4	4.4	12.8
5.0	9.8	21.2	4.4	13.3

#### HIL-.LO - 0.5 LUX

Hoogte (m)				
5.5	10.5	22.9	4.3	13.1
6.0	11.3	24.5	4.3	13.0
6.5	12.1	26.0	4.3	12.9
7.0	12.9	27.5	4.4	12.6
8.0	14.3	30.5	4.5	12.2
9.0	15.7	33.7	4.8	12.3
10.0	17.2	36.7	5.1	12.4

#### HIL-.LO - 0.5 LUX

Hoogte (m)				
11.0	18.7	39.7	5.4	12.6
12.0	20.1	42.5	5.7	13.2
13.0	21.5	45.1	6.0	13.7
14.0	22.8	48.1	6.2	14.3
15.0	24.1	51.1	6.5	15.0
16.0	25.4	54.0	6.7	15.6
17.0	26.6	56.9	6.8	16.1

#### HIL-.LO - 0.5 LUX






Hoogte (m)				
18.0	27.7	59.7	7.0	16.7
19.0	28.9	62.4	7.0	17.2
20.0	30.0	65.1	7.1	17.7
21.0	31.0	67.6	7.0	18.2
22.0	32.1	70.2	7.0	18.6
23.0	33.1	72.7	6.8	19.0
24.0	33.8	75.1	6.5	19.3

#### HIL-.LO - 0.5 LUX






Hoogte (m)				
25.0	34.3	77.4	6.1	19.6
26.0	34.8	79.7	5.5	19.8
27.0	35.3	81.0	4.7	19.9
28.0	34.6	84.2	3.5	19.8
29.0	5.4	86.3	1.2	19.5

## HILED






HIL-WO - 0.5 LUX

Hoogte (m)					
2.0	3.7	8.1	3.7	8.1	
2.5	4.7	10.1	4.7	10.1	
3.0	5.6	12.1	5.6	12.1	
3.5	6.5	13.9	6.5	13.9	
4.0	7.2	15.4	7.2	15.4	
4.5	7.8	17.0	7.8	17.0	
5.0	8.4	18.5	8.4	18.5	






HIL-WO - 0.5 LUX

Hoogte (m)					
5.5	8.9	19.9	8.9	19.9	
6.0	9.4	21.2	9.4	21.2	
6.5	9.8	22.5	9.8	22.5	
7.0	10.2	23.7	10.2	23.7	
8.0	10.9	25.7	10.9	25.7	
9.0	11.5	27.5	11.5	27.5	
10.0	12.0	29.0	12.0	29.0	

HIL-WO - 0.5 LUX

Hoogte (m)					
11.0	12.5	30.4	12.5	30.4	
12.0	13.0	31.7	13.0	31.7	
13.0	13.3	32.9	13.3	32.9	
14.0	13.5	33.9	13.5	33.9	
15.0	13.6	34.9	13.6	34.9	
16.0	13.6	35.8	13.6	35.8	
17.0	13.3	36.6	13.3	36.6	

HIL-WO - 0.5 LUX

Hoogte (m)					
18.0	12.7	37.3	12.7	37.3	
19.0	11.7	37.8	11.7	37.8	
20.0	8.9	38.2	8.9	38.2	
21.0	2.2	38.5	2.2	38.5	

## Spacingtabellen

### INDULUX

IND 1X4A/3 - 0.5 LUX

Hoogte (m)				
2.0	4.7	11.8	3.7	9.0
2.5	5.0	12.7	4.1	10.1
3.0	5.3	13.5	4.4	10.9
3.5	5.4	14.2	4.6	11.6
4.0	5.6	14.7	4.8	12.2
4.5	5.6	15.1	4.9	12.7
5.0	5.6	15.4	4.9	13.2

IND 1X4A/3 - 0.5 LUX

Hoogte (m)				
5.5	5.6	15.7	5.0	13.5
6.0	5.5	15.8	4.9	13.7
6.5	5.4	15.9	4.8	13.9
7.0	5.2	16.0	4.7	14.0
8.0	4.6	15.8	4.2	14.1
9.0	3.7	15.4	3.5	13.8
10.0	2.1	14.6	2.1	13.3

IND 1X4HF - 0.5 LUX

Hoogte (m)				
2.0	5.4	13.4	4.1	9.9
2.5	6.4	16.0	5.0	12.0
3.0	6.8	17.0	5.4	13.2
3.5	7.1	17.9	5.8	14.2
4.0	7.3	18.7	6.1	15.0
4.5	7.5	19.5	6.3	15.8
5.0	7.7	20.1	6.5	16.5

IND 1X4HF - 0.5 LUX

Hoogte (m)				
5.5	7.8	20.6	6.7	17.1
6.0	7.9	21.1	6.8	17.7
6.5	8.0	21.5	6.9	18.1
7.0	8.0	21.8	7.0	18.6
8.0	7.9	22.3	7.0	19.2
9.0	7.7	22.5	6.9	19.6
10.0	7.3	22.6	6.6	19.9





IND 1X4HF - 0.5 LUX

Hoogte (m)				
11.0	6.7	22.5	6.2	19.9
12.0	6.0	22.1	5.6	19.8
13.0	4.9	21.6	4.6	19.4
14.0	3.3	20.8	3.2	18.9







## INDULUX





IND 1X4/24 - 0.5 LUX

Hoogte (m)				
2.0	5.4	13.4	4.1	9.9
2.5	6.1	15.3	4.8	11.6
3.0	6.5	16.3	5.2	12.7
3.5	6.7	17.1	5.6	13.7
4.0	7.0	17.9	5.8	14.5
4.5	7.2	18.6	6.1	15.2
5.0	7.3	19.1	6.2	15.8

IND 1X4/24 - 0.5 LUX

Hoogte (m)				
5.5	7.4	19.6	6.4	16.4
6.0	7.4	20.0	6.5	16.9
6.5	7.5	20.4	6.5	17.3
7.0	7.4	20.6	6.6	17.7
8.0	7.3	21.0	6.5	18.2
9.0	7.0	21.1	6.3	18.5
10.0	6.5	21.1	5.9	18.6






IND 1X4/24 - 0.5 LUX

Hoogte (m)				
11.0	5.8	20.8	5.4	18.5
12.0	4.8	20.3	4.5	18.2
13.0	3.3	19.5	3.2	17.7






## Spacingtabellen

### EVA-.W.






#### EVA-.W. - 5 LUX

Hoogte (m)					
1.0		1.9	4.0	1.9	4.0
1.5		2.6	5.6	2.6	5.6
2.0		1.5	6.0	1.5	6.0
2.5		1.1	6.1	1.1	6.1

#### EVA-.W. - 10 LUX





Hoogte (m)					
1.0		1.8	3.8	1.8	3.8
1.5		1.0	4.1	1.0	4.1
2.0		0.5	3.0	0.5	3.0

#### EVA-.W. - 15 LUX





Hoogte (m)					
1.0		1.5	3.6	1.5	3.6
1.5		0.6	3.5	0.6	3.5

## WWA-LS





### WWA-LS - 0.5 LUX

Hoogte (m)				
2.0	4.4	10.8	4.0	9.8
2.5	4.7	11.7	4.3	10.8
3.0	5.0	12.5	4.6	11.5
3.5	5.2	13.1	4.8	12.2
4.0	5.3	13.8	4.9	12.8
4.5	5.4	14.2	5.0	13.3
5.0	5.4	14.5	5.1	13.6

### WWA-LS - 0.5 LUX

Hoogte (m)				
5.5	5.4	14.8	5.0	13.8
6.0	5.3	15.0	5.0	14.1
6.5	5.3	15.2	4.9	14.3
7.0	5.0	15.2	4.8	14.4
7.5	4.8	15.1	4.5	14.3
8.0	4.6	15.1	4.2	14.2
8.5	4.1	15.0	3.9	14.1

### WWA-LS - 0.5 LUX

Hoogte (m)				
9.0	3.6	14.8	3.4	14.0
9.5	3.1	14.5	2.6	13.8
10.0	1.9	14.0	1.6	13.4

## Spacingtabellen

### WWA-LS

#### WWA-LS - 1 LUX

Hoogte (m)				
2.0	3.5	8.6	3.2	8.0
2.5	3.7	9.3	3.4	8.6
3.0	3.8	9.9	3.5	9.2
3.5	3.8	10.2	3.6	10.6
4.0	3.8	10.5	3.5	10.8
4.5	3.7	10.7	3.5	10.1
5.0	3.5	10.7	3.3	10.1

#### WWA-LS - 1 LUX

Hoogte (m)				
5.5	3.3	10.7	3.1	10.1
6.0	2.9	10.6	2.8	10.0
6.5	2.3	10.4	2.2	9.9
7.0	1.5	10.0	1.5	9.5

#### WWA-LS - 5 LUX

Hoogte (m)				
1.0	1.6	4.0	1.5	3.7
1.5	1.7	4.5	1.6	4.3
2.0	1.7	4.8	1.6	4.5
2.5	1.5	4.8	1.4	4.5
3.0	1.0	4.6	0.8	4.4

#### WWA-LS - 10 LUX

Hoogte (m)				
1.0	1.2	3.2	1.1	3.0
1.5	1.2	3.4	1.1	3.2
2.0	0.8	3.3	0.8	3.1

## Movion® Vluchtrouteverlichting

—  
EL800 Centraal lang - 0.5 LUX

Hoogte (m)				
2.0	1.9	5,1	6.1	12.7
2.5	2.1	5.3	7.4	15.5
3.0	2.2	5.5	8.7	18.2
3.5	2.4	5.8	9.8	20.8
4.0	2.5	6.1	10.8	23.3
4.5	2.6	6.5	11.7	25.7
5.0	2.5	6.8	12.1	28.0

—  
EL800 Centraal lang - 0.5 LUX

Hoogte (m)				
5.5	2.3	7.1	11.9	29.9
6.0	2.1	7.2	11.0	30.7
6.5	2.0	7.2	10.0	31.1
7.0	2.0	7.1	9.4	31.5
7.5	1.9	6.8	8.9	32.1
8.0	1.8	6.3	8.4	32.6
8.5	1.7	5.9	7.9	31.1





—  
EL800 Centraal lang - 1 LUX

Hoogte (m)				
2.0	1.5	3.8	5.8	12.2
2.5	1.7	4.1	7.0	14.8
3.0	1.8	4.5	8.0	17.3
3.5	1.8	4.8	8.6	19.6
4.0	1.6	5.0	8.3	21.5
4.5	1.4	5.1	7.2	22.1
5.0	1.4	5.0	6.6	22.3





## Spacingtabellen

### Movion® Vluchtrouteverlichting





EL800 Centraal lang - 1 LUX

Hoogte (m)				
5.5	1.3	4.7	6.1	23.0
6.0	1.2	4.2	5.6	22.0
6.5	1.0	4.0	4.6	20.0
7.0	0.7	4.0	3.3	18.8

EL800 Centraal lang - 5 LUX

Hoogte (m)				
1.0	0.7	1.8	1.9	5.6
1.5	0.8	2.1	3.8	8.5
2.0	0.6	2.3	3.3	9.9
2.5	0.6	2.0	2.7	10.3
3.0	0.4	1.8	1.9	8.7

EL800 Centraal lang - 10 LUX

Hoogte (m)				
1.0	0.6	1.4	1.2	3.7
1.5	0.4	1.6	2.1	7.0
2.0	0.3	1.3	1.6	6.5

## Movion® Vluchtrouteverlichting

### EL800 Decentraal lang - 0.5 LUX

Hoogte (m)				
2.0	1.8	4.6	6.0	12.6
2.5	1.9	4.8	7.3	15.3
3.0	2.1	5.1	8.5	18.0
3.5	2.2	5.4	9.6	20.5
4.0	2.3	5.8	10.5	22.9
4.5	2.2	6.1	10.9	25.1
5.0	2.1	6.4	10.6	27.0

### EL800 Decentraal lang - 0.5 LUX

Hoogte (m)				
5.5	1.9	6.5	9.7	27.8
6.0	1.8	6.5	8.7	28.0
6.5	1.7	6.3	8.2	28.5
7.0	1.7	5.9	7.7	29.2
7.5	1.5	5.4	7.2	28.4
8.0	1.4	5.2	6.5	26.4
8.5	1.2	5.1	5.4	24.7





### EL800 Decentraal lang - 1 LUX

Hoogte (m)				
2.0	1.5	3.5	5.7	12.1
2.5	1.6	3.8	6.8	14.6
3.0	1.6	4.2	7.6	17.0
3.5	1.5	4.5	7.6	19.0
4.0	1.3	4.6	6.6	19.8
4.5	1.2	4.5	5.9	20.1
5.0	1.2	4.1	5.4	20.7





## Spacingtabellen

### Movion® Vluchtrouteverlichting

EL800 Decentraal lang - 1 LUX

Hoogte (m)				
5.5	1.0	3.7	4.9	19.4
6.0	0.8	3.6	3.9	17.5

EL800 Decentraal lang- 5 LUX

Hoogte (m)				
1.0	0.7	1.6	1.6	5.2
1.5	0.7	2.0	3.4	8.3
2.0	0.6	2.0	2.7	9.0
2.5	0.5	1.7	2.1	8.5



## Movion® Vluchtrouteverlichting

EL800 Centraal wijd - 0.5 LUX

Hoogte (m)				
2.0	5.0	10.7	5.0	10.7
2.5	5.7	12.9	5.7	12.9
3.0	6.1	14.7	6.1	14.7
3.5	5.9	16.0	5.9	16.0
4.0	5.1	16.8	5.1	16.8
4.5	3.2	16.2	3.2	16.2
5.0	2.3	15.7	2.3	15.7





EL800 Centraal wijd - 1 LUX

Hoogte (m)				
2.0	4.3	10.0	4.3	10.0
2.5	4.2	11.3	4.2	11.3
3.0	2.8	11.8	2.8	11.8
3.5	1.6	11.2	1.6	11.2
4.0	1.1	9.8	1.1	9.8





## Spacingtabellen

### Movion® Vluchtrouteverlichting

EL800 Decentraal wijd - 0.5 LUX





Hoogte (m)				
2.0	4.8	10.6	4.8	10.6
2.5	5.4	12.5	5.4	12.5
3.0	5.4	14.1	5.4	14.1
3.5	4.9	15.0	4.9	15.0
4.0	3.0	14.6	3.0	14.6
4.5	2.0	14.1	2.0	14.1
5.0	1.5	12.7	1.5	12.7

EL800 Decentraal wijd - 1 LUX





Hoogte (m)				
2.0	3.8	9.6	3.8	9.6
2.5	3.4	10.6	3.4	10.6
3.0	1.7	10.2	1.7	10.2
3.5	1.1	9.1	1.1	9.1

## Movion® Vluchtrouteaanduiding Hybride





XTH800 Centraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
2.0	1.0	2.8	4.6	11.0
2.5	1.3	3.5	5.7	13.6
3.0	1.4	3.7	6.2	15.0
3.5	1.5	3.6	6.7	16.2
4.0	1.6	3.8	7.1	17.2
4.5	1.8	4.0	7.5	18.2
5.0	1.8	4.3	7.8	19.0

XTH800 Centraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
5.5	1.9	4.6	8.1	19.8
6.0	1.9	4.8	8.3	20.6
6.5	1.8	5.0	8.5	21.3
7.0	1.7	5.2	8.7	21.9
7.5	1.6	5.2	8.9	22.5
8.0	1.5	5.3	9.1	23.0
8.5	1.4	5.3	9.2	23.5





XTH800 Centraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
9.0	1.3	5.2	9.3	24.0
9.5	1.3	5.0	9.4	24.4
10.0	1.3	4.8	9.5	24.8
10.5	1.2	4.6	9.5	25.1
11.0	1.2	4.4	9.4	25.4
11.5	1.2	4.1	9.2	25.7
12.0	1.1	4.0	8.8	26.0





## Spacingtabellen

### Movion® Vluchtrouteaanduiding Hybride





XTH800 Centraal lang (met 1 lux lens) - 1 LUX

Hoogte (m)				
2.0	0.9	2.6	4.3	10.3
2.5	1.1	2.6	4.8	11.5
3.0	1.2	2.7	5.1	12.5
3.5	1.3	3.0	5.5	13.4
4.0	1.3	3.3	5.8	14.2
4.5	1.3	3.5	6.0	14.9
5.0	1.2	3.7	6.2	15.6

XTH800 Centraal lang (met 1 lux lens) - 1 LUX

Hoogte (m)				
5.5	1.1	3.7	6.4	16.1
6.0	1.0	3.7	6.5	16.6
6.5	0.9	3.6	6.6	17.1
7.0	0.9	3.5	6.7	17.5
7.5	0.9	3.2	6.7	17.8
8.0	0.8	3.0	6.6	18.1
8.5	0.8	2.8	6.2	18.4

XTH800 Centraal lang (met 5 lux lens) - 5 LUX

Hoogte (m)				
1.0	0.3	1.2	2.0	4.0
1.5	0.6	1.3	1.1	3.2
2.0	0.6	1.6	1.5	5.6
2.5	0.5	1.7	1.9	7.3
3.0	0.4	1.6	2.5	7.7
3.5	0.4	1.4	3.0	8.1
4.0	0.4	1.2	2.5	8.3
4.5	0.3	1.1	1.5	8.5

## Movion® Vluchtrouteaanduiding Hybride

XTH800 Decentraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
2.0	1.0	2.8	4.6	11.0
2.5	1.2	3.2	5.4	12.9
3.0	1.3	3.3	5.9	14.2
3.5	1.5	3.3	6.3	15.3
4.0	1.6	3.5	6.7	16.2
4.5	1.6	3.9	7.0	17.1
5.0	1.7	4.1	7.3	17.9

XTH800 Decentraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
5.5	1.7	4.4	7.5	18.6
6.0	1.6	4.6	7.7	19.3
6.5	1.5	4.7	7.9	19.9
7.0	1.4	4.7	8.1	20.5
7.5	1.3	4.7	8.2	21.0
8.0	1.2	4.7	8.3	21.5
8.5	1.2	4.5	8.4	21.9





XTH800 Decentraal lang (met 1 lux lens) - 0.5 LUX

Hoogte (m)				
9.0	1.1	4.3	8.5	22.2
9.5	1.1	4.1	8.5	22.6
10.0	1.1	3.9	8.4	22.9
10.5	1.0	3.6	8.2	23.2
11.0	1.0	3.5	7.6	23.4
11.5	1.0	3.3	6.7	23.6
12.0	0.9	3.3	5.8	23.9





## Spacingtabellen

### Movion® Vluchtrouteaanduiding Hybride





XTH800 Decentraal lang (met 1 lux lens) - 1 LUX

Hoogte (m)				
2.0	0.9	2.3	4.1	9.8
2.5	1.0	2.4	4.5	10.8
3.0	1.1	2.6	4.8	11.8
3.5	1.2	2.9	5.1	12.6
4.0	1.2	3.1	5.4	13.3
4.5	1.1	3.3	5.6	14.0
5.0	1.0	3.4	5.7	14.5

XTH800 Decentraal lang (met 1 lux lens) - 1 LUX

Hoogte (m)				
5.5	0.9	3.3	5.9	15.0
6.0	0.8	3.2	6.0	15.5
6.5	0.8	3.0	6.0	15.8
7.0	0.8	2.8	6.0	16.1
7.5	0.7	2.5	5.7	16.4
8.0	0.7	2.4	5.0	16.6
8.5	0.7	2.3	4.1	16.9

XTH800 Decentraal lang (met 5 lux lens) - 5 LUX

Hoogte (m)				
1.0	0.2	1.1	1.9	3.8
1.5	0.5	1.3	0.9	2.8
2.0	0.5	1.5	1.3	4.8
2.5	0.4	1.5	1.4	6.5
3.0	0.3	1.3	1.3	7.1
3.5	0.3	1.1	0.9	7.4
4.0	0.3	1.0	0.2	7.6

---

**ABB b.v.**

**Electrification Business Area**

George Hintzenweg 81, 3068 AX Rotterdam  
Postbus 301, 3000 AH Rotterdam

**Algemene informatie**

[abb.nl/lowvoltage](http://abb.nl/lowvoltage)



**Support**

[abb-elsupport.nl](http://abb-elsupport.nl)







**VanLien**

[vanlien.nl](http://vanlien.nl)



**Volg ABB ook via:**

-  ABB Electrification NL
-  ABB Electrification
-  ABB Electrification
-  ABB Electrification NL