

# 5SNG 0150Q170300

## 62Pak phase leg IGBT Module

$V_{CE} = 1700 \text{ V}$   
 $I_C = 150 \text{ A}$

Ultra low-loss, rugged SPT++ chip-set  
 Smooth switching SPT++ chip-set for good EMC  
 Cu base-plate for low thermal resistance  
 Industry standard package  
 2 switches in one package



### Maximum rated values <sup>1)</sup>

Parameter	Symbol	Conditions	min	max	Unit
Collector-emitter voltage	$V_{CES}$	$V_{GE} = 0 \text{ V}$ , $T_{vj} \geq 25 \text{ °C}$		1700	V
DC collector current	$I_C$	$T_C = 100 \text{ °C}$ , $T_{vj} = 175 \text{ °C}$		150	A
Peak collector current	$I_{CM}$	$t_p = 1 \text{ ms}$		300	A
Gate-emitter voltage	$V_{GES}$		-20	20	V
Total power dissipation	$P_{tot}$	$T_C = 25 \text{ °C}$ , $T_{vj} = 175 \text{ °C}$ , per switch		950	W
DC forward current	$I_F$			150	A
Peak forward current	$I_{FRM}$	$t_p = 1 \text{ ms}$		300	A
Surge current	$I_{FSM}$	$V_R = 0 \text{ V}$ , $T_{vj} = 175 \text{ °C}$ , $t_p = 10 \text{ ms}$ , half-sinewave		750	A
IGBT short circuit SOA	$t_{psc}$	$V_{CC} = 1300 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 1700 \text{ V}$ $V_{GE} \leq 15 \text{ V}$ , $T_{vj} \leq 175 \text{ °C}$		10	$\mu\text{s}$
Isolation voltage	$V_{isol}$	1 min, $f = 50 \text{ Hz}$		4000	V
Junction temperature	$T_{vj}$			175	$^{\circ}\text{C}$
Junction operating temperature	$T_{vj(op)}$		-40	175	$^{\circ}\text{C}$
Case temperature	$T_C$		-40	125 <sup>2)</sup> /150	$^{\circ}\text{C}$
Storage temperature	$T_{stg}$		-40	125	$^{\circ}\text{C}$
Mounting torques <sup>3)</sup>	$M_s$	Base-heatsink, M6 screws	3	6	Nm
	$M_{t1}$	Main terminals, M6 screws	3	6	

<sup>1)</sup> Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747

<sup>2)</sup> for UL1557 compliance  $T_{Cmax}$  must be limited to 125 $^{\circ}\text{C}$

<sup>3)</sup> for detailed mounting instructions refer to ABB Document No. 5SYA 2106

## IGBT characteristic values <sup>4)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector (-emitter) breakdown voltage	$V_{(BR)CES}$	$V_{GE} = 0 \text{ V}$ , $I_C = 10 \text{ mA}$ , $T_{vj} = 25 \text{ °C}$	1700			V
Collector-emitter <sup>5)</sup> saturation voltage	$V_{CE \text{ sat}}$	$I_C = 150 \text{ A}$ , $V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ °C}$	2.25	2.6	V
			$T_{vj} = 125 \text{ °C}$	2.55		V
			$T_{vj} = 175 \text{ °C}$	2.75		V
Collector cut-off current	$I_{CES}$	$V_{CE} = 1700 \text{ V}$ , $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		0.5	mA
			$T_{vj} = 125 \text{ °C}$	0.75		mA
			$T_{vj} = 175 \text{ °C}$	15		mA
Gate leakage current	$I_{GES}$	$V_{CE} = 0 \text{ V}$ , $V_{GE} = \pm 20 \text{ V}$ , $T_{vj} = 175 \text{ °C}$	-1		1	$\mu\text{A}$
Gate-emitter threshold voltage	$V_{GE(th)}$	$I_C = 6 \text{ mA}$ , $V_{CE} = V_{GE}$ , $T_{vj} = 25 \text{ °C}$	4.5		6.5	V
Gate charge	$Q_G$	$I_C = 150 \text{ A}$ , $V_{CE} = 900 \text{ V}$ , $V_{GE} = -15 \text{ V} \dots 15 \text{ V}$		1.1		$\mu\text{C}$
Input capacitance	$C_{ies}$	$V_{CE} = 25 \text{ V}$ , $V_{GE} = 0 \text{ V}$ , $f = 1 \text{ MHz}$ , $T_{vj} = 25 \text{ °C}$		9.6		nF
Output capacitance	$C_{oes}$			0.85		nF
Reverse transfer capacitance	$C_{res}$			0.8		nF
Internal gate resistance	$R_{Gint}$	per switch		3.9		$\Omega$
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	180		ns
			$T_{vj} = 125 \text{ °C}$	190		ns
			$T_{vj} = 175 \text{ °C}$	190		ns
Rise time	$t_r$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	66		ns
			$T_{vj} = 125 \text{ °C}$	68		ns
			$T_{vj} = 175 \text{ °C}$	73		ns
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	220		ns
			$T_{vj} = 125 \text{ °C}$	245		ns
			$T_{vj} = 175 \text{ °C}$	260		ns
Fall time	$t_f$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	185		ns
			$T_{vj} = 125 \text{ °C}$	195		ns
			$T_{vj} = 175 \text{ °C}$	205		ns
Turn-on switching energy	$E_{on}$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	43		mJ
			$T_{vj} = 125 \text{ °C}$	57		mJ
			$T_{vj} = 175 \text{ °C}$	73		mJ
Turn-off switching energy	$E_{off}$	$V_{CC} = 900 \text{ V}$ , $I_C = 150 \text{ A}$ , $R_G = 2.7 \text{ }\Omega$ , $V_{GE} = \pm 15 \text{ V}$ , $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ °C}$	22		mJ
			$T_{vj} = 125 \text{ °C}$	37		mJ
			$T_{vj} = 175 \text{ °C}$	46		mJ
Short circuit current	$I_{SC}$	$t_{psc} \leq 10 \text{ }\mu\text{s}$ , $V_{GE} = 15 \text{ V}$ , $V_{CC} = 1300 \text{ V}$ , $V_{CEM \text{ CHIP}} \leq 1700 \text{ V}$	$T_{vj} = 175 \text{ °C}$	480		A

<sup>4)</sup> Characteristic values according to IEC 60747 - 9

<sup>5)</sup> Collector-emitter saturation voltage is given at chip level

## Diode characteristic values <sup>6)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
Forward voltage <sup>7)</sup>	$V_F$	$I_F = 150 \text{ A}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	1.6	2.2	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1.75		V
			$T_{vj} = 175 \text{ }^\circ\text{C}$	1.7		V
Peak reverse recovery current	$I_{RM}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	175		A
			$T_{vj} = 125 \text{ }^\circ\text{C}$	190		A
			$T_{vj} = 175 \text{ }^\circ\text{C}$	210		A
Recovered charge	$Q_r$	$V_{CC} = 900 \text{ V}$ , $I_F = 150 \text{ A}$ , $V_{GE} = \pm 15 \text{ V}$ , $R_G = 2.7 \text{ } \Omega$ , $di/dt = 3 \text{ kA}/\mu\text{s}$ $L_\sigma = 60 \text{ nH}$ , inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	42		$\mu\text{C}$
			$T_{vj} = 125 \text{ }^\circ\text{C}$	70		$\mu\text{C}$
			$T_{vj} = 175 \text{ }^\circ\text{C}$	98		$\mu\text{C}$
Reverse recovery time	$t_{rr}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	430		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	580		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}$	840		ns
Reverse recovery energy	$E_{rec}$		$T_{vj} = 25 \text{ }^\circ\text{C}$	25		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	40		mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}$	56		mJ

<sup>6)</sup> Characteristic values according to IEC 60747 - 2

<sup>7)</sup> Forward voltage is given at chip level

## Package properties <sup>8)</sup>

Parameter	Symbol	Conditions	min	typ	max	Unit
IGBT thermal resistance junction to case	$R_{th(j-c)IGBT}$	per switch			0.135	K/W
Diode thermal resistance junction to case	$R_{th(j-c)DIODE}$				0.200	K/W
IGBT thermal resistance <sup>3)</sup> case to heatsink	$R_{th(c-s)IGBT}$	IGBT per switch, $\lambda$ grease = $1\text{W}/\text{m} \times \text{K}$		0.033		K/W
Diode thermal resistance <sup>3)</sup> case to heatsink	$R_{th(c-s)DIODE}$	Diode per switch, $\lambda$ grease = $1\text{W}/\text{m} \times \text{K}$		0.050		K/W
Comparative tracking index	CTI		200			
Module stray inductance	$L_{\sigma CE}$	per switch		20		nH
Resistance, terminal-chip	$R_{CC' \rightarrow EE'}$	per switch	$T_C = 25 \text{ }^\circ\text{C}$	0.7		m $\Omega$
			$T_C = 125 \text{ }^\circ\text{C}$	0.98		
			$T_C = 175 \text{ }^\circ\text{C}$	1.12		


<sup>3)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2106

## Mechanical properties <sup>8)</sup>


Parameter	Symbol	Conditions	min	typ	max	Unit
Dimensions	L x W x H	Typical	106.4 x 61.4 x 30.9			mm
Clearance distance in air	$d_a$	according to IEC 60664-1 and EN 50124-1	Term. to base:	23		mm
			Term. to term:	11		
Surface creepage distance	$d_s$	according to IEC 60664-1 and EN 50124-1	Term. to base:	29		mm
			Term. to term:	23		
Mass	m			330		g

<sup>8)</sup> Package and mechanical properties according to IEC 60747 - 15

## Electrical configuration



## Outline drawing <sup>3)</sup>



Note: all dimensions are shown in millimeters

<sup>3)</sup> For detailed mounting instructions refer to ABB Document No. 5SYA 2106

This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. VIII.  
This product has been designed and qualified for Industrial Level.




Fig. 1 Typical on-state characteristics, chip level




Fig. 2 Typical transfer characteristics, chip level




Fig. 3 Typical output characteristics, chip level




Fig. 4 Typical output characteristics, chip level




Fig. 5 Typical switching energies per pulse vs. collector current




Fig. 6 Typical switching energies per pulse vs. gate resistor




Fig. 7 Typical switching times vs. collector current




Fig. 8 Typical switching times vs. gate resistor




Fig. 9 Typical capacitances vs. collector-emitter voltage




Fig. 10 Typical gate charge characteristics




Fig. 11 Turn-off safe operating area (RBSOA)




Fig. 12 Typical reverse recovery characteristics vs. forward current




Fig. 13 Typical reverse recovery characteristics vs. di/dt




Fig. 14 Typical diode forward characteristics, chip level




Fig. 15 Safe operating area diode (SOA)






Fig. 16 Thermal impedance vs. time

Analytical function for transient thermal impedance:

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/\tau_i})$$

IGBT	$R_i$ (K/kW)	13.7	74.6	46.7		
	$\tau_i$ (ms)	0.9	40.2	136		
DIODE	$R_i$ (K/kW)	33.6	51.6	114.9		
	$\tau_i$ (ms)	1.8	137	37.2		

**Related documents:**

- 5SYA 2042 Failure rates of IGBT modules due to cosmic rays
- 5SYA 2045 Thermal runaway during blocking
- 5SYA 2053 Applying IGBT
- 5SYA 2058 Surge currents for IGBT diodes
- 5SYA 2093 Thermal design and temperature ratings of IGBT modules
- 5SYA 2098 Paralleling of IGBT modules

ABB Switzerland Ltd.  
Semiconductors  
Fabrikstrasse 3  
CH-5600 Lenzburg  
Switzerland

Phone: +41 58 586 1419  
Fax: +41 58 586 1306  
E-Mail: [abbsem@ch.abb.com](mailto:abbsem@ch.abb.com)  
Internet: [www.abb.com/semiconductors](http://www.abb.com/semiconductors)

We reserve the right to make technical changes or to modify the contents of this document without prior notice.

We reserve all rights in this document and the information contained therein. Any reproduction or utilization of this document or parts thereof for commercial purposes without our prior written consent is forbidden.

Any liability for use of our products contrary to the instructions in this document is excluded.