


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,
17 positions, linear switching.
Min. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 9,
the preceding pos. was 8.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,
17 linjär koppling.
Min antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 9,
föregående läge var 8.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	

The tap-changer is shown in pos. 9,
the preceding pos. was 8.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 9,
föregående läge var 8.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Cont								
	Year	Week							
Form No.	Dept								
	Rev Ind	Revision	Appd	Year	Week				
Drawn by	Design checked by	Accepted by qual control		Accepted for prod by		Description (English)		DATAORIGINAL	
		L.Oberg		M.Haggmar		CONNECTION DIAGRAM			
		H.Sundberg		A.Wang		Description (own language)		File name	
	Drawing checked by	Issued by Dept	Year	Week			Lang	Sheet	
	N.Gustavsson	CO/TK	14	02				1	
	ABB				1ZSC004308-AAN		Rev Ind	Cont	
								-	