











































Product matrix




















	Area lighting		Area/Flood lighting
	Hazlux® H3 LED	Hazlux® H5 HID	FMR LED
			
Classification			
Optics - IESNA			
Optics - NEMA			
IP/NEMA			
DLC			
Certification			
Wattage	37-138W	50-400W	107-310W
Lumen	5,600-20,000 lm	6,250-7,160 lm	12,000-32,000lm
Voltage	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz
Dimming	0-10V dimming		0-10V dimming



Linear				Flood
Hazlux® 6 DFP LED	Hazlux® 7 XFM LED	WNL LED	LGS LED	Hazlux® 8 FDL
				
				
				
				
				
				
25-87W	29-58W	62-240W	11-48W	50-105W
2,800-10,000lm	2,800-6,600lm	4,000-14,000lm	580-2,300lm	6,400-11,00lm
120-277VAC, 50/60Hz 347-480VAC, 50/60Hz	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz	120-277VAC, 50/60Hz 277-480VAC, 50/60Hz	120-277VAC, 50/60Hz 347-480VAC, 50/60Hz
		0-10V dimming		



Emergency lighting

	VE LED	VR LED	VC LED	VB LED
				
Classification	   		  	
Type	AC Only Self-Powered	DC AC/DC	Self-Powered Remote capacity	Self-Powered Remote capacity
Features	Advanced Diagnostic Nexus®		Advanced Diagnostic Nexus® Time Delay	Advanced Diagnostic Nexus® Time Delay
Spacing	N/A	34'-89'	34'-89'	34'-89'
Certification				
Wattage	1.5-2.5 W	4-6W	20W and 24W	18W-72W
Lumen	N/A	200-540lm	200-540lm	200-540lm
Voltage	120-277VAC	DC: 6V/12V/24V/ 120VDC - 120VAC	120/277VAC	120/277VAC