


Serenga 2

Project covering & stylish



Recessed downlight in black

- Injection moulded - high grade polycarbonate body
- Specially designed lens for optimised light distribution
- Modular, First-Fix installation
- Round or square trim shapes are available as interior design choices
- Ease of installation - unique moulded construction to retain IP rating without additional protection
- Escape route supplied as standard



Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-DEA-M3B	REC M3 CT-NAVEO ESC-L4M BLK	220-240 AC 50Hz	1 x LED 2W	203	3.5 / 3	3	5-40	0.6
SR2-DEA-M3B	REC M3 AUTOTST ESC-4MH BLK	220-240 AC 50Hz			3.5 / 3	3	5-40	0.6
SR2-DEA-230LTB	REC 230V EMEX ESC-L4M BLK	220-240 AC 50/60Hz			3.5 / 3	230V	5-40	0.4
SR2-DEA-230B	REC 230V SL ESC-L4M BLK	220-240 AC/DC 0-60Hz			3.5 / 3	230V	5-40	0.4

Select optical lens for application required

Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2*	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

*Lens included in the box
See spacing tables on pages 128-129



IP Rating	Product type
IP20	flush mount from above
IP42	flush mount from below

