

TECHNICAL DATA SHEET - INTERACTIVE PDF

Beam Clamps, right angle

Stainless steel

Steel City[®]



Right angle beam clamps are designed to secure conduit to a beam, flange, or other angled structural support.

Certifications / Standards:



3-Part Specification:
Tools and Calculators

Features:

- Heavy-duty construction
- Capable of supporting heavy loads
- Type 316 Stainless steel U-Bolt and hex nuts included
- Trade sizes ½" to 2"

Applications:

- Used to secure RMC or IMC across, channel, beams, and angle supports

Conforms to:


- UL2239
- File number: E160899

Material / Finishes:

- 316 Stainless Steel

Product selection and dimensions				
Part no.	Trade size	A inches	B inches	C inches
RC1/2SST	0.50"	2.08"	2.00"	0.21"
RC3/4SST	0.75"	2.27"	2.00"	0.21"
RC1SST	1.00"	2.60"	2.00"	0.23"
RC11/4SST	1.25"	2.94"	2.00"	0.23"
RC11/2SST	1.50"	3.19"	2.00"	0.24"
RC2SST	2.00"	3.74"	2.10"	0.24"

Note: Product must be installed in accordance with applicable national and local electrical codes.



electrification.us.abb.com (US/LATAM)
tnb.ca.abb.com (Canada)
abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB. © 2023 ABB Installation Products Inc. and/or its related companies. All Rights Reserved.