


Temp. 0 10-50 60C

Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



**Industrial Solutions**

**Molded Case Circuit Breaker E 150 Line**

**Current Ratings**

60, 70 and 80 Amperes

**Voltage Ratings**

2 and 3 pole - 600 Vac (250 Vdc)  
3 Pole - (500 Vdc)

**Frequency Rating**

60 Hertz

Types TED, THED, 60-80 Amperes  
Ambient Compensated  
Long-time Delay and Instantaneous  
Time-current Curves  
Curves show ambient-compensated circuit breaker in open air, 10°C to 50°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

**GES6120**

**Adjustments**

Long-time delay thermal trip: notadjustable.  
Instantaneous magnetic trip: not adjustable.

by **ABB**

GE is a registered trademark used under license from General Electric Company