


Temp.  
0 25 40 50 60C



Shift index for long-time delay only.



### Molded Case Circuit Breaker E 100 LINE

### GES6113

**Current Ratings**

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

**Voltage Ratings**

1-pole – 277 Vac (125 Vdc)

2- and 3-pole – 480 Vac (250 Vdc)

**Frequency Rating**

60 Hertz

Type TED, 15-50 Amperes Enclosure Compensated Long-Time Delay and Instantaneous Time-Current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

**Adjustments**

Long-time delay thermal trip: not adjustable.  
Instantaneous magnetic trip: not adjustable.