

MINIATURE CIRCUIT-BREAKERS

Electrical installation solutions for buildings

Miniature circuit-breakers

Index

Quick selection of MCBs	2
-------------------------	---

MCBs S 200

S 200 technical features	28
S 200 series, 6 kA	36
S 200 M series, 10 kA	46
S 200 M UC series, 10 kA	56
SU 200 M series, 10 kA	76
SU 200 MR series, 10 kA	88

MCBs S 300

S 300 technical features	28
S 300 P series, 25kA	65

MCBs SN 201

SN 201 L series, 4.5 kA	94
SN 201 series, 6 kA	95
SN 201 M series, 10 kA	97

MCBs S200C

S200C series from 4,5 kA to 10 kA	98
-----------------------------------	----

MCBs S200 80-100A

S 200 80-100A series, 6 kA	108
----------------------------	-----

MCBs for transportation application

S 200 MT	112
S 200 MT UC	125
S 202 TC	135

S800 standard range

S800 technical features	142
S800P series, 50kA	142
S800S series, 50kA	144
S800N series, 36 kA	146
S800C series, 25 kA	148


S800 for direct current and high voltage

S800S-UC technical features	174
S800S-UC series, up to 1000 VDC	176
S800PV technical features	180
S800PV series, up to 1500 VDC	181
S800PV switch disconnectors	182
S800HV technical features	185
S800HV series, up to 1000 VAC	186

System pro M compact®

Quick selection of MCBs for household and industrial applications

Easy! Find the right range and the corresponding catalogue page at a glance using this selection chart.



System pro M compact®


Quick selection of MCBs for household and industrial applications

Rated current	Poles	Solution
Up to 40 A	2,3,4	S200CL
Up to 40 A	1P+N	SN 201 L
Up to 40 A	1+1,2,3,4	S200C
Up to 40 A	1P+N	SN 201
Up to 63 A	All poles	S 200
Up to 100 A	All poles	80-100A
Up to 40 A	1P+N	SN 201 M
Up to 32 A	2	S200CM
Up to 63 A	All poles	S 200 M
Up to 63 A	All poles	S800B
Up to 63 A	All poles	S800C
Up to 63 A	All poles	S300P
Up to 40 A	All poles	S300P
Up to 63 A	All poles	S800N
Up to 25 A	All poles	S300P
Up to 63A	All poles	S800S



System pro M compact®

Quick selection of MCBs for household and industrial applications




System pro M compact®

Quick selection of MCBs for household and industrial applications

	Rated current	Poles	Solution
→	Up to 100 A	All poles	80-100A
→	Up to 63 A	All poles	S 200, S 200 M
→	Up to 40 A	All poles	S 200 M
→	Up to 63 A	All poles	S800B
→	Up to 63 A	All poles	S 300P
→	Up to 63A	All poles	S800C
→	Up to 63A	All poles	S800N
→	Up to 80...125 A	All poles	S800P
→	Up to 63A	All poles	S800S
→	Up to 125 A	1P, 2P, 3P	S800HV
→	Up to 63 A	1P, 2P, 3P, 4P	S 200 M UC
→	Up to 125 A	All poles	S800S-UC
→	Up to 125 A	All poles	S800-PV

System pro M compact®

Quick selection of MCBs for UL applications (UL 489/CSA 22.2 No. 5)




System pro M compact®

Quick selection of MCBs for UL applications (UL 489/CSA 22.2 No. 5)

Rated current	Wiring/Remark	Poles	Solution
Up to 63 A		1P, 2P, 3P, 4P	SU 200 M
Up to 63 A	Ring Tongue	1P, 2P, 3P, 4P	SU 200 MR
Up to 63A		1P, 2P	SU 200 DC

System pro M compact®

Quick selection of MCBs for rolling stock application IEC 60947-2 and UL1077



System pro M compact®

Quick selection of MCBs for rolling stock application IEC 60947-2 and UL1077

Rated current	Wiring/Remark	Poles	Solutions
Up to 32 A	Screw	All poles	S202TC
Up to 63 A	Screw	All poles	S200MT
Up to 63 A	Screw	All poles	S300P
up to 63 A	Screw / Ring Tongue	All poles	S800C
up to 63 A	Screw / Ring Tongue	All poles	S800N
up to 63 A	Screw / Ring Tongue	All poles	S800S
80...125 A	Screw / Ring Tongue	All poles	S800P
Up to 63 A	Screw	All poles	S200MTUC

Miniature circuit-breakers

Selection table



Series			S 200	S 200 M	S 200 M UC	S 300 P			
Characteristics			B,C,D, K,Z	B,C,D, K,Z	B,C, K, Z	B,C,D, K,Z	B,C,D, K,Z	B,C,D, K,Z	B,C,D, K,Z
Rated current [A]			0.5 ≤ In ≤ 63	0.5 ≤ In ≤ 63	0.2 ≤ In ≤ 63	0.2 ≤ In ≤ 6	8 ≤ In ≤ 25	32 ≤ In ≤ 40	50 ≤ In ≤ 63
Reference standard	Nr. poles	Ue[V]							
IEC/EN 60898	Icn	230/400 6		10	10				
		240/415				25	25	20	15
IEC/EN 60947-2 Alternating current	Icu 1, 1P+N	133	20***	25***		100	50	40	40
		139							
		230	10***	15***		100	25	25	25
		240							
		253							
	2, 3, 4	230	20***	25***	10 ^{*16} /6 ^{*17}				
		240				100	50	40	40
		400	10***	15***					
		415				100	25	25	25
		440	10***	15***	10 ^{*16} /6 ^{*17}	100	15	15	15
	2, 3, 4	500							
		690							
	Ics 1, 1P+N	133	15***	18.7 ^{*8***}					
		139				100	20	20	20
		230	7.5***	11.2 ^{*8***}					
		240				100	12.5	10	7.5
		253			7.5 ^{*16} /6 ^{*17}				
	2, 3, 4	230	15***	18.7 ^{*8***}					
		240				100	20	20	20
		400	7.5***	11.2 ^{*8***}					
		415				100	12.5	10	7.5
		440	7.5***	11.2 ^{*8***}	7.5 ^{*16} /6 ^{*17}	100	7.5	7.5	7.5
	2, 3, 4	500							
		690							
IEC/EN 60947-2 Direct current T=I/R≤5ms for all series, except S280 UC and S800S-UC, where T=I/R<15ms	Icu 1, 1P+N	24	20						
		60	10	10					
		72				25	25	25	25
		125							
		220			10				
	2	250							
		48	20						
		110							
		125	10	10		25	25	25	25
		250							
	3,4	440			10				
		500							
		800							
		375							
		500							
		750							
		1200							

^{*1} only up to 40 A; 10 kA up to 50/63 A

^{*2} only for "D" characteristic

^{*3} values are not for all rated currents

^{*4} 600 V DC for 100, 125 A

^{*5} 1000 V DC for 100, 125 A

^{*6} 3 poles

^{*7} 4 poles

^{*8} relevant product standard: E DIN VDE 0645

(based on IEC/EN 60898-1 and IEC/EN 60947-2)

^{*9} by 250 V DC 1-pole, 600 V 3- and 4-pole

^{*10} by 600 V DC 2-pole

^{*11} ≤ 25 A

^{*12} > 25 A

^{*13} char. B, C

^{*14} only 2 poles (connection in series)

^{*15} UL 1077 only

^{*16} ≤ 40 A

^{*17} > 40 A

^{*18} ≤ 35 A

^{*19} 10-80 A

*** 50kA for 0.5-2A devices

Selection table



NEW

[illegible]

Miniature circuit-breakers

Selection table



Series				S 200	S 200 M	S 200 M UC	S 300 P		
Characteristics				B,C,D, K,Z	B,C,D, K,Z	B,C, K, Z	B,C,D, K,Z	B,C,D, K,Z	B,C,D, K,Z
Rated current [A]				0.5 ≤ In ≤ 63	0.5 ≤ In ≤ 63	0.2 ≤ In ≤ 63	0.2 ≤ In ≤ 25	32 ≤ In ≤ 40	50 ≤ In ≤ 63
IEC/EN 60947-2 Direct current T=I/R≤5ms for all series, except S280 UC and S800S-UC, where T=I/R<15ms	Ics	1, 1P+N	24	20					
			60	10	10				
			72				12.5	10	7.5
			125						
			220			10			
			250						
	2		48	20					
			110						
			125	10	10		12.5	10	7.5
			250			25			
			440			10			
	3,4		500						
			800						
			375						
			500						
			750						
			1200						
UL 1077/ C22.2 No 235 Alternating current	Int. cap.	1, 1P+N	120	10 *15			10	10	10
			240				10	10	10
			277	6 *15	6	6	10	10	10
	2, 3, 4		240	10 *15			10	10	10
			480 Y/277	6 *15	6	6	10	10	10
UL 1077/ C22.2 No 235 Direct current	Int. cap.	1, 1P+N	60	10 *15	10		10	10	10
			125						
			250			10			
	2, 3, 4		125		10		10	10	10
			250						
UL 489/ C22.2 No 5 Alternating current	Int. cap.	1	240						
			277						
	2, 3, 4		240						
UL 489/ C22.2 No 5 Direct current	Int. cap.	1	48						
			60						
			125						
	2		96						
			125						
			250						

*1 only up to 40 A; 10 kA up to 50/63 A

*2 only for "D" characteristic

*3 values are not for all rated currents

*4 600 V DC for 100, 125 A

*5 1000 V DC for 100, 125 A

*6 3 poles

*7 4 poles

*8 relevant product standard: E DIN VDE 0645

(based on IEC/EN 60898-1 and IEC/EN 60947-2)

*9 by 250 V DC 1-pole, 600 V 3- and 4-pole

*10 by 600 V DC 2-pole

*11 ≤ 25 A

*12 > 25 A

*13 char. B, C

*14 only 2 poles (connection in series)

*15 UL 1077 only

*16 ≤ 40 A

*17 > 40 A

*18 ≤ 35 A

*19 10-80 A

Selection table



NEW

[illegible]

Miniature circuit breakers

Selection table



Series			S 200 MT		S 200 MT UC		S202TC
Hazard level acc. EN45545-2			R 26/HL 3	R 26/HL 3	R 26/HL 3	R 26/HL 3	R 26/HL 3
V0 according EN 60695-11-10 and UL94			yes	yes	yes	yes	yes
NFPA-130							
Shock and vibration IEC 617373			Category 1 - Class A/B Body mounted	Category 1 - Class A/B Body mounted	Category 1 - Class A/B Body mounted	Category 1 - Class A/B Body mounted	Category 1 - Class B
Number of Poles			1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P	1P, 2P, 3P, 4P	2P
Characteristics			B, C, D, K, Z	B, C, D, K, Z	B, C, K, Z	B, C, K, Z	B, C
Rated Currents (A)			0.2...40	50...63	0.2...40	50...63	2...32
Breaking Capacity IEC / EN60898	kA	Nr. Poles Ue (V)					
	Icu		240				
IEC / EN60947-2 Alternating current	Icu	1, 1+N	133	25	20		
			139				
		2, 3, 4	240				
			415				
		2, 3, 4, 3+N	230	25	20		
			400	15	10		
		1, 1+N	440	15	10	10	6
			133	18,75	15		
		230	11,25	7,5			
			250		7,5	6	
		2, 3, 4, 3+N	230	18,75	15		
			400	11,25	7,5		
		440	11,25	7,5	7,5	6	
Ics		1, 1P+N	139				
			240				
		2, 3, 4	240				
			415				
IEC / EN60947-2 direct current T=I/R≤5ms for all series except s280 UC and S800S-UC, where T=I/R<15ms	Icu	1, 1P+N	72				
			125				
IEC / EN60947-2 direct current T=I/R≤5ms	Icu	1, 1+N	110		20	20	
			220		10	10	
		2	220		25	25	
			440		10	10	
		3, 4	220		25	25	
			375		10	10	
		440			10	10	
Ics		1, 1+N	60	10	10		
			110		10	10	
		220			10	10	
		2	125	10	10		
		220			20	20	
			250				
		440			10	10	
		3, 4	220		20	20	
			250				
		440			10	10	
UL 1077 Alternating current	I	1	120				
			240				
		277	6, U1		6, U1	6, U1	
		2, 3, 4	240				
		480Y / 277	6, U1		6, U1	6, U1	
UL 1077 direct current	I	1	48	10, U1			
			250		10, U1	10, U1	
Min. 2-poles connecting in series			2, 3, 4	96	10, U1		
Temperature Range			500		10, U1	10, U1	
				-40°C up to + 70°C	-40°C up to + 70°C	-40°C up to + 70°C	-40°C up to + 70°C

Miniature circuit breakers

Selection table



S 300P				
R 26/HL 3	R 26/HL 3	R 26/HL 3	R 26/HL 3	R 26/HL 3
R 22/HL 3	R 22/HL 3	R 22/HL 3	R 22/HL 3	R 22/HL 3
yes	yes	yes	yes	yes
Category 1 - Class A/B Body mounted	Category 1 - Class A/B mounted	Category 1 - Class A/B Body mounted	Category 1 - Class A/B Body mounted	Category 1 - Class A/B Body mounted
1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P, 1P+N, 3P+N	1P, 2P, 3P, 4P, 1P+N, 3P+N
B, C, D, K, Z	B, C, D, K, Z	B, C, D, K, Z	B, C, D, K, Z	B, C, D, K, Z
0,2....6	8....25	32....40	50....63	
25	25	20	15	
25	25	20	15	
100	50	40	40	
100	50	40	40	
100	25	25	25	
100	50	40	40	
100	25	25	25	
100	15	15	15	
100	25	25	25	
100	15	15	15	
100	20	20	20	
100	12,5	10	7,5	
100	20	20	20	
100	12,5	10	7,5	
100	20	20	20	
100	12,5	10	7,5	
100	20	20	20	
100	12,5	10	7,5	
100	7,5	7,5	7,5	
25	25	25	25	
25	25	25	25	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
10, U1	10, U1	10, U1	10, U1	
-40°C up to + 70°C				

High performance circuit-breakers

Selection table



Series			S800P	S800S				S800N	S800C		
Characteristics			B, C, D, K	B,C,D	K	KM	UCB	UCK	B,C,D	B,C,D,K	
Rated current [A]			80, 100, 125	0.5 ≤ In ≤63	0.5 ≤ In ≤63	20 ≤ In ≤ 80	0.5 ≤ In ≤ 125	0.5 ≤ In ≤ 125	6 ≤ In ≤ 63	10 ≤ In ≤ 63	
Breaking capacity [kA]											
Reference standard	Nr. poles	Ue[V]									
IEC/EN 60898	Icn	230/400	25◆● (80 A) 15◆● (100...125 A)	25					20	15	
IEC/EN 60947-2 Alternating current	Icu 1	230									
		240	50	50	50				36	25	
		254	30◆	30	30				20	15	
		289	15◆ (80 A), 10◆ (100...125A)	15	15				10		
		400	6◆ (80 A), 4.5◆ (100...125A)	6	6				4.5		
		580									
	2, 3, 4	400									
		415	50	50	50	50 *6				36	25
		440	30◆	30	30	30 *6				20	15
		500	15◆ (80 A), 10◆ (100...125 A)	15	15				10		
		690	6◆ (80 A), 4.5◆ (100...125A)	6	6	6 *6				4.5	
		1000									
		Ics 1, 1P+N	230								
	240		40	40	40				30	25	
	254			22.5	22.5	22.5				15	10
	289			11	11				8		
	400			4	4	4				3	
	580										
	2, 3, 4	400		40	40						
415		40				40 *6				30	25
440			22.5	22.5				15	10		
500			11	11				8			
690			4	4	4				3		
1000											

◆ Internal factory certificate only

● Characteristics B, C, D

*¹ only up to 40 A; 10 kA up to 50/63 A*² only for "D" characteristic*⁵ 1500 V DC for 4P*⁶ 3 poles*⁷ 4 poles*⁸ relevant product standard: E DIN VDE 0645 (based on IEC/EN 60898-1 and IEC/EN 60947-2)*⁹ by 250 V DC 1-pole, 600 V 3- and 4-pole*¹⁰ by 600 V DC 2-pole*¹¹ ≤ 25 A*¹² > 25 A*¹³ char. B, C*¹⁴ only 2 poles (connection in series)*¹⁵ UL 1077 only*¹⁶ ≤ 40 A*¹⁷ > 40 A*¹⁸ ≤ 35 A*²⁰ for S804U-UCZ only*²¹ for S804U-PVS only

High performance circuit-breakers

Selection table



	S800HV	S800PV- SP
	C, K	PV-SP
	C: 10, 32 K: 0.5 ≤ In ≤ 125	5 ≤ In ≤ 125
	1.5 (0.5 ... 5 A), 4 (6 ... 63 A) 3 (80 ... 125 A)	
	1.5 (0.5 ... 5 A) 4 (6 ... 63 A) 3 (80 ... 125 A)	
	1.5 (0.5 ... 5 A) 2.5 (6 ... 63 A) 2 (80 ... 125 A)	
	1.5 (0.5 ... 5 A) 2.5 (6 ... 63 A) 2 (80 ... 125 A)	

High performance circuit-breakers

Selection table



		S800P		S800S				N800S	S800C	
Series		B, C, D, K		B,C,D	K	KM	UCB	UCK	B,C,D	B,C,D,K
Rated current [A]		80, 100, 125		0.5 ≤ In ≤ 63	0.5 ≤ In ≤ 63	20 ≤ In ≤ 80	0.5 ≤ In ≤ 125	0.5 ≤ In ≤ 125	6 ≤ In ≤ 63	10 ≤ In ≤ 63
Breaking capacity	[kA]									
Reference standard	Nr. poles	Ue[V]								
IEC/EN 60947-2 Direct current T=I/R≤5ms for all series, except S280 UC and S800S-UC, where T=I/R<15ms	1	75								
		125	30◆	30	30				20	10
		250					50	50		
	2	150								
		250	30*	30	30				20	10
		500					50	50		
		800								
	3,4	225								
		300								
		375	30◆◆ ⁶	30 ^{*6}	30 ^{*6}	30 ^{*6}			20 ^{*6}	10 ^{*6}
		500	30◆◆ ⁷	30 ^{*7}	30 ^{*7}				20 ^{*7}	10 ^{*7}
		750					50 ^{*6} 50 (63...125 A) ^{*7}	50 ^{*6} 50 (63...125 A) ^{*7}		
		1000					50 (10...50 A) ^{*7}	50 (10...50 A) ^{*7}		
		1200								
		1500								

◆ Internal factory certificate only

● Characteristics B, C, D

^{*1} only up to 40 A; 10 kA up to 50/63 A^{*2} only for "D" characteristic^{*3} values are not for all rated currents^{*6} 3 poles^{*7} 4 poles^{*8} relevant product standard: E DIN VDE 0645 (based on IEC/EN 60898-1 and IEC/EN 60947-2)^{*9} by 250 V DC 1-pole, 600 V 3- and 4-pole^{*10} by 600 V DC 2-pole^{*11} ≤ 25 A^{*12} > 25 A^{*13} char. B, C^{*14} only 2 poles (connection in series)^{*15} UL 1077 only^{*16} ≤ 40 A^{*17} > 40 A^{*18} ≤ 35 A^{*19} 10-80 A^{*20} for S804U-UCZ only^{*21} for S804U-PVS only

High performance circuit-breakers

Selection table



	S800HV	S800PV-SP
	C, K	PV-SP
	C: 10, 32 K: 0.5 ≤ In ≤ 125	5 ≤ In ≤ 125
		5
		5 *6
		5 *7

High performance circuit-breakers

Selection table

										
Series			S800P	S800S			S800N	S800C		
Characteristics				B, C, D	K	KM	UCB	UCK	B, C, D	B, C, D, K
Rated current [A]				0.5 ≤ In ≤ 63	0.5 ≤ In ≤ 63	20 ≤ In ≤ 80	0.5 ≤ In ≤ 125	0.5 ≤ In ≤ 125	6 ≤ In ≤ 63	10 ≤ In ≤ 63
UL 1077/ C22.2 No 235 Alternating current	Int. 1 cap.	240		30	30					20
		277		14	14					
	2, 3, 4	347		6	6					10
		240		30	30					
		480 Y/277 600Y/347		14 14 6	14 14 6					
UL 1077/ C22.2 No 235 Direct current	Int. 1 cap.	125								10
		250								
	2, 3, 4	125								
		250								10 (2P)
		375 500								10 (3P) 10 (4P)
UL 489/ C22.2 No 5 Alternating current	Int. 1 cap.	240								
		277								
	2, 3, 4	240								
480 Y/277										
UL 489/ C22.2 No 5 Direct current	Int. 1 cap. 2	60								
		125								
	4	600								
UL489B Direct current	4	1000								

*1 only up to 40 A; 10 kA up to 50/63 A

*2 only for "D" characteristic

*3 values are not for all rated currents

*5 1500 V DC for 4P

*6 3 poles

*7 4 poles

*8 relevant product standard:

E DIN VDE 0645 (based on

IEC/EN 60898-1 and IEC/EN 60947-2)

*9 by 250 V DC 1-pole, 600 V

3- and 4-pole

*10 by 600 V DC 2-pole

*11 ≤ 25 A

*12 > 25 A

*14 only 2 poles (connection in series)

*15 UL 1077 only

*16 ≤ 40 A

*17 > 40 A

*18 ≤ 35 A

Selection table

[illegible]

*24 by 225V DC 3-pole

XT2L 125 TMF 35-400

MCB S 300. The next generation of line protection

The new dimension in efficiency and power

IP20 - finger safety.

Twin terminal for separate feeding of busbar and conductor.

Dual DIN-Rail release for easy mounting even with busbars attached.

Easy identification of the product and high resistant laser marking.

Quick identification thanks to laser printed EAN marking.

Trip indicator for easy trip identification on site.

Save your time – all important data available right away.


QR-Code for direct internet access to all Product data/ files.


Contact position indication:
visualization of the contact position, independent from the toggle position.

Captive screws:
don't lose what's important for you.

Dual DIN-Rail release for easy mounting.

Whatever your application need is applicable with a wide range of accessories.





Contact position indication

All System pro M compact® MCBs are suited with a contact position indication (CPI) on the toggle. You can easily identify, if the MCB is in the ON or the OFF position – easy and safe maintenance work is possible. The green/red window indicates the real position of the contacts independently of the toggle position.



Approvals printed on the dome

S 300 MCBs comply to IEC/EN 60898-1 and IEC/EN 60947-2 and carry all relevant approval marks for each market and segment they are destined to. The certification markings are also printed on the dome of the MCB. Thus make it possible to see the markings also in the mounted position. For control and acceptance procedure – certification marks visible on fitted devices on the dome.



Housing material

By using the state-of-the-art housing material, ABB is taking care of the environment. With the latest generation of thermoplastics it's possible to recycle the MCBs – especially the thermoplastic housing-material can be re-used. By using the latest generation of thermoplastics the material stability of all System pro M compact® MCBs is improved. S 300 MCBs are 100% free of halogens – no environmental pollution.



Laser printing

All printings of the S 300 MCBs, like the approvals on the dome and the product identification, are printed by a laser. The laser printing ensures a friction, scratch and solvent resistant marking on the MCBs. Easy identification of the products in case of maintenance or replacements due to safe laser printing.



IP 20 - finger safe terminals

The System pro M compact® MCB's are equipped with 35 mm² + 10 mm² cylinder lift twin terminals, a well proven and reliable technology - designed for sophisticated industrial use. The cross wiring can easily be done by inserting the System pro M compact® busbars into the rear terminal part and then the incoming wires into the front part of the terminal.



Trip indicator

The trip indicator will signalize tripping events of the MCB directly on site. So you can directly identify if the MCB was tripped by e.g. short circuit, overload, shunt trip, etc. or switched Off manually.



QR-Code

The QR-Code will give you direct access to all product related data, certificates and documents.



Dual DIN-Rail Release

With the new Dual DIN-Rail Release the toolless installation and uninstallation will be much faster and easier, even with already attached busbars.




Improved performance

The new level of strong electrical performance ensures high breaking capacity of 25kA and improved energy efficiency for all kinds of high performance applications.

MCB S 200. The details make the difference

A range designed to ensure efficiency and protection





Contact position indication

All System pro M compact® MCBs are suited with a contact position indication (CPI) on the toggle. You can easily identify, if the MCB is in the ON or the OFF position – easy and safe maintenance work is possible.

The green/red window indicates the real position of the contacts independently of the toggle position.



Approvals printed on the dome

S 200 MCBs comply to IEC/EN 60898-1 and IEC/EN 60947-2 and carry all relevant approval marks for each market and segment they are destined to. The certification markings are also printed on the dome of the MCB. Thus make it possible to see the markings also in the mounted position. For control and acceptance procedure – certification marks visible on fitted devices on the dome.



Housing material

By using the state-of-the-art housing material, ABB is taking care of the environment. With the latest generation of thermoplastics it's possible to recycle the MCBs – especially the thermoplastic housing-material can be re-used. By using the latest generation of thermoplastics the material stability of all System pro M compact® MCBs is improved. S200 are 100% free of halogens – no environmental pollution.



Laser printing

All printings of the S 200 and S 200 M MCBs, like the approvals on the dome and the product identification, are printed by a laser. The laser printing ensures a friction, scratch and solvent resistant marking on the MCBs.

Easy identification of the products in case of maintenance or replacements due to safe laser printing.



IP 20 - finger safe terminals

The System pro M compact® MCB's are equipped with 35 mm² + 10 mm² cylinder lift twin terminals, a well proven and reliable technology - designed for sophisticated industrial use.

The cross wiring can easily be done by inserting the System pro M compact® busbars into the rear terminal part and then the incoming wires into the front part of the terminal.

MCB S 200 MT and S 200 MT UC. The details make the difference

A range designed for rolling stock equipments

Twin terminal for separate feeding of busbar and conductor.

IP20 - finger safety.

Easy product name, easy identification, easy life.

Captive screws: don't loose what's important for you.

Wide range of accessories are available for rolling stock and rail infrastructure applications.





Dedicated materials for rolling stock

In the S200 range of MCBs for traction, specific materials are used that are classified with a hazard level R26/HL3 according to EN 45545-2.




Shock and vibration resistance

Shock and vibration resistance Additionally to the high-quality standards and the flammability requirements, rail applications have specific demands that have to be fulfilled like resistance to shocks and vibrations. The resistance to vibrations and shocks of MCBs S 200 has been positively tested according to: IEC 61373 Rolling stock equipment – Shock and vibration tests considering Category 1, Class B.



Open to all sides

All devices can be supplied from top or bottom either with cables or busbars. Can be mounted flexibly in all positions.



High-quality terminal system

The integrated captive terminals and cable connection screws facilitate every electrician's life. ABB guarantees highest safety standards. The certification according to EN 41140 stands for protection against electric shock. And the certification according to the DIN EN 50 274 stands for terminals that are safe from touch by the back of the hand and the finger (IPXXB or IP20). The high safety standards become clear through the integrated and failsafe cable connecting terminals.



Contact position indication

All System pro M compact® MCBs are suited with a contact position indication (CPI) on the toggle. You can easily identify if the MCB is in the ON or the OFF position – easy and safe maintenance work is possible.



Advanced features

Auxiliary switches S2C-H10 (1 NO) and S2C-H01 (1 NC) and all S2C accessories can be retrofitted. They can be mounted individually and without modification of the existing busbar. At the same time, the supply of the MCB remains unaffected.

MCBs

S 200 / S 300 technical features



S 200



S 300

		S 200	S 200 M
General Data	Standards	IEC/EN 60898-1, IEC/EN 60947-2	IEC/EN 60898-1, IEC/EN 60947-2
		UL 1077	UL 1077, CSA 22.2 No. 235
	Poles	1P, 2P, 3P, 4P, 1P+N, 3P+N	
	Tripping characteristics	B, C, D, K, Z	
	Rated current I_n	A	0.5...63 A
	Rated frequency f	Hz	50 / 60 Hz
	Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	440 V AC (phase to phase)
	Overvoltage category	III	
	Pollution degree	3	
Data acc. to IEC/EN 60898-1 (except S 200 M UC data acc. to IEC/EN 60898-2)	Rated operational voltage U_n	V	1P: 230/400 V AC; 1P+N: 230 V AC ; 2...4P: 400 V AC; 3P+N: 400 V AC
	Max. power frequency recovery voltage (U_{max})	V	1P: 253 V AC; 1P+N: 253 V AC; 2P: 440 V AC; 3...4P: 440 V AC; 3P+N: 440 V AC; 1P: 72 V DC; 2P: 125 V DC
	Min. operating voltage	V	12 V AC - 12 V DC
	Rated short-circuit capacity I_{cn}	kA	6 kA 10 kA
	Energy limiting class (B, C)	3	
	Grid distance	mm	35 35
	Rated impulse withstand voltage U_{imp} . (1.2/50 μ s)	kV	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)
	Dielectric test voltage	kV	2 kV (50 / 60Hz, 1 min.)
	Reference temperature for tripping characteristics	°C	B, C, D: 30°C
	Electrical endurance	cycles (OFF-ON-OFF)	$I_n < 32A$: 20,000 ops (AC), $I_n \geq 32A$: 10,000 ops. (AC); 1,000 ops. (DC); (1 cycle 2s - ON, 13s - OFF, $I_n \leq 32A$), (1 cycle 2s - ON, 28s - OFF, $I_n > 32A$)

Note:
* Only acc. to IEC/EN 60898-1

MCBs

S 200 / S 300 technical features

S 200 M UC	S 300 P	SU 200 M	SU 200 MR	SU 200 DC
IEC/EN 60898-2, IEC/EN 60947-2	IEC/EN 60898-1, IEC/EN 60947-2	IEC/EN 60947-2	IEC/EN 60947-2	
UL 1077, CSA 22.2 No. 235	UL 1077, CSA 22.2 No. 235	UL 489, CSA22.2 No.5	UL 489, CSA22.2 No.5	UL 489
1P, 2P, 3P, 4P	1P, 2P, 3P, 4P, 1+N, 3+N	1P, 2P, 3P, 4P	1P, 2P, 3P, 4P	1P, 2P
B, C, K, Z	B, C, D, K, Z	C, K, Z	K	
0 / 50 / 60 Hz		0.2...63 A 0.2...25 A	0.2...63 A	0.2...63A
0 / 50 / 60 Hz	50 / 60 Hz	50 / 60 Hz		DC
440 V AC (phase to phase)	500 V AC	440 V AC (phase to phase)	440 V AC (phase to phase)	
	IV			--
3				--
1P: 230 V AC, 220 V DC 2P: 400 V AC, 440 V DC 3...4P: 400 V AC*	1P: 1+N: 240 V AC, 72 V DC 2P: 415 V AC, 125 V DC 3...4P: 3+N 415 V AC	--		
1P: 253 V AC, 250 V DC 2P: 440 V AC, 500 V DC 3...4P: 440 V AC*	1P: 1+N: 264 V AC, 72 V DC 3...4P: 3+N: 462 V AC 125 V DC	--		
		--		
10 kA	≤ 25 A: 25 kA ≤ 32-40 A: 20 kA > 40 A: 15 kA	--		
		--		
35	In < 25A: 75 In > 25A: 90	--		
	6 kV	--		
		--		
30 °C		--		
		--		

MCBs

S 200 / S 300 technical features



S 200



S 300

			S 200	S 200 M
Data acc. to IEC/EN 60947-2	Rated operational voltage U_e	V	1P: 230 V AC; 1P+N: 230 V AC; 2...4P: 440 V AC; 3P+N: 440 V AC	
	Max. power frequency recovery voltage (U_{max})	V	1P: 253 V AC; 1P+N: 253 V AC; 2P...4P: 462 V AC; 3P+N: 462 V AC; 1P: 72 V DC; 2P: 125 V DC	
	Min. operating voltage	V	12 V AC - 12 V DC	
	Rated ultimate short-circuit breaking capacity I_{cu}	kA	<= 2 A: 50 kA >2 A: 10 kA	<= 2 A: 50 kA >2 A: 10 kA
	Rated service short-circuit breaking capacity I_{cs}	kA	7.5 kA	≤ 40 A: 11.2 kA 50, 63 A: 7.5 kA
	Rated impulse withstand voltage U_{imp} (1.2/50μs)	kV	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)	
	Dielectric test voltage	kV	2 kV (50 / 60Hz, 1 min.)	
	Reference temperature for tripping characteristics	°C	B, C, D: 55°C; K, Z: 20°C	
	Electrical endurance	cycles (OFF-ON-OFF)	In < 32A: 20,000 ops (AC), In ≥ 32A: 10,000 ops. (AC); 1,000 ops. (DC); (1 cycle 2s - ON, 13s - OFF, In ≤ 32A), (1 cyle 2s - ON, 28s - OFF, In > 32A)	

MCBs

S 200 / S 300 technical features

S 200 M UC	S 300 P	SU 200 M	SU 200 MR	SU 200 DC
1P: 253 V AC, 220 V DC 2...4P: 440 V AC, 440 V DC	1P: 240 V AC; 1P+N: 240 V AC; 2...4P: 415 V AC; 3P+N: 415 V AC	1P: 230 V AC 2...4P: 400 V AC	1P: 230 V AC 2...4P: 400 V AC	--
1P: 266 V AC, 250 V DC 2...4P: 462 V AC, 500 V DC	1P: 264 V AC; 1P+N: 264 V AC; 2P...4P: 462 V AC; 3P+N: 462 V AC; 1P: 72 V DC; 2P: 125 V DC	1P: 253/440 V AC; 2...4P: 440 V AC	1P: 253 V AC 2...4P: 440 V AC	--
		12 V AC		12 V DC
≤ 40 A: 10 kA AC; 10 kA DC > 40 A: 6 kA AC; 10 kA DC	≤ 6 A: 100 kA 25kA	10 kA	15 kA	--
≤ 40 A: 7,5 kA AC; 10 kA DC > 40 A: 6 kA(AC; 10 kA DC	≤ 6 A: 100 kA ≤ 25 A: 12.5 kA ≤ 32...40 A: 10 kA > 40 A: 7.5 kA	7.5 kA	≤ 40 A: 11.2 kA; > 40 A: 7.5 kA (AC);	--
	6 kV	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)		--
				--
B, C: 55 °C; K, Z: 20 °C	B,C,D: 55 °C; K,Z: 40 °C	C, K, Z: 30 °C	20 °C	--
In < 32A: 20,000 ops (AC), In ≥ 32A: 10,000 ops.(AC); 1,500 ops. (DC);	In < 32A: 20,000 ops (AC), In ≥ 32A: 10,000 ops (AC); 1,500 ops (DC); (1 cycle 2s - ON, 13s - OFF, In ≤ 32A), (1 cyle 2s - ON, 28s - OFF, In ≥ 32A)		In < 25A: 20,000 ops (AC), In ≥ 25A: 10,000 ops. (AC);	--

MCBs

S 200 / S 300 technical features



S 200



S 300

		S 200	S 200 M
Data acc. to UL / CSA	Rated voltage	V	480Y / 277 V AC;
			480Y / 277 V AC;
		1P: 60 V DC; 2P...4P: 110 V DC	1P: 60 V DC; 2P...4P: 125 V DC
	Rated interrupting capacity acc. to UL 1077	kA	6 kA AC; 10 kA DC
	Short-circuit current rating acc. to UL 489		--
Mechanical Data	Application		Suppl. prot. for general use. Application Codes: TC2, OL0, SC: U1
	Reference temperature for tripping characteristics	°C	B, C, D, K, Z: 25°C
	Electrical endurance	ops.	6,000 ops (AC), 6,000 ops. (DC); 1 cycle (1s - ON, 9s - OFF)
	Housing		Insulation group II, RAL 7035 fire exposure V0 acc.to UL94
	Toggle		Insulation group II, black, sealable
	Contact position indication		Marking on toggle (I ON / 0 OFF), Real CPI (red ON / green OFF)
	Protection degree acc. to EN 60529		IP20*, IP40 in enclosure with cover
	Mechanical endurance	cycles (OFF-ON-OFF)	20,000 ops.
	Shock resistance acc. to IEC/EN 60068-2-27		25 g - 2 shocks - 13 ms
	Vibration resistance acc. to IEC/EN 60068-2-6		5g - 20 cycles at 5...150...5 Hz with load 0.8In
	Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C / RH	28 cycles with 55°C/90-96% and 25°C/95-100%
	Ambient temperature	°C	-25 ... +55°C
	Storage temperature	°C	-40 ... +70°C***

Note:

* Also fulfilling the requirement acc. to the protection degree IPXXB

** Only with accessory: IP20 terminal clip

*** Up to +70°C if the average temperature over a period of 24h is not exceeding 55°C.

S 200 / S 300 technical features

S 200 M UC	S 300 P	SU 200 M	SU 200 MR	SU 200 DC
480Y / 277 V AC	480Y / 277 V AC	240 V AC	480 Y / 277 V AC	1P: ≤ 35 A: 277 V AC; > 35 A: 240 V AC 2...4P: ≤ 35 A: 480 / 277 V AC; > 35 A: 240 V AC
1P: 250 V DC 2...4P: 500 V DC	1P: 60 V DC 2...4P: 125 V DC			1P: 125 V DC 2P: 250 V DC
	10 kA	--		
		10 kA	10 kA	14 kA (UL)
TC1, 0L0, SC: U1	TC2, 0L0, SC: U1		Ring tongue terminal, not for general use	--
	40 °C	C, K, Z: 40 °C	25 °C	K, Z: 40 °C
			6,000 ops. (1 cycle 1s - ON, 9s - OFF)	
Insulation group I, RAL 7035 fire exposure V0 acc.to UL94		Insulation group II, RAL 7035 fire exposure V2 acc.to UL94	Insulation group I, RAL 7035 fire exposure V0 acc.to UL94	
		IP20**, IP40 in enclosure with cover		
	25 g - 2 shocks - 13 ms	25 g - 2 shocks - 13 ms	25 g - 2 shocks - 13 ms	
-25 ... +55°C	-40 ... +70°C	-25 ... +55°C	-25 ... +55°C	-25 ... +55°C
-40 ... +70°C	-50 ... +70°C	-40 ... +70°C	-40 ... +70°C	-40 ... +70°C

MCBs

S 200 / S 300 technical features



S 200



S 300

				S 200	S 200 M
Installation	Terminal				Failsafe bi-directional cylinder-lift terminal
	Cross-section of conductors *1 (top / bottom)	Solid / Stranded	mm²	35 mm² / 35 mm²	
		Flexible	mm²	25 mm² / 25 mm²	
	Cross-section of busbars (top / bottom)	AWG		18 - 4 AWG	14 - 4 AWG
		mm²		10 mm² / 10 mm²	
	Tightening Torque *2	Nm		2.8 Nm	
		in-lbs.		18 in-lbs.	
	Screwdriver	No. 2 Pozidrive			
	Mounting	On DIN rail 35 mm acc. to EN 60715 by fast clip			
	Mounting position	any			
Dimensions and weight	Supply	optional			
	Mounting dimensions acc. to DIN 43880	Mounting dimension 1			
	Pole dimensions (H x D x W)	mm		88 x 69 x 17.5 mm	
	Pole weight	g		approx. 125 g	
Combination with aux. elements	Auxiliary contact	Yes		Yes	
	Signal contact	Yes		Yes	
	Shunt trip	Yes		Yes	
	Undervoltage release	Yes		Yes	
	Motor Operating Device	Yes		Yes	
	Integrated auxiliary switch	Yes		Yes	

*1 All approvals according to the product standards are carried out with copper conductors.

For more details on cable type and cable cross-section, please refer to our technical catalogue (MCB, part B).

*2 Nm-values acc. IEC / in-lbs.-values acc. UL

*3 1 ... 4 mm² (rigid or flexible wires without end sleeves); 1 ... 2.5 mm² (flexible wires with end sleeves)

MCBs

S 200 / S 300 technical features

S 200 M UC	S 300 P	SU 200 M	SU 200 MR	SU 200 DC
			Ring Tongue Terminal	Failsafe bi-directional cylinder- lift terminal
	35 mm ² / 35 mm ²	35mm ² /35mm ²		
	25 mm ² / 25 mm ²	35mm ² /35mm ²		
	18 - 8 AWG	18 - 4 AWG	18 - 4 AWG	
	18 - 8 AWG	18 - 8 AWG		
	18 in-lbs.	25 in-lbs.		
Please note polarity of device	optional	optional	top or bottom	Please note polarity of device
		--	Mounting dimension 1	
85 x 69 x 17.5 mm approx. 125 g	88 x 69 x 17.5 mm approx. 124 g	92 x 71 x 17.5 mm approx. 140g	100 x 71 x 17.5 mm approx. 140g	115 x 69 x 17.5 mm approx. 125 g
Yes	Yes	Yes	Yes	Yes
Yes	Yes	Yes	Yes	Yes
Yes	Yes	Yes	Yes	Yes
Yes	Yes	No	No	No
Yes	Yes	Yes	No	No
Yes	Yes	No	No	No

MCBs

S 200 series B characteristic

S 200 B characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icn=6 kA



S 201



S 202



S 203

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	6	464901	S201-B6	2CDS251001R0065		0.112	10
	10	463805	S201-B10	2CDS251001R0105		0.112	10
	13	465007	S201-B13	2CDS251001R0135		0.115	10
	16	578639	S201-B16	2CDS251001R1165		0.115	10
	20 *1	465106	S201-B20	2CDS251001R0205		0.115	10
	25	465205	S201-B25	2CDS251001R0255		0.115	10
	32 *2	465304	S201-B32	2CDS251001R0325		0.120	10
	40 *3	465403	S201-B40	2CDS251001R0405		0.120	10
	50	550925	S201-B50	2CDS251001R0505		0.120	10
	63	550932	S201-B63	2CDS251001R0635		0.120	10
2	6	466400	S202-B6	2CDS252001R0065		0.224	5
	10	466608	S202-B10	2CDS252001R0105		0.224	5
	13	466707	S202-B13	2CDS252001R0135		0.230	5
	16	466905	S202-B16	2CDS252001R0165		0.230	5
	20	467001	S202-B20	2CDS252001R0205		0.230	5
	25	467100	S202-B25	2CDS252001R0255		0.230	5
	32	467209	S202-B32	2CDS252001R0325		0.240	5
	40	467407	S202-B40	2CDS252001R0405		0.240	5
	50	550949	S202-B50	2CDS252001R0505		0.240	5
	63	550956	S202-B63	2CDS252001R0635		0.240	5
3	6	468602	S203-B6	2CDS253001R0065		0.336	1
	10	468701	S203-B10	2CDS253001R0105		0.336	1
	13	468909	S203-B13	2CDS253001R0135		0.345	1
	16	469005	S203-B16	2CDS253001R0165		0.345	1
	20 *1	469104	S203-B20	2CDS253001R0205		0.345	1
	25	469203	S203-B25	2CDS253001R0255		0.345	1
	32 *2	469302	S203-B32	2CDS253001R0325		0.360	1
	40 *3	469401	S203-B40	2CDS253001R0405		0.360	1
	50	550963	S203-B50	2CDS253001R0505		0.360	1
	63	550970	S203-B63	2CDS253001R0635		0.360	1

*1 suitable for flow-type heaters 12 kW

*2 suitable for flow-type heaters 18 kW

*3 suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series B characteristic



S 204

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	6	528955	S204-B6	2CDS254001R0065		0.448	1
	10	528962	S204-B10	2CDS254001R0105		0.448	1
	13	528979	S204-B13	2CDS254001R0135		0.460	1
	16	528986	S204-B16	2CDS254001R0165		0.460	1
	20	528993	S204-B20	2CDS254001R0205		0.460	1
	25	529006	S204-B25	2CDS254001R0255		0.460	1
	32	529013	S204-B32	2CDS254001R0325		0.480	1
	40	529020	S204-B40	2CDS254001R0405		0.480	1
	50	550987	S204-B50	2CDS254001R0505		0.480	1
	63	550994	S204-B63	2CDS254001R0635		0.480	1

MCBs

S 200 series C characteristic



S 201



S 202

S 200 C characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for resistive and inductive loads with low inrush current.

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icn=6 kA

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	523295	S201-C0.5	2CDS251001R0984		0.112	10
	1	523318	S201-C1	2CDS251001R0014		0.112	10
	1.6	523301	S201-C1.6	2CDS251001R0974		0.112	10
	2	523325	S201-C2	2CDS251001R0024		0.112	10
	3	523332	S201-C3	2CDS251001R0034		0.112	10
	4	523349	S201-C4	2CDS251001R0044		0.112	10
	6	464000	S201-C6	2CDS251001R0064		0.112	10
	8	464109	S201-C8	2CDS251001R0084		0.112	10
	10	464208	S201-C10	2CDS251001R0104		0.112	10
	13	464307	S201-C13	2CDS251001R0134		0.115	10
	16	464406	S201-C16	2CDS251001R0164		0.115	10
	20 * ¹	464505	S201-C20	2CDS251001R0204		0.115	10
	25	464604	S201-C25	2CDS251001R0254		0.115	10
	32 * ²	464703	S201-C32	2CDS251001R0324		0.120	10
	40 * ³	464802	S201-C40	2CDS251001R0404		0.120	10
	50	551007	S201-C50	2CDS251001R0504		0.120	10
	63	551014	S201-C63	2CDS251001R0634		0.120	10
2	0.5	523356	S202-C0.5	2CDS252001R0984		0.224	5
	1	523363	S202-C1	2CDS252001R0014		0.224	5
	1.6	523370	S202-C1.6	2CDS252001R0974		0.224	5
	2	523387	S202-C2	2CDS252001R0024		0.224	5
	3	523394	S202-C3	2CDS252001R0034		0.224	5
	4	523400	S202-C4	2CDS252001R0044		0.224	5
	6	465502	S202-C6	2CDS252001R0064		0.224	5
	8	465601	S202-C8	2CDS252001R0084		0.224	5
	10	465700	S202-C10	2CDS252001R0104		0.224	5
	13	465809	S202-C13	2CDS252001R0134		0.230	5
	16	465908	S202-C16	2CDS252001R0164		0.230	5
	20 * ¹	466004	S202-C20	2CDS252001R0204		0.230	5
	25	466103	S202-C25	2CDS252001R0254		0.230	5
	32 * ²	466202	S202-C32	2CDS252001R0324		0.240	5
	40 * ³	466301	S202-C40	2CDS252001R0404		0.240	5
	50	551045	S202-C50	2CDS252001R0504		0.240	5
	63	551052	S202-C63	2CDS252001R0634		0.240	5

*¹ suitable for flow-type heaters 12 kW

*² suitable for flow-type heaters 18 kW

*³ suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series C characteristic



S 203



S 204

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	1	523424	S203-C1	2CDS253001R0014		0.336	1
	1.6	523431	S203-C1.6	2CDS253001R0974		0.336	1
	2	523448	S203-C2	2CDS253001R0024		0.336	1
	3	523455	S203-C3	2CDS253001R0034		0.336	1
	4	523462	S203-C4	2CDS253001R0044		0.336	1
	6	467506	S203-C6	2CDS253001R0064		0.336	1
	8	467605	S203-C8	2CDS253001R0084		0.336	1
	10	467803	S203-C10	2CDS253001R0104		0.336	1
	13	467902	S203-C13	2CDS253001R0134		0.345	1
	16	468008	S203-C16	2CDS253001R0164		0.345	1
	20 ^{*1}	468107	S203-C20	2CDS253001R0204		0.345	1
	25	468206	S203-C25	2CDS253001R0254		0.345	1
	32 ^{*2}	468305	S203-C32	2CDS253001R0324		0.360	1
	40 ^{*3}	468404	S203-C40	2CDS253001R0404		0.360	1
	50	551069	S203-C50	2CDS253001R0504		0.360	1
	63	551076	S203-C63	2CDS253001R0634		0.360	1
4	0.5	529112	S204-C0.5	2CDS254001R0984		0.448	1
	1	529129	S204-C1	2CDS254001R0014		0.448	1
	1.6	529136	S204-C1.6	2CDS254001R0974		0.448	1
	2	529143	S204-C2	2CDS254001R0024		0.448	1
	3	529150	S204-C3	2CDS254001R0034		0.448	1
	4	529167	S204-C4	2CDS254001R0044		0.448	1
	6	529174	S204-C6	2CDS254001R0064		0.448	1
	8	529181	S204-C8	2CDS254001R0084		0.448	1
	10	529198	S204-C10	2CDS254001R0104		0.448	1
	13	529204	S204-C13	2CDS254001R0134		0.460	1
	16	529211	S204-C16	2CDS254001R0164		0.460	1
	20 ^{*1}	529228	S204-C20	2CDS254001R0204		0.460	1
	25	529235	S204-C25	2CDS254001R0254		0.460	1
	32 ^{*2}	529242	S204-C32	2CDS254001R0324		0.480	1
	40 ^{*3}	529259	S204-C40	2CDS254001R0404		0.480	1
	50	551106	S204-C50	2CDS254001R0504		0.480	1
	63	551113	S204-C63	2CDS254001R0634		0.480	1

^{*1} suitable for flow-type heaters 12 kW

^{*2} suitable for flow-type heaters 18 kW

^{*3} suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series D characteristic

S 200 D characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for circuits which supply loads with high inrush current at the circuit closing (LV/LV transformers, breakdown lamps).

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

I_{cn}=6 kA



S 201



S 202

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	529938	S201-D0.5	2CDS251001R0981		0.112	10
	1	529945	S201-D1	2CDS251001R0011		0.112	10
	1.6	529952	S201-D1.6	2CDS251001R0971		0.112	10
	2	529969	S201-D2	2CDS251001R0021		0.112	10
	3	529976	S201-D3	2CDS251001R0031		0.112	10
	4	529983	S201-D4	2CDS251001R0041		0.112	10
	6	529990	S201-D6	2CDS251001R0061		0.112	10
	8	530002	S201-D8	2CDS251001R0081		0.112	10
	10	530019	S201-D10	2CDS251001R0101		0.112	10
	13	530026	S201-D13	2CDS251001R0131		0.115	10
	16	530033	S201-D16	2CDS251001R0161		0.115	10
	20 * ¹	530040	S201-D20	2CDS251001R0201		0.115	10
	25	530057	S201-D25	2CDS251001R0251		0.115	10
	32 * ²	530064	S201-D32	2CDS251001R0321		0.120	10
	40 * ³	530071	S201-D40	2CDS251001R0401		0.120	10
	63	552004	S201-D63	2CDS251001R0631		0.120	10
2	0.5	530484	S202-D0.5	2CDS252001R0981		0.224	5
	1	530491	S202-D1	2CDS252001R0011		0.224	5
	1.6	530507	S202-D1.6	2CDS252001R0971		0.224	5
	2	530514	S202-D2	2CDS252001R0021		0.224	5
	3	530521	S202-D3	2CDS252001R0031		0.224	5
	4	530538	S202-D4	2CDS252001R0041		0.224	5
	6	530545	S202-D6	2CDS252001R0061		0.224	5
	8	530552	S202-D8	2CDS252001R0081		0.224	5
	10	530583	S202-D10	2CDS252001R0101		0.224	5
	13	530606	S202-D13	2CDS252001R0131		0.230	5
	16	530613	S202-D16	2CDS252001R0161		0.230	5
	20	530637	S202-D20	2CDS252001R0201		0.230	5
	25	530644	S202-D25	2CDS252001R0251		0.230	5
	32	530651	S202-D32	2CDS252001R0321		0.240	5
	40	530668	S202-D40	2CDS252001R0401		0.240	5
	63	552042	S202-D63	2CDS252001R0631		0.240	5

*¹ suitable for flow-type heaters 12 kW
 *² suitable for flow-type heaters 18 kW

*³ suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series D characteristic



S 203



S 204

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	530811	S203-D0.5	2CDS253001R0981		0.336	1
	1	530828	S203-D1	2CDS253001R0011		0.336	1
	1.6	530835	S203-D1.6	2CDS253001R0971		0.336	1
	2	530842	S203-D2	2CDS253001R0021		0.336	1
	3	530859	S203-D3	2CDS253001R0031		0.336	1
	4	530866	S203-D4	2CDS253001R0041		0.336	1
	6	530880	S203-D6	2CDS253001R0061		0.336	1
	8	530897	S203-D8	2CDS253001R0081		0.336	1
	10	530903	S203-D10	2CDS253001R0101		0.336	1
	13	530910	S203-D13	2CDS253001R0131		0.345	1
	16	530927	S203-D16	2CDS253001R0161		0.345	1
	20 * ¹	530934	S203-D20	2CDS253001R0201		0.345	1
	25	530941	S203-D25	2CDS253001R0251		0.345	1
	32 * ²	530958	S203-D32	2CDS253001R0321		0.360	1
	40 * ³	530965	S203-D40	2CDS253001R0401		0.360	1
	50	552059	S203-D50	2CDS253001R0501		0.360	1
	63	552066	S203-D63	2CDS253001R0631		0.360	1
4	0.5	531122	S204-D0.5	2CDS254001R0981		0.448	1
	1	531139	S204-D1	2CDS254001R0011		0.448	1
	1.6	531146	S204-D1.6	2CDS254001R0971		0.448	1
	2	531153	S204-D2	2CDS254001R0021		0.448	1
	3	531160	S204-D3	2CDS254001R0031		0.448	1
	4	531177	S204-D4	2CDS254001R0041		0.448	1
	6	531184	S204-D6	2CDS254001R0061		0.448	1
	8	531191	S204-D8	2CDS254001R0081		0.448	1
	10	531207	S204-D10	2CDS254001R0101		0.448	1
	13	531214	S204-D13	2CDS254001R0131		0.460	1
	16	531221	S204-D16	2CDS254001R0161		0.460	1
	20	531238	S204-D20	2CDS254001R0201		0.460	1
	25	531290	S204-D25	2CDS254001R0251		0.460	1
	32	531306	S204-D32	2CDS254001R0321		0.480	1
	40	531313	S204-D40	2CDS254001R0401		0.480	1
	50	552097	S204-D50	2CDS254001R0501		0.480	1
	63	552103	S204-D63	2CDS254001R0631		0.480	1

*¹ suitable for flow-type heaters 12 kW*² suitable for flow-type heaters 18 kW*³ suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series K characteristic

S 200 K (power) characteristic

Function: protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=10 kA



S 201



S 202

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	507196	S201-K0.5	2CDS251001R0157		0.112	10
	1	507202	S201-K1	2CDS251001R0217		0.112	10
	1.6	507219	S201-K1.6	2CDS251001R0257		0.112	10
	2	507226	S201-K2	2CDS251001R0277		0.112	10
	3	507233	S201-K3	2CDS251001R0317		0.112	10
	4	507240	S201-K4	2CDS251001R0337		0.112	10
	6	507257	S201-K6	2CDS251001R0377		0.112	10
	8	507264	S201-K8	2CDS251001R0407		0.112	10
	10	496117	S201-K10	2CDS251001R0427		0.112	10
	13	507271	S201-K13	2CDS251001R0447		0.115	10
	16	496124	S201-K16	2CDS251001R0467		0.115	10
	20	507288	S201-K20	2CDS251001R0487		0.115	10
	25	507295	S201-K25	2CDS251001R0517		0.115	10
	32	496131	S201-K32	2CDS251001R0537		0.120	10
	40	507301	S201-K40	2CDS251001R0557		0.120	10
	50	551120	S201-K50	2CDS251001R0577		0.120	10
	63	551137	S201-K63	2CDS251001R0607		0.120	10
2	0.5	507318	S202-K0.5	2CDS252001R0157		0.224	5
	1	507325	S202-K1	2CDS252001R0217		0.224	5
	1.6	507332	S202-K1.6	2CDS252001R0257		0.224	5
	2	507349	S202-K2	2CDS252001R0277		0.224	5
	3	507356	S202-K3	2CDS252001R0317		0.224	5
	4	507363	S202-K4	2CDS252001R0337		0.224	5
	6	507370	S202-K6	2CDS252001R0377		0.224	5
	8	507387	S202-K8	2CDS252001R0407		0.224	5
	10	507394	S202-K10	2CDS252001R0427		0.224	5
	13	507400	S202-K13	2CDS252001R0447		0.230	5
	16	507417	S202-K16	2CDS252001R0467		0.230	5
	20	507424	S202-K20	2CDS252001R0487		0.230	5
	25	507431	S202-K25	2CDS252001R0517		0.230	5
	32	507448	S202-K32	2CDS252001R0537		0.240	5
	40	507455	S202-K40	2CDS252001R0557		0.240	5
	50	551168	S202-K50	2CDS252001R0577		0.240	5
	63	551175	S202-K63	2CDS252001R0607		0.240	5

*1 suitable for flow-type heaters 12 kW

*2 suitable for flow-type heaters 18 kW

*3 suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series K characteristic



S 203



S 204

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	507462	S203-K0.5	2CDS253001R0157		0.336	1
	1	507479	S203-K1	2CDS253001R0217		0.336	1
	1.6	507486	S203-K1.6	2CDS253001R0257		0.336	1
	2	507493	S203-K2	2CDS253001R0277		0.336	1
	3	507509	S203-K3	2CDS253001R0317		0.336	1
	4	507516	S203-K4	2CDS253001R0337		0.336	1
	6	507523	S203-K6	2CDS253001R0377		0.336	1
	8	507530	S203-K8	2CDS253001R0407		0.336	1
	10	496148	S203-K10	2CDS253001R0427		0.336	1
	13	507547	S203-K13	2CDS253001R0447		0.345	1
	16	496155	S203-K16	2CDS253001R0467		0.345	1
	20	507554	S203-K20	2CDS253001R0487		0.345	1
	25	507561	S203-K25	2CDS253001R0517		0.345	1
	32	496162	S203-K32	2CDS253001R0537		0.360	1
	40	507578	S203-K40	2CDS253001R0557		0.360	1
	50	551182	S203-K50	2CDS253001R0577		0.360	1
	63	551199	S203-K63	2CDS253001R0607		0.360	1
4	0.5	529266	S204-K0.5	2CDS254001R0157		0.448	1
	1	529273	S204-K1	2CDS254001R0217		0.448	1
	1.6	529280	S204-K1.6	2CDS254001R0257		0.448	1
	2	529297	S204-K2	2CDS254001R0277		0.448	1
	3	529303	S204-K3	2CDS254001R0317		0.448	1
	4	529310	S204-K4	2CDS254001R0337		0.448	1
	6	529327	S204-K6	2CDS254001R0377		0.448	1
	8	529334	S204-K8	2CDS254001R0407		0.448	1
	10	529341	S204-K10	2CDS254001R0427		0.448	1
	13	529358	S204-K13	2CDS254001R0447		0.460	1
	16	529365	S204-K16	2CDS254001R0467		0.460	1
	20	529372	S204-K20	2CDS254001R0487		0.460	1
	25	529389	S204-K25	2CDS254001R0517		0.460	1
	32	529396	S204-K32	2CDS254001R0537		0.480	1
	40	529402	S204-K40	2CDS254001R0557		0.480	1
	50	551229	S204-K50	2CDS254001R0577		0.480	1
	63	551236	S204-K63	2CDS254001R0607		0.480	1

MCBs

S 200 series Z characteristic

S 200 Z characteristic

Function: protection and control of the electronic circuits against lower and long duration overloads and short-circuits.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=10 kA



S 201



S 202

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	530309	S201-Z0.5	2CDS251001R0158		0.112	10
	1	530330	S201-Z1	2CDS251001R0218		0.112	10
	1.6	530347	S201-Z1.6	2CDS251001R0258		0.112	10
	2	530354	S201-Z2	2CDS251001R0278		0.112	10
	3	530361	S201-Z3	2CDS251001R0318		0.112	10
	4	530378	S201-Z4	2CDS251001R0338		0.112	10
	6	530408	S201-Z6	2CDS251001R0378		0.112	10
	8	530415	S201-Z8	2CDS251001R0408		0.112	10
	10	530422	S201-Z10	2CDS251001R0428		0.112	10
	16	530439	S201-Z16	2CDS251001R0468		0.115	10
	20	530446	S201-Z20	2CDS251001R0488		0.115	10
	25	530453	S201-Z25	2CDS251001R0518		0.115	10
	32	530460	S201-Z32	2CDS251001R0538		0.120	10
	40	530477	S201-Z40	2CDS251001R0558		0.120	10
	50	551915	S201-Z50	2CDS251001R0578		0.120	10
	63	551922	S201-Z63	2CDS251001R0608		0.120	10
2	0.5	530682	S202-Z0.5	2CDS252001R0158		0.224	5
	1	530675	S202-Z1	2CDS252001R0218		0.224	5
	1.6	530699	S202-Z1.6	2CDS252001R0258		0.224	5
	2	530705	S202-Z2	2CDS252001R0278		0.224	5
	3	530712	S202-Z3	2CDS252001R0318		0.224	5
	4	530729	S202-Z4	2CDS252001R0338		0.224	5
	6	530736	S202-Z6	2CDS252001R0378		0.224	5
	8	530743	S202-Z8	2CDS252001R0408		0.224	5
	10	530750	S202-Z10	2CDS252001R0428		0.224	5
	16	530767	S202-Z16	2CDS252001R0468		0.230	5
	20	530774	S202-Z20	2CDS252001R0488		0.230	5
	25	530781	S202-Z25	2CDS252001R0518		0.230	5
	32	530798	S202-Z32	2CDS252001R0538		0.240	5
	40	530804	S202-Z40	2CDS252001R0558		0.240	5
	50	551939	S202-Z50	2CDS252001R0578		0.240	5
	63	551946	S202-Z63	2CDS252001R0608		0.240	5

MCBs

S 200 series Z characteristic



S 203



S 204

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	530972	S203-Z0.5	2CDS253001R0158		0.336	1
	1	530989	S203-Z1	2CDS253001R0218		0.336	1
	1.6	530996	S203-Z1.6	2CDS253001R0258		0.336	1
	2	531009	S203-Z2	2CDS253001R0278		0.336	1
	3	531016	S203-Z3	2CDS253001R0318		0.336	1
	4	531023	S203-Z4	2CDS253001R0338		0.336	1
	6	531030	S203-Z6	2CDS253001R0378		0.336	1
	8	531047	S203-Z8	2CDS253001R0408		0.336	1
	10	531054	S203-Z10	2CDS253001R0428		0.336	1
	16	531061	S203-Z16	2CDS253001R0468		0.345	1
	20	531078	S203-Z20	2CDS253001R0488		0.345	1
	25	531085	S203-Z25	2CDS253001R0518		0.345	1
	32	531092	S203-Z32	2CDS253001R0538		0.360	1
	40	531108	S203-Z40	2CDS253001R0558		0.360	1
	50	551953	S203-Z50	2CDS253001R0578		0.360	1
	63	551960	S203-Z63	2CDS253001R0608		0.360	1
4	0.5	530248	S204-Z0.5	2CDS254001R0158		0.448	1
	1	531320	S204-Z1	2CDS254001R0218		0.448	1
	1.6	531443	S204-Z1.6	2CDS254001R0258		0.448	1
	2	531436	S204-Z2	2CDS254001R0278		0.448	1
	3	531337	S204-Z3	2CDS254001R0318		0.448	1
	4	531344	S204-Z4	2CDS254001R0338		0.448	1
	6	531351	S204-Z6	2CDS254001R0378		0.448	1
	8	531368	S204-Z8	2CDS254001R0408		0.448	1
	10	531375	S204-Z10	2CDS254001R0428		0.448	1
	16	531382	S204-Z16	2CDS254001R0468		0.460	1
	20	531399	S204-Z20	2CDS254001R0488		0.460	1
	25	531405	S204-Z25	2CDS254001R0518		0.460	1
	32	531412	S204-Z32	2CDS254001R0538		0.480	1
	40	531429	S204-Z40	2CDS254001R0558		0.480	1
	50	551977	S204-Z50	2CDS254001R0578		0.480	1
	63	551984	S204-Z63	2CDS254001R0608		0.480	1

MCBs

S 200 series M-B characteristic

S 200 M-B characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icn=10 kA



S 201 M



S 202 M



S 203 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	6	549424	S201M-B6	2CDS271001R0065		0.112	10
	10	549431	S201M-B10	2CDS271001R0105		0.112	10
	13	549448	S201M-B13	2CDS271001R0135		0.115	10
	16	549455	S201M-B16	2CDS271001R0165		0.115	10
	20 ^{*1}	549462	S201M-B20	2CDS271001R0205		0.115	10
	25	549479	S201M-B25	2CDS271001R0255		0.115	10
	32 ^{*2}	549486	S201M-B32	2CDS271001R0325		0.120	10
	40 ^{*3}	549493	S201M-B40	2CDS271001R0405		0.120	10
	50	543811	S201M-B50	2CDS271001R0505		0.120	10
	63	543828	S201M-B63	2CDS271001R0635		0.120	10
2	6	549585	S202M-B6	2CDS272001R0065		0.224	5
	10	549592	S202M-B10	2CDS272001R0105		0.224	5
	13	549608	S202M-B13	2CDS272001R0135		0.230	5
	16	549615	S202M-B16	2CDS272001R0165		0.230	5
	20	549622	S202M-B20	2CDS272001R0205		0.230	5
	25	549639	S202M-B25	2CDS272001R0255		0.230	5
	32	549646	S202M-B32	2CDS272001R0325		0.240	5
	40	549653	S202M-B40	2CDS272001R0405		0.240	5
	50	543859	S202M-B50	2CDS272001R0505		0.240	5
	63	543866	S202M-B63	2CDS272001R0635		0.240	5
3	6	549660	S203M-B 6	2CDS273001R0065		0.336	1
	10	549677	S203M-B10	2CDS273001R0105		0.336	1
	13	549684	S203M-B13	2CDS273001R0135		0.345	1
	16	549691	S203M-B16	2CDS273001R0165		0.345	1
	20 ^{*1}	549707	S203M-B20	2CDS273001R0205		0.345	1
	25	549714	S203M-B25	2CDS273001R0255		0.345	1
	32 ^{*2}	549721	S203M-B32	2CDS273001R0325		0.360	1
	40 ^{*3}	549738	S203M-B40	2CDS273001R0405		0.360	1
	50	543873	S203M-B50	2CDS273001R0505		0.360	1
	63	543880	S203M-B63	2CDS273001R0635		0.360	1

^{*1} suitable for flow-type heaters 12 kW

^{*2} suitable for flow-type heaters 18 kW

^{*3} suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series M-B characteristic



S 204 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	6	549820	S204M-B 6	2CDS274001R0065		0.448	1
	10	549837	S204M-B10	2CDS274001R0105		0.448	1
	13	549844	S204M-B13	2CDS274001R0135		0.460	1
	16	549851	S204M-B16	2CDS274001R0165		0.460	1
	20	549868	S204M-B20	2CDS274001R0205		0.460	1
	25	549875	S204M-B25	2CDS274001R0255		0.460	1
	32	549882	S204M-B32	2CDS274001R0325		0.480	1
	40	549899	S204M-B40	2CDS274001R0405		0.480	1
	50	543910	S204M-B50	2CDS274001R0505		0.480	1
	63	543927	S204M-B63	2CDS274001R0635		0.480	1

MCBs

S 200 series M-C characteristic

S 200 M-C characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for resistive and inductive loads with low inrush current.

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icn=10 kA



S 201 M



S 202 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	549905	S201M-C0.5	2CDS271001R0984		0.112	10
	1	549929	S201M-C1	2CDS271001R0014		0.112	10
	1.6	549912	S201M-C1.6	2CDS271001R0974		0.112	10
	2	549936	S201M-C2	2CDS271001R0024		0.112	10
	3	549943	S201M-C3	2CDS271001R0034		0.112	10
	4	549950	S201M-C4	2CDS271001R0044		0.112	10
	6	549967	S201M-C6	2CDS271001R0064		0.112	10
	8	549974	S201M-C8	2CDS271001R0084		0.112	10
	10	549981	S201M-C10	2CDS271001R0104		0.112	10
	13	549998	S201M-C13	2CDS271001R0134		0.115	10
	16	550000	S201M-C16	2CDS271001R0164		0.115	10
	20 * ¹	550017	S201M-C20	2CDS271001R0204		0.115	10
	25	550024	S201M-C25	2CDS271001R0254		0.115	10
	32 * ²	550031	S201M-C32	2CDS271001R0324		0.120	10
	40 * ³	550048	S201M-C40	2CDS271001R0404		0.120	10
	50	543934	S201M-C50	2CDS271001R0504		0.120	10
	63	543941	S201M-C63	2CDS271001R0634		0.120	10
2	0.5	550208	S202M-C0.5	2CDS272001R0984		0.224	5
	1	550222	S202M-C1	2CDS272001R0014		0.224	5
	1.6	550215	S202M-C1.6	2CDS272001R0974		0.224	5
	2	550239	S202M-C2	2CDS272001R0024		0.224	5
	3	550246	S202M-C3	2CDS272001R0034		0.224	5
	4	550253	S202M-C4	2CDS272001R0044		0.224	5
	6	550260	S202M-C6	2CDS272001R0064		0.224	5
	8	550277	S202M-C8	2CDS272001R0084		0.224	5
	10	550284	S202M-C10	2CDS272001R0104		0.224	5
	13	550291	S202M-C13	2CDS272001R0134		0.230	5
	16	550307	S202M-C16	2CDS272001R0164		0.230	5
	20	550314	S202M-C20	2CDS272001R0204		0.230	5
	25	550321	S202M-C25	2CDS272001R0254		0.230	5
	32	550338	S202M-C32	2CDS272001R0324		0.240	5
	40	550345	S202M-C40	2CDS272001R0404		0.240	5
	50	543972	S202M-C50	2CDS272001R0504		0.240	5
	63	543989	S202M-C63	2CDS272001R0634		0.240	5

*¹ suitable for flow-type heaters 12 kW

*² suitable for flow-type heaters 18 kW

*³ suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series M-C characteristic



S 203 M



S 204 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	550352	S203M-C0.5	2CDS273001R0984		0.336	1
	1	550376	S203M-C1	2CDS273001R0014		0.336	1
	1.6	550369	S203M-C1.6	2CDS273001R0974		0.336	1
	2	550383	S203M-C2	2CDS273001R0024		0.336	1
	3	550390	S203M-C3	2CDS273001R0034		0.336	1
	4	550406	S203M-C4	2CDS273001R0044		0.336	1
	6	550413	S203M-C6	2CDS273001R0064		0.336	1
	8	550420	S203M-C8	2CDS273001R0084		0.336	1
	10	550437	S203M-C10	2CDS273001R0104		0.336	1
	13	550444	S203M-C13	2CDS273001R0134		0.345	1
	16	550451	S203M-C16	2CDS273001R0164		0.345	1
	20 ^{*1}	550468	S203M-C20	2CDS273001R0204		0.345	1
	25	550475	S203M-C25	2CDS273001R0254		0.345	1
	32 ^{*2}	550482	S203M-C32	2CDS273001R0324		0.360	1
	40 ^{*3}	550499	S203M-C40	2CDS273001R0404		0.360	1
	50	543996	S203M-C50	2CDS273001R0504		0.360	1
	63	544009	S203M-C63	2CDS273001R0634		0.360	1
4	0.5	550659	S204M-C0.5	2CDS274001R0984		0.448	1
	1	550673	S204M-C1	2CDS274001R0014		0.448	1
	1.6	550666	S204M-C1.6	2CDS274001R0974		0.448	1
	2	550680	S204M-C2	2CDS274001R0024		0.448	1
	3	550697	S204M-C3	2CDS274001R0034		0.448	1
	4	550703	S204M-C4	2CDS274001R0044		0.448	1
	6	550710	S204M-C6	2CDS274001R0064		0.448	1
	8	550727	S204M-C8	2CDS274001R0084		0.448	1
	10	550734	S204M-C10	2CDS274001R0104		0.448	1
	13	550741	S204M-C13	2CDS274001R0134		0.460	1
	16	550758	S204M-C16	2CDS274001R0164		0.460	1
	20	550765	S204M-C20	2CDS274001R0204		0.460	1
	25	550772	S204M-C25	2CDS274001R0254		0.460	1
	32	550789	S204M-C32	2CDS274001R0324		0.480	1
	40	550796	S204M-C40	2CDS274001R0404		0.480	1
	50	544030	S204M-C50	2CDS274001R0504		0.480	1
	63	544047	S204M-C63	2CDS274001R0634		0.480	1

^{*1} suitable for flow-type heaters 12 kW

^{*3} suitable for flow-type heaters 21, 24 and 27 kW

^{*2} suitable for flow-type heaters 18 kW

MCBs

S 200 series M-D characteristic

S 200 M-D characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for circuits which supply loads with high inrush current at the circuit closing (LV/LV transformers, breakdown lamps).

Applications: residential, commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icn=10 kA



S 201 M



S 202 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	599832	S201M-D0.5	2CDS271001R0981		0.112	10
	1	500313	S201M-D1	2CDS271001R0011		0.112	10
	1.6	599825	S201M-D1.6	2CDS271001R0971		0.112	10
	2	599337	S201M-D2	2CDS271001R0021		0.112	10
	3	599351	S201M-D3	2CDS271001R0031		0.112	10
	4	599357	S201M-D4	2CDS271001R0041		0.112	10
	6	599399	S201M-D6	2CDS271001R0061		0.112	10
	8	599405	S201M-D8	2CDS271001R0081		0.112	10
	10	599429	S201M-D10	2CDS271001R0101		0.112	10
	13	663267	S201M-D13	2CDS271001R0131		0.115	10
	16	599450	S201M-D16	2CDS271001R0161		0.115	10
	20 * ¹	500467	S201M-D20	2CDS271001R0201		0.115	10
	25	599498	S201M-D25	2CDS271001R0251		0.115	10
	32 * ²	599566	S201M-D32	2CDS271001R0321		0.120	10
	40 * ³	599610	S201M-D40	2CDS271001R0401		0.120	10
	50	599702	S201M-D50	2CDS271001R0501		0.120	10
	63	599818	S201M-D63	2CDS271001R0631		0.120	10
2	0.5	600880	S202M-D0.5	2CDS272001R0981		0.224	5
	1	600361	S202M-D1	2CDS272001R0011		0.224	5
	1.6	600873	S202M-D1.6	2CDS272001R0971		0.224	5
	2	600385	S202M-D2	2CDS272001R0021		0.224	5
	3	600408	S202M-D3	2CDS272001R0031		0.224	5
	4	600422	S202M-D4	2CDS272001R0041		0.224	5
	6	600446	S202M-D6	2CDS272001R0061		0.224	5
	8	600453	S202M-D8	2CDS272001R0081		0.224	5
	10	600477	S202M-D10	2CDS272001R0101		0.224	5
	13	663274	S202M-D13	2CDS272001R0131		0.230	5
	16	600507	S202M-D16	2CDS272001R0161		0.230	5
	20	600514	S202M-D20	2CDS272001R0201		0.230	5
	25	600545	S202M-D25	2CDS272001R0251		0.230	5
	32	600613	S202M-D32	2CDS272001R0321		0.240	5
	40	600668	S202M-D40	2CDS272001R0401		0.240	5
	50	600750	S202M-D50	2CDS272001R0501		0.240	5
	63	600866	S202M-D63	2CDS272001R0631		0.240	5

*¹ suitable for flow-type heaters 12 kW

*² suitable for flow-type heaters 18 kW

*³ suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series M-D characteristic



S 203 M



S 204 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	601412	S203M-D0.5	2CDS273001R0981		0.336	1
	1	600897	S203M-D1	2CDS273001R0011		0.336	1
	1.6	601405	S203M-D1.6	2CDS273001R0971		0.336	1
	2	600910	S203M-D2	2CDS273001R0021		0.336	1
	3	600934	S203M-D3	2CDS273001R0031		0.336	1
	4	600958	S203M-D4	2CDS273001R0041		0.336	1
	6	600972	S203M-D6	2CDS273001R0061		0.336	1
	8	600989	S203M-D8	2CDS273001R0081		0.336	1
	10	601009	S203M-D10	2CDS273001R0101		0.336	1
	13	663281	S203M-D13	2CDS273001R0131		0.345	1
	16	601030	S203M-D16	2CDS273001R0161		0.345	1
	20 ^{*1}	601047	S203M-D20	2CDS273001R0201		0.345	1
	25	601078	S203M-D25	2CDS273001R0251		0.345	1
	32 ^{*2}	601146	S203M-D32	2CDS273001R0321		0.360	1
	40 ^{*3}	601191	S203M-D40	2CDS273001R0401		0.360	1
	50	601283	S203M-D50	2CDS273001R0501		0.360	1
	63	601399	S203M-D63	2CDS273001R0631		0.360	1
4	0.5	602143	S204M-D0.5	2CDS274001R0981		0.448	1
	1	601634	S204M-D1	2CDS274001R0011		0.448	1
	1.6	602136	S204M-D1.6	2CDS274001R0971		0.448	1
	2	601658	S204M-D2	2CDS274001R0021		0.448	1
	3	601672	S204M-D3	2CDS274001R0031		0.448	1
	4	601696	S204M-D4	2CDS274001R0041		0.448	1
	6	601719	S204M-D6	2CDS274001R0061		0.448	1
	8	601726	S204M-D8	2CDS274001R0081		0.448	1
	10	601740	S204M-D10	2CDS274001R0101		0.448	1
	13	663298	S204M-D13	2CDS274001R0131		0.460	1
	16	601771	S204M-D16	2CDS274001R0161		0.460	1
	20	601788	S204M-D20	2CDS274001R0201		0.460	1
	25	601818	S204M-D25	2CDS274001R0251		0.460	1
	32	601887	S204M-D32	2CDS274001R0321		0.480	1
	40	601931	S204M-D40	2CDS274001R0401		0.480	1
	50	602013	S204M-D50	2CDS274001R0501		0.480	1
	63	602129	S204M-D63	2CDS274001R0631		0.480	1

^{*1} suitable for flow-type heaters 12 kW

^{*2} suitable for flow-type heaters 18 kW

^{*3} suitable for flow-type heaters 21, 24 and 27 kW

MCBs

S 200 series M-K characteristic

S 200 M-K (power) characteristic

Function: protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=15 kA



S 201 M



S 202 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	599436	S201M-K0.5	2CDS271001R0157		0.112	10
	1	599474	S201M-K1	2CDS271001R0217		0.112	10
	1.6	599504	S201M-K1.6	2CDS271001R0257		0.112	10
	2	599528	S201M-K2	2CDS271001R0277		0.112	10
	3	599542	S201M-K3	2CDS271001R0317		0.112	10
	4	599573	S201M-K4	2CDS271001R0337		0.112	10
	6	599597	S201M-K6	2CDS271001R0377		0.112	10
	8	599627	S201M-K8	2CDS271001R0407		0.112	10
	10	599641	S201M-K10	2CDS271001R0427		0.112	10
	13	659390	S201M-K13	2CDS271001R0447		0.115	10
	16	599665	S201M-K16	2CDS271001R0467		0.115	10
	20	599689	S201M-K20	2CDS271001R0487		0.115	10
	25	599719	S201M-K25	2CDS271001R0517		0.115	10
	32	599733	S201M-K32	2CDS271001R0537		0.120	10
	40	599757	S201M-K40	2CDS271001R0557		0.120	10
	50	599771	S201M-K50	2CDS271001R0577		0.120	10
	63	599795	S201M-K63	2CDS271001R0607		0.120	10
2	0.5	600484	S202M-K0.5	2CDS272001R0157		0.224	5
	1	600521	S202M-K1	2CDS272001R0217		0.224	5
	1.6	600552	S202M-K1.6	2CDS272001R0257		0.224	5
	2	600576	S202M-K2	2CDS272001R0277		0.224	5
	3	600590	S202M-K3	2CDS272001R0317		0.224	5
	4	600620	S202M-K4	2CDS272001R0337		0.224	5
	6	600644	S202M-K6	2CDS272001R0377		0.224	5
	8	600675	S202M-K8	2CDS272001R0407		0.224	5
	10	600699	S202M-K10	2CDS272001R0427		0.224	5
	13	659406	S202M-K13	2CDS272001R0447		0.230	5
	16	600712	S202M-K16	2CDS272001R0467		0.230	5
	20	600736	S202M-K20	2CDS272001R0487		0.230	5
	25	600767	S202M-K25	2CDS272001R0517		0.230	5
	32	600781	S202M-K32	2CDS272001R0537		0.240	5
	40	600804	S202M-K40	2CDS272001R0557		0.240	5
	50	600828	S202M-K50	2CDS272001R0577		0.240	5
	63	600842	S202M-K63	2CDS272001R0607		0.240	5

MCBs

S 200 series M-K characteristic



S 203 M



S 204 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	601016	S203M-K0.5	2CDS273001R0157		0.336	1
	1	601054	S203M-K1	2CDS273001R0217		0.336	1
	1.6	601085	S203M-K1.6	2CDS273001R0257		0.336	1
	2	601108	S203M-K2	2CDS273001R0277		0.336	1
	3	601122	S203M-K3	2CDS273001R0317		0.336	1
	4	601153	S203M-K4	2CDS273001R0337		0.336	1
	6	601177	S203M-K6	2CDS273001R0377		0.336	1
	8	601207	S203M-K8	2CDS273001R0407		0.336	1
	10	601221	S203M-K10	2CDS273001R0427		0.336	1
	13	659413	S203M-K13	2CDS273001R0447		0.345	1
	16	601245	S203M-K16	2CDS273001R0467		0.345	1
	20	601269	S203M-K20	2CDS273001R0487		0.345	1
	25	601290	S203M-K25	2CDS273001R0517		0.345	1
	32	601313	S203M-K32	2CDS273001R0537		0.360	1
	40	601337	S203M-K40	2CDS273001R0557		0.360	1
	50	601351	S203M-K50	2CDS273001R0577		0.360	1
	63	601375	S203M-K63	2CDS273001R0607		0.360	1
4	0.5	601757	S204M-K0.5	2CDS274001R0157		0.448	1
	1	601795	S204M-K1	2CDS274001R0217		0.448	1
	1.6	601825	S204M-K1.6	2CDS274001R0257		0.448	1
	2	601849	S204M-K2	2CDS274001R0277		0.448	1
	3	601863	S204M-K3	2CDS274001R0317		0.448	1
	4	601894	S204M-K4	2CDS274001R0337		0.448	1
	6	601917	S204M-K6	2CDS274001R0377		0.448	1
	8	601948	S204M-K8	2CDS274001R0407		0.448	1
	10	601962	S204M-K10	2CDS274001R0427		0.448	1
	13	659420	S204M-K13	2CDS274001R0447		0.460	1
	16	601986	S204M-K16	2CDS274001R0467		0.460	1
	20	602006	S204M-K20	2CDS274001R0487		0.460	1
	25	602020	S204M-K25	2CDS274001R0517		0.460	1
	32	602044	S204M-K32	2CDS274001R0537		0.480	1
	40	602068	S204M-K40	2CDS274001R0557		0.480	1
	50	602082	S204M-K50	2CDS274001R0577		0.480	1
	63	602105	S204M-K63	2CDS274001R0607		0.480	1

MCBs

S 200 series M-Z characteristic

S 200 M-Z characteristic

Function: protection and control of the electronic circuits against lower and long duration overloads and short-circuits.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=15 kA



S 201 M



S 202 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	599443	S201M-Z0.5	2CDS271001R0158		0.112	10
	1	599481	S201M-Z1	2CDS271001R0218		0.112	10
	1.6	599511	S201M-Z1.6	2CDS271001R0258		0.112	10
	2	599535	S201M-Z2	2CDS271001R0278		0.112	10
	3	599559	S201M-Z3	2CDS271001R0318		0.112	10
	4	599580	S201M-Z4	2CDS271001R0338		0.112	10
	6	599603	S201M-Z6	2CDS271001R0378		0.112	10
	8	599634	S201M-Z8	2CDS271001R0408		0.112	10
	10	599658	S201M-Z10	2CDS271001R0428		0.112	10
	16	599672	S201M-Z16	2CDS271001R0468		0.115	10
	20	599696	S201M-Z20	2CDS271001R0488		0.115	10
	25	599726	S201M-Z25	2CDS271001R0518		0.115	10
	32	599740	S201M-Z32	2CDS271001R0538		0.120	10
	40	599764	S201M-Z40	2CDS271001R0558		0.120	10
	50	599788	S201M-Z50	2CDS271001R0578		0.120	10
	63	599801	S201M-Z63	2CDS271001R0608		0.120	10
2	0.5	600491	S202M-Z0.5	2CDS272001R0158		0.224	5
	1	600538	S202M-Z1	2CDS272001R0218		0.224	5
	1.6	600569	S202M-Z1.6	2CDS272001R0258		0.224	5
	2	600583	S202M-Z2	2CDS272001R0278		0.224	5
	3	600606	S202M-Z3	2CDS272001R0318		0.224	5
	4	600637	S202M-Z4	2CDS272001R0338		0.224	5
	6	600651	S202M-Z6	2CDS272001R0378		0.224	5
	8	600682	S202M-Z8	2CDS272001R0408		0.224	5
	10	600705	S202M-Z10	2CDS272001R0428		0.224	5
	16	600729	S202M-Z16	2CDS272001R0468		0.230	5
	20	600743	S202M-Z20	2CDS272001R0488		0.230	5
	25	600774	S202M-Z25	2CDS272001R0518		0.230	5
	32	600798	S202M-Z32	2CDS272001R0538		0.240	5
	40	600811	S202M-Z40	2CDS272001R0558		0.240	5
	50	600835	S202-MZ50	2CDS272001R0578		0.240	5
	63	600859	S202M-Z63	2CDS272001R0608		0.240	5

MCBs

S 200 series M-Z characteristic



S 203 M



S 204 M

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	601023	S203M-Z0.5	2CDS273001R0158		0.336	1
	1	601061	S203M-Z1	2CDS273001R0218		0.336	1
	1.6	601092	S203M-Z1.6	2CDS273001R0258		0.336	1
	2	601115	S203M-Z2	2CDS273001R0278		0.336	1
	3	601139	S203M-Z3	2CDS273001R0318		0.336	1
	4	601160	S203M-Z4	2CDS273001R0338		0.336	1
	6	601184	S203M-Z6	2CDS273001R0378		0.336	1
	8	601214	S203M-Z8	2CDS273001R0408		0.336	1
	10	601238	S203M-Z10	2CDS273001R0428		0.336	1
	16	601252	S203M-Z16	2CDS273001R0468		0.345	1
	20	601276	S203M-Z20	2CDS273001R0488		0.345	1
	25	601306	S203M-Z25	2CDS273001R0518		0.345	1
	32	601320	S203M-Z32	2CDS273001R0538		0.360	1
	40	601344	S203M-Z40	2CDS273001R0558		0.360	1
	50	601368	S203M-Z50	2CDS273001R0578		0.360	1
	63	601382	S203M-Z63	2CDS273001R0608		0.360	1
4	0.5	601764	S204M-Z0.5	2CDS274001R0158		0.448	1
	1	601810	S204M-Z1	2CDS274001R0218		0.448	1
	1.6	601832	S204M-Z1.6	2CDS274001R0258		0.448	1
	2	601856	S204M-Z2	2CDS274001R0278		0.448	1
	3	601870	S204M-Z3	2CDS274001R0318		0.448	1
	4	601900	S204M-Z4	2CDS274001R0338		0.448	1
	6	601924	S204M-Z6	2CDS274001R0378		0.448	1
	8	601955	S204M-Z8	2CDS274001R0408		0.448	1
	10	601979	S204M-Z10	2CDS274001R0428		0.448	1
	16	601993	S204M-Z16	2CDS274001R0468		0.460	1
	20	659628	S204M-Z20	2CDS274001R0488		0.460	1
	25	602037	S204M-Z25	2CDS274001R0518		0.460	1
	32	602051	S204M-Z32	2CDS274001R0538		0.480	1
	40	602075	S204M-Z40	2CDS274001R0558		0.480	1
	50	602099	S204M-Z50	2CDS274001R0578		0.480	1
	63	602112	S204M-Z63	2CDS274001R0608		0.480	1

*1 U_{Bmax} 125 V ... with 2 poles connected in series

MCBs

S 200 series M UC B characteristic

Universal current range

S 200 M UC B characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Applications: Industrial.

Standard: IEC/EN 60898-2, IEC/EN 60947-2, UL1077, CSA 22.2 No. 235

(for DC applications, please note polarity of device)

Icu=10 kA



S 201 M UC



S 202 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	6	4430596	S201M-B6UC	2CDS271061R0065		0.117	10
	10	4430602	S201M-B10UC	2CDS271061R0105		0.117	10
	13	4430619	S201M-B13UC	2CDS271061R0135		0.120	10
	16	4430626	S201M-B16UC	2CDS271061R0165		0.120	10
	20	4430633	S201M-B20UC	2CDS271061R0205		0.120	10
	25	4430640	S201M-B25UC	2CDS271061R0255		0.120	10
	32	4430657	S201M-B32UC	2CDS271061R0325		0.125	10
	40	4430664	S201M-B40UC	2CDS271061R0405		0.125	10
	50	4430671	S201M-B50UC	2CDS271061R0505		0.125	10
	63	4430688	S201M-B63UC	2CDS271061R0635		0.125	10
2	6	4432811	S202M-B6UC	2CDS272061R0065		0.234	5
	10	4432828	S202M-B10UC	2CDS272061R0105		0.234	5
	13	4432835	S202M-B13UC	2CDS272061R0135		0.240	5
	16	4432842	S202M-B16UC	2CDS272061R0165		0.240	5
	20	4432859	S202M-B20UC	2CDS272061R0205		0.240	5
	25	4432866	S202M-B25UC	2CDS272061R0255		0.240	5
	32	4432873	S202M-B32UC	2CDS272061R0325		0.250	5
	40	4432880	S202M-B40UC	2CDS272061R0405		0.250	5
	50	4432897	S202M-B50UC	2CDS272061R0505		0.250	5
	63	4432903	S202M-B63UC	2CDS272061R0635		0.250	5

MCBs

S 200 series M UC B characteristic

Universal current range



S 203 M UC



S 204 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	6	4435034	S203M-B6UC	2CDS273061R0065		0.351	1
	10	4435041	S203M-B10UC	2CDS273061R0105		0.351	1
	13	4435058	S203M-B13UC	2CDS273061R0135		0.360	1
	16	4435065	S203M-B16UC	2CDS273061R0165		0.360	1
	20	4435072	S203M-B20UC	2CDS273061R0205		0.360	1
	25	4435089	S203M-B25UC	2CDS273061R0255		0.360	1
	32	4435096	S203M-B32UC	2CDS273061R0325		0.375	1
	40	4435102	S203M-B40UC	2CDS273061R0405		0.375	1
	50	4435119	S203M-B50UC	2CDS273061R0505		0.375	1
	63	4435126	S203M-B63UC	2CDS273061R0635		0.375	1
4	6	4437250	S204M-B6UC	2CDS274061R0065		0.468	1
	10	4437267	S204M-B10UC	2CDS274061R0105		0.468	1
	13	4437274	S204M-B13UC	2CDS274061R0135		0.480	1
	16	4437281	S204M-B16UC	2CDS274061R0165		0.480	1
	20	4437298	S204M-B20UC	2CDS274061R0205		0.480	1
	25	4437304	S204M-B25UC	2CDS274061R0255		0.480	1
	32	4437311	S204M-B32UC	2CDS274061R0325		0.500	1
	40	4437328	S204M-B40UC	2CDS274061R0405		0.500	1
	50	4437335	S204M-B50UC	2CDS274061R0505		0.500	1
	63	4437342	S204M-B63UC	2CDS274061R0635		0.500	1

MCBs

S 200 series M UC C characteristic

Universal current range



S 201 M UC



S 202 M UC

S 200 M UC C characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Applications: Industrial.

Standard: IEC/EN 60898-2, IEC/EN 60947-2, UL1077, CSA 22.2 No. 235

(for DC applications, please note polarity of device)

Icu=10 kA

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	4430695	S201M-C0.5UC	2CDS271061R0984		0.117	10
	1	4430701	S201M-C1UC	2CDS271061R0014		0.117	10
	1.6	4430718	S201M-C1.6UC	2CDS271061R0974		0.117	10
	2	4430725	S201M-C2UC	2CDS271061R0024		0.117	10
	3	4430732	S201M-C3UC	2CDS271061R0034		0.117	10
	4	4430749	S201M-C4UC	2CDS271061R0044		0.117	10
	6	4430756	S201M-C6UC	2CDS271061R0064		0.117	10
	8	4430763	S201M-C8UC	2CDS271061R0084		0.117	10
	10	4430770	S201M-C10UC	2CDS271061R0104		0.117	10
	13	4430787	S201M-C13UC	2CDS271061R0134		0.120	10
	16	4430794	S201M-C16UC	2CDS271061R0164		0.120	10
	20	4430800	S201M-C20UC	2CDS271061R0204		0.120	10
	25	4430817	S201M-C25UC	2CDS271061R0254		0.120	10
	32	4430824	S201M-C32UC	2CDS271061R0324		0.125	10
	40	4430831	S201M-C40UC	2CDS271061R0404		0.125	10
	50	4430848	S201M-C50UC	2CDS271061R0504		0.125	10
	63	4430855	S201M-C63UC	2CDS271061R0634		0.125	10
2	0.5	4432910	S202M-C0.5UC	2CDS272061R0984		0.234	5
	1	4432927	S202M-C1UC	2CDS272061R0014		0.234	5
	1.6	4432934	S202M-C1.6UC	2CDS272061R0974		0.234	5
	2	4432941	S202M-C2UC	2CDS272061R0024		0.234	5
	3	4432958	S202M-C3UC	2CDS272061R0034		0.234	5
	4	4432965	S202M-C4UC	2CDS272061R0044		0.234	5
	6	4432972	S202M-C6UC	2CDS272061R0064		0.234	5
	8	4432989	S202M-C8UC	2CDS272061R0084		0.234	5
	10	4432996	S202M-C10UC	2CDS272061R0104		0.234	5
	13	4433009	S202M-C13UC	2CDS272061R0134		0.240	5
	16	4433016	S202M-C16UC	2CDS272061R0164		0.240	5
	20	4433023	S202M-C20UC	2CDS272061R0204		0.240	5
	25	4433030	S202M-C25UC	2CDS272061R0254		0.240	5
	32	4433047	S202M-C32UC	2CDS272061R0324		0.250	5
	40	4433054	S202M-C40UC	2CDS272061R0404		0.250	5
	50	4433061	S202M-C50UC	2CDS272061R0504		0.250	5
	63	4433078	S202M-C63UC	2CDS272061R0634		0.250	5

MCBs

S 200 series M UC C characteristic

Universal current range



S 203 M UC



S 204 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	4435133	S203M-C0.5UC	2CDS273061R0984		0.351	1
	1	4435140	S203M-C1UC	2CDS273061R0014		0.351	1
	1.6	4435157	S203M-C1.6UC	2CDS273061R0974		0.351	1
	2	4435164	S203M-C2UC	2CDS273061R0024		0.351	1
	3	4435171	S203M-C3UC	2CDS273061R0034		0.351	1
	4	4435188	S203M-C4UC	2CDS273061R0044		0.351	1
	6	4435195	S203M-C6UC	2CDS273061R0064		0.351	1
	8	4435201	S203M-C8UC	2CDS273061R0084		0.351	1
	10	4435218	S203M-C10UC	2CDS273061R0104		0.351	1
	13	4435225	S203M-C13UC	2CDS273061R0134		0.360	1
	16	4435232	S203M-C16UC	2CDS273061R0164		0.360	1
	20	4435249	S203M-C20UC	2CDS273061R0204		0.360	1
	25	4435256	S203M-C25UC	2CDS273061R0254		0.360	1
	32	4435263	S203M-C32UC	2CDS273061R0324		0.375	1
	40	4435270	S203M-C40UC	2CDS273061R0404		0.375	1
	50	4435287	S203M-C50UC	2CDS273061R0504		0.375	1
	63	4435294	S203M-C63UC	2CDS273061R0634		0.375	1
4	0.5	4437359	S204M-C0.5UC	2CDS274061R0984		0.468	1
	1	4437366	S204M-C1UC	2CDS274061R0014		0.468	1
	1.6	4437373	S204M-C1.6UC	2CDS274061R0974		0.468	1
	2	4437380	S204M-C2UC	2CDS274061R0024		0.468	1
	3	4437397	S204M-C3UC	2CDS274061R0034		0.468	1
	4	4437403	S204M-C4UC	2CDS274061R0044		0.468	1
	6	4437410	S204M-C6UC	2CDS274061R0064		0.468	1
	8	4437427	S204M-C8UC	2CDS274061R0084		0.468	1
	10	4437434	S204M-C10UC	2CDS274061R0104		0.468	1
	13	4437441	S204M-C13UC	2CDS274061R0134		0.480	1
	16	4437458	S204M-C16UC	2CDS274061R0164		0.480	1
	20	4437465	S204M-C20UC	2CDS274061R0204		0.480	1
	25	4437472	S204M-C25UC	2CDS274061R0254		0.480	1
	32	4437489	S204M-C32UC	2CDS274061R0324		0.500	1
	40	4437496	S204M-C40UC	2CDS274061R0404		0.500	1
	50	4437502	S204M-C50UC	2CDS274061R0504		0.500	1
	63	4437519	S204M-C63UC	2CDS274061R0634		0.500	1

MCBs

S 200 series M UC – Universal current range K characteristic

S 200 M UC K characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Applications: Industrial.

Standard: IEC/EN 60947-2, UL1077, CSA 22.2 No. 235

(for DC applications, please note polarity of device)

Icu=10 kA



S 201 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.2	4430862	S201M-K0.2UC	2CDS271061R0087		0.117	10
	0.3	4430879	S201M-K0.3UC	2CDS271061R0117		0.117	10
	0.5	4430886	S201M-K0.5UC	2CDS271061R0157		0.117	10
	0.75	4430893	S201M-K0.75UC	2CDS271061R0187		0.117	10
	1	4430909	S201M-K1UC	2CDS271061R0217		0.117	10
	1.6	4430916	S201M-K1.6UC	2CDS271061R0257		0.117	10
	2	4430923	S201M-K2UC	2CDS271061R0277		0.117	10
	3	4430930	S201M-K3UC	2CDS271061R0317		0.117	10
	4	4430947	S201M-K4UC	2CDS271061R0337		0.117	10
	5	4430954	S201M-K5UC	2CDS271061R0357		0.117	10
	6	4430961	S201M-K6UC	2CDS271061R0377		0.117	10
	8	4430978	S201M-K8UC	2CDS271061R0407		0.117	10
	10	4430985	S201M-K10UC	2CDS271061R0427		0.117	10
	13	4430992	S201M-K13UC	2CDS271061R0447		0.120	10
	15	4431005	S201M-K15UC	2CDS271061R0457		0.120	10
	16	4431012	S201M-K16UC	2CDS271061R0467		0.120	10
	20	4431029	S201M-K20UC	2CDS271061R0487		0.120	10
	25	4431036	S201M-K25UC	2CDS271061R0517		0.120	10
	30	4431043	S201M-K30UC	2CDS271061R0527		0.125	10
	32	4431050	S201M-K32UC	2CDS271061R0537		0.125	10
	35	4431067	S201M-K35UC	2CDS271061R0547		0.125	10
	40	4431074	S201M-K40UC	2CDS271061R0557		0.125	10
	50	4431081	S201M-K50UC	2CDS271061R0577		0.125	10
	60	4431098	S201M-K60UC	2CDS271061R0587		0.125	10
	63	4431104	S201M-K63UC	2CDS271061R0607		0.125	10

MCBs

S 200 series M UC – Universal current range K characteristic



S 202 M UC



S 203 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
2	0.2	4433085	S202M-K0.2UC	2CDS272061R0087		0.234	5
	0.3	4433092	S202M-K0.3UC	2CDS272061R0117		0.234	5
	0.5	4433108	S202M-K0.5UC	2CDS272061R0157		0.234	5
	0.75	4433115	S202M-K0.75UC	2CDS272061R0187		0.234	5
	1	4433122	S202M-K1UC	2CDS272061R0217		0.234	5
	1.6	4433139	S202M-K1.6UC	2CDS272061R0257		0.234	5
	2	4433146	S202M-K2UC	2CDS272061R0277		0.234	5
	3	4433153	S202M-K3UC	2CDS272061R0317		0.234	5
	4	4433160	S202M-K4UC	2CDS272061R0337		0.234	5
	5	4433177	S202M-K5UC	2CDS272061R0357		0.234	5
	6	4433184	S202M-K6UC	2CDS272061R0377		0.234	5
	8	4433191	S202M-K8UC	2CDS272061R0407		0.234	5
	10	4433207	S202M-K10UC	2CDS272061R0427		0.234	5
	13	4433214	S202M-K13UC	2CDS272061R0447		0.240	5
	15	4433221	S202M-K15UC	2CDS272061R0457		0.240	5
	16	4433238	S202M-K16UC	2CDS272061R0467		0.240	5
	20	4433245	S202M-K20UC	2CDS272061R0487		0.240	5
	25	4433252	S202M-K25UC	2CDS272061R0517		0.240	5
	30	4433269	S202M-K30UC	2CDS272061R0527		0.250	5
	32	4433276	S202M-K32UC	2CDS272061R0537		0.250	5
	35	4433283	S202M-K35UC	2CDS272061R0547		0.250	5
3	40	4433290	S202M-K40UC	2CDS272061R0557		0.250	5
	50	4433306	S202M-K50UC	2CDS272061R0577		0.250	5
	60	4433313	S202M-K60UC	2CDS272061R0587		0.250	5
	63	4433320	S202M-K63UC	2CDS272061R0607		0.250	5
	0.2	4435300	S203M-K0.2UC	2CDS273061R0087		0.351	1
	0.3	4435317	S203M-K0.3UC	2CDS273061R0117		0.351	1
	0.5	4435324	S203M-K0.5UC	2CDS273061R0157		0.351	1
	0.75	4435331	S203M-K0.75UC	2CDS273061R0187		0.351	1
	1	4435348	S203M-K1UC	2CDS273061R0217		0.351	1
	1.6	4435355	S203M-K1.6UC	2CDS273061R0257		0.351	1
	2	4435362	S203M-K2UC	2CDS273061R0277		0.351	1
	3	4435379	S203M-K3UC	2CDS273061R0317		0.351	1
	4	4435386	S203M-K4UC	2CDS273061R0337		0.351	1
	5	4435393	S203M-K5UC	2CDS273061R0357		0.351	1
	6	4435409	S203M-K6UC	2CDS273061R0377		0.351	1
	8	4435416	S203M-K8UC	2CDS273061R0407		0.351	1
	10	4435423	S203M-K10UC	2CDS273061R0427		0.351	1
	13	4435430	S203M-K13UC	2CDS273061R0447		0.360	1
	15	4435447	S203M-K15UC	2CDS273061R0457		0.360	1
	16	4435454	S203M-K16UC	2CDS273061R0467		0.360	1
	20	4435461	S203M-K20UC	2CDS273061R0487		0.360	1
	25	4435478	S203M-K25UC	2CDS273061R0517		0.360	1
	30	4435485	S203M-K30UC	2CDS273061R0527		0.375	1
	32	4435492	S203M-K32UC	2CDS273061R0537		0.375	1
	35	4435508	S203M-K35UC	2CDS273061R0547		0.375	1
	40	4435515	S203M-K40UC	2CDS273061R0557		0.375	1
	50	4435522	S203M-K50UC	2CDS273061R0577		0.375	1
	60	4435539	S203M-K60UC	2CDS273061R0587		0.375	1
	63	4435546	S203M-K63UC	2CDS273061R0607		0.375	1

MCBs

S 200 series M UC – Universal current range K characteristic



S 204 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	0.2	4437526	S204M-K0.2UC	2CDS274061R0087		0.468	1
	0.3	4437533	S204M-K0.3UC	2CDS274061R0117		0.468	1
	0.5	4437540	S204M-K0.5UC	2CDS274061R0157		0.468	1
	0.75	4437557	S204M-K0.75UC	2CDS274061R0187		0.468	1
	1	4437564	S204M-K1UC	2CDS274061R0217		0.468	1
	1.6	4437571	S204M-K1.6UC	2CDS274061R0257		0.468	1
	2	4437588	S204M-K2UC	2CDS274061R0277		0.468	1
	3	4437595	S204M-K3UC	2CDS274061R0317		0.468	1
	4	4437601	S204M-K4UC	2CDS274061R0337		0.468	1
	5	4437618	S204M-K5UC	2CDS274061R0357		0.468	1
	6	4437625	S204M-K6UC	2CDS274061R0377		0.468	1
	8	4437632	S204M-K8UC	2CDS274061R0407		0.468	1
	10	4437649	S204M-K10UC	2CDS274061R0427		0.468	1
	13	4437656	S204M-K13UC	2CDS274061R0447		0.480	1
	15	4437663	S204M-K15UC	2CDS274061R0457		0.480	1
	16	4437670	S204M-K16UC	2CDS274061R0467		0.480	1
	20	4437687	S204M-K20UC	2CDS274061R0487		0.480	1
	25	4437694	S204M-K25UC	2CDS274061R0517		0.480	1
	30	4437700	S204M-K30UC	2CDS274061R0527		0.500	1
	32	4437717	S204M-K32UC	2CDS274061R0537		0.500	1
	35	4437724	S204M-K35UC	2CDS274061R0547		0.500	1
	40	4437731	S204M-K40UC	2CDS274061R0557		0.500	1
	50	4437748	S204M-K50UC	2CDS274061R0577		0.500	1
	60	4437755	S204M-K60UC	2CDS274061R0587		0.500	1
	63	4437762	S204M-K63UC	2CDS274061R0607		0.500	1

MCBs

S 200 series M UC – Universal current range Z characteristic

S 200 M UC Z characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Applications: Industrial.

Standard: IEC/EN 60947-2, UL1077, CSA 22.2 No. 235

(for DC applications, please note polarity of device)

Icu=10 kA



S 201 M UC



S 202 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	4431111	S201M-Z0.5UC	2CDS271061R0158		0.117	1
	1	4431128	S201M-Z1UC	2CDS271061R0218		0.117	1
	1.6	4431135	S201M-Z1.6UC	2CDS271061R0258		0.117	1
	2	4431142	S201M-Z2UC	2CDS271061R0278		0.117	1
	3	4431159	S201M-Z3UC	2CDS271061R0318		0.117	1
	4	4431166	S201M-Z4UC	2CDS271061R0338		0.117	1
	5	4431173	S201M-Z5UC	2CDS271061R0358		0.117	1
	6	4431180	S201M-Z6UC	2CDS271061R0378		0.117	1
	8	4431197	S201M-Z8UC	2CDS271061R0408		0.117	1
	10	4431203	S201M-Z10UC	2CDS271061R0428		0.117	1
	15	4431227	S201M-Z15UC	2CDS271061R0458		0.120	1
	16	4431234	S201M-Z16UC	2CDS271061R0468		0.120	1
	20	4431241	S201M-Z20UC	2CDS271061R0488		0.120	1
	25	4431258	S201M-Z25UC	2CDS271061R0518		0.120	1
	30	4431265	S201M-Z30UC	2CDS271061R0528		0.125	1
	32	4431272	S201M-Z32UC	2CDS271061R0538		0.125	1
	35	4431289	S201M-Z35UC	2CDS271061R0548		0.125	1
	40	4431296	S201M-Z40UC	2CDS271061R0558		0.125	1
	50	4431302	S201M-Z50UC	2CDS271061R0578		0.125	1
	60	4431319	S201M-Z60UC	2CDS271061R0588		0.125	1
	63	4431326	S201M-Z63UC	2CDS271061R0608		0.125	1
2	0.5	4433337	S202M-Z0.5UC	2CDS272061R0158		0.234	5
	1	4433344	S202M-Z1UC	2CDS272061R0218		0.234	5
	1.6	4433351	S202M-Z1.6UC	2CDS272061R0258		0.234	5
	2	4433368	S202M-Z2UC	2CDS272061R0278		0.234	5
	3	4433375	S202M-Z3UC	2CDS272061R0318		0.234	5
	4	4433382	S202M-Z4UC	2CDS272061R0338		0.234	5
	5	4433399	S202M-Z5UC	2CDS272061R0358		0.234	5
	6	4433405	S202M-Z6UC	2CDS272061R0378		0.234	5
	8	4433412	S202M-Z8UC	2CDS272061R0408		0.234	5
	10	4433429	S202M-Z10UC	2CDS272061R0428		0.234	5
	15	4433443	S202M-Z15UC	2CDS272061R0458		0.240	5
	16	4433450	S202M-Z16UC	2CDS272061R0468		0.240	5
	20	4433467	S202M-Z20UC	2CDS272061R0488		0.240	5
	25	4433474	S202M-Z25UC	2CDS272061R0518		0.240	5
	30	4433481	S202M-Z30UC	2CDS272061R0528		0.250	5
	32	4433498	S202M-Z32UC	2CDS272061R0538		0.250	5
	35	4433504	S202M-Z35UC	2CDS272061R0548		0.250	5
	40	4433511	S202M-Z40UC	2CDS272061R0558		0.250	5
	50	4433528	S202M-Z50UC	2CDS272061R0578		0.250	5
	60	4433535	S202M-Z60UC	2CDS272061R0588		0.250	5
	63	4433542	S202M-Z63UC	2CDS272061R0608		0.250	5

MCBs

S 200 series M UC – Universal current range Z characteristic



S 203 M UC



S 204 M UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.5	4435553	S203M-Z0.5UC	2CDS273061R0158		0.351	1
	1	4435560	S203M-Z1UC	2CDS273061R0218		0.351	1
	1.6	4435577	S203M-Z1.6UC	2CDS273061R0258		0.351	1
	2	4435584	S203M-Z2UC	2CDS273061R0278		0.351	1
	3	4435591	S203M-Z3UC	2CDS273061R0318		0.351	1
	4	4435607	S203M-Z4UC	2CDS273061R0338		0.351	1
	5	4435614	S203M-Z5UC	2CDS273061R0358		0.351	1
	6	4435621	S203M-Z6UC	2CDS273061R0378		0.351	1
	8	4435638	S203M-Z8UC	2CDS273061R0408		0.351	1
	10	4435645	S203M-Z10UC	2CDS273061R0428		0.351	1
	15	4435669	S203M-Z15UC	2CDS273061R0458		0.360	1
	16	4435676	S203M-Z16UC	2CDS273061R0468		0.360	1
	20	4435683	S203M-Z20UC	2CDS273061R0488		0.360	1
	25	4435690	S203M-Z25UC	2CDS273061R0518		0.360	1
	30	4435706	S203M-Z30UC	2CDS273061R0528		0.375	1
	32	4435713	S203M-Z32UC	2CDS273061R0538		0.375	1
	35	4435720	S203M-Z35UC	2CDS273061R0548		0.375	1
	40	4435737	S203M-Z40UC	2CDS273061R0558		0.375	1
	50	4435744	S203M-Z50UC	2CDS273061R0578		0.375	1
	60	4435751	S203M-Z60UC	2CDS273061R0588		0.375	1
	63	4435768	S203M-Z63UC	2CDS273061R0608		0.375	1
4	0.5	4437779	S204M-Z0.5UC	2CDS274061R0158		0.468	1
	1	4437786	S204M-Z1UC	2CDS274061R0218		0.468	1
	1.6	4437793	S204M-Z1.6UC	2CDS274061R0258		0.468	1
	2	4437809	S204M-Z2UC	2CDS274061R0278		0.468	1
	3	4437816	S204M-Z3UC	2CDS274061R0318		0.468	1
	4	4437823	S204M-Z4UC	2CDS274061R0338		0.468	1
	5	4437830	S204M-Z5UC	2CDS274061R0358		0.468	1
	6	4437847	S204M-Z6UC	2CDS274061R0378		0.468	1
	8	4437854	S204M-Z8UC	2CDS274061R0408		0.468	1
	10	4437861	S204M-Z10UC	2CDS274061R0428		0.468	1
	15	4437885	S204M-Z15UC	2CDS274061R0458		0.480	1
	16	4437892	S204M-Z16UC	2CDS274061R0468		0.480	1
	20	4437908	S204M-Z20UC	2CDS274061R0488		0.480	1
	25	4437915	S204M-Z25UC	2CDS274061R0518		0.480	1
	30	4437922	S204M-Z30UC	2CDS274061R0528		0.500	1
	32	4437939	S204M-Z32UC	2CDS274061R0538		0.500	1
	35	4437946	S204M-Z35UC	2CDS274061R0548		0.500	1
	40	4437953	S204M-Z40UC	2CDS274061R0558		0.500	1
	50	4437960	S204M-Z50UC	2CDS274061R0578		0.500	1
	60	4437977	S204M-Z60UC	2CDS274061R0588		0.500	1
	63	4437984	S204M-Z63UC	2CDS274061R0608		0.500	1

MCBs

S 300 series P-B characteristic

S 300 P-B characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.

Applications: commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icu=25 kA; 100 kA (≤ 6 A)

Icn=25 kA (≤ 25 A); 20 kA (32-40 A); 15 kA (> 40 A);



S 301 P



S 302 P



S 303 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	6	9080583	S301P-B6	2CDS381001R0065		0.120	10
	8	9086011	S301P-B8	2CDS381001R0085		0.120	10
	10	9080521	S301P-B10	2CDS381001R0105		0.120	10
	13	9080484	S301P-B13	2CDS381001R0135		0.123	10
	16	9080439	S301P-B16	2CDS381001R0165		0.123	10
	20	9080392	S301P-B20	2CDS381001R0205		0.123	10
	25	9080347	S301P-B25	2CDS381001R0255		0.123	10
	32	9080255	S301P-B32	2CDS381001R0325		0.128	10
	40	9080187	S301P-B40	2CDS381001R0405		0.128	10
	50	9080064	S301P-B50	2CDS381001R0505		0.128	10
	63	9079938	S301P-B63	2CDS381001R0635		0.128	10
2	6	9078993	S302P-B6	2CDS382001R0065		0.240	5
	8	9086059	S302P-B8	2CDS382001R0085		0.240	5
	10	9078931	S302P-B10	2CDS382001R0105		0.240	5
	13	9078894	S302P-B13	2CDS382001R0135		0.246	5
	16	9078849	S302P-B16	2CDS382001R0165		0.246	5
	20	9078801	S302P-B20	2CDS382001R0205		0.246	5
	25	9078757	S302P-B25	2CDS382001R0255		0.246	5
	32	9078665	S302P-B32	2CDS382001R0325		0.256	5
	40	9078597	S302P-B40	2CDS382001R0405		0.256	5
	50	9078474	S302P-B50	2CDS382001R0505		0.256	5
	63	9078344	S302P-B63	2CDS382001R0635		0.256	5
3	6	9078191	S303P-B6	2CDS383001R0065		0.360	1
	8	9086073	S303P-B8	2CDS383001R0085		0.360	1
	10	9078139	S303P-B10	2CDS383001R0105		0.360	1
	13	9078092	S303P-B13	2CDS383001R0135		0.369	1
	16	9078047	S303P-B16	2CDS383001R0165		0.369	1
	20	9078009	S303P-B20	2CDS383001R0205		0.369	1
	25	9077958	S303P-B25	2CDS383001R0255		0.369	1
	32	9077866	S303P-B32	2CDS383001R0325		0.384	1
	40	9077798	S303P-B40	2CDS383001R0405		0.384	1
	50	9077675	S303P-B50	2CDS383001R0505		0.384	1
	63	9077545	S303P-B63	2CDS383001R0635		0.384	1

MCBs

S 300 series P-B characteristic



S 304 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	6	9076593	S304P-B6	2CDS384001R0065		0.480	1
	8	9086110	S304P-B8	2CDS384001R0085		0.480	1
	10	9076531	S304P-B10	2CDS384001R0105		0.480	1
	13	9076494	S304P-B13	2CDS384001R0135		0.492	1
	16	9076449	S304P-B16	2CDS384001R0165		0.492	1
	20	9135559	S304P-B20	2CDS384001R0205		0.492	1
	25	9076357	S304P-B25	2CDS384001R0255		0.492	1
	32	9076265	S304P-B32	2CDS384001R0325		0.512	1
	40	9076197	S304P-B40	2CDS384001R0405		0.512	1
	50	9076074	S304P-B50	2CDS384001R0505		0.512	1
	63	9075947	S304P-B63	2CDS384001R0635		0.512	1

With disconnecting neutral NA



S 301 P NA

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+NA	6	9079785	S301P-B6NA	2CDS381103R0065		0.233	5
	8	9086035	S301P-B8NA	2CDS381103R0085		0.233	5
	10	9079730	S301P-B10NA	2CDS381103R0105		0.233	5
	13	9079693	S301P-B13NA	2CDS381103R0135		0.236	5
	16	9079648	S301P-B16NA	2CDS381103R0165		0.236	5
	20	9079600	S301P-B20NA	2CDS381103R0205		0.236	5
	25	9079556	S301P-B25NA	2CDS381103R0255		0.241	5
	32	9079464	S301P-B32NA	2CDS381103R0325		0.246	5
	40	9079396	S301P-B40NA	2CDS381103R0405		0.246	5
	50	9079273	S301P-B50NA	2CDS381103R0505		0.246	5
	63	9079143	S301P-B63NA	2CDS381103R0635		0.246	5
3+NA	6	9077392	S303P-B6NA	2CDS383103R0065		0.473	1
	8	9086097	S303P-B8NA	2CDS383103R0085		0.473	1
	10	9077330	S303P-B10NA	2CDS383103R0105		0.473	1
	13	9077293	S303P-B13NA	2CDS383103R0135		0.482	1
	16	9077248	S303P-B16NA	2CDS383103R0165		0.482	1
	20	9135641	S303P-B20NA	2CDS383103R0205		0.482	1
	25	9077156	S303P-B25NA	2CDS383103R0255		0.487	1
	32	9077064	S303P-B32NA	2CDS383103R0325		0.502	1
	40	9076999	S303P-B40NA	2CDS383103R0405		0.502	1
	50	9076876	S303P-B50NA	2CDS383103R0505		0.502	1
	63	9076746	S303P-B63NA	2CDS383103R0635		0.502	1



S 303 P NA

MCBs

S 300 series P-C characteristic

S 300 P-C characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.

Applications: commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icu=25 kA; 100 kA (≤ 6 A)

Icn=25 kA (≤ 25 A); 20 kA (32-40 A); 15 kA (> 40 A);



S 301 P



S 302 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0,5	9079891	S301P-C0,5	2CDS381001R0984		0.120	10
	1	9080675	S301P-C1	2CDS381001R0014		0.120	10
	1,6	9079914	S301P-C1,6	2CDS381001R0974		0.120	10
	2	9080651	S301P-C2	2CDS381001R0024		0.120	10
	3	9080637	S301P-C3	2CDS381001R0034		0.120	10
	4	9080613	S301P-C4	2CDS381001R0044		0.120	10
	6	9080590	S301P-C6	2CDS381001R0064		0.120	10
	8	9080569	S301P-C8	2CDS381001R0084		0.120	10
	10	9080538	S301P-C10	2CDS381001R0104		0.120	10
	13	9080491	S301P-C13	2CDS381001R0134		0.123	10
	16	9080446	S301P-C16	2CDS381001R0164		0.123	10
	20	9080408	S301P-C20	2CDS381001R0204		0.123	10
	25	9080354	S301P-C25	2CDS381001R0254		0.123	10
	32	9080262	S301P-C32	2CDS381001R0324		0.128	10
	40	9080194	S301P-C40	2CDS381001R0404		0.128	10
	50	9080071	S301P-C50	2CDS381001R0504		0.128	10
	63	9079945	S301P-C63	2CDS381001R0634		0.128	10
2	0,5	9078306	S302P-C0,5	2CDS382001R0984		0.240	5
	1	9079082	S302P-C1	2CDS382001R0014		0.240	5
	1,6	9078320	S302P-C1,6	2CDS382001R0974		0.240	5
	2	9079068	S302P-C2	2CDS382001R0024		0.240	5
	3	9079044	S302P-C3	2CDS382001R0034		0.240	5
	4	9079020	S302P-C4	2CDS382001R0044		0.240	5
	6	9079006	S302P-C6	2CDS382001R0064		0.240	5
	8	9078979	S302P-C8	2CDS382001R0084		0.240	5
	10	9078948	S302P-C10	2CDS382001R0104		0.240	5
	13	9078900	S302P-C13	2CDS382001R0134		0.246	5
	16	9078856	S302P-C16	2CDS382001R0164		0.246	5
	20	9078818	S302P-C20	2CDS382001R0204		0.246	5
	25	9078764	S302P-C25	2CDS382001R0254		0.246	5
	32	9078672	S302P-C32	2CDS382001R0324		0.256	5
	40	9078603	S302P-C40	2CDS382001R0404		0.256	5
	50	9078481	S302P-C50	2CDS382001R0504		0.256	5
	63	9078351	S302P-C63	2CDS382001R0634		0.256	5

MCBs

S 300 series P-C characteristic



S 303 P



S 304 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0,5	9077507	S303P-C0,5	2CDS383001R0984		0.360	1
	1	9078283	S303P-C1	2CDS383001R0014		0.360	1
	1,6	9077521	S303P-C1,6	2CDS383001R0974		0.360	1
	2	9078269	S303P-C2	2CDS383001R0024		0.360	1
	3	9078245	S303P-C3	2CDS383001R0034		0.360	1
	4	9078221	S303P-C4	2CDS383001R0044		0.360	1
	6	9078207	S303P-C6	2CDS383001R0064		0.360	1
	8	9078177	S303P-C8	2CDS383001R0084		0.360	1
	10	9078146	S303P-C10	2CDS383001R0104		0.360	1
	13	9078108	S303P-C13	2CDS383001R0134		0.369	1
	16	9078054	S303P-C16	2CDS383001R0164		0.369	1
	20	9078016	S303P-C20	2CDS383001R0204		0.369	1
	25	9077965	S303P-C25	2CDS383001R0254		0.369	1
	32	9077873	S303P-C32	2CDS383001R0324		0.384	1
	40	9077804	S303P-C40	2CDS383001R0404		0.384	1
	50	9077682	S303P-C50	2CDS383001R0504		0.384	1
	63	9077552	S303P-C63	2CDS383001R0634		0.384	1
4	0,5	9135511	S304P-C0,5	2CDS384001R0984		0.480	1
	1	9076685	S304P-C1	2CDS384001R0014		0.480	1
	1,6	9075923	S304P-C1,6	2CDS384001R0974		0.480	1
	2	9076661	S304P-C2	2CDS384001R0024		0.480	1
	3	9076647	S304P-C3	2CDS384001R0034		0.480	1
	4	9076623	S304P-C4	2CDS384001R0044		0.480	1
	6	9135573	S304P-C6	2CDS384001R0064		0.480	1
	8	9076579	S304P-C8	2CDS384001R0084		0.480	1
	10	9076548	S304P-C10	2CDS384001R0104		0.480	1
	13	9135566	S304P-C13	2CDS384001R0134		0.492	1
	16	9076456	S304P-C16	2CDS384001R0164		0.492	1
	20	9076418	S304P-C20	2CDS384001R0204		0.492	1
	25	9076364	S304P-C25	2CDS384001R0254		0.492	1
	32	9076272	S304P-C32	2CDS384001R0324		0.512	1
	40	9135689	S304P-C40	2CDS384001R0404		0.512	1
	50	9076081	S304P-C50	2CDS384001R0504		0.512	1
	63	9075954	S304P-C63	2CDS384001R0634		0.512	1

MCBs

S 300 series P-D characteristic

S 300 P-D characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.

Applications: commercial and industrial.

Standard: IEC/EN 60898-1, IEC/EN 60947-2

Icu=25 kA; 100 kA (≤ 6 A)

Icn=25 kA (≤ 25 A); 20 kA (32-40 A); 15 kA (> 40 A);



S 301 P



S 302 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0,5	9079907	S301P-D0,5	2CDS381001R0981		0.120	10
	1	9080682	S301P-D1	2CDS381001R0011		0.120	10
	1,6	9079921	S301P-D1,6	2CDS381001R0971		0.120	10
	2	9080668	S301P-D2	2CDS381001R0021		0.120	10
	3	9080644	S301P-D3	2CDS381001R0031		0.120	10
	4	9080620	S301P-D4	2CDS381001R0041		0.120	10
	6	9080606	S301P-D6	2CDS381001R0061		0.120	10
	8	9080576	S301P-D8	2CDS381001R0081		0.120	10
	10	9080545	S301P-D10	2CDS381001R0101		0.120	10
	13	9080507	S301P-D13	2CDS381001R0131		0.123	10
	16	9080453	S301P-D16	2CDS381001R0161		0.123	10
	20	9080415	S301P-D20	2CDS381001R0201		0.123	10
	25	9080361	S301P-D25	2CDS381001R0251		0.123	10
	32	9080279	S301P-D32	2CDS381001R0321		0.128	10
	40	9080200	S301P-D40	2CDS381001R0401		0.128	10
	50	9080088	S301P-D50	2CDS381001R0501		0.128	10
	63	9079952	S301P-D63	2CDS381001R0631		0.128	10
2	0,5	9078313	S302P-D0,5	2CDS382001R0981		0.240	5
	1	9079099	S302P-D1	2CDS382001R0011		0.240	5
	1,6	9078337	S302P-D1,6	2CDS382001R0971		0.240	5
	2	9079075	S302P-D2	2CDS382001R0021		0.240	5
	3	9079051	S302P-D3	2CDS382001R0031		0.240	5
	4	9079037	S302P-D4	2CDS382001R0041		0.240	5
	6	9079013	S302P-D6	2CDS382001R0061		0.240	5
	8	9078986	S302P-D8	2CDS382001R0081		0.240	5
	10	9078955	S302P-D10	2CDS382001R0101		0.240	5
	13	9078917	S302P-D13	2CDS382001R0131		0.246	5
	16	9078863	S302P-D16	2CDS382001R0161		0.246	5
	20	9078825	S302P-D20	2CDS382001R0201		0.246	5
	25	9078771	S302P-D25	2CDS382001R0251		0.246	5
	32	9078689	S302P-D32	2CDS382001R0321		0.256	5
	40	9078610	S302P-D40	2CDS382001R0401		0.256	5
	50	9078498	S302P-D50	2CDS382001R0501		0.256	5
	63	9078368	S302P-D63	2CDS382001R0631		0.256	5

MCBs

S 300 series P-D characteristic



S 303 P



S 304 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0,5	9077514	S303P-D0,5	2CDS383001R0981		0.360	1
	1	9078290	S303P-D1	2CDS383001R0011		0.360	1
	1,6	9077538	S303P-D1,6	2CDS383001R0971		0.360	1
	2	9078276	S303P-D2	2CDS383001R0021		0.360	1
	3	9078252	S303P-D3	2CDS383001R0031		0.360	1
	4	9078238	S303P-D4	2CDS383001R0041		0.360	1
	6	9078214	S303P-D6	2CDS383001R0061		0.360	1
	8	9078184	S303P-D8	2CDS383001R0081		0.360	1
	10	9078153	S303P-D10	2CDS383001R0101		0.360	1
	13	9078115	S303P-D13	2CDS383001R0131		0.369	1
	16	9078061	S303P-D16	2CDS383001R0161		0.369	1
	20	9078023	S303P-D20	2CDS383001R0201		0.369	1
	25	9077972	S303P-D25	2CDS383001R0251		0.369	1
	32	9077880	S303P-D32	2CDS383001R0321		0.384	1
	40	9077811	S303P-D40	2CDS383001R0401		0.384	1
	50	9077699	S303P-D50	2CDS383001R0501		0.384	1
	63	9077569	S303P-D63	2CDS383001R0631		0.384	1
4	0,5	9075916	S304P-D0,5	2CDS384001R0981		0.480	1
	1	9076692	S304P-D1	2CDS384001R0011		0.480	1
	1,6	9075930	S304P-D1,6	2CDS384001R0971		0.480	1
	2	9076678	S304P-D2	2CDS384001R0021		0.480	1
	3	9076654	S304P-D3	2CDS384001R0031		0.480	1
	4	9076630	S304P-D4	2CDS384001R0041		0.480	1
	6	9076616	S304P-D6	2CDS384001R0061		0.480	1
	8	9076586	S304P-D8	2CDS384001R0081		0.480	1
	10	9076555	S304P-D10	2CDS384001R0101		0.480	1
	13	9076517	S304P-D13	2CDS384001R0131		0.492	1
	16	9076463	S304P-D16	2CDS384001R0161		0.492	1
	20	9076425	S304P-D20	2CDS384001R0201		0.492	1
	25	9076371	S304P-D25	2CDS384001R0251		0.492	1
	32	9076289	S304P-D32	2CDS384001R0321		0.512	1
	40	9076210	S304P-D40	2CDS384001R0401		0.512	1
	50	9076098	S304P-D50	2CDS384001R0501		0.512	1
	63	9075961	S304P-D63	2CDS384001R0631		0.512	1

MCBs

S 300 series P-K characteristic

S 300 P-K (power) characteristic

Function: protection and control of the circuits like motors, transformers and auxiliary circuits, against overloads and short-circuits.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=25 kA; 100 kA (≤ 6 A)



S 301 P

Number of poles	Rated current I_n A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0,2	9080552	S301P-K0,2	2CDS381001R0087		0.120	10
	0,3	9080514	S301P-K0,3	2CDS381001R0117		0.120	10
	0,5	9080477	S301P-K0,5	2CDS381001R0157		0.120	10
	0,75	9080422	S301P-K0,75	2CDS381001R0187		0.120	10
	1	9080385	S301P-K1	2CDS381001R0217		0.120	10
	1,6	9080330	S301P-K1,6	2CDS381001R0257		0.120	10
	2	9080316	S301P-K2	2CDS381001R0277		0.120	10
	3	9080293	S301P-K3	2CDS381001R0317		0.120	10
	4	9080248	S301P-K4	2CDS381001R0337		0.120	10
	6	9080224	S301P-K6	2CDS381001R0377		0.120	10
	8	9080170	S301P-K8	2CDS381001R0407		0.120	10
	10	9080156	S301P-K10	2CDS381001R0427		0.120	10
	13	9080132	S301P-K13	2CDS381001R0447		0.123	10
	16	9080125	S301P-K16	2CDS381001R0467		0.123	10
	20	9080101	S301P-K20	2CDS381001R0487		0.123	10
	25	9080057	S301P-K25	2CDS381001R0517		0.123	10
	32	9080033	S301P-K32	2CDS381001R0537		0.128	10
	40	9080019	S301P-K40	2CDS381001R0557		0.128	10
	50	9079990	S301P-K50	2CDS381001R0577		0.128	10
	63	9079976	S301P-K63	2CDS381001R0607		0.128	10

MCBs

S 300 series P-K characteristic



S 302 P



S 303 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
2	0,2	9078962	S302P-K0,2	2CDS382001R0087		0.240	5
	0,3	9078924	S302P-K0,3	2CDS382001R0117		0.240	5
	0,5	9078887	S302P-K0,5	2CDS382001R0157		0.240	5
	0,75	9078832	S302P-K0,75	2CDS382001R0187		0.240	5
	1	9078795	S302P-K1	2CDS382001R0217		0.240	5
	1,6	9078740	S302P-K1,6	2CDS382001R0257		0.240	5
	2	9078726	S302P-K2	2CDS382001R0277		0.240	5
	3	9078702	S302P-K3	2CDS382001R0317		0.240	5
	4	9078658	S302P-K4	2CDS382001R0337		0.240	5
	6	9078634	S302P-K6	2CDS382001R0377		0.240	5
	8	9078580	S302P-K8	2CDS382001R0407		0.240	5
	10	9078566	S302P-K10	2CDS382001R0427		0.240	5
	13	9078542	S302P-K13	2CDS382001R0447		0.246	5
	16	9078535	S302P-K16	2CDS382001R0467		0.246	5
	20	9078511	S302P-K20	2CDS382001R0487		0.246	5
	25	9078467	S302P-K25	2CDS382001R0517		0.246	5
	32	9078443	S302P-K32	2CDS382001R0537		0.256	5
	40	9078429	S302P-K40	2CDS382001R0557		0.256	5
	50	9078405	S302P-K50	2CDS382001R0577		0.256	5
	63	9078382	S302P-K63	2CDS382001R0607		0.256	5
3	0,2	9078160	S303P-K0,2	2CDS383001R0087		0.360	1
	0,3	9078122	S303P-K0,3	2CDS383001R0117		0.360	1
	0,5	9078085	S303P-K0,5	2CDS383001R0157		0.360	1
	0,75	9078030	S303P-K0,75	2CDS383001R0187		0.360	1
	1	9077996	S303P-K1	2CDS383001R0217		0.360	1
	1,6	9077941	S303P-K1,6	2CDS383001R0257		0.360	1
	2	9077927	S303P-K2	2CDS383001R0277		0.360	1
	3	9077903	S303P-K3	2CDS383001R0317		0.360	1
	4	9077859	S303P-K4	2CDS383001R0337		0.360	1
	6	9077835	S303P-K6	2CDS383001R0377		0.360	1
	8	9077781	S303P-K8	2CDS383001R0407		0.360	1
	10	9077767	S303P-K10	2CDS383001R0427		0.360	1
	13	9077743	S303P-K13	2CDS383001R0447		0.369	1
	16	9077736	S303P-K16	2CDS383001R0467		0.369	1
	20	9077712	S303P-K20	2CDS383001R0487		0.369	1
	25	9077668	S303P-K25	2CDS383001R0517		0.369	1
	32	9077644	S303P-K32	2CDS383001R0537		0.384	1
	40	9077620	S303P-K40	2CDS383001R0557		0.384	1
	50	9077606	S303P-K50	2CDS383001R0577		0.384	1
	63	9077583	S303P-K63	2CDS383001R0607		0.384	1

MCBs

S 300 series P-K characteristic



S 304 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	0,2	9076562	S304P-K0,2	2CDS384001R0087		0.480	1
	0,3	9076524	S304P-K0,3	2CDS384001R0117		0.480	1
	0,5	9076487	S304P-K0,5	2CDS384001R0157		0.480	1
	0,75	9076432	S304P-K0,75	2CDS384001R0187		0.480	1
	1	9076395	S304P-K1	2CDS384001R0217		0.480	1
	1,6	9076340	S304P-K1,6	2CDS384001R0257		0.480	1
	2	9076326	S304P-K2	2CDS384001R0277		0.480	1
	3	9135542	S304P-K3	2CDS384001R0317		0.480	1
	4	9076258	S304P-K4	2CDS384001R0337		0.480	1
	6	9076234	S304P-K6	2CDS384001R0377		0.480	1
	8	9076180	S304P-K8	2CDS384001R0407		0.480	1
	10	9076166	S304P-K10	2CDS384001R0427		0.480	1
	13	9076142	S304P-K13	2CDS384001R0447		0.492	1
	16	9076135	S304P-K16	2CDS384001R0467		0.492	1
	20	9076111	S304P-K20	2CDS384001R0487		0.492	1
	25	9076067	S304P-K25	2CDS384001R0517		0.492	1
	32	9076043	S304P-K32	2CDS384001R0537		0.512	1
	40	9076029	S304P-K40	2CDS384001R0557		0.512	1
	50	9135528	S304P-K50	2CDS384001R0577		0.512	1
	63	9075985	S304P-K63	2CDS384001R0607		0.512	1

MCBs

S 300 series P-Z characteristic

S 300 P-Z characteristic

Function: protection and control of the electronic circuits against lower and long duration overloads and short-circuits.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=25 kA; 100 kA (≤6 A)



S 301 P



S 302 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0,5	9080460	S301P-Z0,5	2CDS381001R0158		0.120	10
	1	9080378	S301P-Z1	2CDS381001R0218		0.120	10
	1,6	9080323	S301P-Z1,6	2CDS381001R0258		0.120	10
	2	9080309	S301P-Z2	2CDS381001R0278		0.120	10
	3	9080286	S301P-Z3	2CDS381001R0318		0.120	10
	4	9080231	S301P-Z4	2CDS381001R0338		0.120	10
	6	9080217	S301P-Z6	2CDS381001R0378		0.120	10
	8	9080163	S301P-Z8	2CDS381001R0408		0.120	10
	10	9080149	S301P-Z10	2CDS381001R0428		0.120	10
	16	9080118	S301P-Z16	2CDS381001R0468		0.123	10
	20	9080095	S301P-Z20	2CDS381001R0488		0.123	10
	25	9080040	S301P-Z25	2CDS381001R0518		0.123	10
	32	9080026	S301P-Z32	2CDS381001R0538		0.128	10
	40	9080002	S301P-Z40	2CDS381001R0558		0.128	10
	50	9079983	S301P-Z50	2CDS381001R0578		0.128	10
	63	9079969	S301P-Z63	2CDS381001R0608		0.128	10
2	0,5	9078870	S302P-Z0,5	2CDS382001R0158		0.240	5
	1	9078788	S302P-Z1	2CDS382001R0218		0.240	5
	1,6	9078733	S302P-Z1,6	2CDS382001R0258		0.240	5
	2	9078719	S302P-Z2	2CDS382001R0278		0.240	5
	3	9078696	S302P-Z3	2CDS382001R0318		0.240	5
	4	9078641	S302P-Z4	2CDS382001R0338		0.240	5
	6	9078627	S302P-Z6	2CDS382001R0378		0.240	5
	8	9078573	S302P-Z8	2CDS382001R0408		0.240	5
	10	9078559	S302P-Z10	2CDS382001R0428		0.240	5
	16	9078528	S302P-Z16	2CDS382001R0468		0.246	5
	20	9078504	S302P-Z20	2CDS382001R0488		0.246	5
	25	9078450	S302P-Z25	2CDS382001R0518		0.246	5
	32	9078436	S302P-Z32	2CDS382001R0538		0.256	5
	40	9078412	S302P-Z40	2CDS382001R0558		0.256	5
	50	9078399	S302P-Z50	2CDS382001R0578		0.256	5
	63	9078375	S302P-Z63	2CDS382001R0608		0.256	5

MCBs

S 300 series P-Z characteristic



S 303 P



S 304 P

Number of poles	Rated current In A	Bbn 401677 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0,5	9078078	S303P-Z0,5	2CDS383001R0158		0.360	1
	1	9077989	S303P-Z1	2CDS383001R0218		0.360	1
	1,6	9077934	S303P-Z1,6	2CDS383001R0258		0.360	1
	2	9077910	S303P-Z2	2CDS383001R0278		0.360	1
	3	9077897	S303P-Z3	2CDS383001R0318		0.360	1
	4	9077842	S303P-Z4	2CDS383001R0338		0.360	1
	6	9077828	S303P-Z6	2CDS383001R0378		0.360	1
	8	9077774	S303P-Z8	2CDS383001R0408		0.360	1
	10	9077750	S303P-Z10	2CDS383001R0428		0.360	1
	16	9077729	S303P-Z16	2CDS383001R0468		0.369	1
	20	9077705	S303P-Z20	2CDS383001R0488		0.369	1
	25	9077651	S303P-Z25	2CDS383001R0518		0.369	1
	32	9077637	S303P-Z32	2CDS383001R0538		0.384	1
	40	9077613	S303P-Z40	2CDS383001R0558		0.384	1
	50	9077590	S303P-Z50	2CDS383001R0578		0.384	1
	63	9077576	S303P-Z63	2CDS383001R0608		0.384	1
4	0,5	9076470	S304P-Z0,5	2CDS384001R0158		0.480	1
	1	9076388	S304P-Z1	2CDS384001R0218		0.480	1
	1,6	9076333	S304P-Z1,6	2CDS384001R0258		0.480	1
	2	9076319	S304P-Z2	2CDS384001R0278		0.480	1
	3	9076296	S304P-Z3	2CDS384001R0318		0.480	1
	4	9076241	S304P-Z4	2CDS384001R0338		0.480	1
	6	9076227	S304P-Z6	2CDS384001R0378		0.480	1
	8	9076173	S304P-Z8	2CDS384001R0408		0.480	1
	10	9076159	S304P-Z10	2CDS384001R0428		0.480	1
	16	9076128	S304P-Z16	2CDS384001R0468		0.492	1
	20	9135535	S304P-Z20	2CDS384001R0488		0.492	1
	25	9076050	S304P-Z25	2CDS384001R0518		0.492	1
	32	9076036	S304P-Z32	2CDS384001R0538		0.512	1
	40	9076012	S304P-Z40	2CDS384001R0558		0.512	1
	50	9075992	S304P-Z50	2CDS384001R0578		0.512	1
	63	9075978	S304P-Z63	2CDS384001R0608		0.512	1

MCBs

SU 200 M series technical characteristic

General Data		
Standards	UL 489, CSA 22.2 No. 5, IEC/EN 60947-2	
Poles	1P, 2P, 3P, 4P	
Tripping characteristics	C, K, Z	
Rated current In	0.2 - 63 A	
Rated frequency f	50 / 60 Hz, DC (0 Hz)	
Rated insulation voltage Ui acc. to IEC/EN 60664-1	440 V AC (phase to phase)	
Overvoltage category	III	
Pollution degree	3	
IEC/EN 60947-2		
Rated operational voltage Ue	1P: 230 V AC; 2P, 3P, 4P: 400 V AC	
Max. power frequency recovery voltage Umax AC	1P: 253 V AC; 2P, 3P, 4P: 440 V AC	
Min. operating voltage	12 V AC, 12 V DC	
Rated ultimate short-circuit breaking capacity Icu	15 kA	
Rated service short-circuit breaking capacity Ics	≤ 40 A: 11.25 kA > 40 A: 7.5 kA	
Rated impulse withstand voltage Uimp (1.2/50µs)	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)	
Dielectric test voltage	2 kV (50 / 60Hz, 1 min.)	
Reference temperature for tripping characteristics	30 °C	
Electrical endurance	cycles (OFF-ON-OFF)	In < 30 A: 20,000 ops (AC), In ≥ 30 A: 10,000 ops. (AC); 1 cycle (2 s - ON, 13 s - OFF, In ≤ 32 A), 1 cycle (2 s - ON, 28 s - OFF, In > 32 A)
UL / CSA		
Rated voltage	AC	1P: 277 V AC up to 40 A for C, Z char.,
	AC	277 V AC up to 35 A for K char., 240 V AC
	AC	2P, 3P, 4P: 480 Y / 277 V AC up to 40 A for C, Z char.,
	AC	480 Y / 277 V AC up to 35 A for K char., 240 V AC
	DC	1P: 48 V DC; 2P: 96 V DC (2p in series)
Rated interrupting capacity acc. to UL 1077	–	
Short-circuit current rating acc. to UL 489	10 kA	
Application	–	
Reference temperature for tripping characteristics	40 °C	
Electrical endurance	cycles (OFF-ON-OFF)	6,000 ops (AC), 6,000 ops. (DC); 1 cycle (1 s - ON, 9 s - OFF)

MCBs

SU 200 M series technical characteristic

Mechanical data	
Housing	Insulation group II, RAL 7035
Toggle	Insulation group II, black, sealable
Contact position indication	Real CPI (green OFF / red ON)
Protection degree acc. to DIN EN 60529	IP20*, IP40 in enclosure with cover
Mechanical endurance	20,000 ops.
Shock resistance acc. to IEC/EN 60068-2-27	25 g - 2 shocks - 13 ms
Vibration resistance acc. to IEC/EN 60068-2-6	5g - 20 cycles at 5...150...5 Hz with load 0.8 In
Environmental conditions (damp heat cyclic) acc. to IEC/EN 60068-2-30	28 cycles with 55°C/90-96% and 25°C/95-100%
Ambient temperature	-25 ... +55°C
Storage temperature	-40 ... +70 °C
Installation	
Terminal	Failsafe bi-directional cylinder-lift terminal
Cross-section of conductors (top/bottom)	solid, stranded: 35 mm ² / 35 mm ² flexible: 25 mm ² / 25 mm ² 18 – 4 AWG
Cross-section of busbars (top/bottom)	10 mm ² / 10 mm ² 18 – 8 AWG
Torque	2.8 Nm AWG 18-16: 13.3 in-lbs. AWG 14-10: 17.7 in-lbs. AWG 8-4: 39.8 in-lbs.
Screwdriver	No. 2 Pozidrive
Mounting	On DIN rail 35 mm acc. to EN 60715 by fast clip
Mounting position	any
Supply	optional
Dimensions and weight	
Mounting dimensions acc. to DIN 43880	Mounting dimension 3
Pole dimensions (H x D x W)	111 x 69 x 17.5 mm
Pole weight approx.	125 g
Combination with auxiliary elements	
Auxiliary contact	Yes
Signal contact	Yes
Shunt trip	Yes

* Also fulfilling the requirements acc. to the protection degree IPXXB

MCBs

SU 200 M series C characteristic

SU 200 M-C characteristic

Number of poles	Rated current	Bbn 4016779	Order details		Price 1 piece	Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code		kg	pc.
1	0.5	930741	SU201M-C0,5	2CDS271337R0984		0.122	1
	1	930758	SU201M-C1	2CDS271337R0014		0.122	1
	1.6	930765	SU201M-C1,6	2CDS271337R0974		0.122	1
	2	930772	SU201M-C2	2CDS271337R0024		0.122	1
	3	930789	SU201M-C3	2CDS271337R0034		0.122	1
	4	930796	SU201M-C4	2CDS271337R0044		0.122	1
	5	930802	SU201M-C5	2CDS271337R0054		0.122	1
	6	930819	SU201M-C6	2CDS271337R0064		0.122	1
	8	930833	SU201M-C8	2CDS271337R0084		0.122	1
	10	930840	SU201M-C10	2CDS271337R0104		0.122	1
	13	930857	SU201M-C13	2CDS271337R0134		0.125	1
	15	930864	SU201M-C15	2CDS271337R0154		0.125	1
	16	930871	SU201M-C16	2CDS271337R0164		0.125	1
	20	930888	SU201M-C20	2CDS271337R0204		0.125	1
	25	930895	SU201M-C25	2CDS271337R0254		0.125	1
	30	930901	SU201M-C30	2CDS271337R0304		0.130	1
	32	930918	SU201M-C32	2CDS271337R0324		0.130	1
	35	930925	SU201M-C35	2CDS271337R0354		0.130	1
	40	930932	SU201M-C40	2CDS271337R0404		0.130	1
	50	930949	SU201M-C50	2CDS271337R0504		0.130	1
	60	930956	SU201M-C60	2CDS271337R0604		0.130	1
	63	930963	SU201M-C63	2CDS271337R0634		0.130	1

MCBs

SU 200 M series C characteristic

Number of poles	Rated current	Bbn 4016779	Order details		Price 1 piece	Weight 1 piece	Pack unit
			Type code	Order code		kg	pc.
2	0.5	930970	SU202M-C0,5	2CDS272337R0984		0.244	1
	1	930987	SU202M-C1	2CDS272337R0014		0.244	1
	1.6	930994	SU202M-C1,6	2CDS272337R0974		0.244	1
	2	931007	SU202M-C2	2CDS272337R0024		0.244	1
	3	931014	SU202M-C3	2CDS272337R0034		0.244	1
	4	931021	SU202M-C4	2CDS272337R0044		0.244	1
	5	931038	SU202M-C5	2CDS272337R0054		0.244	1
	6	931045	SU202M-C6	2CDS272337R0064		0.244	1
	8	931069	SU202M-C8	2CDS272337R0084		0.244	1
	10	931076	SU202M-C10	2CDS272337R0104		0.244	1
	13	931083	SU202M-C13	2CDS272337R0134		0.250	1
	15	931090	SU202M-C15	2CDS272337R0154		0.250	1
	16	931106	SU202M-C16	2CDS272337R0164		0.250	1
	20	931113	SU202M-C20	2CDS272337R0204		0.250	1
	25	931120	SU202M-C25	2CDS272337R0254		0.250	1
	30	931137	SU202M-C30	2CDS272337R0304		0.260	1
	32	931144	SU202M-C32	2CDS272337R0324		0.260	1
	35	931151	SU202M-C35	2CDS272337R0354		0.260	1
	40	931168	SU202M-C40	2CDS272337R0404		0.260	1
	50	931175	SU202M-C50	2CDS272337R0504		0.260	1
	60	931182	SU202M-C60	2CDS272337R0604		0.260	1
	63	931199	SU202M-C63	2CDS272337R0634		0.260	1
3	0.5	931205	SU203M-C0,5	2CDS273337R0984		0.366	1
	1	931212	SU203M-C1	2CDS273337R0014		0.366	1
	1.6	931229	SU203M-C1,6	2CDS273337R0974		0.366	1
	2	931236	SU203M-C2	2CDS273337R0024		0.366	1
	3	931243	SU203M-C3	2CDS273337R0034		0.366	1
	4	931250	SU203M-C4	2CDS273337R0044		0.366	1
	5	931267	SU203M-C5	2CDS273337R0054		0.366	1
	6	931274	SU203M-C6	2CDS273337R0064		0.366	1
	8	931298	SU203M-C8	2CDS273337R0084		0.366	1
	10	931304	SU203M-C10	2CDS273337R0104		0.366	1
	13	931311	SU203M-C13	2CDS273337R0134		0.375	1
	15	931328	SU203M-C15	2CDS273337R0154		0.375	1
	16	931335	SU203M-C16	2CDS273337R0164		0.375	1
	20	931342	SU203M-C20	2CDS273337R0204		0.375	1
	25	931359	SU203M-C25	2CDS273337R0254		0.375	1
	30	931366	SU203M-C30	2CDS273337R0304		0.390	1
	32	931373	SU203M-C32	2CDS273337R0324		0.390	1
	35	931380	SU203M-C35	2CDS273337R0354		0.390	1
	40	931397	SU203M-C40	2CDS273337R0404		0.390	1
	50	931403	SU203M-C50	2CDS273337R0504		0.390	1
	60	931410	SU203M-C60	2CDS273337R0604		0.390	1
	63	931427	SU203M-C63	2CDS273337R0634		0.390	1

MCBs

SU 200 M series C characteristic

Number of poles	Rated current	Bbn 4016779	Order details		Price 1 piece	Weight 1 piece	Pack unit
			Type code	Order code			
	In A	EAN				kg	pc.
4	0.5	931434	SU204M-C0,5	2CDS274337R0984		0.488	1
	1	931441	SU204M-C1	2CDS274337R0014		0.488	1
	1.6	931458	SU204M-C1,6	2CDS274337R0974		0.488	1
	2	931465	SU204M-C2	2CDS274337R0024		0.488	1
	3	931472	SU204M-C3	2CDS274337R0034		0.488	1
	4	931489	SU204M-C4	2CDS274337R0044		0.488	1
	5	931496	SU204M-C5	2CDS274337R0054		0.488	1
	6	931502	SU204M-C6	2CDS274337R0064		0.488	1
	8	931526	SU204M-C8	2CDS274337R0084		0.488	1
	10	931533	SU204M-C10	2CDS274337R0104		0.488	1
	13	931540	SU204M-C13	2CDS274337R0134		0.500	1
	15	931557	SU204M-C15	2CDS274337R0154		0.500	1
	16	931564	SU204M-C16	2CDS274337R0164		0.500	1
	20	931571	SU204M-C20	2CDS274337R0204		0.500	1
	25	931588	SU204M-C25	2CDS274337R0254		0.500	1
	30	931595	SU204M-C30	2CDS274337R0304		0.520	1
	32	931601	SU204M-C32	2CDS274337R0324		0.520	1
	35	931618	SU204M-C35	2CDS274337R0354		0.520	1
	40	931625	SU204M-C40	2CDS274337R0404		0.520	1
	50	931632	SU204M-C50	2CDS274337R0504		0.520	1
	60	931649	SU204M-C60	2CDS274337R0604		0.520	1
	63	931656	SU204M-C63	2CDS274337R0634		0.520	1

MCBs

SU 200 M series K characteristic

SU 200 M-K characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.2	929967	SU201M-K0,2	2CDS271337R0087		0.122	1
	0.3	929974	SU201M-K0,3	2CDS271337R0117		0.122	1
	0.5	929981	SU201M-K0,5	2CDS271337R0157		0.122	1
	0.75	929998	SU201M-K0,75	2CDS271337R0187		0.122	1
	1	930000	SU201M-K1	2CDS271337R0217		0.122	1
	1.6	930017	SU201M-K1,6	2CDS271337R0257		0.122	1
	2	930024	SU201M-K2	2CDS271337R0277		0.122	1
	3	930031	SU201M-K3	2CDS271337R0317		0.122	1
	4	930048	SU201M-K4	2CDS271337R0337		0.122	1
	5	930055	SU201M-K5	2CDS271337R0357		0.122	1
	6	930062	SU201M-K6	2CDS271337R0377		0.122	1
	8	930086	SU201M-K8	2CDS271337R0407		0.122	1
	10	930093	SU201M-K10	2CDS271337R0427		0.122	1
	13	930109	SU201M-K13	2CDS271337R0447		0.125	1
	15	930116	SU201M-K15	2CDS271337R0457		0.125	1
	16	930123	SU201M-K16	2CDS271337R0467		0.125	1
	20	930130	SU201M-K20	2CDS271337R0487		0.125	1
	25	930147	SU201M-K25	2CDS271337R0517		0.125	1
	30	930154	SU201M-K30	2CDS271337R0527		0.130	1
	32	930161	SU201M-K32	2CDS271337R0537		0.130	1
	35	930178	SU201M-K35	2CDS271337R0547		0.130	1
	40	930185	SU201M-K40	2CDS271337R0557		0.130	1
	50	930192	SU201M-K50	2CDS271337R0577		0.130	1
	60	930208	SU201M-K60	2CDS271337R0587		0.130	1
	63	930215	SU201M-K63	2CDS271337R0607		0.130	1

MCBs

SU 200 M series K characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
2	0.2	932585	SU202M-K0,2	2CDS272337R0087		0.244	1
	0.3	932592	SU202M-K0,3	2CDS272337R0117		0.244	1
	0.5	932608	SU202M-K0,5	2CDS272337R0157		0.244	1
	0.75	932615	SU202M-K0,75	2CDS272337R0187		0.244	1
	1	932622	SU202M-K1	2CDS272337R0217		0.244	1
	1.6	932639	SU202M-K1,6	2CDS272337R0257		0.244	1
	2	932646	SU202M-K2	2CDS272337R0277		0.244	1
	3	932653	SU202M-K3	2CDS272337R0317		0.244	1
	4	932660	SU202M-K4	2CDS272337R0337		0.244	1
	5	932677	SU202M-K5	2CDS272337R0357		0.244	1
	6	932684	SU202M-K6	2CDS272337R0377		0.244	1
	8	932707	SU202M-K8	2CDS272337R0407		0.244	1
	10	932714	SU202M-K10	2CDS272337R0427		0.244	1
	13	932721	SU202M-K13	2CDS272337R0447		0.250	1
	15	932738	SU202M-K15	2CDS272337R0457		0.250	1
	16	932745	SU202M-K16	2CDS272337R0467		0.250	1
	20	932752	SU202M-K20	2CDS272337R0487		0.250	1
	25	932769	SU202M-K25	2CDS272337R0517		0.250	1
	30	932776	SU202M-K30	2CDS272337R0527		0.260	1
	32	932783	SU202M-K32	2CDS272337R0537		0.260	1
	35	932790	SU202M-K35	2CDS272337R0547		0.260	1
	40	932806	SU202M-K40	2CDS272337R0557		0.260	1
	50	932813	SU202M-K50	2CDS272337R0577		0.260	1
	60	932820	SU202M-K60	2CDS272337R0587		0.260	1
	63	932837	SU202M-K63	2CDS272337R0607		0.260	1

MCBs

SU 200 M series K characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.2	930222	SU203M-K0,2	2CDS273337R0087		0.366	1
	0.3	930239	SU203M-K0,3	2CDS273337R0117		0.366	1
	0.5	930246	SU203M-K0,5	2CDS273337R0157		0.366	1
	0.75	930253	SU203M-K0,75	2CDS273337R0187		0.366	1
	1	930260	SU203M-K1	2CDS273337R0217		0.366	1
	1.6	930277	SU203M-K1,6	2CDS273337R0257		0.366	1
	2	930284	SU203M-K2	2CDS273337R0277		0.366	1
	3	930291	SU203M-K3	2CDS273337R0317		0.366	1
	4	930307	SU203M-K4	2CDS273337R0337		0.366	1
	5	930314	SU203M-K5	2CDS273337R0357		0.366	1
	6	930321	SU203M-K6	2CDS273337R0377		0.366	1
	8	930345	SU203M-K8	2CDS273337R0407		0.366	1
	10	930352	SU203M-K10	2CDS273337R0427		0.366	1
	13	930369	SU203M-K13	2CDS273337R0447		0.375	1
	15	930376	SU203M-K15	2CDS273337R0457		0.375	1
	16	930383	SU203M-K16	2CDS273337R0467		0.375	1
	20	930390	SU203M-K20	2CDS273337R0487		0.375	1
	25	930406	SU203M-K25	2CDS273337R0517		0.375	1
	30	930413	SU203M-K30	2CDS273337R0527		0.390	1
	32	930420	SU203M-K32	2CDS273337R0537		0.390	1
	35	930437	SU203M-K35	2CDS273337R0547		0.390	1
	40	930444	SU203M-K40	2CDS273337R0557		0.390	1
	50	930451	SU203M-K50	2CDS273337R0577		0.390	1
	60	930468	SU203M-K60	2CDS273337R0587		0.390	1
	63	930475	SU203M-K63	2CDS273337R0607		0.390	1

MCBs

SU 200 M series K characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	0.2	930482	SU204M-K0,2	2CDS274337R0087		0.488	1
	0.3	930499	SU204M-K0,3	2CDS274337R0117		0.488	1
	0.5	930505	SU204M-K0,5	2CDS274337R0157		0.488	1
	0.75	930512	SU204M-K0,75	2CDS274337R0187		0.488	1
	1	930529	SU204M-K1	2CDS274337R0217		0.488	1
	1.6	930536	SU204M-K1,6	2CDS274337R0257		0.488	1
	2	930543	SU204M-K2	2CDS274337R0277		0.488	1
	3	930550	SU204M-K3	2CDS274337R0317		0.488	1
	4	930567	SU204M-K4	2CDS274337R0337		0.488	1
	5	930574	SU204M-K5	2CDS274337R0357		0.488	1
	6	930581	SU204M-K6	2CDS274337R0377		0.488	1
	8	930604	SU204M-K8	2CDS274337R0407		0.488	1
	10	930611	SU204M-K10	2CDS274337R0427		0.488	1
	13	930628	SU204M-K13	2CDS274337R0447		0.500	1
	15	930635	SU204M-K15	2CDS274337R0457		0.500	1
	16	930642	SU204M-K16	2CDS274337R0467		0.500	1
	20	930659	SU204M-K20	2CDS274337R0487		0.500	1
	25	930666	SU204M-K25	2CDS274337R0517		0.500	1
	30	930673	SU204M-K30	2CDS274337R0527		0.520	1
	32	930680	SU204M-K32	2CDS274337R0537		0.520	1
	35	930697	SU204M-K35	2CDS274337R0547		0.520	1
	40	930703	SU204M-K40	2CDS274337R0557		0.520	1
	50	930710	SU204M-K50	2CDS274337R0577		0.520	1
	60	930727	SU204M-K60	2CDS274337R0587		0.520	1
	63	930734	SU204M-K63	2CDS274337R0607		0.520	1

MCBs

SU 200 M series Z characteristic

SU 200 M-Z characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.5	932844	SU201M-Z0,5	2CDS271337R0158		0.122	1
	1	932851	SU201M-Z1	2CDS271337R0218		0.122	1
	1.6	932868	SU201M-Z1,6	2CDS271337R0258		0.122	1
	2	932875	SU201M-Z2	2CDS271337R0278		0.122	1
	3	932882	SU201M-Z3	2CDS271337R0318		0.122	1
	4	932899	SU201M-Z4	2CDS271337R0338		0.122	1
	5	932905	SU201M-Z5	2CDS271337R0358		0.122	1
	6	932912	SU201M-Z6	2CDS271337R0378		0.122	1
	8	932936	SU201M-Z8	2CDS271337R0408		0.122	1
	10	932943	SU201M-Z10	2CDS271337R0428		0.122	1
	13	932950	SU201M-Z13	2CDS271337R0448		0.125	1
	15	932967	SU201M-Z15	2CDS271337R0458		0.125	1
	16	932974	SU201M-Z16	2CDS271337R0468		0.125	1
	20	932981	SU201M-Z20	2CDS271337R0488		0.125	1
	25	932998	SU201M-Z25	2CDS271337R0518		0.125	1
	30	933001	SU201M-Z30	2CDS271337R0528		0.130	1
	32	933018	SU201M-Z32	2CDS271337R0538		0.130	1
	35	933025	SU201M-Z35	2CDS271337R0548		0.130	1
	40	933032	SU201M-Z40	2CDS271337R0558		0.130	1
	50	933049	SU201M-Z50	2CDS271337R0578		0.130	1
	60	933056	SU201M-Z60	2CDS271337R0588		0.130	1
	63	933063	SU201M-Z63	2CDS271337R0608		0.130	1

MCBs

SU 200 M series Z characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
2	0.5	933070	SU202M-Z0,5	2CDS272337R0158		0.244	1
	1	933087	SU202M-Z1	2CDS272337R0218		0.244	1
	1.6	933094	SU202M-Z1,6	2CDS272337R0258		0.244	1
	2	933100	SU202M-Z2	2CDS272337R0278		0.244	1
	3	933117	SU202M-Z3	2CDS272337R0318		0.244	1
	4	933124	SU202M-Z4	2CDS272337R0338		0.244	1
	5	933131	SU202M-Z5	2CDS272337R0358		0.244	1
	6	933148	SU202M-Z6	2CDS272337R0378		0.244	1
	8	933162	SU202M-Z8	2CDS272337R0408		0.244	1
	10	933179	SU202M-Z10	2CDS272337R0428		0.244	1
	13	933186	SU202M-Z13	2CDS272337R0448		0.250	1
	15	933193	SU202M-Z15	2CDS272337R0458		0.250	1
	16	933209	SU202M-Z16	2CDS272337R0468		0.250	1
	20	933216	SU202M-Z20	2CDS272337R0488		0.250	1
	25	933223	SU202M-Z25	2CDS272337R0518		0.250	1
	30	933230	SU202M-Z30	2CDS272337R0528		0.260	1
	32	933247	SU202M-Z32	2CDS272337R0538		0.260	1
	35	933254	SU202M-Z35	2CDS272337R0548		0.260	1
	40	933261	SU202M-Z40	2CDS272337R0558		0.260	1
	50	933278	SU202M-Z50	2CDS272337R0578		0.260	1
	60	933285	SU202M-Z60	2CDS272337R0588		0.260	1
	63	933292	SU202M-Z63	2CDS272337R0608		0.260	1
3	0.5	933308	SU203M-Z0,5	2CDS273337R0158		0.366	1
	1	933315	SU203M-Z1	2CDS273337R0218		0.366	1
	1.6	933322	SU203M-Z1,6	2CDS273337R0258		0.366	1
	2	933339	SU203M-Z2	2CDS273337R0278		0.366	1
	3	933346	SU203M-Z3	2CDS273337R0318		0.366	1
	4	933353	SU203M-Z4	2CDS273337R0338		0.366	1
	5	933360	SU203M-Z5	2CDS273337R0358		0.366	1
	6	933377	SU203M-Z6	2CDS273337R0378		0.366	1
	8	933391	SU203M-Z8	2CDS273337R0408		0.366	1
	10	933407	SU203M-Z10	2CDS273337R0428		0.366	1
	13	933414	SU203M-Z13	2CDS273337R0448		0.375	1
	15	933421	SU203M-Z15	2CDS273337R0458		0.375	1
	16	933438	SU203M-Z16	2CDS273337R0468		0.375	1
	20	933445	SU203M-Z20	2CDS273337R0488		0.375	1
	25	933452	SU203M-Z25	2CDS273337R0518		0.375	1
	30	933469	SU203M-Z30	2CDS273337R0528		0.390	1
	32	933476	SU203M-Z32	2CDS273337R0538		0.390	1
	35	933483	SU203M-Z35	2CDS273337R0548		0.390	1
	40	933490	SU203M-Z40	2CDS273337R0558		0.390	1
	50	933506	SU203M-Z50	2CDS273337R0578		0.390	1
	60	933513	SU203M-Z60	2CDS273337R0588		0.390	1
	63	933520	SU203M-Z63	2CDS273337R0608		0.390	1

MCBs

SU 200 M series Z characteristic

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
4	0.5	933537	SU204M-Z0,5	2CDS274337R0158		0.488	1
	1	933544	SU204M-Z1	2CDS274337R0218		0.488	1
	1.6	933551	SU204M-Z1,6	2CDS274337R0258		0.488	1
	2	933568	SU204M-Z2	2CDS274337R0278		0.488	1
	3	933575	SU204M-Z3	2CDS274337R0318		0.488	1
	4	933582	SU204M-Z4	2CDS274337R0338		0.488	1
	5	933599	SU204M-Z5	2CDS274337R0358		0.488	1
	6	933605	SU204M-Z6	2CDS274337R0378		0.488	1
	8	933629	SU204M-Z8	2CDS274337R0408		0.488	1
	10	933636	SU204M-Z10	2CDS274337R0428		0.488	1
	13	933643	SU204M-Z13	2CDS274337R0448		0.500	1
	15	933650	SU204M-Z15	2CDS274337R0458		0.500	1
	16	933667	SU204M-Z16	2CDS274337R0468		0.500	1
	20	933674	SU204M-Z20	2CDS274337R0488		0.500	1
	25	933681	SU204M-Z25	2CDS274337R0518		0.500	1
	30	933698	SU204M-Z30	2CDS274337R0528		0.520	1
	32	933704	SU204M-Z32	2CDS274337R0538		0.520	1
	35	933711	SU204M-Z35	2CDS274337R0548		0.520	1
	40	933728	SU204M-Z40	2CDS274337R0558		0.520	1
	50	933735	SU204M-Z50	2CDS274337R0578		0.520	1
	60	933742	SU204M-Z60	2CDS274337R0588		0.520	1
	63	933759	SU204M-Z63	2CDS274337R0608		0.520	1

MCBs

Circuit breaker SU 200 MR series, 10kA

The SU200 MR is a high-performance circuit breaker with ring cable lug connections conforming to UL 489; CSA 22.2. No. 5 and IEC/EN 60947-2 standards. The integrated captive connecting screws simplify the connection of electric lines, provides extra protection and saves time.



SU201 MR



SU202 MR

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1	0.2	956192	SU201MR-K0.2	2CDS271347R0087		0.122	1
	0.3	956215	SU201MR-K0.3	2CDS271347R0117		0.122	1
	0.5	956239	SU201MR-K0.5	2CDS271347R0157		0.122	1
	0.75	956253	SU201MR-K0.75	2CDS271347R0187		0.122	1
	1	956277	SU201MR-K1	2CDS271347R0217		0.122	1
	1.6	956291	SU201MR-K1.6	2CDS271347R0257		0.122	1
	2	956314	SU201MR-K2	2CDS271347R0277		0.122	1
	3	956338	SU201MR-K3	2CDS271347R0317		0.122	1
	4	956352	SU201MR-K4	2CDS271347R0337		0.122	1
	5	956376	SU201MR-K5	2CDS271347R0357		0.122	1
	6	956390	SU201MR-K6	2CDS271347R0377		0.122	1
	8	956413	SU201MR-K8	2CDS271347R0407		0.122	1
	10	956437	SU201MR-K10	2CDS271347R0427		0.122	1
	13	956451	SU201MR-K13	2CDS271347R0447		0.125	1
	15	956475	SU201MR-K15	2CDS271347R0457		0.125	1
	16	956499	SU201MR-K16	2CDS271347R0467		0.125	1
	20	956512	SU201MR-K20	2CDS271347R0487		0.125	1
	25	956536	SU201MR-K25	2CDS271347R0517		0.125	1
	30	956550	SU201MR-K30	2CDS271347R0527		0.130	1
	32	956574	SU201MR-K32	2CDS271347R0537		0.130	1
	35	956598	SU201MR-K35	2CDS271347R0547		0.130	1
2	0.2	957175	SU202MR-K0.2	2CDS272347R0087		0.244	1
	0.3	957199	SU202MR-K0.3	2CDS272347R0117		0.244	1
	0.5	957212	SU202MR-K0.5	2CDS272347R0157		0.244	1
	0.75	957236	SU202MR-K0.75	2CDS272347R0187		0.244	1
	1	957250	SU202MR-K1	2CDS272347R0217		0.244	1
	1.6	957274	SU202MR-K1.6	2CDS272347R0257		0.244	1
	2	957298	SU202MR-K2	2CDS272347R0277		0.244	1
	3	957311	SU202MR-K3	2CDS272347R0317		0.244	1
	4	957335	SU202MR-K4	2CDS272347R0337		0.244	1
	5	957359	SU202MR-K5	2CDS272347R0357		0.244	1
	6	957373	SU202MR-K6	2CDS272347R0377		0.244	1
	8	957397	SU202MR-K8	2CDS272347R0407		0.244	1
	10	957410	SU202MR-K10	2CDS272347R0427		0.244	1
	13	957434	SU202MR-K13	2CDS272347R0447		0.250	1
	15	957458	SU202MR-K15	2CDS272347R0457		0.250	1
	16	957472	SU202MR-K16	2CDS272347R0467		0.250	1
	20	957496	SU202MR-K20	2CDS272347R0487		0.250	1
	25	957519	SU202MR-K25	2CDS272347R0517		0.250	1
	30	957533	SU202MR-K30	2CDS272347R0527		0.260	1
	32	957557	SU202MR-K32	2CDS272347R0537		0.260	1
	35	957571	SU202MR-K35	2CDS272347R0547		0.260	1
	40	957595	SU202MR-K40	2CDS272347R0557		0.260	1
	50	957618	SU202MR-K50	2CDS272347R0577		0.260	1
	60	957632	SU202MR-K60	2CDS272347R0587		0.260	1
	63	957656	SU202MR-K63	2CDS272347R0607		0.260	1

MCBs

Circuit breaker SU 200 MR series, 10kA



SU203 MR




SU204 MR

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	0.2	958172	SU203MR-K0.2	2CDS273347R0087		0.366	1
	0.3	958196	SU203MR-K0.3	2CDS273347R0117		0.366	1
	0.5	958219	SU203MR-K0.5	2CDS273347R0157		0.366	1
	0.75	958233	SU203MR-K0.75	2CDS273347R0187		0.366	1
	1	958257	SU203MR-K1	2CDS273347R0217		0.366	1
	1.6	958271	SU203MR-K1.6	2CDS273347R0257		0.366	1
	2	958295	SU203MR-K2	2CDS273347R0277		0.366	1
	3	958318	SU203MR-K3	2CDS273347R0317		0.366	1
	4	958332	SU203MR-K4	2CDS273347R0337		0.366	1
	5	958356	SU203MR-K5	2CDS273347R0357		0.366	1
	6	958370	SU203MR-K6	2CDS273347R0377		0.366	1
	8	958394	SU203MR-K8	2CDS273347R0407		0.366	1
	10	958417	SU203MR-K10	2CDS273347R0427		0.366	1
	13	958431	SU203MR-K13	2CDS273347R0447		0.375	1
	15	958455	SU203MR-K15	2CDS273347R0457		0.375	1
	16	958479	SU203MR-K16	2CDS273347R0467		0.375	1
	20	958493	SU203MR-K20	2CDS273347R0487		0.375	1
	25	958516	SU203MR-K25	2CDS273347R0517		0.375	1
	30	958530	SU203MR-K30	2CDS273347R0527		0.390	1
	32	958554	SU203MR-K32	2CDS273347R0537		0.390	1
	35	958578	SU203MR-K35	2CDS273347R0547		0.390	1
	40	958592	SU203MR-K40	2CDS273347R0557		0.390	1
	50	958615	SU203MR-K50	2CDS273347R0577		0.390	1
	60	958639	SU203MR-K60	2CDS273347R0587		0.390	1
	63	958653	SU203MR-K63	2CDS273347R0607		0.390	1
4	0.2	959179	SU204MR-K0.2	2CDS274347R0087		0.488	1
	0.3	959193	SU204MR-K0.3	2CDS274347R0117		0.488	1
	0.5	959216	SU204MR-K0.5	2CDS274347R0157		0.488	1
	0.75	959230	SU204MR-K0.75	2CDS274347R0187		0.488	1
	1	959254	SU204MR-K1	2CDS274347R0217		0.488	1
	1.6	959278	SU204MR-K1.6	2CDS274347R0257		0.488	1
	2	959292	SU204MR-K2	2CDS274347R0277		0.488	1
	3	959315	SU204MR-K3	2CDS274347R0317		0.488	1
	4	959339	SU204MR-K4	2CDS274347R0337		0.488	1
	5	959353	SU204MR-K5	2CDS274347R0357		0.488	1
	6	959377	SU204MR-K6	2CDS274347R0377		0.488	1
	8	959391	SU204MR-K8	2CDS274347R0407		0.488	1
	10	959414	SU204MR-K10	2CDS274347R0427		0.488	1
	13	959438	SU204MR-K13	2CDS274347R0447		0.500	1
	15	959452	SU204MR-K15	2CDS274347R0457		0.500	1
	16	959476	SU204MR-K16	2CDS274347R0467		0.500	1
	20	959490	SU204MR-K20	2CDS274347R0487		0.500	1
	25	959513	SU204MR-K25	2CDS274347R0517		0.500	1
	30	959537	SU204MR-K30	2CDS274347R0527		0.520	1
	32	959551	SU204MR-K32	2CDS274347R0537		0.520	1
	35	959575	SU204MR-K35	2CDS274347R0547		0.520	1
	40	959599	SU204MR-K40	2CDS274347R0557		0.520	1
	50	959612	SU204MR-K50	2CDS274347R0577		0.520	1
	60	959636	SU204MR-K60	2CDS274347R0587		0.520	1
	63	959650	SU204MR-K63	2CDS274347R0607		0.520	1

MCB SN 201. The details make the difference

A range designed to ensure efficiency and protection





Space for insulated screwdrivers: the larger neutral hole allows the use of an insulated screwdriver to tighten the screws of both wire terminals, ensuring maximum safety of the operation.



Two bistable fixing devices for maximum ease of use: due to larger size of the DIN rail fixing system, made with 2 bistable fixing devices, the same screwdriver used for tightening the terminals can also be used for assembling and disassembling the device.



With the practical label carrier fitted in the SN201 circuit-breakers you can give maximum visibility to the information relating to the protected loads.



The SN201 fully integrates with the range of System pro M compact® miniature circuit-breakers, sharing the wide selection of accessories available through a dedicated interface (half module), which also can be used as auxiliary contact.

Miniature circuit-breakers

SN 201 series - 1P+N in one module housing



SN 201

General Data	Standards	
	Number of poles	
	Tripping characteristics	
	Rated current I_n	A
	Rated frequency f	Hz
	Rated insulation voltage U_i acc. to IEC/EN 60664-1	V
	Overvoltage category	
	Pollution degree	
Data acc. to IEC/EN 60898-1	Rated operational voltage U_e	V
	Max. power frequency recovery voltage (U_{max})	V
	Min. operating voltage	V
	Rated short-circuit capacity I_{cn}	kA
	Rated making and breaking capacity of one individual pole I_{cn1}	kA
	Energy limiting class (B, C characteristics)	
	Grid distance	mm
	Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	kV
	Dielectric test voltage (at ind. freq. for 1 min.)	kV
	Reference temperature for tripping characteristics	°C
	Electrical endurance	cycles (OFF-ON-OFF)
Data acc. to IEC/EN 60947-2 (Only referring to internal short circuit test)	Rated ultimate short-circuit breaking capacity I_{cu}	kA
	Rated service short-circuit breaking capacity I_{cs}	kA
Mechanical Data	Housing type	
	Toggle type	
	Contact position indication	
	Protection degree acc. to EN 60529	
	Mechanical endurance	cycles (OFF-ON-OFF)
	Resistance to Shock acc. to IEC 60068-2-27	
	Resistance to Vibrations acc. to IEC 60068-2-6	
	Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH
	Ambient temperature (with daily average $\leq +35^\circ\text{C}$)	°C
	Storage temperature	°C
Installation	Terminal type (top/bottom)	
	Cross-section of conductors (top/bottom) Stranded / Solid	mm ²
	Cross-section of conductors (top/bottom) Flexible	mm ²
	Wire Stripping Length	mm
	Tightening torque	Nm
	Screwdriver	
	Mounting type	
	Mounting Position	
	Supply from	
Dimensions and weight	Pole dimensions (H x D x W)	mm
	Pole weight	g
Combination with aux. elements	Auxiliary contact	
	Auxiliary/Signal contact	
	Shunt trip	
	Undervoltage release	

*1 SN201 and SN201M series in B and D characteristic are available for rated current $I_n \geq 6$ A

Miniature circuit-breakers

SN 201 series - 1P+N in one module housing

SN 201 L	SN 201	SN 201 M
IEC/EN 60898-1		
1P + N		
B, C	B, C, D	B, C
2...40 A *1		
50 / 60 Hz		
500 V AC		
III		
2		
230 V AC		
254 V AC		
12 V AC		
4.5 kA	6 kA	10 kA
4.5 kA	6 kA	6 kA
3		
35		
4 kV (test voltage 6,2kV at sea level, 5kV at 2000m)		
2 kV (50 / 60Hz)		
30°C		
10.000		
6 kA	10 kA	10 kA
4.5 kA	6 kA	7.5 kA
Insulation group II, RAL 7035		
Insulation group IIIA, black, sealable in ON/OFF positions		
Marking on toggle (I ON / 0 OFF)		
Housing: IP4X; Terminals: IP2X		
20000		
30 g - 2 shocks - 13 ms		
0.35mm or 5g - 20 cycles at 5...150...5 Hz without load		
28 cycles with 55°C/90-96% and 25°C/95-100%		
-25 ... +55°C		
-40 ... +70°C		
Fail-safe cage terminal		
16 mm ² / 16 mm ²		
10 mm ² / 10 mm ²		
11 mm		
1.2 Nm		
No. 2 Pozidrive		
On DIN rail 35 mm acc. to EN 60715 by fast clip		
any		
Top/Bottom terminals		
85 x 68.9 x 17.6 mm		
115		
Yes		
Yes		
Yes (with coupling interface)		
Yes (with coupling interface)		

MCBs

SN 201 L series B and C characteristic



SN 201 L

SN 201 L - B characteristic

Function: overload and short-circuit protection of circuits in final distribution; protection of long cable lengths in TN and IT systems.

Applications: residential.

Standard: IEC/EN 60898-1

Icn: 4.5 kA

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	2	087359	SN201LB2	2CSS245101R0025		0.110	6
	4	087458	SN201LB4	2CSS245101R0045		0.110	6
	6	087557	SN201LB6	2CSS245101R0065		0.110	6
	10	087656	SN201LB10	2CSS245101R0105		0.110	6
	16	087755	SN201LB16	2CSS245101R0165		0.110	6
	20	087854	SN201LB20	2CSS245101R0205		0.110	6
	25	087953	SN201LB25	2CSS245101R0255		0.110	6
	32	088059	SN201LB32	2CSS245101R0325		0.110	6
	40	088158	SN201LB40	2CSS245101R0405		0.110	6

SN 201 L - C characteristic

Function: overload and short-circuit protection of circuits in final distribution; protection of resistive and inductive loads with low inrush current.

Applications: residential.

Standard: IEC/EN 60898-1

Icn: 4.5 kA



SN 201 L

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	2	088257	SN201LC2	2CSS245101R0024		0.110	6
	4	088356	SN201LC4	2CSS245101R0044		0.110	6
	6	088455	SN201LC6	2CSS245101R0064		0.110	6
	10	088554	SN201LC10	2CSS245101R0104		0.110	6
	16	088653	SN201LC16	2CSS245101R0164		0.110	6
	20	088752	SN201LC20	2CSS245101R0204		0.110	6
	25	088851	SN201LC25	2CSS245101R0254		0.110	6
	32	088950	SN201LC32	2CSS245101R0324		0.110	6
	40	089056	SN201LC40	2CSS245101R0404		0.110	6

MCBs

SN 201 series B and C characteristic



SN 201

SN 201 - B characteristic

Function: overload and short-circuits protection of circuits in final distribution; protection of long cable lengths in TN and IT systems.

Applications: residential and commercial.

Standard: IEC/EN 60898-1

Icn: 6 kA

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	6	090755	SN201B6	2CSS255101R0065		0.110	6
	10	090854	SN201B10	2CSS255101R0105		0.110	6
	13	743514	SN201B13	2CSS255101R0135		0.110	6
	16	090953	SN201B16	2CSS255101R0165		0.110	6
	20	091059	SN201B20	2CSS255101R0205		0.110	6
	25	091158	SN201B25	2CSS255101R0255		0.110	6
	32	091257	SN201B32	2CSS255101R0325		0.110	6
	40	091356	SN201B40	2CSS255101R0405		0.110	6

SN 201 - C characteristic

Function: overload and short-circuit protection of circuits in final distribution; protection of resistive and inductive loads with low inrush current.

Applications: residential and commercial.

Standard: IEC/EN 60898-1

Icn: 6 kA



SN 201

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	2	091462	SN201C2	2CSS255101R0024		0.110	6
	3	130260	SN201C3	2CSS255101R0034		0.110	6
	4	091561	SN201C4	2CSS255101R0044		0.110	6
	6	091660	SN201C6	2CSS255101R0064		0.110	6
	10	091769	SN201C10	2CSS255101R0104		0.110	6
	13	091868	SN201C13	2CSS255101R0134		0.110	6
	16	091967	SN201C16	2CSS255101R0164		0.110	6
	20	092063	SN201C20	2CSS255101R0204		0.110	6
	25	092162	SN201C25	2CSS255101R0254		0.110	6
	32	092261	SN201C32	2CSS255101R0324		0.110	6
	40	092360	SN201C40	2CSS255101R0404		0.110	6



MCBs

SN 201 series D characteristic



SN 201

SN 201 - D characteristic

Function: protection and control of the circuits against overloads and short-circuits in final distribution; protection for circuits which supply loads with high inrush current at the circuit closing.

Applications: residential and commercial.

Standard: IEC/EN 60898-1

Icn: 6 kA

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	6	092452	SN201D6	2CSS255101R0061		0.110	6
	10	092551	SN201D10	2CSS255101R0101		0.110	6
	16	092650	SN201D16	2CSS255101R0161		0.110	6
	20	092759	SN201D20	2CSS255101R0201		0.110	6
	25	092858	SN201D25	2CSS255101R0251		0.110	6
	32	092957	SN201D32	2CSS255101R0321		0.110	6
	40	093053	SN201D40	2CSS255101R0401		0.110	6

MCBs

SN 201 M series B and C characteristic



SN 201 M

SN 201 M - B characteristic

Function: overloads and short-circuit protection of circuits in final distribution; protection of long cable lengths in TN and IT systems.

Applications: residential and commercial.

Standard: IEC/EN 60898-1

Icn: 10 kA

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	6	093152	SN201MB6	2CSS275101R0065		0.110	6
	10	093251	SN201MB10	2CSS275101R0105		0.110	6
	16	093350	SN201MB16	2CSS275101R0165		0.110	6
	20	093459	SN201MB20	2CSS275101R0205		0.110	6
	25	093558	SN201MB25	2CSS275101R0255		0.110	6
	32	093657	SN201MB32	2CSS275101R0325		0.110	6
	40	093756	SN201MB40	2CSS275101R0405		0.110	6

SN 201 M - C characteristic

Function: overload and short-circuit protection of circuits in final distribution; protection of resistive and inductive loads with low inrush current.

Applications: residential and commercial.

Standard: IEC/EN 60898-1

Icn: 10 kA



SN 201 M

Number of poles	Rated current In A	Bbn 8012542 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
1+N	2	093855	SN201MC2	2CSS275101R0024		0.110	6
	4	093954	SN201MC4	2CSS275101R0044		0.110	6
	6	094050	SN201MC6	2CSS275101R0064		0.110	6
	10	094159	SN201MC10	2CSS275101R0104		0.110	6
	16	094258	SN201MC16	2CSS275101R0164		0.110	6
	20	094357	SN201MC20	2CSS275101R0204		0.110	6
	25	094456	SN201MC25	2CSS275101R0254		0.110	6
	32	094555	SN201MC32	2CSS275101R0324		0.110	6
	40	094654	SN201MC40	2CSS275101R0404		0.110	6

S200C Compact MCBs

Save up to 50% more of space in the installation

Easy to install

- Supply possible either from top or bottom side, with cables or busbars.
- All screws are on the same level for a fast and easy installation

Guaranteed security

Indication of the contacts status with I-ON/O-FF indication in green/red on the toggle

Dedicated space for QR CODE

Dedicated space for QR code with relevant product information

High performance clips

To facilitate the mounting and dismounting operation, guaranteeing an easy removal from a battery of device supplied with busbars

Laser printed information

Main technical information and product code are laser printed on the front side, visible also when the device is installed

Combination with accessories

Possibility to mount signal and auxiliary contacts either on right or left side - compatibility with all System Pro M compact accessories through the new SCC-IH6R



S200C series

One-sight overview



1P+1P
1 module



2P
1 module



3P
2 modules



4P
2 modules





Auxiliary SCC
auxiliary contact
and signal contact

- **S2011C: 1P+1P in 1M** - 6 kA braking capacity, B and C char up to 20 A.
- **S202C: 2P in 1M** - From 4,5 kA to 10 kA breaking capacity, B and C char up to 40 A. Including a dedicated version for traction.
- **S203C: 3P in 2M** - 6 kA breaking capacity, B and C char up to 32 A.
- **S204C: 4P in 2M** - 6 kA breaking capacity, B and C char up to 32 A.
- **SCC-IH6R auxiliary contact, SCC-S6R signal contact**

3 levels of breaking capacity

10 rated current variants



MCBs

S2011C - Technical features

S2011C			
Standards			
IEC/EN 60898-1			
Electrical features			
Number of poles			1P+1P
Number of modules			1M
Tripping Characteristic			B, C
Rated current I_n	A		$1 \leq I_n \leq 20$
Rated operational voltage U_e	V		240
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V		500 V AC
Overvoltage category			III
Pollution degree			2
Rated frequency f	Hz		50/60
Min operating voltage	V AC/DC		12
Max operating voltage	V AC		264
	V DC		48
Rated short-circuit capacity acc. to IEC/EN 60898-1	I_{cn}	A	6000
Rated short circuit breaking capacity acc. to IEC/EN 60947-2 (only referring to internal short circuit test)	ultimate I_{cu}	kA	6
	service I_{cs}	kA	6
Rated making and breaking capacity of one individual pole	I_{cn1}	A	6000
Rated short circuit breaking capacity acc. to IEC/EN 60947-2 in DC (only referring to internal short circuit test, tc 4ms)	ultimate I_{cu}	kA	6 kA @ 48 VDC
Grid distance	mm		35
Rated impulse withstand voltage (1.2/50μs) U_{imp}	kV		4 kV
Dielectric test voltage at ind. freq. for 1 min.	kV		2.5 kV (50 / 60Hz, 1 min.)
Energy limiting class			3
Mechanical features			
Housing type			Insulation group I, RAL 7035
Toggle type			Insulation group II, Black RAL 9005, sealable in ON-OFF positions
Electrical endurance		cycles (OFF-ON-OFF)	7000
Mechanical endurance		cycles (OFF-ON-OFF)	7000
Contact position indication (CPI)			Marking on toggle (I ON / 0 OFF)
Protection degree acc. to EN 60529	housing		IP40
	terminals		IP20
Resistance to Shock acc. to IEC 60068-2-27			40 g (x,y,z) - 18 shocks - 5ms half sinusoidal
Resistance to Vibrations acc. to IEC 60068-2-6			0.35 mm or 5g - 20 cycles at 5...150...5 Hz
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30		°C/RH	28 cycles with 55 °C/90–96 % and 25 °C/95–100 %
Reference temperature for tripping characteristics		°C	30
Ambient temperature (with daily average $\leq +35$ °C)		°C	-25...+55
Storage temperature		°C	-40...+70
Installation			
Terminal type	top / bottom		Fail-safe cage terminal
Cross-section of conductors (Solid/ Stranded)	top / bottom	mm ²	16/16
Cross-section of conductors (Flexible)	top / bottom	mm ²	10/10
Cross-section of busbars	top / bottom	mm ²	10/10
Tightening torque	top / bottom	Nm	1,2
Wire Stripping Length		mm	10
Screwdriver			No. 2 Pozidrive
Mounting type			on DIN rail EN 60715 (35 mm) by means of mounting clip
Mounting position			Vertical & Horizontal
Supply from			Top/Bottom terminals
Dimensions and weight			
Dimensions (H×D×W)	mm		85 x 69 x 17,6 mm
Weight	g		120
Combination with auxiliary elements			
Combinable with accessories and auxiliaries			YES, SCC-IH6R, SCC-S6R

MCBs

S202C - Technical features

		S202C L	S202C	S202C M
Standards				
Electrical features				
Number of poles		2P	2P	2P
Number of modules		1M	1M	1M
Tripping Characteristic		B, C	B, C	B, C
Rated current I _n	A	2 ≤ I _n ≤ 40	2 ≤ I _n ≤ 40	2 ≤ I _n ≤ 32
Rated operational voltage U _e	V	240	240	240
Rated insulation voltage U _i acc. to IEC/EN 60664-1	V	500 V AC	500 V AC	500 V AC
Overvoltage category		III	III	III
Pollution degree		2	2	2
Rated frequency f	Hz	50/60	50/60	50/60
Min operating voltage	V AC/DC	12	12	12
Max operating voltage	V AC	253	253	253
	V DC	110	110	110
Rated short-circuit capacity acc. to IEC/EN 60898-1 I _{cn}	A	4500	6000	10000
Rated short circuit breking capacity acc. to IEC/EN 60947-2	ultimate I _{cu}	kA	6	10
(only referring to internal short circuit test)				
	service I _{cs}	kA	4.5	6
Rated making and breaking capacity of one individual pole	I _{cn1}	A	4500	6000
Rated short circuit breaking capacity acc. to IEC/EN 60947-2 in DC	ultimate I _{cu}	kA	4.5 kA @ 110 VDC	6 kA @ 110 VDC
(only referring to internal short circuit test, tc 4ms)				-
Grid distance	mm	35	35	60
Rated impulse withstand voltage (1.2/50μs) U _{imp}	kV	4 kV	4 kV	4 kV
Dielectric test voltage at ind. freq. for 1 min.	kV	2.5 kV (50 / 60Hz, 1 min.)	2.5 kV (50 / 60Hz, 1 min.)	2.5 kV (50 / 60Hz, 1 min.)
Energy limiting class			3	
Mechanical features				
Housing type		Insulation group I, RAL 7035		
Toggle type		Insulation group II, Black RAL 9005, sealable in ON-OFF positions		
Electrical endurance	cycles (OFF-ON-OFF)	7000		
Mechanical endurance	cycles (OFF-ON-OFF)	7000		
Contact position indication (CPI)		Marking on toggle (I ON / 0 OFF)		
Protection degree acc. to EN 60529	housing		IP40	
	terminals		IP20	
Resistance to Shock acc. to IEC 60068-2-27		40 g (x,y,z) - 18 shocks - 5 ms half sinusoidal		
Resistance to Vibrations acc. to IEC 60068-2-6		0.35 mm or 5 g - 20 cycles at 5...150...5 Hz		
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	28 cycles with 55 °C/90–96 % and 25 °C/95–100 %		
Reference temperature for tripping characteristics	°C	30		
Ambient temperature (with daily average ≤ +35 °C)	°C	-25...+55		
Storage temperature	°C	-40...+70		
Installation				
Terminal type	top / bottom		Fail-safe cage terminal	
Cross-section of conductors (Solid/ Stranded)	top / bottom	mm²	16/16	
Cross-section of conductors (Flexible)	top / bottom	mm²	10/10	
Cross-section of busbars	top / bottom	mm²	10/10	
Tightening torque	top / bottom	Nm	1,2	
Wire Stripping Length		mm	10	
Screwdriver			No. 2 Pozidrive	
Mounting type			on DIN rail EN 60715 (35 mm) by means of mounting clip	
Mounting position			Vertical & Horizontal	
Supply from			Top/Bottom terminals	
Dimensions and weight				
Dimensions (H×D×W)	mm		85 x 69 x 17,6 mm	
Weight	g		125	
Combination with auxiliary elements				
Combinable with accessories and auxiliaries			YES, SCC-IH6R, SCC-S6R	

MCBs

S203C - Technical features

S203C			
Standards			
IEC/EN 60898-1			
Electrical features			
Number of poles			3P
Number of modules			2M
Tripping Characteristic			B, C
Rated current I_n	A		$2 \leq I_n \leq 32$
Rated operational voltage U_e	V		415
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V		500 V AC
Overvoltage category			III
Pollution degree			2
Rated frequency f	Hz		50/60
Min operating voltage	V AC/DC		12
Max operating voltage	V		440
Rated short-circuit capacity acc. to IEC/EN 60898-1	I_{cn}	A	6000
Rated short circuit breking capacity acc. to IEC/EN 60947-2 (only referring to internal short circuit test)	ultimate I_{cu}	kA	6
	service I_{cs}	kA	6
Rated making and breaking capacity of one individual pole	I_{cn1}	A	4500
Rated short circuit breaking capacity acc. to IEC/EN 60947-2 in DC (only referring to internal short circuit test, tc 4ms)	ultimate I_{cu}	kA	NA
Grid distance	mm		35
Rated impulse withstand voltage (1.2/50µs) U_{imp}	kV		4 kV
Dielectric test voltage at ind. freq. for 1 min.	kV		2.5 kV (50 / 60Hz, 1 min.)
Energy limiting class			3
Mechanical features			
Housing type			Insulation group I, RAL 7035
Toggle type			Insulation group II, Black RAL 9005, sealable in ON-OFF positions
Electrical endurance	cycles (OFF-ON-OFF)		7000
Mechanical endurance	cycles (OFF-ON-OFF)		7000
Contact position indication (CPI)			Marking on toggle (I ON / 0 OFF)
Protection degree acc. to EN 60529	housing		IP40
	terminals		IP20
Resistance to Shock acc. to IEC 60068-2-27			40 g (x,y,z) - 18 shocks - 5 ms half sinusoidal
Resistance to Vibrations acc. to IEC 60068-2-6			0.35 mm or 5 g - 20 cycles at 5...150...5 Hz
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH		28 cycles with 55 °C/90–96 % and 25 °C/95–100 %
Reference temperature for tripping characteristics	°C		30
Ambient temperature (with daily average $\leq +35$ °C)	°C		-25...+55
Storage temperature	°C		-40...+70
Installation			
Terminal type	top / bottom		Fail-safe cage terminal
Cross-section of conductors (Solid/ Stranded)	top / bottom	mm ²	16/16
Cross-section of conductors (Flexible)	top / bottom	mm ²	10/10
Cross-section of busbars	top / bottom	mm ²	10/10
Tightening torque	top / bottom	Nm	1,2
Wire Stripping Length		mm	10
Screwdriver			No. 2 Pozidrive
Mounting type			on DIN rail EN 60715 (35 mm) by means of mounting clip
Mounting position			Vertical & Horizontal
Supply from			Top/Bottom terminals
Dimensions and weight			
Dimensions (H×D×W)	mm		85 x 69 x 35,4 mm
Weight	g		190
Combination with auxiliary elements			
Combinable with accessories and auxiliaries			YES, SCC-IH6R, SCC-IH6L

MCBs

S204C - Technical features

S204C		
Standards		
IEC/EN 60898-1		
Electrical features		
Number of poles		4P
Number of modules		2M
Tripping Characteristic		B, C
Rated current I_n	A	$2 \leq I_n \leq 32$
Rated operational voltage U_e	V	415
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	500 V AC
Overvoltage category		III
Pollution degree		2
Rated frequency f	Hz	50/60
Min operating voltage	V AC/DC	12
Max operating voltage	V AC	440
	V DC	220
Rated short-circuit capacity acc. to IEC/EN 60898-1	I_{cn} A	6000
Rated short circuit breking capacity acc. to IEC/EN 60947-2 (only referring to internal short circuit test)	ultimate I_{cu} kA	6
	service I_{cs} kA	6
Rated making and breaking capacity of one individual pole	I_{cn1} A	4500
Rated short circuit breaking capacity acc. to IEC/EN 60947-2 in DC (only referring to internal short circuit test, tc 4ms)	ultimate I_{cu} kA	6kA @ 220 VDC
Grid distance	mm	35
Rated impulse withstand voltage (1.2/50μs) U_{imp}	kV	4 kV
Dielectric test voltage at ind. freq. for 1 min.	kV	2.5 kV (50 / 60Hz, 1 min.)
Energy limiting class		3
Mechanical features		
Housing type		Insulation group I, RAL 7035
Toggle type		Insulation group II, Black RAL 9005, sealable in ON-OFF positions
Electrical endurance	cycles (OFF-ON-OFF)	7000
Mechanical endurance	cycles (OFF-ON-OFF)	7000
Contact position indication (CPI)		Marking on toggle (I ON / 0 OFF)
Protection degree acc. to EN 60529	housing	IP40
	terminals	IP20
Resistance to Shock acc. to IEC 60068-2-27		40 g (x,y,z) - 18 shocks - 5 ms half sinusoidal
Resistance to Vibrations acc. to IEC 60068-2-6		0.35 mm or 5 g - 20 cycles at 5...150...5 Hz
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	28 cycles with 55 °C/90–96 % and 25 °C/95–100 %
Reference temperature for tripping characteristics	°C	30
Ambient temperature (with daily average $\leq +35$ °C)	°C	-25...+55
Storage temperature	°C	-40...+70
Installation		
Terminal type	top / bottom	Fail-safe cage terminal
Cross-section of conductors (Solid/ Stranded)	top / bottom mm ²	16/16
Cross-section of conductors (Flexible)	top / bottom mm ²	10/10
Cross-section of busbars	top / bottom mm ²	10/10
Tightening torque	top / bottom Nm	1,2
Wire Stripping Length	mm	10
Screwdriver		No. 2 Pozidrive
Mounting type		on DIN rail EN 60715 (35 mm) by means of mounting clip
Mounting position		Vertical & Horizontal
Supply from		Top/Bottom terminals
Dimensions and weight		
Dimensions (H×D×W)	mm	85 x 69 x 35,4 mm
Weight	g	250
Combination with auxiliary elements		
Combinable with accessories and auxiliaries		YES, SCC-IH6R, SCC-IH6L

MCBs

S200C Compact MCBs - Ordering data

S2011C: 1P+1P in 1M

Function: protection and control of the circuits against overloads and short-circuits

Applications: residential, commercial

Standard: IEC/EN 60898-1



S2011C

Number of poles	Breaking capacity	Tripping Char.	Rated Current I _n A	Bbn 8012542 EAN	Order details		Weight 1 piece kg	Pack unit pc.
					Type code	Order code		
1P+1P	6kA	B	2	731559	S2011C-B2	2CSS257420R0025	0,120	6
			4	731658	S2011C-B4	2CSS257420R0045	0,120	6
			6	731757	S2011C-B6	2CSS257420R0065	0,120	6
			10	731856	S2011C-B10	2CSS257420R0105	0,120	6
			13	731955	S2011C-B13	2CSS257420R0135	0,120	6
			16	732051	S2011C-B16	2CSS257420R0165	0,120	6
			20	732150	S2011C-B20	2CSS257420R0205	0,120	6
		C	1	732259	S2011C-C1	2CSS257420R0014	0,120	6
			2	732358	S2011C-C2	2CSS257420R0024	0,120	6
			4	732457	S2011C-C4	2CSS257420R0044	0,120	6
			6	732556	S2011C-C6	2CSS257420R0064	0,120	6
			10	732655	S2011C-C10	2CSS257420R0104	0,120	6
			13	732754	S2011C-C13	2CSS257420R0134	0,120	6
			16	732853	S2011C-C16	2CSS257420R0164	0,120	6
			20	732952	S2011C-C20	2CSS257420R0204	0,120	6

MCBs

S200C Compact MCBs - Ordering data



S202CM

S202C: 2P in 1M

Function: protection and control of the circuits against overloads and short-circuits

Applications: residential, commercial

Standard: IEC/EN 60898-1

Number of poles	Breaking capacity	Tripping Char.	Rated Current I _n A	Bbn 8012542 EAN	Order details		Weight 1 piece kg	Pack unit pc.
					Type code	Order code		
2P	4,5kA	C	2	733058	S202CL-C2	2CSS242420R0024	0,125	6
			4	733157	S202CL-C4	2CSS242420R0044	0,125	6
			6	733256	S202CL-C6	2CSS242420R0064	0,125	6
			10	733355	S202CL-C10	2CSS242420R0104	0,125	6
			16	733454	S202CL-C16	2CSS242420R0164	0,125	6
			20	733553	S202CL-C20	2CSS242420R0204	0,125	6
			25	733652	S202CL-C25	2CSS242420R0254	0,125	6
			32	733751	S202CL-C32	2CSS242420R0324	0,125	6
			40	733850	S202CL-C40	2CSS242420R0404	0,125	6
	6kA	B	2	733959	S202C-B2	2CSS252420R0025	0,125	6
			4	734055	S202C-B4	2CSS252420R0045	0,125	6
			6	734154	S202C-B6	2CSS252420R0065	0,125	6
			10	734253	S202C-B10	2CSS252420R0105	0,125	6
			13	734352	S202C-B13	2CSS252420R0135	0,125	6
			16	734451	S202C-B16	2CSS252420R0165	0,125	6
			20	734550	S202C-B20	2CSS252420R0205	0,125	6
			25	734659	S202C-B25	2CSS252420R0255	0,125	6
			32	734758	S202C-B32	2CSS252420R0325	0,125	6
			40	734857	S202C-B40	2CSS252420R0405	0,125	6
		C	2	734956	S202C-C2	2CSS252420R0024	0,125	6
			4	735052	S202C-C4	2CSS252420R0044	0,125	6
			6	735151	S202C-C6	2CSS252420R0064	0,125	6
			10	735250	S202C-C10	2CSS252420R0104	0,125	6
			13	735359	S202C-C13	2CSS252420R0134	0,125	6
			15	735458	S202C-C15	2CSS252420R0154	0,125	6
			16	735557	S202C-C16	2CSS252420R0164	0,125	6
			20	735656	S202C-C20	2CSS252420R0204	0,125	6
			25	735755	S202C-C25	2CSS252420R0254	0,125	6
			32	735854	S202C-C32	2CSS252420R0324	0,125	6
			40	735953	S202C-C40	2CSS252420R0404	0,125	6
	10kA	B	2	737056	S202CM-B2	2CSS272420R0025	0,125	6
			4	737155	S202CM-B4	2CSS272420R0045	0,125	6
			6	737254	S202CM-B6	2CSS272420R0065	0,125	6
			10	737353	S202CM-B10	2CSS272420R0105	0,125	6
			13	737452	S202CM-B13	2CSS272420R0135	0,125	6
			16	737551	S202CM-B16	2CSS272420R0165	0,125	6
			20	737650	S202CM-B20	2CSS272420R0205	0,125	6
			25	737759	S202CM-B25	2CSS272420R0255	0,125	6
			32	737858	S202CM-B32	2CSS272420R0325	0,125	6
		C	2	736059	S202CM-C2	2CSS272420R0024	0,125	6
			4	736158	S202CM-C4	2CSS272420R0044	0,125	6
			6	736257	S202CM-C6	2CSS272420R0064	0,125	6
			10	736356	S202CM-C10	2CSS272420R0104	0,125	6
			13	736455	S202CM-C13	2CSS272420R0134	0,125	6
			15	736554	S202CM-C15	2CSS272420R0154	0,125	6
			16	736653	S202CM-C16	2CSS272420R0164	0,125	6
			20	736752	S202CM-C20	2CSS272420R0204	0,125	6
			25	736851	S202CM-C25	2CSS272420R0254	0,125	6
			32	736950	S202CM-C32	2CSS272420R0324	0,125	6

MCBs

S200C Compact MCBs - Ordering data



S203C

S203C: 3P in 2M

Function: protection and control of the circuits against overloads and short-circuits

Applications: residential, commercial, industrial

Standard: IEC/EN 60898-1

Number of poles	Breaking capacity	Tripping Char.	Rated Current I _n A	Bbn 8012542 EAN	Order details		Weight 1 piece kg	Pack unit pc.
					Type code	Order code		
3P	6kA	B	6	737957	S203C-B6	2CSS253420R0065	0,190	1
			10	738053	S203C-B10	2CSS253420R0105	0,190	1
			16	738152	S203C-B16	2CSS253420R0165	0,190	1
			20	738251	S203C-B20	2CSS253420R0205	0,190	1
			25	738350	S203C-B25	2CSS253420R0255	0,190	1
			32	738459	S203C-B32	2CSS253420R0325	0,190	1
		C	6	738558	S203C-C6	2CSS253420R0064	0,190	1
			10	738657	S203C-C10	2CSS253420R0104	0,190	1
			16	738756	S203C-C16	2CSS253420R0164	0,190	1
			20	738855	S203C-C20	2CSS253420R0204	0,190	1
			25	738954	S203C-C25	2CSS253420R0254	0,190	1
			32	739050	S203C-C32	2CSS253420R0324	0,190	1

MCBs

S200C Compact MCBs - Ordering data

S204C: 4P in 2M

Function: protection and control of the circuits against overloads and short-circuits

Applications: residential, commercial, industrial

Standard: IEC/EN 60898-1



S204C

Number of poles	Breaking capacity	Tripping Char.	Rated Current I_n A	Bbn 8012542 EAN	Order details		Weight 1 piece kg	Pack unit pc.
					Type code	Order code		
4P	6kA	B	6	739159	S204C-B6	2CSS254420R0065	0,240	1
			10	739258	S204C-B10	2CSS254420R0105	0,240	1
			16	739357	S204C-B16	2CSS254420R0165	0,240	1
			20	739456	S204C-B20	2CSS254420R0205	0,240	1
			25	739555	S204C-B25	2CSS254420R0255	0,240	1
			32	739654	S204C-B32	2CSS254420R0325	0,240	1
		C	6	739753	S204C-C6	2CSS254420R0064	0,240	1
			10	739852	S204C-C10	2CSS254420R0104	0,240	1
			16	739951	S204C-C16	2CSS254420R0164	0,240	1
			20	740056	S204C-C20	2CSS254420R0204	0,240	1
			25	740155	S204C-C25	2CSS254420R0254	0,240	1
			32	740254	S204C-C32	2CSS254420R0324	0,240	1

MCBs

S 200 80A-100A series technical features



S 200 80-100A

S 200 80A-100A	
General Data	
Standards	IEC/EN 60898-1, IEC/EN 60947-2
Poles	1P, 2P, 3P, 4P, 1P+N, 3P+N
Tripping characteristics	B, C
Rated current I_n	80 A, 100 A
Rated frequency f	50/60 Hz
Rated insulation voltage U_i acc. to IEC/EN 60664-1 (VDE 0110-1)	440 V AC
Overvoltage category	III
Pollution degree	3
IEC/EN 60898-1	
Rated operational voltage U_n	1P: 230/400 V AC; 1P+N: 230 V AC; 2P, 3P, 4P, 3P+N: 400 V AC
Max. power frequency recovery voltage U_{max}	1P: 253/440 V AC; 1P+N: 253 V AC; 2P, 3P, 4P, 3P+N: 440 V AC
Min. operating voltage	12 V AC
Rated short-circuit capacity I_{cn}	6 kA
Grid distance	35
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)
Dielectrical test voltage	2 kV (50/60 Hz, 1 min.)
Reference temperature for tripping characteristics	B, C: 30 °C
Electrical endurance	cycles (OFF-ON-OFF) 10,000 ops. (AC); one cycle 2 s - ON, 28 s - OFF
IEC/EN 60947-2	
Rated operational voltage U_e	1P, 1P+N: 230 V AC; 2P, 3P, 4P, 3P+N: 400 V AC; 1P: 60V DC; 2P: 110V DC
Max. power frequency recovery voltage U_{max}	1P, 1P+N: 253 V AC; 2P, 3P, 4P, 3P+N: 440 V AC; 1P: 60V DC; 2P: 110V DC
Min. operating voltage	12 V AC
Rated ultimate short-circuit breaking capacity I_{cu}	6 kA
Rated service short-circuit breaking capacity I_{cs}	6 kA
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)
Dielectrical test voltage	2 kV (50/60 Hz, 1 min.)

MCBs

S 200 80A-100A series technical features



S 200 80-100A

Reference temperature for tripping characteristics	B, C: 55 °C
Electrical endurance	10,000 ops. (AC); one cycle 2 s - ON, 28 s - OFF
Mechanical data	
Housing	Insulation group I, RAL 7035
Toggle	Insulation group II, black, sealable
Contact position indication	Real CPI (red ON/green OFF)
Protection degree acc. to DIN EN 60529	IP20 ¹⁾ , IP40 in enclosure with cover
Mechanical endurance cycles (OFF-ON-OFF)	20,000 ops.
Shock resistance acc. to DIN EN 60068-2-27	25 g, 2 shocks, 13 ms
Vibration resistance acc. to DIN EN 60068-2-6	5 g, 20 cycles at 5...150...5 Hz at 0.8 I _n
Environmental conditions (Damp heat cyclic) acc. to DIN EN 60068-2-30	28 cycles with 55 °C/90-96 % and 25 °C/95-100 %
Ambient temperature	-25 ... +55 °C
Storage temperature	-40 ... +70 °C
S 200 80A-100A	
Installation	
Terminal	Failsafe bi-directional cache clamp
Cross-section of conductors (top/bottom)	solid, stranded: 50 mm ² / 50 mm ² flexible: 50 mm ² / 50 mm ²
Cross-section of busbars (top/bottom)	16 mm ² / 16 mm ²
Torque	3.0 Nm
Screwdriver	Nr. 2 Pozidriv
Mounting	On DIN rail 35 mm acc. to EN 60715 by fast clip
Mounting position	any
Supply	any
Dimensions and weight	
Mounting dimensions acc. to DIN 43880	Mounting dimension 1
Pole dimensions (H x T x B)	88.8 x 69 x 17.5
Pole weight	approx. 126 g
Combination with auxiliary elements	
Auxiliary contact	Yes
Signal/auxiliary contact	Yes
Shunt trip	Yes
Undervoltage release	Yes
Motor Operating Device	Yes

MCBs

S 200 80A-100A



S 201 80-100A



S 202 80-100A



S 203 80-100A



S 204 80-100A



S 201 80-100A NA



S 203 80-100A NA

The miniature circuit breakers of the System pro M compact® series S 200 provide state-of-the-art safety and comfort. They stand out due to their high performance and the wide range of accessories and approvals.

The additional electrical currents 80 A and 100 A complement the current portfolio of the System pro M compact® and offer maximum performance in a single module width.

- Clear contact position indication in red/green ("real CPI")
- Unique, patented twin terminal with captive screws and an increased opening for cables up to max. 50 mm², finger-proof (IP20)
- Busbar slot in the back for best visibility during installation
- High performance in building installations and industrial applications up to 6 kA at U_e = 400 V AC acc. to IEC/EN 60947-2 and IEC/EN 60898-1
- Individual product identification code
- Approved acc. to IEC/EN 60898-1 and IEC/EN 60947-2 for global use

Number of poles	Rated current In A	Bbn 4016779 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
B characteristic							
1	80	916516	S201-B80	2CDS251001R0805		0.128	10
	100	916530	S201-B100	2CDS251001R0825		0.128	10
2	80	916677	S202-B80	2CDS252001R0805		0.256	5
	100	916691	S202-B100	2CDS252001R0825		0.256	5
3	80	916271	S203-B80	2CDS253001R0805		0.384	1
	100	916295	S203-B100	2CDS253001R0825		0.384	1
4	80	916431	S204-B80	2CDS254001R0805		0.512	1
	100	916455	S204-B100	2CDS254001R0825		0.512	1
1+NA	80	916592	S201-B80NA	2CDS251103R0805		0.256	5
	100	916615	S201-B100NA	2CDS251103R0825		0.256	5
3+NA	80	916356	S203-B80NA	2CDS253103R0805		0.512	1
	100	916370	S203-B100NA	2CDS253103R0825		0.512	1
C characteristic							
1	80	916509	S201-C80	2CDS251001R0804		0.128	10
	100	916523	S201-C100	2CDS251001R0824		0.128	10
2	80	916660	S202-C80	2CDS252001R0804		0.256	5
	100	916684	S202-C100	2CDS252001R0824		0.256	5
3	80	916264	S203-C80	2CDS253001R0804		0.384	1
	100	916288	S203-C100	2CDS253001R0824		0.384	1
4	80	916424	S204-C80	2CDS254001R0804		0.512	1
	100	916448	S204-C100	2CDS254001R0824		0.512	1
1+NA	80	916585	S201-C80NA	2CDS251103R0804		0.256	5
	100	916608	S201-C100NA	2CDS251103R0824		0.256	5
3+NA	80	916349	S203-C80NA	2CDS253103R0804		0.512	1
	100	916363	S203-C100NA	2CDS253103R0824		0.512	1

MCBs

S 200 MT series technical features



S 200 MT

		S 200 MT
General Data	Standards	IEC/EN 60898-1, IEC/EN 60947-2 UL 1077, CSA 22.2 No. 235 GB/T 14048.2, GB/T 10963.1
	Poles	1P, 2P, 3P, 4P, 1P+N, 3P+N
	Tripping characteristics	B, C, D, K, Z
	Rated current I_n	from 0.2 ... 63 A
	Rated frequency f	50 / 60 Hz
	Rated insulation voltage U_i acc. to IEC/EN 60664-1	440 V AC
	Overvoltage category	III
	Pollution degree	3
	Electrical endurance	ops. $I_n < 32A$: 20,000 ops (AC), $I_n \geq 32A$: 10,000 ops. (AC); 1,000 ops. (DC); 1 cycle (2s - ON, 13s - OFF, $I_n \leq 32A$), 1 cycle (2s - ON, 28s - OFF, $I_n > 32A$)
Data acc. to IEC/EN 60947-2	Rated operational voltage U_n	1P: 230 V AC; 1P+N: 230 V AC; 2...4P: 440 V AC; 3P+N: 440 V AC
	Max. power frequency recovery voltage (U_{max})	1P: 253 V AC; 1P+N: 253 V AC; 2P...4P: 462 V AC; 3P+N: 462 V AC; 1P: 72 V DC; 2P: 125 V DC
	Min. operating voltage	12 V AC - 12 V DC
	Rated ultimate short-circuit breaking capacity I_{cn}	15 kA
	Rated service short-circuit breaking capacity I_{cn}	$\leq 40 A$: 11.2 kA 50, 63 A: 7.5 kA
	Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)
	Dielectric test voltage	2 kV (50 / 60 Hz, 1 min.)
	Reference temperature for tripping characteristics	B, C, D: 30°C K, Z: 55°C
Data acc. to IEC/EN 60898-1	Rated operational voltage U_n	1P: 230/400 V AC; 1P+N: 230 V AC; 2...4P: 400 V AC; 3P+N: 400 V AC
	Max. power frequency recovery voltage (U_{max})	1P: 253 V AC; 1P+N: 253 V AC; 2P: 440 V AC; 3...4P: 440 V AC; 3P+N: 440 V AC;
	Min. operating voltage	12 V AC - 12 V DC
	Rated short-circuit capacity I_{cn}	10 kA
	Energy limiting class (B, C up to 40 A)	3
	Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	4 kV (test voltage 6.2 kV at sea level, 5 kV at 2,000 m)
	Dielectric test voltage	2 kV (50 / 60 Hz, 1 min.)
	Reference temperature for tripping characteristics	B, C, D: 30 °C
Data acc. to UL1077/CSA 22.2 No. 235	Rated voltage	1 P: 277 V AC; 2...4 P: 277 V / 480Y 1P: 60 V DC; 2P...4P: 125 V DC
	Rated interrupting capacity acc. to UL 1077	6 kA AC; 10 kA DC
	Short-circuit current rating acc. to UL 489	--
	Application	Suppl. prot. for general use. Application Codes: TC2, OL0, SC: U1
	Reference temperature for tripping characteristics	B, C, D, K, Z: 25 °C
	Electrical endurance	ops. 6,000 ops (AC), 6,000 ops. (DC); 1 cycle (1 s - ON, 9 s - OFF)

MCBs

S 200 MT series technical features



S 200 MT

S 200 MT		
Mechanical Data	Housing	Insulation group I, RAL 7035
	Toggle	Insulation group II, black, sealable
	Contact position indication	Real CPI (green OFF / red ON)
	Protection degree acc. to EN 60529	IP20, IP40 in enclosure with cover
	Mechanical endurance	ops. 20,000 ops.
	Shock resistance acc. to IEC/EN 60068-2-27	25g - 2 shocks - 13 ms
	Vibration resistance acc. to IEC/EN 60068-2-6	5 g - 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 I _n
	Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	28 cycles with 55 °C/90-96 % and 25 °C/95-100 %
	Ambient temperature	-40 ... +70 °C the average temperature during a day is not exceeding +35°C
	Storage temperature	-40 ... +70 °C
Installation	Terminal	Failsafe bi-directional cylinder-lift terminal
	Cross-section of conductors (top/bottom)	
	Solid / Stranded	0.75 ... 35 mm ²
	Flexible	0.75 ... 25 mm ²
	Solid / Stranded	18 - 10 AWG
	Flexible	18 - 4 AWG
	Cross-section of busbars (top/bottom)	10 / 10 mm ² 14 - 8 AWG
	Tightening Torque	2.8 Nm 18 in-lbs.
	Screwdriver	No. 2 Pozidrive
	Mounting	on DIN rail 35 mm acc. to EN 60715 by fast clip
Dimensions and weight	Mounting position	any
	Supply	optional
	Mounting dimensions acc. to DIN 43880	Mounting dimension 1
Combination with auxiliary elements	Pole dimensions (H x D x W)	88 x 69 x 17.5 mm
	Pole weight	ca. 115 g

MCBs

S 200 MT series B characteristic

S 200 MT series

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables AC systems;

Standards: IEC/EN 60947-2 Icu = 15 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373



S 201 MT



S 202 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	1	9122023	S201MT-B1	2CDS271445R0015	0.112	10
	2	9128742	S201MT-B2	2CDS271445R0025	0.112	10
	3	9128773	S201MT-B3	2CDS271445R0035	0.112	10
	4	9128803	S201MT-B4	2CDS271445R0045	0.112	10
	5	9128834	S201MT-B5	2CDS271445R0055	0.112	10
	6	9128865	S201MT-B6	2CDS271445R0065	0.112	10
	8	9128896	S201MT-B8	2CDS271445R0085	0.112	10
	10	9128933	S201MT-B10	2CDS271445R0105	0.112	10
	13	9128971	S201MT-B13	2CDS271445R0135	0.115	10
	15	9129008	S201MT-B15	2CDS271445R0155	0.115	10
	16	9129053	S201MT-B16	2CDS271445R0165	0.115	10
	20	9129107	S201MT-B20	2CDS271445R0205	0.115	10
	25	9129152	S201MT-B25	2CDS271445R0255	0.115	10
	30	9129220	S201MT-B30	2CDS271445R0305	0.120	10
	32	9129275	S201MT-B32	2CDS271445R0325	0.120	10
	35	9129329	S201MT-B35	2CDS271445R0355	0.120	10
	40	9129398	S201MT-B40	2CDS271445R0405	0.120	10
	50	9129541	S201MT-B50	2CDS271445R0505	0.120	10
	60	9129718	S201MT-B60	2CDS271445R0605	0.120	10
	63	9129763	S201MT-B63	2CDS271445R0635	0.120	10
2	1	9130943	S202MT-B1	2CDS272445R0015	0.224	5
	2	9130974	S202MT-B2	2CDS272445R0025	0.224	5
	3	9131001	S202MT-B3	2CDS272445R0035	0.224	5
	4	9131032	S202MT-B4	2CDS272445R0045	0.224	5
	5	9131063	S202MT-B5	2CDS272445R0055	0.224	5
	6	9131094	S202MT-B6	2CDS272445R0065	0.224	5
	8	9131124	S202MT-B8	2CDS272445R0085	0.224	5
	10	9131162	S202MT-B10	2CDS272445R0105	0.224	5
	13	9131209	S202MT-B13	2CDS272445R0135	0.230	5
	15	9131230	S202MT-B15	2CDS272445R0155	0.230	5
	16	9131285	S202MT-B16	2CDS272445R0165	0.230	5
	20	9131339	S202MT-B20	2CDS272445R0205	0.230	5
	25	9131384	S202MT-B25	2CDS272445R0255	0.230	5
	30	9131452	S202MT-B30	2CDS272445R0305	0.240	5
	32	9131506	S202MT-B32	2CDS272445R0325	0.240	5
	35	9131551	S202MT-B35	2CDS272445R0355	0.240	5
	40	9131629	S202MT-B40	2CDS272445R0405	0.240	5
	50	9131773	S202MT-B50	2CDS272445R0505	0.240	5
	60	9131940	S202MT-B60	2CDS272445R0605	0.240	5
	63	9131995	S202MT-B63	2CDS272445R0635	0.240	5
Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		

MCBs

S 200 MT series B characteristic



S 203 MT



S 204 MT

3	1	9132060	S203MT-B1	2CDS273445R0015	0.336	1
	2	9132091	S203MT-B2	2CDS273445R0025	0.336	1
	3	9132121	S203MT-B3	2CDS273445R0035	0.336	1
	4	9132152	S203MT-B4	2CDS273445R0045	0.336	1
	5	9132183	S203MT-B5	2CDS273445R0055	0.336	1
	6	9132213	S203MT-B6	2CDS273445R0065	0.336	1
	8	9132244	S203MT-B8	2CDS273445R0085	0.336	1
	10	9132282	S203MT-B10	2CDS273445R0105	0.336	1
	13	9132329	S203MT-B13	2CDS273445R0135	0.345	1
	15	9132350	S203MT-B15	2CDS273445R0155	0.345	1
	16	9132404	S203MT-B16	2CDS273445R0165	0.345	1
	20	9132442	S203MT-B20	2CDS273445R0205	0.345	1
	25	9132497	S203MT-B25	2CDS273445R0255	0.345	1
	30	9132565	S203MT-B30	2CDS273445R0305	0.360	1
	32	9132619	S203MT-B32	2CDS273445R0325	0.360	1
	35	9132664	S203MT-B35	2CDS273445R0355	0.360	1
	40	9132732	S203MT-B40	2CDS273445R0405	0.360	1
	50	9132886	S203MT-B50	2CDS273445R0505	0.360	1
	60	9133050	S203MT-B60	2CDS273445R0605	0.360	1
	63	9133104	S203MT-B63	2CDS273445R0635	0.360	1
4	1	9134286	S204MT-B1	2CDS274445R0015	0.448	1
	2	9134316	S204MT-B2	2CDS274445R0025	0.448	1
	3	9134347	S204MT-B3	2CDS274445R0035	0.448	1
	4	9134378	S204MT-B4	2CDS274445R0045	0.448	1
	5	9134408	S204MT-B5	2CDS274445R0055	0.448	1
	6	9134439	S204MT-B6	2CDS274445R0065	0.448	1
	8	9134460	S204MT-B8	2CDS274445R0085	0.448	1
	10	9134507	S204MT-B10	2CDS274445R0105	0.448	1
	13	9134545	S204MT-B13	2CDS274445R0135	0.460	1
	15	9134576	S204MT-B15	2CDS274445R0155	0.460	1
	16	9134620	S204MT-B16	2CDS274445R0165	0.460	1
	20	9134668	S204MT-B20	2CDS274445R0205	0.460	1
	25	9134712	S204MT-B25	2CDS274445R0255	0.460	1
	30	9134781	S204MT-B30	2CDS274445R0305	0.480	1
	32	9134835	S204MT-B32	2CDS274445R0325	0.480	1
	35	9134880	S204MT-B35	2CDS274445R0355	0.480	1
	40	9134958	S204MT-B40	2CDS274445R0405	0.480	1
	50	9135108	S204MT-B50	2CDS274445R0505	0.480	1
	60	9135276	S204MT-B60	2CDS274445R0605	0.480	1
	63	9135320	S204MT-B63	2CDS274445R0635	0.480	1

MCBs

S 200 MT series C characteristic

S 200 MT series

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables AC systems;

Standards: IEC/EN 60947-2 Icu = 15 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373



S 201 MT



S 202 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	0.5	9129800	S201MT-C0.5	2CDS271445R0984	0.112	10
	1	9128711	S201MT-C1	2CDS271445R0014	0.112	10
	1.6	9129787	S201MT-C1.6	2CDS271445R0974	0.112	10
	2	9128735	S201MT-C2	2CDS271445R0024	0.112	10
	3	9128766	S201MT-C3	2CDS271445R0034	0.112	10
	4	9128797	S201MT-C4	2CDS271445R0044	0.112	10
	5	9128827	S201MT-C5	2CDS271445R0054	0.112	10
	6	9128858	S201MT-C6	2CDS271445R0064	0.112	10
	8	9128889	S201MT-C8	2CDS271445R0084	0.112	10
	10	9128926	S201MT-C10	2CDS271445R0104	0.112	10
	13	9128964	S201MT-C13	2CDS271445R0134	0.115	10
	15	9128995	S201MT-C15	2CDS271445R0154	0.115	10
	16	9129046	S201MT-C16	2CDS271445R0164	0.115	10
	20	9129091	S201MT-C20	2CDS271445R0204	0.115	10
	25	9129145	S201MT-C25	2CDS271445R0254	0.115	10
	30	9129213	S201MT-C30	2CDS271445R0304	0.120	10
	32	9129268	S201MT-C32	2CDS271445R0324	0.120	10
	35	9129312	S201MT-C35	2CDS271445R0354	0.120	10
	40	9129381	S201MT-C40	2CDS271445R0404	0.120	10
	50	9129534	S201MT-C50	2CDS271445R0504	0.120	10
	60	9129701	S201MT-C60	2CDS271445R0604	0.120	10
	63	9129756	S201MT-C63	2CDS271445R0634	0.120	10
2	0.5	9132039	S202MT-C0.5	2CDS272445R0984	0.224	5
	1	9130936	S202MT-C1	2CDS272445R0014	0.224	5
	1.6	9132015	S202MT-C1.6	2CDS272445R0974	0.224	5
	2	9130967	S202MT-C2	2CDS272445R0024	0.224	5
	3	9130998	S202MT-C3	2CDS272445R0034	0.224	5
	4	9131025	S202MT-C4	2CDS272445R0044	0.224	5
	5	9131056	S202MT-C5	2CDS272445R0054	0.224	5
	6	9131087	S202MT-C6	2CDS272445R0064	0.224	5
	8	9131117	S202MT-C8	2CDS272445R0084	0.224	5
	10	9131155	S202MT-C10	2CDS272445R0104	0.224	5
	13	9131193	S202MT-C13	2CDS272445R0134	0.230	5
	15	9131223	S202MT-C15	2CDS272445R0154	0.230	5
	16	9131278	S202MT-C16	2CDS272445R0164	0.230	5
	20	9131322	S202MT-C20	2CDS272445R0204	0.230	5
	25	9131377	S202MT-C25	2CDS272445R0254	0.230	5
	30	9131445	S202MT-C30	2CDS272445R0304	0.240	5
	32	9131490	S202MT-C32	2CDS272445R0324	0.240	5
	35	9131544	S202MT-C35	2CDS272445R0354	0.240	5
	40	9131612	S202MT-C40	2CDS272445R0404	0.240	5
	50	9131766	S202MT-C50	2CDS272445R0504	0.240	5
	60	9131933	S202MT-C60	2CDS272445R0604	0.240	5
	63	9131988	S202MT-C63	2CDS272445R0634	0.240	5

MCBs

S 200 MT series C characteristic



S 203 MT



S 204 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
3	0.5	9133142	S203MT-C0.5	2CDS273445R0984	0.336	1
	1	9132053	S203MT-C1	2CDS273445R0014	0.336	1
	1.6	9133128	S203MT-C1.6	2CDS273445R0974	0.336	1
	2	9132084	S203MT-C2	2CDS273445R0024	0.336	1
	3	9132114	S203MT-C3	2CDS273445R0034	0.336	1
	4	9132145	S203MT-C4	2CDS273445R0044	0.336	1
	5	9132176	S203MT-C5	2CDS273445R0054	0.336	1
	6	9132206	S203MT-C6	2CDS273445R0064	0.336	1
	8	9132237	S203MT-C8	2CDS273445R0084	0.336	1
	10	9132275	S203MT-C10	2CDS273445R0104	0.336	1
	13	9132312	S203MT-C13	2CDS273445R0134	0.345	1
	15	9132343	S203MT-C15	2CDS273445R0154	0.345	1
	16	9132398	S203MT-C16	2CDS273445R0164	0.345	1
	20	9132435	S203MT-C20	2CDS273445R0204	0.345	1
	25	9132480	S203MT-C25	2CDS273445R0254	0.345	1
	30	9132558	S203MT-C30	2CDS273445R0304	0.360	1
	32	9132602	S203MT-C32	2CDS273445R0324	0.360	1
	35	9132657	S203MT-C35	2CDS273445R0354	0.360	1
	40	9132725	S203MT-C40	2CDS273445R0404	0.360	1
	50	9132879	S203MT-C50	2CDS273445R0504	0.360	1
	60	9133043	S203MT-C60	2CDS273445R0604	0.360	1
	63	9133098	S203MT-C63	2CDS273445R0634	0.360	1
4	0.5	9135368	S204MT-C0.5	2CDS274445R0984	0.448	1
	1	9134279	S204MT-C1	2CDS274445R0014	0.448	1
	1.6	9135344	S204MT-C1.6	2CDS274445R0974	0.448	1
	2	9134309	S204MT-C2	2CDS274445R0024	0.448	1
	3	9134330	S204MT-C3	2CDS274445R0034	0.448	1
	4	9134361	S204MT-C4	2CDS274445R0044	0.448	1
	5	9134392	S204MT-C5	2CDS274445R0054	0.448	1
	6	9134422	S204MT-C6	2CDS274445R0064	0.448	1
	8	9134453	S204MT-C8	2CDS274445R0084	0.448	1
	10	9134491	S204MT-C10	2CDS274445R0104	0.448	1
	13	9134538	S204MT-C13	2CDS274445R0134	0.460	1
	15	9134569	S204MT-C15	2CDS274445R0154	0.460	1
	16	9134613	S204MT-C16	2CDS274445R0164	0.460	1
	20	9134651	S204MT-C20	2CDS274445R0204	0.460	1
	25	9134705	S204MT-C25	2CDS274445R0254	0.460	1
	30	9134774	S204MT-C30	2CDS274445R0304	0.480	1
	32	9134828	S204MT-C32	2CDS274445R0324	0.480	1
	35	9134873	S204MT-C35	2CDS274445R0354	0.480	1
	40	9134941	S204MT-C40	2CDS274445R0404	0.480	1
	50	9135092	S204MT-C50	2CDS274445R0504	0.480	1
	60	9135269	S204MT-C60	2CDS274445R0604	0.480	1
	63	9135313	S204MT-C63	2CDS274445R0634	0.480	1

MCBs

S 200 MT series D characteristic

S 200 MT series

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables AC systems;

Standards: IEC/EN 60947-2 Icu = 15 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373



S 201 MT



S 202 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	0.5	9129794	S201MT-D0.5	2CDS271445R0981	0.112	10
	1	9128704	S201MT-D1	2CDS271445R0011	0.112	10
	1.6	9129770	S201MT-D1.6	2CDS271445R0971	0.112	10
	2	9128728	S201MT-D2	2CDS271445R0021	0.112	10
	3	9128759	S201MT-D3	2CDS271445R0031	0.112	10
	4	9128780	S201MT-D4	2CDS271445R0041	0.112	10
	5	9128810	S201MT-D5	2CDS271445R0051	0.112	10
	6	9128841	S201MT-D6	2CDS271445R0061	0.112	10
	8	9128872	S201MT-D8	2CDS271445R0081	0.112	10
	10	9128919	S201MT-D10	2CDS271445R0101	0.112	10
	13	9128957	S201MT-D13	2CDS271445R0131	0.115	10
	15	9128988	S201MT-D15	2CDS271445R0151	0.115	10
	16	9129039	S201MT-D16	2CDS271445R0161	0.115	10
	20	9129084	S201MT-D20	2CDS271445R0201	0.115	10
	25	9129138	S201MT-D25	2CDS271445R0251	0.115	10
	30	9129206	S201MT-D30	2CDS271445R0301	0.120	10
	32	9129251	S201MT-D32	2CDS271445R0321	0.120	10
	35	9129305	S201MT-D35	2CDS271445R0351	0.120	10
	40	9129374	S201MT-D40	2CDS271445R0401	0.120	10
	50	9129527	S201MT-D50	2CDS271445R0501	0.120	10
	60	9129695	S201MT-D60	2CDS271445R0601	0.120	10
	63	9129749	S201MT-D63	2CDS271445R0631	0.120	10
2	0.5	9132022	S202MT-D0.5	2CDS272445R0981	0.224	5
	1	9130929	S202MT-D1	2CDS272445R0011	0.224	5
	1.6	9132008	S202MT-D1.6	2CDS272445R0971	0.224	5
	2	9130950	S202MT-D2	2CDS272445R0021	0.224	5
	3	9130981	S202MT-D3	2CDS272445R0031	0.224	5
	4	9131018	S202MT-D4	2CDS272445R0041	0.224	5
	5	9131049	S202MT-D5	2CDS272445R0051	0.224	5
	6	9131070	S202MT-D6	2CDS272445R0061	0.224	5
	8	9131100	S202MT-D8	2CDS272445R0081	0.224	5
	10	9131148	S202MT-D10	2CDS272445R0101	0.224	5
	13	9131186	S202MT-D13	2CDS272445R0131	0.230	5
	15	9131216	S202MT-D15	2CDS272445R0151	0.230	5
	16	9131261	S202MT-D16	2CDS272445R0161	0.230	5
	20	9131315	S202MT-D20	2CDS272445R0201	0.230	5
	25	9131360	S202MT-D25	2CDS272445R0251	0.230	5
	30	9131438	S202MT-D30	2CDS272445R0301	0.240	5
	32	9131483	S202MT-D32	2CDS272445R0321	0.240	5
	35	9131537	S202MT-D35	2CDS272445R0351	0.240	5
	40	9131605	S202MT-D40	2CDS272445R0401	0.240	5
	50	9131759	S202MT-D50	2CDS272445R0501	0.240	5
	60	9131926	S202MT-D60	2CDS272445R0601	0.240	5
	63	9131971	S202MT-D63	2CDS272445R0631	0.240	5

MCBs

S 200 MT series D characteristic



S 203 MT



S 204 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
3	0.5	9133135	S203MT-D0.5	2CDS273445R0981	0.336	1
	1	9132046	S203MT-D1	2CDS273445R0011	0.336	1
	1.6	9133111	S203MT-D1.6	2CDS273445R0971	0.336	1
	2	9132077	S203MT-D2	2CDS273445R0021	0.336	1
	3	9132107	S203MT-D3	2CDS273445R0031	0.336	1
	4	9132138	S203MT-D4	2CDS273445R0041	0.336	1
	5	9132169	S203MT-D5	2CDS273445R0051	0.336	1
	6	9132190	S203MT-D6	2CDS273445R0061	0.336	1
	8	9132220	S203MT-D8	2CDS273445R0081	0.336	1
	10	9132268	S203MT-D10	2CDS273445R0101	0.336	1
	13	9132305	S203MT-D13	2CDS273445R0131	0.345	1
	15	9132336	S203MT-D15	2CDS273445R0151	0.345	1
	16	9132381	S203MT-D16	2CDS273445R0161	0.345	1
	20	9132428	S203MT-D20	2CDS273445R0201	0.345	1
	25	9132473	S203MT-D25	2CDS273445R0251	0.345	1
	30	9132541	S203MT-D30	2CDS273445R0301	0.360	1
	32	9132596	S203MT-D32	2CDS273445R0321	0.360	1
	35	9132640	S203MT-D35	2CDS273445R0351	0.360	1
	40	9132718	S203MT-D40	2CDS273445R0401	0.360	1
	50	9132862	S203MT-D50	2CDS273445R0501	0.360	1
	60	9133036	S203MT-D60	2CDS273445R0601	0.360	1
	63	9133081	S203MT-D63	2CDS273445R0631	0.360	1
4	0.5	9135351	S204MT-D0.5	2CDS274445R0981	0.448	1
	1	9134262	S204MT-D1	2CDS274445R0011	0.448	1
	1.6	9135337	S204MT-D1.6	2CDS274445R0971	0.448	1
	2	9134293	S204MT-D2	2CDS274445R0021	0.448	1
	3	9134323	S204MT-D3	2CDS274445R0031	0.448	1
	4	9134354	S204MT-D4	2CDS274445R0041	0.448	1
	5	9134385	S204MT-D5	2CDS274445R0051	0.448	1
	6	9134415	S204MT-D6	2CDS274445R0061	0.448	1
	8	9134446	S204MT-D8	2CDS274445R0081	0.448	1
	10	9134484	S204MT-D10	2CDS274445R0101	0.448	1
	13	9134521	S204MT-D13	2CDS274445R0131	0.460	1
	15	9134552	S204MT-D15	2CDS274445R0151	0.460	1
	16	9134606	S204MT-D16	2CDS274445R0161	0.460	1
	20	9134644	S204MT-D20	2CDS274445R0201	0.460	1
	25	9134699	S204MT-D25	2CDS274445R0251	0.460	1
	30	9134767	S204MT-D30	2CDS274445R0301	0.480	1
	32	9134811	S204MT-D32	2CDS274445R0321	0.480	1
	35	9134866	S204MT-D35	2CDS274445R0351	0.480	1
	40	9134934	S204MT-D40	2CDS274445R0401	0.480	1
	50	9135085	S204MT-D50	2CDS274445R0501	0.480	1
	60	9135252	S204MT-D60	2CDS274445R0601	0.480	1
	63	9135306	S204MT-D63	2CDS274445R0631	0.480	1

MCBs

S 200 MT series K characteristic

S 200 MT series

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables AC systems;

Standards: IEC/EN 60947-2

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373



S 201 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	0.2	9128902	S201MT-K0.2	2CDS271445R0087	0.112	10
	0.3	9128940	S201MT-K0.3	2CDS271445R0117	0.112	10
	0.5	9129015	S201MT-K0.5	2CDS271445R0157	0.112	10
	0.75	9129077	S201MT-K0.75	2CDS271445R0187	0.112	10
	1	9129114	S201MT-K1	2CDS271445R0217	0.112	10
	1.6	9129169	S201MT-K1.6	2CDS271445R0257	0.112	10
	2	9129183	S201MT-K2	2CDS271445R0277	0.112	10
	3	9129237	S201MT-K3	2CDS271445R0317	0.112	10
	4	9129282	S201MT-K4	2CDS271445R0337	0.112	10
	5	9129336	S201MT-K5	2CDS271445R0357	0.112	10
	6	9129350	S201MT-K6	2CDS271445R0377	0.112	10
	8	9129404	S201MT-K8	2CDS271445R0407	0.112	10
	10	9129428	S201MT-K10	2CDS271445R0427	0.112	10
	13	9129442	S201MT-K13	2CDS271445R0447	0.115	10
	15	9129466	S201MT-K15	2CDS271445R0457	0.115	10
	16	9129480	S201MT-K16	2CDS271445R0467	0.115	10
	20	9129503	S201MT-K20	2CDS271445R0487	0.115	10
	25	9129558	S201MT-K25	2CDS271445R0517	0.115	10
	30	9129572	S201MT-K30	2CDS271445R0527	0.120	10
	32	9129596	S201MT-K32	2CDS271445R0537	0.120	10
	35	9129619	S201MT-K35	2CDS271445R0547	0.120	10
	40	9129633	S201MT-K40	2CDS271445R0557	0.120	10
	50	9129657	S201MT-K50	2CDS271445R0577	0.120	10
	60	9129671	S201MT-K60	2CDS271445R0587	0.120	10
	63	9129725	S201MT-K63	2CDS271445R0607	0.120	10

MCBs

S 200 MT series K characteristic



S 202 MT



S 203 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
2	0.2	9131131	S202MT-K0.2	2CDS272445R0087	0.224	5
	0.3	9131179	S202MT-K0.3	2CDS272445R0117	0.224	5
	0.5	9131247	S202MT-K0.5	2CDS272445R0157	0.224	5
	0.75	9131292	S202MT-K0.75	2CDS272445R0187	0.224	5
	1	9131346	S202MT-K1	2CDS272445R0217	0.224	5
	1.6	9131391	S202MT-K1.6	2CDS272445R0257	0.224	5
	2	9131414	S202MT-K2	2CDS272445R0277	0.224	5
	3	9131469	S202MT-K3	2CDS272445R0317	0.224	5
	4	9131513	S202MT-K4	2CDS272445R0337	0.224	5
	5	9131568	S202MT-K5	2CDS272445R0357	0.224	5
	6	9131582	S202MT-K6	2CDS272445R0377	0.224	5
	8	9131636	S202MT-K8	2CDS272445R0407	0.224	5
	10	9131650	S202MT-K10	2CDS272445R0427	0.224	5
	13	9131674	S202MT-K13	2CDS272445R0447	0.230	5
	15	9131698	S202MT-K15	2CDS272445R0457	0.230	5
	16	9131711	S202MT-K16	2CDS272445R0467	0.230	5
	20	9131735	S202MT-K20	2CDS272445R0487	0.230	5
	25	9131780	S202MT-K25	2CDS272445R0517	0.230	5
	30	9131803	S202MT-K30	2CDS272445R0527	0.240	5
	32	9131827	S202MT-K32	2CDS272445R0537	0.240	5
	35	9131841	S202MT-K35	2CDS272445R0547	0.240	5
	40	9131865	S202MT-K40	2CDS272445R0557	0.240	5
	50	9131889	S202MT-K50	2CDS272445R0577	0.240	5
	60	9131902	S202MT-K60	2CDS272445R0587	0.240	5
	63	9131957	S202MT-K63	2CDS272445R0607	0.240	5
3	0.2	9132251	S203MT-K0.2	2CDS273445R0087	0.336	1
	0.3	9132299	S203MT-K0.3	2CDS273445R0117	0.336	1
	0.5	9132367	S203MT-K0.5	2CDS273445R0157	0.336	1
	0.75	9132411	S203MT-K0.75	2CDS273445R0187	0.336	1
	1	9132459	S203MT-K1	2CDS273445R0217	0.336	1
	1.6	9132503	S203MT-K1.6	2CDS273445R0257	0.336	1
	2	9132527	S203MT-K2	2CDS273445R0277	0.336	1
	3	9132572	S203MT-K3	2CDS273445R0317	0.336	1
	4	9132626	S203MT-K4	2CDS273445R0337	0.336	1
	5	9132671	S203MT-K5	2CDS273445R0357	0.336	1
	6	9132695	S203MT-K6	2CDS273445R0377	0.336	1
	8	9132749	S203MT-K8	2CDS273445R0407	0.336	1
	10	9132763	S203MT-K10	2CDS273445R0427	0.336	1
	13	9132787	S203MT-K13	2CDS273445R0447	0.345	1
	15	9132800	S203MT-K15	2CDS273445R0457	0.345	1
	16	9132824	S203MT-K16	2CDS273445R0467	0.345	1
	20	9132848	S203MT-K20	2CDS273445R0487	0.345	1
	25	9132893	S203MT-K25	2CDS273445R0517	0.345	1
	30	9132916	S203MT-K30	2CDS273445R0527	0.360	1
	32	9132930	S203MT-K32	2CDS273445R0537	0.360	1
	35	9132954	S203MT-K35	2CDS273445R0547	0.360	1
	40	9132978	S203MT-K40	2CDS273445R0557	0.360	1
	50	9132992	S203MT-K50	2CDS273445R0577	0.360	1
	60	9133012	S203MT-K60	2CDS273445R0587	0.360	1
	63	9133067	S203MT-K63	2CDS273445R0607	0.360	1

MCBs

S 200 MT series K characteristic



S 204 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
4	0.2	9134477	S204MT-K0.2	2CDS274445R0087	0.448	1
	0.3	9134514	S204MT-K0.3	2CDS274445R0117	0.448	1
	0.5	9134583	S204MT-K0.5	2CDS274445R0157	0.448	1
	0.75	9134637	S204MT-K0.75	2CDS274445R0187	0.448	1
	1	9134675	S204MT-K1	2CDS274445R0217	0.448	1
	1.6	9134729	S204MT-K1.6	2CDS274445R0257	0.448	1
	2	9134743	S204MT-K2	2CDS274445R0277	0.448	1
	3	9134798	S204MT-K3	2CDS274445R0317	0.448	1
	4	9134842	S204MT-K4	2CDS274445R0337	0.448	1
	5	9134897	S204MT-K5	2CDS274445R0357	0.448	1
	6	9134910	S204MT-K6	2CDS274445R0377	0.448	1
	8	9134965	S204MT-K8	2CDS274445R0407	0.448	1
	10	9134989	S204MT-K10	2CDS274445R0427	0.448	1
	13	9135009	S204MT-K13	2CDS274445R0447	0.460	1
	15	9135023	S204MT-K15	2CDS274445R0457	0.460	1
	16	9135047	S204MT-K16	2CDS274445R0467	0.460	1
	20	9135061	S204MT-K20	2CDS274445R0487	0.460	1
	25	9135115	S204MT-K25	2CDS274445R0517	0.460	1
	30	9135139	S204MT-K30	2CDS274445R0527	0.480	1
	32	9135153	S204MT-K32	2CDS274445R0537	0.480	1
	35	9135177	S204MT-K35	2CDS274445R0547	0.480	1
	40	9135191	S204MT-K40	2CDS274445R0557	0.480	1
	50	9135214	S204MT-K50	2CDS274445R0577	0.480	1
	60	9135238	S204MT-K60	2CDS274445R0587	0.480	1
	63	9135283	S204MT-K63	2CDS274445R0607	0.480	1

MCBs

S 200 MT series Z characteristic

S 200 MT series

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables AC systems;

Standards: IEC/EN 60947-2 Icu = 15 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373



S 201 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	0.5	9129022	S201MT-Z0.5	2CDS271445R0158	0.112	10
	1	9129121	S201MT-Z1	2CDS271445R0218	0.112	10
	1.6	9129176	S201MT-Z1.6	2CDS271445R0258	0.112	10
	2	9129190	S201MT-Z2	2CDS271445R0278	0.112	10
	3	9129244	S201MT-Z3	2CDS271445R0318	0.112	10
	4	9129299	S201MT-Z4	2CDS271445R0338	0.112	10
	5	9129343	S201MT-Z5	2CDS271445R0358	0.112	10
	6	9129367	S201MT-Z6	2CDS271445R0378	0.112	10
	8	9129411	S201MT-Z8	2CDS271445R0408	0.112	10
	10	9129435	S201MT-Z10	2CDS271445R0428	0.112	10
	13	9129459	S201MT-Z13	2CDS271445R0448	0.115	10
	15	9129473	S201MT-Z15	2CDS271445R0458	0.115	10
	16	9129497	S201MT-Z16	2CDS271445R0468	0.115	10
	20	9129510	S201MT-Z20	2CDS271445R0488	0.115	10
	25	9129565	S201MT-Z25	2CDS271445R0518	0.115	10
	30	9129589	S201MT-Z30	2CDS271445R0528	0.120	10
	32	9129602	S201MT-Z32	2CDS271445R0538	0.120	10
	35	9129626	S201MT-Z35	2CDS271445R0548	0.120	10
	40	9129640	S201MT-Z40	2CDS271445R0558	0.120	10
	50	9129664	S201MT-Z50	2CDS271445R0578	0.120	10
	60	9129688	S201MT-Z60	2CDS271445R0588	0.120	10
	63	9129732	S201MT-Z63	2CDS271445R0608	0.120	10

MCBs

S 200 MT series Z characteristic



S 202 MT



S 203 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
2	0.5	9131254	S202MT-Z0.5	2CDS272445R0158	0.224	5
	1	9131353	S202MT-Z1	2CDS272445R0218	0.224	5
	1.6	9131407	S202MT-Z1.6	2CDS272445R0258	0.224	5
	2	9131421	S202MT-Z2	2CDS272445R0278	0.224	5
	3	9131476	S202MT-Z3	2CDS272445R0318	0.224	5
	4	9131520	S202MT-Z4	2CDS272445R0338	0.224	5
	5	9131575	S202MT-Z5	2CDS272445R0358	0.224	5
	6	9131599	S202MT-Z6	2CDS272445R0378	0.224	5
	8	9131643	S202MT-Z8	2CDS272445R0408	0.224	5
	10	9131667	S202MT-Z10	2CDS272445R0428	0.224	5
	13	9131681	S202MT-Z13	2CDS272445R0448	0.230	5
	15	9131704	S202MT-Z15	2CDS272445R0458	0.230	5
	16	9131728	S202MT-Z16	2CDS272445R0468	0.230	5
	20	9131742	S202MT-Z20	2CDS272445R0488	0.230	5
	25	9131797	S202MT-Z25	2CDS272445R0518	0.230	5
	30	9131810	S202MT-Z30	2CDS272445R0528	0.240	5
	32	9131834	S202MT-Z32	2CDS272445R0538	0.240	5
	35	9131858	S202MT-Z35	2CDS272445R0548	0.240	5
	40	9131872	S202MT-Z40	2CDS272445R0558	0.240	5
	50	9131896	S202MT-Z50	2CDS272445R0578	0.240	5
	60	9131919	S202MT-Z60	2CDS272445R0588	0.240	5
	63	9131964	S202MT-Z63	2CDS272445R0608	0.240	5
3	0.5	9132374	S203MT-Z0.5	2CDS273445R0158	0.336	1
	1	9132466	S203MT-Z1	2CDS273445R0218	0.336	1
	1.6	9132510	S203MT-Z1.6	2CDS273445R0258	0.336	1
	2	9132534	S203MT-Z2	2CDS273445R0278	0.336	1
	3	9132589	S203MT-Z3	2CDS273445R0318	0.336	1
	4	9132633	S203MT-Z4	2CDS273445R0338	0.336	1
	5	9132688	S203MT-Z5	2CDS273445R0358	0.336	1
	6	9132701	S203MT-Z6	2CDS273445R0378	0.336	1
	8	9132756	S203MT-Z8	2CDS273445R0408	0.336	1
	10	9132770	S203MT-Z10	2CDS273445R0428	0.336	1
	13	9132794	S203MT-Z13	2CDS273445R0448	0.345	1
	15	9132817	S203MT-Z15	2CDS273445R0458	0.345	1
	16	9132831	S203MT-Z16	2CDS273445R0468	0.345	1
	20	9132855	S203MT-Z20	2CDS273445R0488	0.345	1
	25	9132909	S203MT-Z25	2CDS273445R0518	0.345	1
	30	9132923	S203MT-Z30	2CDS273445R0528	0.360	1
	32	9132947	S203MT-Z32	2CDS273445R0538	0.360	1
	35	9132961	S203MT-Z35	2CDS273445R0548	0.360	1
	40	9132985	S203MT-Z40	2CDS273445R0558	0.360	1
	50	9133005	S203MT-Z50	2CDS273445R0578	0.360	1
	60	9133029	S203MT-Z60	2CDS273445R0588	0.360	1
	63	9133074	S203MT-Z63	2CDS273445R0608	0.360	1

MCBs

S 200 MT series Z characteristic



S 204 MT

Number of poles	Rated current [A]	Bbn 401677 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
4	0.5	9134590	S204MT-Z0.5	2CDS274445R0158	0.448	1
	1	9134682	S204MT-Z1	2CDS274445R0218	0.448	1
	1.6	9134736	S204MT-Z1.6	2CDS274445R0258	0.448	1
	2	9134750	S204MT-Z2	2CDS274445R0278	0.448	1
	3	9134804	S204MT-Z3	2CDS274445R0318	0.448	1
	4	9134859	S204MT-Z4	2CDS274445R0338	0.448	1
	5	9134903	S204MT-Z5	2CDS274445R0358	0.448	1
	6	9134927	S204MT-Z6	2CDS274445R0378	0.448	1
	8	9134972	S204MT-Z8	2CDS274445R0408	0.448	1
	10	9134996	S204MT-Z10	2CDS274445R0428	0.448	1
	13	9135016	S204MT-Z13	2CDS274445R0448	0.460	1
	15	9135030	S204MT-Z15	2CDS274445R0458	0.460	1
	16	9135054	S204MT-Z16	2CDS274445R0468	0.460	1
	20	9135078	S204MT-Z20	2CDS274445R0488	0.460	1
	25	9135122	S204MT-Z25	2CDS274445R0518	0.460	1
	30	9135146	S204MT-Z30	2CDS274445R0528	0.480	1
	32	9135160	S204MT-Z32	2CDS274445R0538	0.480	1
	35	9135184	S204MT-Z35	2CDS274445R0548	0.480	1
	40	9135207	S204MT-Z40	2CDS274445R0558	0.480	1
	50	9135221	S204MT-Z50	2CDS274445R0578	0.480	1
	60	9135245	S204MT-Z60	2CDS274445R0588	0.480	1
	63	9135290	S204MT-Z63	2CDS274445R0608	0.480	1

MCBs

S 200 MT UC series technical features



S 201 MT UC

S 200 MT UC		
Standards	Product Standard	IEC/EN 60947-2
	Hazard level acc. to EN 45545-2	R26/HL3
	Resistance to shocks and vibrations acc. to IEC 61373	Category 1 - Class A/B - Body mounted
General data	Poles	1P, 2P, 3P, 4P
	Tripping characteristics	B, C, K, Z
	Rated current I_n	A 0.2 - 63 A
	Rated frequency f	Hz 0/50/60 Hz
	Rated insulation voltage U_i acc. to IEC/EN 60664-1	V 253 V AC (phase to ground), 440 V AC (phase to phase)
	Overvoltage category	III
	Pollution degree	3
Data acc. to IEC/EN 60947-2	Rated operational voltage U_e	V 1P: 253 V AC, 220 V DC 2...4P: 440 V AC, 440 V DC
	Max. power frequency recovery voltage (U_{max})	V 1P: 266 V AC, 250 V DC 2...4P: 462 V AC, 500 V DC
	Min. operating voltage	V 12 V AC – 12 V DC
	Rated ultimate short-circuit breaking capacity I_{cu}	kA ≤ 40 A: 10 kA (AC); 10 kA (DC) >40 A: 6 kA (AC); 10 kA (DC)
	Rated service short-circuit breaking capacity I_{cs}	kA ≤ 40 A: 7.5 kA (AC); 10 kA (DC) >40 A: 6 kA (AC); 10 kA (DC)
	Rated impulse withstand voltage U_{imp} . (1.2/50 μ s)	kV 4 kV (test voltage 6.2 kV at sea level; 5 kV at 2,000 m)
	Dielectric test voltage	kV 2 kV (50/60 Hz, 1 min)
	Reference temperature for tripping characteristics	°C B, C: 55 °C; K, Z: 20 °C
	Electrical endurance	ops. $I_n < 32$ A: 20,000 ops. (AC), $I_n \geq 32$ A: 10,000 ops. (AC); 1,500 ops. (DC)

MCBs

S 200 MT UC series technical features



S 201 MT UC

				S 200 MT UC
Mechanical data	Housing			Insulation group I, RAL 7035
	Toggle			Insulation group II, black, sealable
	Contact position indicator			Real CPI (green OFF / red ON)
	Protection degree acc. to EN 60529			IP20, IP40 in enclosure with cover
	Mechanical endurance		ops.	20,000 ops.
	Shock resistance acc. to IEC/EN 60068-2-27			25 g - 2 shocks - 13 ms
	Vibration resistance acc. to IEC/EN 60068-2-6			5 g - 20 cycles at 5 ... 150 ... 5 Hz at 0.8 In
	Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30		°C/RH	28 cycles with 55 °C/90-96 % and 25 °C/95-100 %
	Ambient temperature (with daily average ≤ +35 °C)		°C	-40...+70°C
	Storage temperature		°C	-40 ... +70 °C
Installation	Terminal type			Failsafe bi-directional cylinder-lift terminal
	Cross-section of conductors (top/bottom)	solid/stranded	mm²	35 mm² / 35 mm²
		flexible	mm²	25 mm² / 25 mm²
			AWG	14 – 4 AWG (Cu only)
	Cross-section of busbars		mm²	10 mm² / 10 mm²
			AWG	14 – 8 AWG
	Tightening torque	IEC	Nm	2.8 Nm
		UL	in-lbs.	18 in-lbs.
	Screwdriver			No. 2 Pozidriv
	Mounting			on DIN-Rail 35 mm, acc. to EN 60715 by fast clip
Mounting position			any	
Supply			Please note polarity of device	
Dimensions and weight	Mounting dimensions acc. to DIN 43880			1
	Pole dimensions (H x D x W)		mm	85 x 69 x 17.5 mm
	Pole weight		g	approx. 125 g
Combination with auxiliary elements	See table			

MCBs

S 200 MT UC series B characteristic

Universal current range

S 200 MT UC series B characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Standards: IEC/EN 60947-2 Icu=10 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373

(for DC applications, please note polarity of device)



S 201 MT UC



S 202 MT UC



S 203 MT UC



S 204 MT UC

Number of poles	Rated current In A	Bbn 401361 EAN	Order details		Weight 1 piece kg	Pack unit pc.
			Type code	Order code		
1	6	4464911	S201MT-B6UC	2CDS271065R0065	0.117	10
	10	4464928	S201MT-B10UC	2CDS271065R0105	0.117	10
	13	4464935	S201MT-B13UC	2CDS271065R0135	0.120	10
	16	4464942	S201MT-B16UC	2CDS271065R0165	0.120	10
	20	4464959	S201MT-B20UC	2CDS271065R0205	0.120	10
	25	4464966	S201MT-B25UC	2CDS271065R0255	0.120	10
	32	4464973	S201MT-B32UC	2CDS271065R0325	0.125	10
	40	4464980	S201MT-B40UC	2CDS271065R0405	0.125	10
	50	4464997	S201MT-B50UC	2CDS271065R0505	0.125	10
2	63	4465000	S201MT-B63UC	2CDS271065R0635	0.125	10
	6	4465215	S202MT-B6UC	2CDS272065R0065	0.234	5
	10	4465222	S202MT-B10UC	2CDS272065R0105	0.234	5
	13	4465239	S202MT-B13UC	2CDS272065R0135	0.240	5
	16	4465246	S202MT-B16UC	2CDS272065R0165	0.240	5
	20	4465253	S202MT-B20UC	2CDS272065R0205	0.240	5
	25	4465260	S202MT-B25UC	2CDS272065R0255	0.240	5
	32	4465277	S202MT-B32UC	2CDS272065R0325	0.250	5
	40	4465284	S202MT-B40UC	2CDS272065R0405	0.250	5
3	50	4465291	S202MT-B50UC	2CDS272065R0505	0.250	5
	63	4465307	S202MT-B63UC	2CDS272065R0635	0.250	5
	6	4465512	S203MT-B6UC	2CDS273065R0065	0.351	1
	10	4465529	S203MT-B10UC	2CDS273065R0105	0.351	1
	13	4465536	S203MT-B13UC	2CDS273065R0135	0.360	1
	16	4465543	S203MT-B16UC	2CDS273065R0165	0.360	1
	20	4465550	S203MT-B20UC	2CDS273065R0205	0.360	1
	25	4465567	S203MT-B25UC	2CDS273065R0255	0.360	1
	32	4465574	S203MT-B32UC	2CDS273065R0325	0.375	1
4	40	4465581	S203MT-B40UC	2CDS273065R0405	0.375	1
	50	4465598	S203MT-B50UC	2CDS273065R0505	0.375	1
	63	4465604	S203MT-B63UC	2CDS273065R0635	0.375	1
	6	4465819	S204MT-B6UC	2CDS274065R0065	0.468	1
	10	4465826	S204MT-B10UC	2CDS274065R0105	0.468	1
	13	4465833	S204MT-B13UC	2CDS274065R0135	0.480	1
	16	4465840	S204MT-B16UC	2CDS274065R0165	0.480	1
	20	4465857	S204MT-B20UC	2CDS274065R0205	0.480	1
	25	4465864	S204MT-B25UC	2CDS274065R0255	0.480	1
	32	4465871	S204MT-B32UC	2CDS274065R0325	0.500	1
	40	4465888	S204MT-B40UC	2CDS274065R0405	0.500	1
	50	4465895	S204MT-B50UC	2CDS274065R0505	0.500	1
	63	4465901	S204MT-B63UC	2CDS274065R0635	0.500	1

MCBs

S 200 MT UC series C characteristic

Universal current range

S 200 MT UC series C characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Standards: IEC/EN 60947-2 Icu=10 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373

(for DC applications, please note polarity of device)



S 201 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
1	0.5	4448843	S201MT-C0,5UC	2CDS271065R0984	0.117	10
	1	4448218	S201MT-C1UC	2CDS271065R0014	0.117	10
	1.6	4448836	S201MT-C1,6UC	2CDS271065R0974	0.117	10
	2	4448225	S201MT-C2UC	2CDS271065R0024	0.117	10
	3	4448232	S201MT-C3UC	2CDS271065R0034	0.117	10
	4	4448249	S201MT-C4UC	2CDS271065R0044	0.117	10
	6	4448256	S201MT-C6UC	2CDS271065R0064	0.117	10
	8	4448263	S201MT-C8UC	2CDS271065R0084	0.117	10
	10	4448287	S201MT-C10UC	2CDS271065R0104	0.117	10
	13	4448300	S201MT-C13UC	2CDS271065R0134	0.120	10
	16	4448331	S201MT-C16UC	2CDS271065R0164	0.120	10
	20	4448355	S201MT-C20UC	2CDS271065R0204	0.120	10
	25	4448386	S201MT-C25UC	2CDS271065R0254	0.120	10
	32	4448454	S201MT-C32UC	2CDS271065R0324	0.125	10
	40	4448522	S201MT-C40UC	2CDS271065R0404	0.125	10
	50	4448652	S201MT-C50UC	2CDS271065R0504	0.125	10
	63	4448829	S201MT-C63UC	2CDS271065R0634	0.125	10



S 202 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
2	0.5	4449451	S202MT-C0,5UC	2CDS272065R0984	0.234	5
	1	4448850	S202MT-C1UC	2CDS272065R0014	0.234	5
	1.6	4449444	S202MT-C1,6UC	2CDS272065R0974	0.234	5
	2	4448867	S202MT-C2UC	2CDS272065R0024	0.234	5
	3	4448874	S202MT-C3UC	2CDS272065R0034	0.234	5
	4	4448881	S202MT-C4UC	2CDS272065R0044	0.234	5
	6	4448898	S202MT-C6UC	2CDS272065R0064	0.234	5
	8	4448904	S202MT-C8UC	2CDS272065R0084	0.234	5
	10	4448928	S202MT-C10UC	2CDS272065R0104	0.234	5
	13	4448942	S202MT-C13UC	2CDS272065R0134	0.240	5
	16	4448973	S202MT-C16UC	2CDS272065R0164	0.240	5
	20	4448997	S202MT-C20UC	2CDS272065R0204	0.240	5
	25	4449024	S202MT-C25UC	2CDS272065R0254	0.240	5
	32	4449093	S202MT-C32UC	2CDS272065R0324	0.250	5
	40	4449161	S202MT-C40UC	2CDS272065R0404	0.250	5
	50	4449291	S202MT-C50UC	2CDS272065R0504	0.250	5
	63	4449437	S202MT-C63UC	2CDS272065R0634	0.250	5

MCBs

S 200 MT UC series C characteristic

Universal current range



S 203 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
3	0.5	4448201	S203MT-C0,5UC	2CDS273065R0984	0.351	1
	1	4447600	S203MT-C1UC	2CDS273065R0014	0.351	1
	1.6	4448195	S203MT-C1,6UC	2CDS273065R0974	0.351	1
	2	4447617	S203MT-C2UC	2CDS273065R0024	0.351	1
	3	4447624	S203MT-C3UC	2CDS273065R0034	0.351	1
	4	4447631	S203MT-C4UC	2CDS273065R0044	0.351	1
	6	4447648	S203MT-C6UC	2CDS273065R0064	0.351	1
	8	4447655	S203MT-C8UC	2CDS273065R0084	0.351	1
	10	4447679	S203MT-C10UC	2CDS273065R0104	0.351	1
	13	4447693	S203MT-C13UC	2CDS273065R0134	0.360	1
	16	4447723	S203MT-C16UC	2CDS273065R0164	0.360	1
	20	4447747	S203MT-C20UC	2CDS273065R0204	0.360	1
	25	4447778	S203MT-C25UC	2CDS273065R0254	0.360	1
	32	4447846	S203MT-C32UC	2CDS273065R0324	0.375	1
	40	4447914	S203MT-C40UC	2CDS273065R0404	0.375	1
	50	4448041	S203MT-C50UC	2CDS273065R0504	0.375	1
	63	4448188	S203MT-C63UC	2CDS273065R0634	0.375	1



S 204 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
4	0.5	4447563	S204MT-C0,5UC	2CDS274065R0984	0.468	1
	1	4446948	S204MT-C1UC	2CDS274065R0014	0.468	1
	1.6	4447556	S204MT-C1,6UC	2CDS274065R0974	0.468	1
	2	4446955	S204MT-C2UC	2CDS274065R0024	0.468	1
	3	4446962	S204MT-C3UC	2CDS274065R0034	0.468	1
	4	4446979	S204MT-C4UC	2CDS274065R0044	0.468	1
	6	4446986	S204MT-C6UC	2CDS274065R0064	0.468	1
	8	4446993	S204MT-C8UC	2CDS274065R0084	0.468	1
	10	4447013	S204MT-C10UC	2CDS274065R0104	0.468	1
	13	4447037	S204MT-C13UC	2CDS274065R0134	0.480	1
	16	4447068	S204MT-C16UC	2CDS274065R0164	0.480	1
	20	4447082	S204MT-C20UC	2CDS274065R0204	0.480	1
	25	4447112	S204MT-C25UC	2CDS274065R0254	0.480	1
	32	4447181	S204MT-C32UC	2CDS274065R0324	0.500	1
	40	4447259	S204MT-C40UC	2CDS274065R0404	0.500	1
	50	4447389	S204MT-C50UC	2CDS274065R0504	0.500	1
	63	4447549	S204MT-C63UC	2CDS274065R0634	0.500	1

MCBs

S 200 MT UC series K characteristic

Universal current range

S 200 MT UC series K characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Standards: IEC/EN 60947-2 Icu=10 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373

(for DC applications, please note polarity of device)



S 201 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
1	0.2	4448270	S201MT-K0,2UC	2CDS271065R0087	0.117	10
	0.3	4448294	S201MT-K0,3UC	2CDS271065R0117	0.117	10
	0.5	4448317	S201MT-K0,5UC	2CDS271065R0157	0.117	10
	0.75	4448348	S201MT-K0,75UC	2CDS271065R0187	0.117	10
	1	4448362	S201MT-K1UC	2CDS271065R0217	0.117	10
	1.6	4448393	S201MT-K1,6UC	2CDS271065R0257	0.117	10
	2	4448416	S201MT-K2UC	2CDS271065R0277	0.117	10
	3	4448430	S201MT-K3UC	2CDS271065R0317	0.117	10
	4	4448461	S201MT-K4UC	2CDS271065R0337	0.117	10
	5	4448485	S201MT-K5UC	2CDS271065R0357	0.117	10
	6	4448508	S201MT-K6UC	2CDS271065R0377	0.117	10
	8	4448539	S201MT-K8UC	2CDS271065R0407	0.117	10
	10	4448553	S201MT-K10UC	2CDS271065R0427	0.117	10
	13	4448577	S201MT-K13UC	2CDS271065R0447	0.120	10
	15	4448591	S201MT-K15UC	2CDS271065R0457	0.120	10
	16	4448614	S201MT-K16UC	2CDS271065R0467	0.120	10
	20	4448638	S201MT-K20UC	2CDS271065R0487	0.120	10
	25	4448669	S201MT-K25UC	2CDS271065R0517	0.120	10
	30	4448683	S201MT-K30UC	2CDS271065R0527	0.125	10
	32	4448706	S201MT-K32UC	2CDS271065R0537	0.125	10
	35	4448720	S201MT-K35UC	2CDS271065R0547	0.125	10
	40	4448744	S201MT-K40UC	2CDS271065R0557	0.125	10
	50	4448768	S201MT-K50UC	2CDS271065R0577	0.125	10
	60	4448782	S201MT-K60UC	2CDS271065R0587	0.125	10
	63	4448805	S201MT-K63UC	2CDS271065R0607	0.125	10

MCBs

S 200 MT UC series K characteristic

Universal current range



S 202 MT UC



S 203 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
2	0.2	4448911	S202MT-K0,2UC	2CDS272065R0087	0.234	5
	0.3	4448935	S202MT-K0,3UC	2CDS272065R0117	0.234	5
	0.5	4448959	S202MT-K0,5UC	2CDS272065R0157	0.234	5
	0.75	4448980	S202MT-K0,75UC	2CDS272065R0187	0.234	5
	1	4449000	S202MT-K1UC	2CDS272065R0217	0.234	5
	1.6	4449031	S202MT-K1,6UC	2CDS272065R0257	0.234	5
	2	4449055	S202MT-K2UC	2CDS272065R0277	0.234	5
	3	4449079	S202MT-K3UC	2CDS272065R0317	0.234	5
	4	4449109	S202MT-K4UC	2CDS272065R0337	0.234	5
	5	4449123	S202MT-K5UC	2CDS272065R0357	0.234	5
	6	4449147	S202MT-K6UC	2CDS272065R0377	0.234	5
	8	4449178	S202MT-K8UC	2CDS272065R0407	0.234	5
	10	4449192	S202MT-K10UC	2CDS272065R0427	0.234	5
	13	4449215	S202MT-K13UC	2CDS272065R0447	0.240	5
	15	4449239	S202MT-K15UC	2CDS272065R0457	0.240	5
	16	4449253	S202MT-K16UC	2CDS272065R0467	0.240	5
	20	4449277	S202MT-K20UC	2CDS272065R0487	0.240	5
	25	4449307	S202MT-K25UC	2CDS272065R0517	0.240	5
	30	4449321	S202MT-K30UC	2CDS272065R0527	0.250	5
	32	4449345	S202MT-K32UC	2CDS272065R0537	0.250	5
	35	4449369	S202MT-K35UC	2CDS272065R0547	0.250	5
3	40	4449383	S202MT-K40UC	2CDS272065R0557	0.250	5
	50	4449406	S202MT-K50UC	2CDS272065R0577	0.250	5
	60	4449420	S202MT-K60UC	2CDS272065R0587	0.250	5
	63	4447587	S202MT-K63UC	2CDS272065R0607	0.250	5
	0.2	4447662	S203MT-K0,2UC	2CDS273065R0087	0.351	1
	0.3	4447686	S203MT-K0,3UC	2CDS273065R0117	0.351	1
	0.5	4447709	S203MT-K0,5UC	2CDS273065R0157	0.351	1
	0.75	4447730	S203MT-K0,75UC	2CDS273065R0187	0.351	1
	1	4447754	S203MT-K1UC	2CDS273065R0217	0.351	1
	1.6	4447785	S203MT-K1,6UC	2CDS273065R0257	0.351	1
	2	4447808	S203MT-K2UC	2CDS273065R0277	0.351	1
	3	4447822	S203MT-K3UC	2CDS273065R0317	0.351	1
	4	4447853	S203MT-K4UC	2CDS273065R0337	0.351	1
	5	4447877	S203MT-K5UC	2CDS273065R0357	0.351	1
	6	4447891	S203MT-K6UC	2CDS273065R0377	0.351	1
	8	4447921	S203MT-K8UC	2CDS273065R0407	0.351	1
	10	4447945	S203MT-K10UC	2CDS273065R0427	0.351	1
	13	4447969	S203MT-K13UC	2CDS273065R0447	0.360	1
	15	4447983	S203MT-K15UC	2CDS273065R0457	0.360	1
	16	4448003	S203MT-K16UC	2CDS273065R0467	0.360	1
	20	4448027	S203MT-K20UC	2CDS273065R0487	0.360	1
	25	4448058	S203MT-K25UC	2CDS273065R0517	0.360	1
	30	4448072	S203MT-K30UC	2CDS273065R0527	0.375	1
	32	4448096	S203MT-K32UC	2CDS273065R0537	0.375	1
	35	4448119	S203MT-K35UC	2CDS273065R0547	0.375	1
	40	4448133	S203MT-K40UC	2CDS273065R0557	0.375	1
	50	4448157	S203MT-K50UC	2CDS273065R0577	0.375	1
	60	4448171	S203MT-K60UC	2CDS273065R0587	0.375	1
	63	4446924	S203MT-K63UC	2CDS273065R0607	0.375	1

MCBs

S 200 MT UC series K characteristic

Universal current range



S 204 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
4	0.2	4447006	S204MT-K0,2UC	2CDS274065R0087	0.468	1
	0.3	4447020	S204MT-K0,3UC	2CDS274065R0117	0.468	1
	0.5	4447044	S204MT-K0,5UC	2CDS274065R0157	0.468	1
	0.75	4447075	S204MT-K0,75UC	2CDS274065R0187	0.468	1
	1	4447099	S204MT-K1UC	2CDS274065R0217	0.468	1
	1.6	4447129	S204MT-K1,6UC	2CDS274065R0257	0.468	1
	2	4447143	S204MT-K2UC	2CDS274065R0277	0.468	1
	3	4447167	S204MT-K3UC	2CDS274065R0317	0.468	1
	4	4447198	S204MT-K4UC	2CDS274065R0337	0.468	1
	5	4447211	S204MT-K5UC	2CDS274065R0357	0.468	1
	6	4447235	S204MT-K6UC	2CDS274065R0377	0.468	1
	8	4447266	S204MT-K8UC	2CDS274065R0407	0.468	1
	10	4447280	S204MT-K10UC	2CDS274065R0427	0.468	1
	13	4447303	S204MT-K13UC	2CDS274065R0447	0.480	1
	15	4447327	S204MT-K15UC	2CDS274065R0457	0.480	1
	16	4447341	S204MT-K16UC	2CDS274065R0467	0.480	1
	20	4447365	S204MT-K20UC	2CDS274065R0487	0.480	1
	25	4447396	S204MT-K25UC	2CDS274065R0517	0.480	1
	30	4447419	S204MT-K30UC	2CDS274065R0527	0.500	1
	32	4447433	S204MT-K32UC	2CDS274065R0537	0.500	1
	35	4447457	S204MT-K35UC	2CDS274065R0547	0.500	1
	40	4447471	S204MT-K40UC	2CDS274065R0557	0.500	1
	50	4447495	S204MT-K50UC	2CDS274065R0577	0.500	1
	60	4447518	S204MT-K60UC	2CDS274065R0587	0.500	1
	63	4449468	S204MT-K63UC	2CDS274065R0607	0.500	1

MCBs

S 200 MT UC series Z characteristic

Universal current range

S 200 MT UC series Z characteristic

Function: protection and control of the circuits against overloads and short-circuits; protection of big length cables in TN and IT systems; version dedicated to application in direct current circuits for voltages up to 220 V DC 1 pole and 440 V DC 2, 3 and 4 poles.

Standards: IEC/EN 60947-2 Icu=10 kA

Hazard level R26/HL3 according to EN 45545

Category 1 - Class A/B (Body mounted) according to IEC 61373

(for DC applications, please note polarity of device)



S 201 MT UC



S 202 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
1	0.5	4448324	S201MT-Z0,5UC	2CDS271065R0158	0.117	10
	1	4448379	S201MT-Z1UC	2CDS271065R0218	0.117	10
	1.6	4448409	S201MT-Z1,6UC	2CDS271065R0258	0.117	10
	2	4448423	S201MT-Z2UC	2CDS271065R0278	0.117	10
	3	4448447	S201MT-Z3UC	2CDS271065R0318	0.117	10
	4	4448478	S201MT-Z4UC	2CDS271065R0338	0.117	10
	5	4448492	S201MT-Z5UC	2CDS271065R0358	0.117	10
	6	4448515	S201MT-Z6UC	2CDS271065R0378	0.117	10
	8	4448546	S201MT-Z8UC	2CDS271065R0408	0.117	10
	10	4448560	S201MT-Z10UC	2CDS271065R0428	0.117	10
	15	4448607	S201MT-Z15UC	2CDS271065R0458	0.120	10
	16	4448621	S201MT-Z16UC	2CDS271065R0468	0.120	10
	20	4448645	S201MT-Z20UC	2CDS271065R0488	0.120	10
	25	4448676	S201MT-Z25UC	2CDS271065R0518	0.120	10
	30	4448690	S201MT-Z30UC	2CDS271065R0528	0.125	10
	32	4448713	S201MT-Z32UC	2CDS271065R0538	0.125	10
	35	4448737	S201MT-Z35UC	2CDS271065R0548	0.125	10
	40	4448751	S201MT-Z40UC	2CDS271065R0558	0.125	10
	50	4448775	S201MT-Z50UC	2CDS271065R0578	0.125	10
	60	4448799	S201MT-Z60UC	2CDS271065R0588	0.125	10
	63	4448812	S201MT-Z63UC	2CDS271065R0608	0.125	10
2	0.5	4448966	S202MT-Z0,5UC	2CDS272065R0158	0.234	5
	1	4449017	S202MT-Z1UC	2CDS272065R0218	0.234	5
	1.6	4449048	S202MT-Z1,6UC	2CDS272065R0258	0.234	5
	2	4449062	S202MT-Z2UC	2CDS272065R0278	0.234	5
	3	4449086	S202MT-Z3UC	2CDS272065R0318	0.234	5
	4	4449116	S202MT-Z4UC	2CDS272065R0338	0.234	5
	5	4449130	S202MT-Z5UC	2CDS272065R0358	0.234	5
	6	4449154	S202MT-Z6UC	2CDS272065R0378	0.234	5
	8	4449185	S202MT-Z8UC	2CDS272065R0408	0.234	5
	10	4449208	S202MT-Z10UC	2CDS272065R0428	0.234	5
	15	4449246	S202MT-Z15UC	2CDS272065R0458	0.240	5
	16	4449260	S202MT-Z16UC	2CDS272065R0468	0.240	5
	20	4449284	S202MT-Z20UC	2CDS272065R0488	0.240	5
	25	4449314	S202MT-Z25UC	2CDS272065R0518	0.240	5
	30	4449338	S202MT-Z30UC	2CDS272065R0528	0.250	5
	32	4449352	S202MT-Z32UC	2CDS272065R0538	0.250	5
	35	4449376	S202MT-Z35UC	2CDS272065R0548	0.250	5
	40	4449390	S202MT-Z40UC	2CDS272065R0558	0.250	5
	50	4449413	S202MT-Z50UC	2CDS272065R0578	0.250	5
	60	4447570	S202MT-Z60UC	2CDS272065R0588	0.250	5
	63	4447594	S202MT-Z63UC	2CDS272065R0608	0.250	5

MCBs

S 200 MT UC series Z characteristic

Universal current range



S 203 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A	EAN	Type code	Order code	kg	pc.
3	0.5	4447716	S203MT-Z0,5UC	2CDS273065R0158	0.351	1
	1	4447761	S203MT-Z1UC	2CDS273065R0218	0.351	1
	1.6	4447792	S203MT-Z1,6UC	2CDS273065R0258	0.351	1
	2	4447815	S203MT-Z2UC	2CDS273065R0278	0.351	1
	3	4447839	S203MT-Z3UC	2CDS273065R0318	0.351	1
	4	4447860	S203MT-Z4UC	2CDS273065R0338	0.351	1
	5	4447884	S203MT-Z5UC	2CDS273065R0358	0.351	1
	6	4447907	S203MT-Z6UC	2CDS273065R0378	0.351	1
	8	4447938	S203MT-Z8UC	2CDS273065R0408	0.351	1
	10	4447952	S203MT-Z10UC	2CDS273065R0428	0.351	1
	15	4447990	S203MT-Z15UC	2CDS273065R0458	0.360	1
	16	4448010	S203MT-Z16UC	2CDS273065R0468	0.360	1
	20	4448034	S203MT-Z20UC	2CDS273065R0488	0.360	1
	25	4448065	S203MT-Z25UC	2CDS273065R0518	0.360	1
	30	4448089	S203MT-Z30UC	2CDS273065R0528	0.375	1
	32	4448102	S203MT-Z32UC	2CDS273065R0538	0.375	1
	35	4448126	S203MT-Z35UC	2CDS273065R0548	0.375	1
	40	4448140	S203MT-Z40UC	2CDS273065R0558	0.375	1
	50	4448164	S203MT-Z50UC	2CDS273065R0578	0.375	1
	60	4446917	S203MT-Z60UC	2CDS273065R0588	0.375	1
	63	4446931	S203MT-Z63UC	2CDS273065R0608	0.375	1



S 204 MT UC

Number of poles	Rated current	Bbn 401361	Order details		Weight 1 piece	Pack unit
	In A		EAN	Type code		
4	0.5	4447051	S204MT-Z0,5UC	2CDS274065R0158	0.468	1
	1	4447105	S204MT-Z1UC	2CDS274065R0218	0.468	1
	1.6	4447136	S204MT-Z1,6UC	2CDS274065R0258	0.468	1
	2	4447150	S204MT-Z2UC	2CDS274065R0278	0.468	1
	3	4447174	S204MT-Z3UC	2CDS274065R0318	0.468	1
	4	4447204	S204MT-Z4UC	2CDS274065R0338	0.468	1
	5	4447228	S204MT-Z5UC	2CDS274065R0358	0.468	1
	6	4447242	S204MT-Z6UC	2CDS274065R0378	0.468	1
	8	4447273	S204MT-Z8UC	2CDS274065R0408	0.468	1
	10	4447297	S204MT-Z10UC	2CDS274065R0428	0.468	1
	15	4447334	S204MT-Z15UC	2CDS274065R0458	0.480	1
	16	4447358	S204MT-Z16UC	2CDS274065R0468	0.480	1
	20	4447372	S204MT-Z20UC	2CDS274065R0488	0.480	1
	25	4447402	S204MT-Z25UC	2CDS274065R0518	0.480	1
	30	4447426	S204MT-Z30UC	2CDS274065R0528	0.500	1
	32	4447440	S204MT-Z32UC	2CDS274065R0538	0.500	1
	35	4447464	S204MT-Z35UC	2CDS274065R0548	0.500	1
	40	4447488	S204MT-Z40UC	2CDS274065R0558	0.500	1
	50	4447501	S204MT-Z50UC	2CDS274065R0578	0.500	1
	60	4447525	S204MT-Z60UC	2CDS274065R0588	0.500	1
	63	4447532	S204MT-Z63UC	2CDS274065R0608	0.500	1

MCBs

S 202 TC technical features



S 202 TC

			S 202 TC
General data	Standards		IEC/EN 60898-1
	Number of poles		2P
	Number of modules		1
	Tripping Characteristic		B, C
	Rated current I_n	A	$2 \leq I_n \leq 32$
	Rated voltage U_e	V	240
	Insulation voltage U_i	V	500 V AC
	Overvoltage category		III
	Pollution degree		2
	Rated frequency	Hz	50/60
	Min operating voltage	V AC/DC	12
	Max operating voltage	V	253
	Rated breaking capacity acc. to IEC/EN 60898-1	I_{cn}	A 6000
	Rated breaking capacity acc. to IEC/EN 60947-2 (only referring to internal short circuit test)	ultimate I_{cu}	kA 6
		service I_{cs}	kA 6
	Rated breaking capacity I_{cn1} acc. to IEC/EN 60898-1	I_{cn1}	A 6000
	Rated breaking capacity acc. to IEC/EN 60947-2 in DC (only referring to internal short circuit test, poles connected in series, tc 4ms)	ultimate I_{cu}	kA 6 kA @ 110 VDC
	Rated impulse withstand voltage (1.2/50) U_{imp}	kV	4 kV
	Dielectric test voltage at ind. freq. for 1 min.	kV	2.5 kV (50 / 60Hz, 1 min.)
	Grid distance	mm	35
	Energy limiting class		3
Mechanical features	Housing		Insulation group I, RAL 7035
	Toggle		Insulation group II, Black RAL 9005, sealable in ON-OFF positions
	Electrical life	operations	7000
	Mechanical life	operations	7000
	Protection degree acc. to EN 60529	housing	IP40
		terminals	IP20
	Shock resistance acc. to IEC/EN 60068-2-27		40 g (x,y,z) - 18 shocks - 5 ms half sinusoidal
	Vibration resistance acc. to IEC/EN 60068-2-6		0.35 mm or 5 g - 20 cycles at 5...150...5 Hz
	Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	28 cycles with 55 °C/90–96 % and 25 °C/95–100 %
	Reference temperature for setting of thermal element	°C	30
	Ambient temperature (with daily average $\leq +35$ °C)	°C	-25...+55
	Storage temperature	°C	-40...+70
Installation	Terminal type	top / bottom	Fail-safe terminals, bi-directional cylinder-lift terminal (shock protected)
	Terminal size for cables	top / bottom	mm ² 10 flexible /16 rigid top & bottom
	Terminal size for busbars	top / bottom	mm ² 10/10
	Tightening torque	top / bottom	Nm 3
	Stripping length of the cable	mm	12
	Mounting		on DIN rail EN 60715 (35 mm) by means of mounting clip
	Mounting position		Vertical & Horizontal
Dimensions and weight	Supply from		Top/Bottom terminals
	Dimensions (H×D×W)	mm	86×70×17.8 mm
	Weight	g	125
Combination with auxiliary elements	Combinable with accessories and auxiliaries		YES, SCC-IH6R, SCC-IH6L

MCBs

S 202 TC characteristic



S 202 TC: 2P in 1M for traction

Function: protection and control of the circuits against overloads and short-circuits

Applications: traction

Standard: IEC/EN 60898-1

Plastic material acc. to UL94 and IEC/EN 60695-11-10: V0

Classification according to EN 45545-1:2013 and EN 45545-2:2013+A1:2015: R26/HL3, R22/HL3

Shocks and vibrations according to standard IEC/ EN 61373: Category 1, class B

N. poles	Breaking capacity	Tripping Char.	Rated Current In A	Bbn 8012542 EAN	Order details		Weight 1 piece kg	Pack unit pc.
					Type code	Order code		
2P	6kA	B	2	740353	S202TC-B2	2CSS252421R0025	0,125	6
			4	740452	S202TC-B4	2CSS252421R0045	0,125	6
			6	740551	S202TC-B6	2CSS252421R0065	0,125	6
			10	740650	S202TC-B10	2CSS252421R0105	0,125	6
			16	740759	S202TC-B16	2CSS252421R0165	0,125	6
			20	740858	S202TC-B20	2CSS252421R0205	0,125	6
			25	740957	S202TC-B25	2CSS252421R0255	0,125	6
			32	741053	S202TC-B32	2CSS252421R0325	0,125	6
		C	2	741152	S202TC-C2	2CSS252421R0024	0,125	6
			4	741251	S202TC-C4	2CSS252421R0044	0,125	6
			6	741350	S202TC-C6	2CSS252421R0064	0,125	6
			10	741459	S202TC-C10	2CSS252421R0104	0,125	6
			16	741558	S202TC-C16	2CSS252421R0164	0,125	6
			20	741657	S202TC-C20	2CSS252421R0204	0,125	6
			25	741756	S202TC-C25	2CSS252421R0254	0,125	6
			32	741855	S202TC-C32	2CSS252421R0324	0,125	6

Notes



High Performance MCB S800

Incomparable performances to meet the highest demand

Product marking

Clear and easy identification of product name and relevant characteristics

Interchangeable terminals

Possibility of having failsafe cage or ringlug terminal connections

QR code

Quick access to product main details and relevant documentation

Toggle position indication (TPI)

Clear identification of the moving contact (ON-OFF-TRIP)

Contact position indication (CPI)

Clear visualization of the device status

Suitable for upgrading your applications

Compatible with a wide range of accessories





Housing materials


The S800 range is designed with specific plastic materials to satisfy fire and smoke requirements in traction applications.

Plastic material V0 according to UL94 and classified with Hazard level R26/HL3; R22/HL2 according to EN45545-2 standard.



Shock and vibration resistance

The S800 range is tested according to IEC 61373 for Rolling stock equipment – Shock and vibration tests, meeting the requirements Category 1 / Class B.



Play it safe: display the operational state

3 status of the device, clearly identified with toggle position: ON-OFF-TRIP.

The trip position in the middle, identifies if the devices has tripped due to overcurrent.

OFF position indicates manual tripping.

In both cases contacts are opened and CPI becomes green.



Cage and ringlug terminals

Interchangeable terminal adapter, makes easy to change from cage to ring terminals, guarantying easy installation with high level of flexibility. Fast and safe connection of the conductors is ensured by the “onboard terminal shutter” integrated into the body of the terminal, thereby preventing incorrect under-clamping of the connections.



Reliability at high performance

The S800 product series guarantees a complete safe electrical isolation of the circuit in compliance to IEC 60947-2. It offers high breaking capacity and high rated current to cover different applications.



Wide range of accessories

The S800 range is compatible with a wide range of accessories that extend the functions of the MCB. Functioning not only as a protection device, but also for remote control and monitoring of the installation.

The range of accessories include auxiliary contacts, aux/signal contacts, remote switching unit, short circuit limiter, shunt operation releases, undervoltage releases, RCD block and busbars.

MCBs technical details

S800 range features



Compact high performance MCB with unbeatable short circuit performances

- **Compact:** the S800 series are high performance MCBs with compact dimension in only **27mm width per pole (1.5 module per pole)**.
- **High short circuit capacity:** the series can reach high short circuit performance capacity **up to 50kA** thanks to a specially designed double arcing chamber system, with two arcing chambers per pole (except for S800B with only one).
- **Energy and current limiting:** this technology allows not only to reach high short circuit breaking capacity, but also to limit the specific let-through energy and I peak current during a short circuit event.
- **Selectivity and back-up:** selectivity with upstream overcurrent protection devices (fuses, MCCB). Very good back-up performances to downstream protection devices.
- **Compatible with a wide set of accessories** adding additional features to the product.
- **Wide range up to 125A** with different versions to cover several applications

Compliant to standard IEC/EN 60947-2

Standard ranges for whatever application where high performances are required as datacenter, industries, hospitals, telecommunication,

- **S800B:** Icu ultimate short-circuit breaking capacity up to **16kA**; rated current **32...63A**
- **S800C:** Icu ultimate short-circuit breaking capacity up to **25kA**; rated current **10...63A**
- **S800N:** Icu ultimate short-circuit breaking capacity up to **36kA**; rated current **6...63A**
- **S800S:** Icu ultimate short-circuit breaking capacity up to **50kA**; rated current **0.5...63A** (with dedicated codes available in ring terminal version and specific KM codes with only magnetic protection)
- **S800P:** Icu ultimate short-circuit breaking capacity up to 50kA; rated current 80, 100, 125 A (with dedicated codes available in Ring terminal version)

Specific ranges for direct current and high voltage applications

UC range non-polarized, for universal current application

- **S800S-UC:** Icu up to 50kA up to 1000 VDC; rated current 0,5...125A (with dedicated codes available in Ring terminal version)

PV range for DC applications and specific for photovoltaic

- **S800PV-SP:** Icu 5kA up to **1500 VDC**; rated current 5...125A, non-polarized
- **S800PV-SD:** **switch disconnecter** with Icw 1,5kA up to **1500 VDC**; rated current 32, 63, 125 A
- **S800PV-M-H:** **polarized switch disconnecter** with Icw 1,5kA up to **1000 VDC**; rated current 32, 63, 100 A

HV range for high voltage applications in AC as power conversion systems

- **S800HV:** Icu up to 4kA up to **1000 VAC**; rated current 0,5...125A

Compliant to standard UL489

- **S800U:** interrupting rating up to **50kA**; rated current **10...100A**
- **S800U-PV (Photovoltaic):** interrupting rating **3kA at 1000 VDC**, rated current **5A**
- **S800U-PVSP (Photovoltaic):** interrupting rating **3kA at 1500 VDC**, rated current **5A**
- **S800U-UC (universal current):** interrupting rating **10kA at 600 VDC**, rated current **10...80A**

Suitable for traction applications

- Plastic materials meeting fire and smoke requirements in traction applications. Plastic material V0 according to UL94 and classified with Hazard level R26/HL3; R22/HL2 according to EN45545-2 standard..
- Range tested according to **IEC 61373** for Rolling stock equipment – Shock and vibration tests, meeting the requirements **Category 1 / Class B**.

MCBs technical details

S800 range features



*Middle position of switch lever, see picture

Play it safe: display the operational state

3 status of the device, clearly identified with toggle position: ON-OFF-TRIP.

The trip position in the middle, identifies if the device has tripped due to overcurrent.

OFF position indicates manual tripping.

In both cases contacts are opened and CPI becomes green.

In OFF position (0 position), the device guarantees safe electrical isolation of the circuit according to IEC 60947-2 standard.

Cage and ring terminals

S800 series is available with cage terminals plus dedicated codes with ring terminals, meeting the different installation needs.

In addition, interchangeable terminal adapter, makes easy to change from cage to ring terminals, guarantying easy installation with high level of flexibility.

Fast and safe connection of the conductors is ensured by the “onboard terminal shutter” integrated into the body of the terminal, thereby preventing incorrect under-clamping of the connections.



MCBs

S800P series technical features



S800P

		S800P
Performance	Tripping characteristics	B, C, D, K
	Standards	IEC/EN 60947-2, UL 1077 (80, 100 A)
	Number of Poles	1, 2, 3, 4
	Rated current I_n	80 ... 125 A
	Rated frequency f	50/60 Hz
	Rated insulation voltage U_i acc. to IEC/EN 60664-1 (V)	AC 690 V
	Rated impulse withstand voltage U_{imp} . (1.2/50 μ s)	6 kV
	Dielectric test voltage at ind. freq. for 1 min.	2.4 kV
	Overvoltage category	III
	Pollution degree	3
	Suitability for isolation	Yes
	Grid distance	50 mm
(based on internal test only)		
Data acc. to IEC/EN 60947-2	Rated operational voltage U_e	AC 240/400 V (1-pole) AC 415/690 V (multi-pole) DC 125 V (1-pole) DC 250 V (2-pole) DC 375 V (3-pole) DC 500 V (4-pole)
	Min. operating voltage	AC/DC 12 V
	Rated ultimate short-circuit capacity I_{cu} (Single pole / Multi pole)	AC 240/415 V = 50 kA AC 254/440 V = 30 kA AC 289/500 V = 15 kA (80 A) AC 289/500 V = 10 kA (100...125 A) AC 400/690 V = 6 kA (80 A) AC 400/690 V = 4.5 kA (100...125 A) DC 125 V (1-pole) = 30 kA DC 250 V (2-pole) = 30 kA DC 375 V (3-pole) = 30 kA DC 500 V (4-pole) = 30 kA
	Rated service short-circuit capacity I_{cs} (Single pole / Multi pole)	AC 240/415 V = 40 kA
	Reference temperature for tripping characteristics	30°C (Char. B, C, D) 40°C (Char. K)
	Electrical and Mechanical Endurance - cycle (OFF-ON-OFF)	80...100 A: 6000 electrical / 10000 mechanical 125 A: 4000 electrical / 8000 mechanical
	Rated short-circuit capacity I_{cn}	Char. B, C, D: AC 230/400 V = 25 kA (80 A) AC 230/400 V = 15 kA (100...125 A)
Data acc. to UL 1077/ C22.2 No 235, Supplementary Protector	Alternating current: int. cap.	1P AC 240 = 20 kA (80...100A) AC 277 = 10 kA (80...100A) 2P, 3P, 4P AC 240 V = 20 kA (80...100A) AC 277 V = 10 kA (80...100A)
	Direct current: int. cap.	DC 125 V (1P) = 10 kA (80...100A) DC 250 V (2P) = 10 kA (80...100A) DC 375 V (3P) = 10 kA (80...100A) DC 500 V (4P) = 10 kA (80...100A)

MCBs

S800P series technical features



S800P

S800P		
Mechanical Data	Housing type	Material group I, RAL 7035
	Toggle type	Black, lockable
	Plastic classification acc. to UL94	V0
	Classification acc. to EN45545-2 component requirement / hazard level	R26 / HL3; R22 / HL2
	Protection degree acc. to EN 60529	IP20; IP40 (under the cover frame)
	Resistance to shock acc. to IEC/EN 60068-2-27	5g / 30ms, Test Ea
	Shock resistance acc. to IEC/EN 61373	5g / 30ms, Cat 1 / Class B
	Resistance to Vibrations acc. to IEC 60068-2-6	5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I _e , Test Fc
	Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	16 hours 70°C
	Environmental condition (damp heat) acc. to IEC/EN 60068-2-30	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
	Environmental condition (low temp) acc. to IEC/EN 60068-2-1	16 hours -25°C
	Ambient temperature (with daily average ≤ +35 °C)	-40....+70°C
	Storage temperature	-40 ... +70°C
Installation	Terminal type	Failsafe cage or ringlug terminal
	Connections (top/bottom) – Cu only	1 ... 50 flexible mm ² 1 ... 70 Solid (Rigid / Stranded) mm ²
	Tightening torque	3.5 (Nm) 31 (in-lbs)
	Wire stripping length	19 mm
	Screwdriver	POZI 2
	Mounting type	EN 60715
	Mounting position	Any
	Supply from	Top and bottom
Dimensions and Weight	Pole dimensions (H x L x W)	95 x 82.5 x 27* mm
	Pole weight	Ca. 240 g

* On multi-pole versions, rated current 125A is equipped with a lateral cover of 4.5mm on each product side. Overall product width increases of 9mm

	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA 800
Combination with aux. Elements	Yes	Yes	Yes	Yes	Yes	Yes	No	Yes	Yes	Yes

MCBs

S800S series technical features

		S800S	S803S-KM
General Data			
Tripping characteristics		B, C, D, K,	KM
Standards		IEC/EN 60947-2, EN 60898-1, UL 1077	IEC/EN 60947-2
Number of poles		1 ... 4	3
Rated current I_n	A	0.5 ... 63	10 ... 80
Rated frequency f	Hz	50/60	50/60
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	AC 690	AC 690
Rated impulse withstand voltage U_{imp} (1.2/50µs)	kV	8	8
Dielectric test voltage at ind. freq. for 1 min.	kV	2.4	2.4
Overvoltage category		IV	IV
Pollution degree		3	3
Suitability for isolation		yes	yes
Grid distance	mm	50	-
Data acc. to IEC/EN 60898-1			
Rated operational voltage U_e	V	AC 230/400	-
Min. operating voltage	V	AC 12	-
Rated short-circuit capacity I_{cn}	kA	Char. B, C, D: 230/400V (10 ... 63A) = 25 kA	-
Reference temperature for tripping characteristics	°C	30°C (Char. B, C, D)	-
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	10...32 A: 10000 electrical / 10000 mechanical 40...63 A: 6000 electrical / 10000 mechanical	-
Service short-circuit capacity I_{cs}	kA	Char. B, C, D: 230/400V (10 ... 63A) = 12.5 kA	-
Energy limiting class		3	-
Data acc. to IEC/EN 60947-2			
Rated operational voltage U_e	V	AC 240/400 V (1-pole) AC 415/690 V (multi-pole) DC 125 (1-pole) DC 250 (2-pole) DC 375 (3-pole) DC 500 (4-pole)	AC 415/690 V
Min. operating voltage	V	AC/DC 12 V	AC/DC 12 V
Rated ultimate short-circuit capacity I_{cu} (Single pole / Multi pole)	kA	AC 240/415 V = 50 kA AC 254/440 V = 30 kA AC 289/500 V = 15 kA AC 400/690 V = 6 kA DC 125 V (1-pole) = 30 kA DC 250 V (2-pole) = 30 kA DC 375 V (3-pole) = 30 kA DC 500 V (4-pole) = 30 kA	AC 415V = 50 kA AC 440V = 30 kA AC 690V = 6 kA DC 375 V = 30 kA
Rated service short-circuit capacity I_{cs} (Single pole / Multi pole)	kA	AC 240/415 V = 40 kA AC 254/440 V = 22.5 kA AC 289/500 V = 11 kA AC 400/690 V = 4 kA DC 125 V (1-pole) = 30 kA DC 250 V (2-pole) = 30 kA DC 375 V (3-pole) = 30 kA DC 500 V (4-pole) = 30 kA	DC 375 V = 30 kA
Reference temperature for tripping characteristics	°C	B, C, D: 30 °C K: 40 °C	only magnetic release
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	0.5...32 A: 10000 electrical / 10000 mechanical 40...63 A: 6000 electrical / 10000 mechanical	10 ... 32 A: 10000 electrical/ 10000 mechanical 40 ... 80 A: 6000 electrical/ 4000 mechanical

MCBs

S800S series technical features

S800S / S803S-KM		
Data acc. to UL 1077/ C22.2 No 235, Supplementary Protector (only for S800S)		
Alternating current:		1
int. cap.		240: 30 (0.5...63A) 277: 14 (0.5...63A) 347: 6 (0.5...63A)
		2,3,4
		240: 30 (0.5...63A) 480 Y/277: 14 (0.5...63A) 600 Y/347: 6 (0.5...63A)
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Classification for the component requirement / hazard level acc. to EN45545-2		R26 / HL3; R22 / HL2
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Shock & Vibration Resistance acc. to IEC 61373		5g / 30ms, Cat 1 / Class B
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I _e , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1	°C/RH	16 hours -40°C
Ambient temperature (with daily average ≤ +35 °C)	°C	-40...+70
Storage temperature	°C	-40 ... +70
Installation		
Terminal type		Failsafe cage or ringlug terminal
Connections (top/bottom) – C _u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
	AWG	10 - 30 A: 14 AWG – 2 AWG
	(S800S only)	40 - 63 A: 14 AWG – 2 AWG
Tightening torque	Nm	3.5
	in-lbs.	31
Wire stripping length	mm	19
Screwdriver		POZI 2
Mounting type		EN 60715
Mounting position		Any
Supply from		Top and bottom
Dimensions and weight		
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27*
Pole weight	g	ca. 240

* On multi-pole versions, rated current 125A is equipped with a lateral cover of 4.5mm on each product side. Overall product width increases of 9mm

	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	yes	yes	no	yes	yes	yes

MCBs

S800N series technical features

S800N		
General Data		
Tripping characteristics		B, C, D
Standards		IEC/EN 60947-2, EN 60898-1
Number of poles		1 ... 4
Rated current I_n	A	6 ... 63
Rated frequency f	Hz	50/60
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	AC 690
Rated impulse withstand voltage U_{imp} (1.2/50µs)	kV	8
Dielectric test voltage at ind. freq. for 1 min.	kV	2.4
Overvoltage category		IV
Pollution degree		3
Suitability for isolation		yes
Grid distance	mm	50
Data acc. to IEC/EN 60898-1		
Rated operational voltage U_e	V	AC 230/400
Min. operating voltage	V	AC 12
Rated short-circuit capacity I_{cn}	kA	AC 230/400V (10 ... 63A) = 20 kA
Reference temperature for tripping characteristics	°C	30°C (Char. B, C, D)
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	10...32 A: 10000 electrical / 10000 mechanical 40...63 A: 6000 electrical / 10000 mechanical
Service short-circuit capacity I_{cs}	kA	230/400V (10 ... 63A) = 10 kA
Energy limiting class		3
Data acc. to IEC/EN 60947-2		
Rated operational voltage U_e	V	AC 240/400 V (1-pole) AC 415/690 V (multi-pole) DC 125 (1-pole) DC 250 (2-pole) DC 375 (3-pole) DC 500 (4-pole)
Min. operating voltage	V	AC/DC 12 V
Rated ultimate short-circuit capacity I_{cu} (Single pole / Multi pole)	kA	AC 240/415 V = 36 kA AC 254/440 V = 20 kA AC 289/500 V = 10 kA AC 400/690 V = 4.5 kA DC 125 V (1-pole) = 20 kA DC 250 V (2-pole) = 20 kA DC 375 V (3-pole) = 20 kA DC 500 V (4-pole) = 20 kA
Rated service short-circuit capacity I_{cs} (Single pole / Multi pole)	kA	AC 240/415 V = 30 kA AC 254/440 V = 15 kA AC 289/500 V = 8 kA AC 400/690 V = 3 kA DC 125 V (1-pole) = 20 kA DC 250 V (2-pole) = 20 kA DC 375 V (3-pole) = 20 kA DC 500 V (4-pole) = 20 kA
Reference temperature for tripping characteristics	°C	30°C
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	6 ... 32 A: 10000 electrical/10000 mechanical 40 ... 63 A: 6000 electrical/10000 mechanical
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Classification for the component requirement / hazard level acc. to EN45545-2		R26 / HL3; R22 / HL2
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Shock & Vibration Resistance acc. to IEC 61373		5g / 30ms, Cat 1 / Class B
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I_n , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1	°C/RH	16 hours -40°C
Ambient temperature (with daily average ≤ +35°C)	°C	-40...70
Storage temperature	°C	-40 ... +70

MCBs

S800N series technical features

S800N		
Installation		
Terminal type		Failsafe cage or ringlug terminal
Connections (top/bottom) – C _u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
Tightening torque	Nm	3.5
	in-lbs.	31
Wire stripping length	mm	19
Screwdriver		POZI 2
Mounting type		EN 60715
Mounting position		Any
Supply from		Top and bottom
Dimensions and weight		
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27
Pole weight	g	ca. 240

	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	yes	yes	no	yes	yes	yes

MCBs

S800C series technical features

S800C		
General Data		
Tripping characteristics		B, C, D, K
Standards		IEC/EN 60947-2, EN 60898-1, UL 1077
Number of poles		1 ... 4
Rated current I_n	A	10 ... 63
Rated frequency f	Hz	50/60
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	AC 500
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	kV	8
Dielectric test voltage at ind. freq. for 1 min.	kV	2.4
Overvoltage category		IV
Pollution degree		3
Suitability for isolation		yes
Grid distance	mm	50
Data acc. to IEC/EN 60898-1		
Rated operational voltage U_e	V	AC 230/400
Min. operating voltage	V	AC 12
Rated short-circuit capacity I_{cn}	kA	15 kA
Reference temperature for tripping characteristics	°C	30°C (Char. B, C, D)
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	10 ... 32 A: 10 000 electrical/10 000 mechanical 40 ... 63 A: 6000 electrical/10 000 mechanical
Service short-circuit capacity I_{cs}	kA	Char. B, C, D: 230/400 V = 7.5 kA
Energy limiting class		3
Data acc. to IEC/EN 60947-2		
Rated operational voltage U_e	V	AC 240/254 V (1-pole) AC 415/440 V (multi-pole) DC 125 (1-pole) DC 250 (2-pole) DC 375 (3-pole) DC 500 (4-pole)
Min. operating voltage	V	AC/DC 12 V
Rated ultimate short-circuit capacity I_{cu} (Single pole / Multi pole)	kA	AC 240/415 V = 25 kA AC 254/440 V = 15 kA DC 125 V (1-pole) = 10 kA DC 250 V (2-pole) = 10 kA DC 375 V (3-pole) = 10 kA DC 500 V (4-pole) = 10 kA
Rated service short-circuit capacity I_{cs} (Single pole / Multi pole)	kA	AC 240/415 V = 25 kA AC 254/440 V = 10 kA DC 125 V (1-pole) = 10 kA DC 250 V (2-pole) = 10 kA DC 375 V (3-pole) = 10 kA DC 500 V (4-pole) = 10 kA
Reference temperature for tripping characteristics	°C	B, C, D: 30°C K: 40°C
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	6 ... 32 A: 10 000 electrical/10 000 mechanical 40 ... 63 A: 6000 electrical/10 000 mechanical
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Classification for the component requirement / hazard level acc. to EN45545-2		R26 / HL3; R22 / HL2
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Shock & Vibration Resistance acc. to IEC 61373		5g / 30ms, Cat 1 / Class B
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I_n , Test Fc 2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	16 hours 70°C
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours -40°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1		16 hours -40°C
Ambient temperature (with daily average $\leq +35^\circ\text{C}$)	°C	-40...+70
Storage temperature	°C	-40 ... +70
Data acc. to UL 1077/ C22.2 No 235, Supplementary Protector		
Alternating current: int. cap.		1P AC 240 = 20 kA AC 277 = 10 kA 2P, 3P, 4P AC 240 V = 20 kA AC 277 V = 10 kA
Direct current: int. cap.		DC 125 V (1P) = 10 kA DC 250 V (2P) = 10 kA DC 375 V (3P) = 10 kA DC 500 V (4P) = 10 kA

MCBs

S800C series technical features

S800C										
Installation										
Terminal type		Failsafe cage or ringlug terminal								
Connections (top/bottom) – C _u only	mm²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)								
	AWG	10 - 30 A: 14 AWG – 2 AWG 40 - 63 A: 14 AWG – 2 AWG								
Tightening torque	Nm	3.5								
	in-lbs.	31								
Wire stripping length	mm	19								
Screwdriver		POZI 2								
Mounting type		EN 60715								
Mounting position		Any								
Supply from		Top and bottom								
Dimensions and weight										
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27								
Pole weight	g	ca. 240								
	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	yes	yes	no	yes	yes	yes

MCBs

S800B series technical features

S800B										
General Data										
Tripping characteristics		B, C, D, K								
Standards		IEC/EN 60947-2,EN 60898-1								
Number of poles		1 ... 4								
Rated current I _n	A	32 ... 63								
Rated frequency f	Hz	50/60								
Rated insulation voltage U _i acc. to IEC/EN 60664-1	V	AC 500								
Rated impulse withstand voltage U _{imp} (1.2/50µs)	kV	6								
Dielectric test voltage at ind. freq. for 1 min.	kV	1.8								
Overvoltage category		III								
Pollution degree		3								
Suitability for isolation		yes								
Grid distance	mm	50								
Data acc. to IEC/EN 60898-1										
Rated operational voltage U _e	V	AC 230/400								
Min. operating voltage	V	AC 12								
Rated short-circuit capacity I _{cn}	kA	AC 230/400 = 10 kA								
Reference temperature for tripping characteristics	°C	B, C, D: 30°C								
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	4000								
Service short-circuit capacity I _{cs}	kA	AC 230/400V = 7.5 kA								
Data acc. to IEC/EN 60947-2										
Rated operational voltage U _e	V	AC 230/400								
Min. operating voltage	V	AC/DC 12 V								
Rated ultimate short-circuit capacity I _{cu}	kA	AC 230/400 V = 16 kA DC 75 V (1-pole) = 10 kA DC 150 V (2-pole) = 10 kA DC 225 V (3-pole) = 10 kA DC 300 V (4-pole) = 10 kA								
Rated service short-circuit capacity I _{cs}	kA	10 kA								
Reference temperature for tripping characteristics	°C	B, C, D: 30°C K: 40 °C								
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	32...63 A: 1500 electrical / 10000 mechanical								
Energy limiting class										
		3								
Mechanical Data										
Housing type		Material group I, RAL 7035								
Toggle type		black, lockable								
Plastic classification acc. to UL94		V0								
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)								
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea								
Shock resistance acc. To IEC/EN 61373		5g / 30ms, Cat 1 / Class B								
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz /1 mm 13.2 - 100Hz / 0.7g with load 80% x I _e , Test Fc								
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh								
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C								
Environmental condition (low temp) acc. to IEC/EN 60068-2-1		16 hours -40°C								
Ambient temperature (with daily average ≤ +35°C)	°C	-40....+70								
Storage temperature	°C	-40... +70								
Installation										
Terminal type		Failsafe cage or ringlug terminal								
Connections (top/bottom) – C _u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)								
Tightening torque	Nm in-lbs.	3.5 31								
Wire stripping length	mm	19								
Screwdriver		POZI 2								
Mounting type		EN 60715								
Mounting position		Any								
Supply from		Top and bottom								
Dimensions and weight										
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27								
Pole weight	g	ca. 240								
	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	no	no	no	yes	yes	yes

High performance MCBs

S800P series, B characteristic

S800P - B Characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA



S800P

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	516833	S801P-B80	2CCG001214R0001	0.245	1
	100	516840	S801P-B100	2CCG001215R0001	0.245	1
	125	516857	S801P-B125	2CCG001216R0001	0.245	1
2	80	516864	S802P-B80	2CCG001217R0001	0.490	1
	100	516871	S802P-B100	2CCG001218R0001	0.490	1
	125	516888	S802P-B125	2CCG001219R0001	0.515	1
3	80	516895	S803P-B80	2CCG001220R0001	0.740	1
	100	516901	S803P-B100	2CCG001221R0001	0.740	1
	125	516918	S803P-B125	2CCG001222R0001	0.765	1
4	80	516925	S804P-B80	2CCG001223R0001	0.980	1
	100	516932	S804P-B100	2CCG001224R0001	0.980	1
	125	516949	S804P-B125	2CCG001225R0001	1.005	1

S800P - B Characteristic with ringlug terminal connection

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA



S800P

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517311	S801P-B80-R	2CCG001262R0001	0.255	1
	100	517472	S801P-B100-R	2CCG001278R0001	0.255	1
	125	517632	S801P-B125-R	2CCG001294R0001	0.255	1
2	80	517359	S802P-B80-R	2CCG001266R0001	0.510	1
	100	517519	S802P-B100-R	2CCG001282R0001	0.510	1
	125	517670	S802P-B125-R	2CCG001298R0001	0.535	1
3	80	517397	S803P-B80-R	2CCG001270R0001	0.761	1
	100	517557	S803P-B100-R	2CCG001286R0001	0.761	1
	125	517717	S803P-B125-R	2CCG001302R0001	0.790	1
4	80	517434	S804P-B80-R	2CCG001274R0001	1.015	1
	100	517595	S804P-B100-R	2CCG001290R0001	1.015	1
	125	517755	S804P-B125-R	2CCG001306R0001	1.045	1

High performance MCBs

S800P series, C characteristic



S800P

S800P - C Characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for resistive and inductive loads with low inrush current; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	516956	S801P-C80	2CCG001226R0001	0.245	1
	100	516963	S801P-C100	2CCG001227R0001	0.245	1
	125	516970	S801P-C125	2CCG001228R0001	0.245	1
2	80	516987	S802P-C80	2CCG001229R0001	0.490	1
	100	516994	S802P-C100	2CCG001230R0001	0.490	1
	125	517007	S802P-C125	2CCG001231R0001	0.515	1
3	80	517014	S803P-C80	2CCG001232R0001	0.740	1
	100	517021	S803P-C100	2CCG001233R0001	0.740	1
	125	517038	S803P-C125	2CCG001234R0001	0.765	1
4	80	517045	S804P-C80	2CCG001235R0001	0.980	1
	100	517052	S804P-C100	2CCG001236R0001	0.980	1
	125	517069	S804P-C125	2CCG001237R0001	1.005	1

S800P - C Characteristic with ringlug terminal connection

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for resistive and inductive loads with low inrush current; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA



S800P

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517328	S801P-C80-R	2CCG001263R0001	0.255	1
	100	517489	S801P-C100-R	2CCG001279R0001	0.255	1
	125	517649	S801P-C125-R	2CCG001295R0001	0.255	1
2	80	517366	S802P-C80-R	2CCG001267R0001	0.510	1
	100	517526	S802P-C100-R	2CCG001283R0001	0.510	1
	125	517687	S802P-C125-R	2CCG001299R0001	0.535	1
3	80	517403	S803P-C80-R	2CCG001271R0001	0.761	1
	100	517564	S803P-C100-R	2CCG001287R0001	0.761	1
	125	517724	S803P-C125-R	2CCG001303R0001	0.790	1
4	80	517441	S804P-C80-R	2CCG001275R0001	1.015	1
	100	517601	S804P-C100-R	2CCG001291R0001	1.015	1
	125	517762	S804P-C125-R	2CCG001307R0001	1.045	1

High performance MCBs

S800P series, D characteristic

S800P - D Characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for circuits which supply loads with high inrush current at the circuit closing (motors, LV / LV transformers, breakdown lamps); very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA



S800P

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517076	S801P-D80	2CCG001238R0001	0.245	1
	100	517083	S801P-D100	2CCG001239R0001	0.245	1
	125	517090	S801P-D125	2CCG001240R0001	0.245	1
2	80	517106	S802P-D80	2CCG001241R0001	0.490	1
	100	517113	S802P-D100	2CCG001242R0001	0.490	1
	125	517120	S802P-D125	2CCG001243R0001	0.515	1
3	80	517137	S803P-D80	2CCG001244R0001	0.740	1
	100	517144	S803P-D100	2CCG001245R0001	0.740	1
	125	517151	S803P-D125	2CCG001246R0001	0.765	1
4	80	517168	S804P-D80	2CCG001247R0001	0.980	1
	100	517175	S804P-D100	2CCG001248R0001	0.980	1
	125	517182	S804P-D125	2CCG001249R0001	1.005	1

S800P - D Characteristic with ringlug terminal connection

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for circuits which supply loads with high inrush current at the circuit closing (motors, LV / LV transformers, breakdown lamps); very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA



S800P

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517335	S801P-D80-R	2CCG001264R0001	0.255	1
	100	517496	S801P-D100-R	2CCG001280R0001	0.255	1
	125	517656	S801P-D125-R	2CCG001296R0001	0.255	1
2	80	517373	S802P-D80-R	2CCG001268R0001	0.510	1
	100	517533	S802P-D100-R	2CCG001284R0001	0.510	1
	125	517694	S802P-D125-R	2CCG001300R0001	0.535	1
3	80	517410	S803P-D80-R	2CCG001272R0001	0.761	1
	100	517571	S803P-D100-R	2CCG001288R0001	0.761	1
	125	517731	S803P-D125-R	2CCG001304R0001	0.790	1
4	80	517458	S804P-D80-R	2CCG001276R0001	1.015	1
	100	517618	S804P-D100-R	2CCG001292R0001	1.015	1
	125	517779	S804P-D125-R	2CCG001308R0001	1.045	1

High performance MCBs

S800P series, K characteristic



S800P

S800P - K Characteristic

Function: protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits when a high breaking capacity is required; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517199	S801P-K80	2CCG001250R0001	0.245	1
	100	517205	S801P-K100	2CCG001251R0001	0.245	1
	125	517212	S801P-K125	2CCG001252R0001	0.245	1
2	80	517229	S802P-K80	2CCG001253R0001	0.490	1
	100	517236	S802P-K100	2CCG001254R0001	0.490	1
	125	517243	S802P-K125	2CCG001255R0001	0.515	1
3	80	517250	S803P-K80	2CCG001256R0001	0.740	1
	100	517267	S803P-K100	2CCG001257R0001	0.740	1
	125	517274	S803P-K125	2CCG001258R0001	0.765	1
4	80	517281	S804P-K80	2CCG001259R0001	0.980	1
	100	517298	S804P-K100	2CCG001260R0001	0.980	1
	125	517304	S804P-K125	2CCG001261R0001	1.005	1

S800P - K Characteristic with ringlug terminal connection

Function: protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits when a high breaking capacity is required; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2

Icu=50kA

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	80	517342	S801P-K80-R	2CCG001265R0001	0.255	1
	100	517502	S801P-K100-R	2CCG001281R0001	0.255	1
	125	517663	S801P-K125-R	2CCG001297R0001	0.255	1
2	80	517380	S802P-K80-R	2CCG001269R0001	0.510	1
	100	517540	S802P-K100-R	2CCG001285R0001	0.510	1
	125	517700	S802P-K125-R	2CCG001301R0001	0.535	1
3	80	517427	S803P-K80-R	2CCG001273R0001	0.761	1
	100	517588	S803P-K100-R	2CCG001289R0001	0.761	1
	125	517748	S803P-K125-R	2CCG001305R0001	0.790	1
4	80	517465	S804P-K80-R	2CCG001277R0001	1.015	1
	100	517625	S804P-K100-R	2CCG001293R0001	1.015	1
	125	517786	S804P-K125-R	2CCG001309R0001	1.045	1



S800P

High performance MCBs

S800S series with cage terminal, B characteristic

S800S-B characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2, UL 1077, supplementary protector

I_{cn}=25kA

I_{cu}=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	498979	S801S-B0,5	2CCF019841R0001	0.24	1
	1	498986	S801S-B1	2CCF019842R0001	0.24	1
	1.6	498993	S801S-B1,6	2CCF019843R0001	0.24	1
	2	499105	S801S-B2	2CCF019844R0001	0.24	1
	2.5	499112	S801S-B2,5	2CCF019845R0001	0.24	1
	3	499129	S801S-B3	2CCF019846R0001	0.24	1
	4	499136	S801S-B4	2CCF019847R0001	0.24	1
	5	499143	S801S-B5	2CCF019848R0001	0.24	1
	6	408107	S801S-B6	2CCS861001R0065	0.24	1
	8	411329	S801S-B8	2CCS861001R0085	0.24	1
	10	200008	S801S-B10	2CCS861001R0105	0.24	1
	13	200015	S801S-B13	2CCS861001R0135	0.24	1
	16	200022	S801S-B16	2CCS861001R0165	0.24	1
	20	200039	S801S-B20	2CCS861001R0205	0.24	1
	25	200046	S801S-B25	2CCS861001R0255	0.24	1
	32	200053	S801S-B32	2CCS861001R0325	0.24	1
	40	200060	S801S-B40	2CCS861001R0405	0.24	1
	50	200077	S801S-B50	2CCS861001R0505	0.24	1
	63	200084	S801S-B63	2CCS861001R0635	0.24	1
2	0.5	499310	S802S-B0,5	2CCF019865R0001	0.49	1
	1	499327	S802S-B1	2CCF019866R0001	0.49	1
	1.6	499334	S802S-B1,6	2CCF019867R0001	0.49	1
	2	499341	S802S-B2	2CCF019868R0001	0.49	1
	2.5	499358	S802S-B2,5	2CCF019869R0001	0.49	1
	3	499365	S802S-B3	2CCF019870R0001	0.49	1
	4	499372	S802S-B4	2CCF019871R0001	0.49	1
	5	499389	S802S-B5	2CCF019872R0001	0.49	1
	6	408114	S802S-B6	2CCS862001R0065	0.49	1
	8	411336	S802S-B8	2CCS862001R0085	0.49	1
	10	200121	S802S-B10	2CCS862001R0105	0.49	1
	13	200138	S802S-B13	2CCS862001R0135	0.49	1
	16	200145	S802S-B16	2CCS862001R0165	0.49	1
	20	200152	S802S-B20	2CCS862001R0205	0.49	1
	25	200169	S802S-B25	2CCS862001R0255	0.49	1
	32	200176	S802S-B32	2CCS862001R0325	0.49	1
	40	200183	S802S-B40	2CCS862001R0405	0.49	1
	50	200190	S802S-B50	2CCS862001R0505	0.49	1
	63	200206	S802S-B63	2CCS862001R0635	0.49	1

High performance MCBs

S800S series with cage terminal, B characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	499556	S803S-B0,5	2CCF019889R0001	0.74	1
	1	499563	S803S-B1	2CCF019890R0001	0.74	1
	1.6	499570	S803S-B1,6	2CCF019891R0001	0.74	1
	2	499587	S803S-B2	2CCF019892R0001	0.74	1
	2.5	499594	S803S-B2,5	2CCF019893R0001	0.74	1
	3	499600	S803S-B3	2CCF019894R0001	0.74	1
	4	499617	S803S-B4	2CCF019895R0001	0.74	1
	5	499624	S803S-B5	2CCF019896R0001	0.74	1
	6	408121	S803S-B6	2CCS863001R0065	0.74	1
	8	411343	S803S-B8	2CCS863001R0085	0.74	1
	10	200244	S803S-B10	2CCS863001R0105	0.74	1
	13	200251	S803S-B13	2CCS863001R0135	0.74	1
	16	200268	S803S-B16	2CCS863001R0165	0.74	1
	20	200275	S803S-B20	2CCS863001R0205	0.74	1
	25	200282	S803S-B25	2CCS863001R0255	0.74	1
	32	200299	S803S-B32	2CCS863001R0325	0.74	1
	40	200305	S803S-B40	2CCS863001R0405	0.74	1
	50	200312	S803S-B50	2CCS863001R0505	0.74	1
	63	200329	S803S-B63	2CCS863001R0635	0.74	1
4	0.5	499792	S804S-B0,5	2CCF019913R0001	0.98	1
	1	499808	S804S-B1	2CCF019914R0001	0.98	1
	1.6	499815	S804S-B1,6	2CCF019915R0001	0.98	1
	2	499822	S804S-B2	2CCF019916R0001	0.98	1
	2.5	499839	S804S-B2,5	2CCF019917R0001	0.98	1
	3	499846	S804S-B3	2CCF019918R0001	0.98	1
	4	499853	S804S-B4	2CCF019919R0001	0.98	1
	5	499860	S804S-B5	2CCF019920R0001	0.98	1
	6	408138	S804S-B6	2CCS864001R0065	0.98	1
	8	411350	S804S-B8	2CCS864001R0085	0.98	1
	10	200367	S804S-B10	2CCS864001R0105	0.98	1
	13	200374	S804S-B13	2CCS864001R0135	0.98	1
	16	200381	S804S-B16	2CCS864001R0165	0.98	1
	20	200398	S804S-B20	2CCS864001R0205	0.98	1
	25	200404	S804S-B25	2CCS864001R0255	0.98	1
	32	200411	S804S-B32	2CCS864001R0325	0.98	1
	40	200428	S804S-B40	2CCS864001R0405	0.98	1
	50	200435	S804S-B50	2CCS864001R0505	0.98	1
	63	200442	S804S-B63	2CCS864001R0635	0.98	1

High performance MCBs

S800S series with cage terminal, C characteristic

S800S-C characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for resistive and inductive loads with low in-rush current; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2, UL 1077, supplementary protector

Icn=25kA

Icu=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	499150	S801S-C0,5	2CCF019849R0001	0.24	1
	1	499167	S801S-C1	2CCF019850R0001	0.24	1
	1.6	499174	S801S-C1,6	2CCF019851R0001	0.24	1
	2	499181	S801S-C2	2CCF019852R0001	0.24	1
	2.5	499198	S801S-C2,5	2CCF019853R0001	0.24	1
	3	499204	S801S-C3	2CCF019854R0001	0.24	1
	4	499211	S801S-C4	2CCF019855R0001	0.24	1
	5	499228	S801S-C5	2CCF019856R0001	0.24	1
	6	408145	S801S-C6	2CCS861001R0064	0.24	1
	8	411367	S801S-C8	2CCS861001R0084	0.24	1
	10	200480	S801S-C10	2CCS861001R0104	0.24	1
	13	200497	S801S-C13	2CCS861001R0134	0.24	1
	16	200503	S801S-C16	2CCS861001R0164	0.24	1
	20	200510	S801S-C20	2CCS861001R0204	0.24	1
	25	200527	S801S-C25	2CCS861001R0254	0.24	1
	32	200534	S801S-C32	2CCS861001R0324	0.24	1
	40	200541	S801S-C40	2CCS861001R0404	0.24	1
	50	200558	S801S-C50	2CCS861001R0504	0.24	1
	63	200565	S801S-C63	2CCS861001R0634	0.24	1
2	0.5	499396	S802S-C0,5	2CCF019873R0001	0.49	1
	1	499402	S802S-C1	2CCF019874R0001	0.49	1
	1.6	499419	S802S-C1,6	2CCF019875R0001	0.49	1
	2	499426	S802S-C2	2CCF019876R0001	0.49	1
	2.5	499433	S802S-C2,5	2CCF019877R0001	0.49	1
	3	499440	S802S-C3	2CCF019878R0001	0.49	1
	4	499457	S802S-C4	2CCF019879R0001	0.49	1
	5	499464	S802S-C5	2CCF019880R0001	0.49	1
	6	408152	S802S-C6	2CCS862001R0064	0.49	1
	8	411374	S802S-C8	2CCS862001R0084	0.49	1
	10	200602	S802S-C10	2CCS862001R0104	0.49	1
	13	200619	S802S-C13	2CCS862001R0134	0.49	1
	16	200626	S802S-C16	2CCS862001R0164	0.49	1
	20	200633	S802S-C20	2CCS862001R0204	0.49	1
	25	200640	S802S-C25	2CCS862001R0254	0.49	1
	32	200657	S802S-C32	2CCS862001R0324	0.49	1
	40	200664	S802S-C40	2CCS862001R0404	0.49	1
	50	200671	S802S-C50	2CCS862001R0504	0.49	1
	63	200688	S802S-C63	2CCS862001R0634	0.49	1

High performance MCBs

S800S series with cage terminal, C characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	499631	S803S-C0,5	2CCF019897R0001	0.74	1
	1	499648	S803S-C1	2CCF019898R0001	0.74	1
	1.6	499655	S803S-C1,6	2CCF019899R0001	0.74	1
	2	499662	S803S-C2	2CCF019900R0001	0.74	1
	2.5	499679	S803S-C2,5	2CCF019901R0001	0.74	1
	3	499686	S803S-C3	2CCF019902R0001	0.74	1
	4	499693	S803S-C4	2CCF019903R0001	0.74	1
	5	499709	S803S-C5	2CCF019904R0001	0.74	1
	6	408169	S803S-C6	2CCS863001R0064	0.74	1
	8	411381	S803S-C8	2CCS863001R0084	0.74	1
	10	200725	S803S-C10	2CCS863001R0104	0.74	1
	13	200732	S803S-C13	2CCS863001R0134	0.74	1
	16	200749	S803S-C16	2CCS863001R0164	0.74	1
	20	200756	S803S-C20	2CCS863001R0204	0.74	1
	25	200763	S803S-C25	2CCS863001R0254	0.74	1
	32	200770	S803S-C32	2CCS863001R0324	0.74	1
	40	200787	S803S-C40	2CCS863001R0404	0.74	1
	50	200794	S803S-C50	2CCS863001R0504	0.74	1
	63	200800	S803S-C63	2CCS863001R0634	0.74	1
4	0.5	499877	S804S-C0,5	2CCF019921R0001	0.98	1
	1	499884	S804S-C1	2CCF019922R0001	0.98	1
	1.6	499891	S804S-C1,6	2CCF019923R0001	0.98	1
	2	499907	S804S-C2	2CCF019924R0001	0.98	1
	2.5	499914	S804S-C2,5	2CCF019925R0001	0.98	1
	3	499921	S804S-C3	2CCF019926R0001	0.98	1
	4	499938	S804S-C4	2CCF019927R0001	0.98	1
	5	499945	S804S-C5	2CCF019928R0001	0.98	1
	6	408176	S804S-C6	2CCS864001R0064	0.98	1
	8	411398	S804S-C8	2CCS864001R0084	0.98	1
	10	200848	S804S-C10	2CCS864001R0104	0.98	1
	13	200855	S804S-C13	2CCS864001R0134	0.98	1
	16	200862	S804S-C16	2CCS864001R0164	0.98	1
	20	200879	S804S-C20	2CCS864001R0204	0.98	1
	25	200886	S804S-C25	2CCS864001R0254	0.98	1
	32	200893	S804S-C32	2CCS864001R0324	0.98	1
	40	200909	S804S-C40	2CCS864001R0404	0.98	1
	50	200916	S804S-C50	2CCS864001R0504	0.98	1
	63	200923	S804S-C63	2CCS864001R0634	0.98	1

High performance MCBs

S800S series with cage terminal, D characteristic

S800S-D characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for circuits which supply loads with high in-rush current at the circuit closing (motors, LV / LV transformers, breakdown lamps); very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2, UL 1077, supplementary protector

I_{cn}=25kA

I_{cu}=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	499235	S801S-D0,5	2CCF019857R0001	0.24	1
	1	499242	S801S-D1	2CCF019858R0001	0.24	1
	1.6	499259	S801S-D1,6	2CCF019859R0001	0.24	1
	2	499266	S801S-D2	2CCF019860R0001	0.24	1
	2.5	499273	S801S-D2,5	2CCF019861R0001	0.24	1
	3	499280	S801S-D3	2CCF019862R0001	0.24	1
	4	499297	S801S-D4	2CCF019863R0001	0.24	1
	5	499303	S801S-D5	2CCF019864R0001	0.24	1
	6	408183	S801S-D6	2CCS861001R0061	0.24	1
	8	411404	S801S-D8	2CCS861001R0081	0.24	1
	10	200961	S801S-D10	2CCS861001R0101	0.24	1
	13	200978	S801S-D13	2CCS861001R0131	0.24	1
	16	200985	S801S-D16	2CCS861001R0161	0.24	1
	20	200992	S801S-D20	2CCS861001R0201	0.24	1
	25	201005	S801S-D25	2CCS861001R0251	0.24	1
	32	201012	S801S-D32	2CCS861001R0321	0.24	1
	40	201029	S801S-D40	2CCS861001R0401	0.24	1
	50	201036	S801S-D50	2CCS861001R0501	0.24	1
	63	201043	S801S-D63	2CCS861001R0631	0.24	1
2	0.5	499471	S802S-D0,5	2CCF019881R0001	0.49	1
	1	499488	S802S-D1	2CCF019882R0001	0.49	1
	1.6	499495	S802S-D1,6	2CCF019883R0001	0.49	1
	2	499501	S802S-D2	2CCF019884R0001	0.49	1
	2.5	499518	S802S-D2,5	2CCF019885R0001	0.49	1
	3	499525	S802S-D3	2CCF019886R0001	0.49	1
	4	499532	S802S-D4	2CCF019887R0001	0.49	1
	5	499549	S802S-D5	2CCF019888R0001	0.49	1
	6	408190	S802S-D6	2CCS862001R0061	0.49	1
	8	411411	S802S-D8	2CCS862001R0081	0.49	1
	10	201081	S802S-D10	2CCS862001R0101	0.49	1
	13	201098	S802S-D13	2CCS862001R0131	0.49	1
	16	201104	S802S-D16	2CCS862001R0161	0.49	1
	20	201111	S802S-D20	2CCS862001R0201	0.49	1
	25	201128	S802S-D25	2CCS862001R0251	0.49	1
	32	201135	S802S-D32	2CCS862001R0321	0.49	1
	40	201142	S802S-D40	2CCS862001R0401	0.49	1
	50	201159	S802S-D50	2CCS862001R0501	0.49	1
	63	201166	S802S-D63	2CCS862001R0631	0.49	1

High performance MCBs

S800S series with cage terminal, D characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	499716	S803S-D0,5	2CCF019905R0001	0.74	1
	1	499723	S803S-D1	2CCF019906R0001	0.74	1
	1.6	499730	S803S-D1,6	2CCF019907R0001	0.74	1
	2	499747	S803S-D2	2CCF019908R0001	0.74	1
	2.5	499754	S803S-D2,5	2CCF019909R0001	0.74	1
	3	499761	S803S-D3	2CCF019910R0001	0.74	1
	4	499778	S803S-D4	2CCF019911R0001	0.74	1
	5	499785	S803S-D5	2CCF019912R0001	0.74	1
	6	408206	S803S-D6	2CCS863001R0061	0.74	1
	8	411428	S803S-D8	2CCS863001R0081	0.74	1
	10	201203	S803S-D10	2CCS863001R0101	0.74	1
	13	201210	S803S-D13	2CCS863001R0131	0.74	1
	16	201227	S803S-D16	2CCS863001R0161	0.74	1
	20	201234	S803S-D20	2CCS863001R0201	0.74	1
	25	201241	S803S-D25	2CCS863001R0251	0.74	1
	32	201258	S803S-D32	2CCS863001R0321	0.74	1
	40	201265	S803S-D40	2CCS863001R0401	0.74	1
	50	201272	S803S-D50	2CCS863001R0501	0.74	1
	63	201289	S803S-D63	2CCS863001R0631	0.74	1
4	0.5	499952	S804S-D0,5	2CCF019929R0001	0.98	1
	1	499969	S804S-D1	2CCF019930R0001	0.98	1
	1.6	499976	S804S-D1,6	2CCF019931R0001	0.98	1
	2	499983	S804S-D2	2CCF019932R0001	0.98	1
	2.5	499990	S804S-D2,5	2CCF019933R0001	0.98	1
	3	500009	S804S-D3	2CCF019934R0001	0.98	1
	4	500016	S804S-D4	2CCF019935R0001	0.98	1
	5	500023	S804S-D5	2CCF019936R0001	0.98	1
	6	408213	S804S-D6	2CCS864001R0061	0.98	1
	8	411435	S804S-D8	2CCS864001R0081	0.98	1
	10	201326	S804S-D10	2CCS864001R0101	0.98	1
	13	201333	S804S-D13	2CCS864001R0131	0.98	1
	16	201340	S804S-D16	2CCS864001R0161	0.98	1
	20	201357	S804S-D20	2CCS864001R0201	0.98	1
	25	201364	S804S-D25	2CCS864001R0251	0.98	1
	32	201371	S804S-D32	2CCS864001R0321	0.98	1
	40	201388	S804S-D40	2CCS864001R0401	0.98	1
	50	201395	S804S-D50	2CCS864001R0501	0.98	1
	63	201401	S804S-D63	2CCS864001R0631	0.98	1

High performance MCBs

S800S series with cage terminal, K characteristic

S800S-K characteristic

Function: protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits when a high breaking capacity is required; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream. Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2, UL 1077, supplementary protector

Icu=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	500030	S801S-K0,5	2CCF019937R0001	0.24	1
	1	500047	S801S-K1	2CCF019938R0001	0.24	1
	1.6	500054	S801S-K1,6	2CCF019939R0001	0.24	1
	2	500061	S801S-K2	2CCF019940R0001	0.24	1
	2.5	500078	S801S-K2,5	2CCF019941R0001	0.24	1
	3	500085	S801S-K3	2CCF019942R0001	0.24	1
	4	500092	S801S-K4	2CCF019943R0001	0.24	1
	5	500108	S801S-K5	2CCF019944R0001	0.24	1
	6	408220	S801S-K6	2CCS861001R0067	0.24	1
	8	411442	S801S-K8	2CCS861001R0407	0.24	1
	10	201449	S801S-K10	2CCS861001R0427	0.24	1
	13	201456	S801S-K13	2CCS861001R0447	0.24	1
	16	201463	S801S-K16	2CCS861001R0467	0.24	1
	20	201470	S801S-K20	2CCS861001R0487	0.24	1
	25	201487	S801S-K25	2CCS861001R0517	0.24	1
	32	201494	S801S-K32	2CCS861001R0537	0.24	1
	40	201500	S801S-K40	2CCS861001R0557	0.24	1
	50	201517	S801S-K50	2CCS861001R0577	0.24	1
	63	201524	S801S-K63	2CCS861001R0597	0.24	1
2	0.5	500115	S802S-K0,5	2CCF019945R0001	0.49	1
	1	500122	S802S-K1	2CCF019946R0001	0.49	1
	1.6	500139	S802S-K1,6	2CCF019947R0001	0.49	1
	2	500146	S802S-K2	2CCF019948R0001	0.49	1
	2.5	500153	S802S-K2,5	2CCF019949R0001	0.49	1
	3	500160	S802S-K3	2CCF019950R0001	0.49	1
	4	500177	S802S-K4	2CCF019951R0001	0.49	1
	5	500184	S802S-K5	2CCF019952R0001	0.49	1
	6	408237	S802S-K6	2CCS862001R0067	0.49	1
	8	411459	S802S-K8	2CCS862001R0407	0.49	1
	10	201562	S802S-K10	2CCS862001R0427	0.49	1
	13	201579	S802S-K13	2CCS862001R0447	0.49	1
	16	201586	S802S-K16	2CCS862001R0467	0.49	1
	20	201593	S802S-K20	2CCS862001R0487	0.49	1
	25	201609	S802S-K25	2CCS862001R0517	0.49	1
	32	201616	S802S-K32	2CCS862001R0537	0.49	1
	40	201623	S802S-K40	2CCS862001R0557	0.49	1
	50	201630	S802S-K50	2CCS862001R0577	0.49	1
	63	201647	S802S-K63	2CCS862001R0597	0.49	1

High performance MCBs

S800S series with cage terminal, K characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	500191	S803S-K0,5	2CCF019953R0001	0.74	1
	1	500207	S803S-K1	2CCF019954R0001	0.74	1
	1.6	500214	S803S-K1,6	2CCF019955R0001	0.74	1
	2	500221	S803S-K2	2CCF019956R0001	0.74	1
	2.5	500238	S803S-K2,5	2CCF019957R0001	0.74	1
	3	500245	S803S-K3	2CCF019958R0001	0.74	1
	4	500252	S803S-K4	2CCF019959R0001	0.74	1
	5	500269	S803S-K5	2CCF019960R0001	0.74	1
	6	408244	S803S-K6	2CCS863001R0067	0.74	1
	8	411466	S803S-K8	2CCS863001R0407	0.74	1
	10	201685	S803S-K10	2CCS863001R0427	0.74	1
	13	201692	S803S-K13	2CCS863001R0447	0.74	1
	16	201708	S803S-K16	2CCS863001R0467	0.74	1
	20	201715	S803S-K20	2CCS863001R0487	0.74	1
	25	201722	S803S-K25	2CCS863001R0517	0.74	1
	32	201739	S803S-K32	2CCS863001R0537	0.74	1
	40	201746	S803S-K40	2CCS863001R0557	0.74	1
	50	201753	S803S-K50	2CCS863001R0577	0.74	1
	63	201760	aS803S-K63	2CCS863001R0597	0.74	1
4	0.5	500276	S804S-K0,5	2CCF019961R0001	0.98	1
	1	500283	S804S-K1	2CCF019962R0001	0.98	1
	1.6	500290	S804S-K1,6	2CCF019963R0001	0.98	1
	2	500306	S804S-K2	2CCF019964R0001	0.98	1
	2.5	500313	S804S-K2,5	2CCF019965R0001	0.98	1
	3	500320	S804S-K3	2CCF019966R0001	0.98	1
	4	500337	S804S-K4	2CCF019967R0001	0.98	1
	5	500344	S804S-K5	2CCF019968R0001	0.98	1
	6	408251	S804S-K6	2CCS864001R0067	0.98	1
	8	411473	S804S-K8	2CCS864001R0407	0.98	1
	10	201807	S804S-K10	2CCS864001R0427	0.98	1
	13	201814	S804S-K13	2CCS864001R0447	0.98	1
	16	201821	S804S-K16	2CCS864001R0467	0.98	1
	20	201838	S804S-K20	2CCS864001R0487	0.98	1
	25	201845	S804S-K25	2CCS864001R0517	0.98	1
	32	201852	S804S-K32	2CCS864001R0537	0.98	1
	40	201869	S804S-K40	2CCS864001R0557	0.98	1
	50	201876	S804S-K50	2CCS864001R0577	0.98	1
	63	201883	S804S-K63	2CCS864001R0597	0.98	1

High performance MCBs

S800S series KM characteristic



S803S

S800S-KM characteristic with cage terminal

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; only magnetic version dedicated to protect motors; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream; version dedicated to application in direct current circuits.

Applications: industrial, motor protection.

Standard: IEC/EN 60947-2

Icu=50kA

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	10	441104	S803S-KM10	2CCF019559R0001	0.735	1
	16	441111	S803S-KM16	2CCF019560R0001	0.735	1
	20	202194	S803S-KM20	2CCS863001R0486	0.74	1
	25	202200	S803S-KM25	2CCS863001R0516	0.74	1
	32	202217	S803S-KM32	2CCS863001R0536	0.74	1
	40	202224	S803S-KM40	2CCS863001R0556	0.74	1
	50	202231	S803S-KM50	2CCS863001R0576	0.74	1
	63	202248	S803S-KM63	2CCS863001R0596	0.74	1
	80	202255	S803S-KM80	2CCS863001R0626	0.74	1

*M stands for magnetic tripping only

S800S-KM-R characteristic with ring terminal connection

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; only magnetic version dedicated to protect motors; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream; version dedicated to application in direct current circuits.

Applications: industrial, motor protection.

Standard: IEC/EN 60947-2

Icu=50kA



S803S

Number of poles	Rated current In A	Bbn 7612271 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	20	210830	S803S-KM20-R	2CCS863002R0486		0.735	1
	25	210847	S803S-KM25-R	2CCS863002R0516		0.735	1
	32	210854	S803S-KM32-R	2CCS863002R0536		0.735	1
	40	207786	S803S-KM40-R	2CCS863002R0556		0.735	1
	50	207793	S803S-KM50-R	2CCS863002R0576		0.735	1
	63	207809	S803S-KM63-R	2CCS863002R0596		0.735	1
	80	207816	S803S-KM80-R	2CCS863002R0626		0.735	1

High performance MCBs

S800N series with cage terminal, B characteristic

S800N-B characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2

Icn=20 kA

Icu=36 kA



S801N



S802N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	6	408428	S801N-B6	2CCS891001R0065	0.24	1
	8	411640	S801N-B8	2CCS891001R0085	0.24	1
	10	203801	S801N-B10	2CCS891001R0105	0.24	1
	13	203818	S801N-B13	2CCS891001R0135	0.24	1
	16	203825	S801N-B16	2CCS891001R0165	0.24	1
	20	203832	S801N-B20	2CCS891001R0205	0.24	1
	25	203849	S801N-B25	2CCS891001R0255	0.24	1
	32	203856	S801N-B32	2CCS891001R0325	0.24	1
	40	203863	S801N-B40	2CCS891001R0405	0.24	1
	50	203870	S801N-B50	2CCS891001R0505	0.24	1
	63	203887	S801N-B63	2CCS891001R0635	0.24	1
2	6	408435	S802N-B6	2CCS892001R0065	0.48	1
	8	411657	S802N-B8	2CCS892001R0085	0.48	1
	10	203924	S802N-B10	2CCS892001R0105	0.48	1
	13	203931	S802N-B13	2CCS892001R0135	0.48	1
	16	203948	S802N-B16	2CCS892001R0165	0.48	1
	20	203955	S802N-B20	2CCS892001R0205	0.48	1
	25	203962	S802N-B25	2CCS892001R0255	0.48	1
	32	203979	S802N-B32	2CCS892001R0325	0.48	1
	40	203986	S802N-B40	2CCS892001R0405	0.48	1
	50	203993	S802N-B50	2CCS892001R0505	0.48	1
	63	204006	S802N-B63	2CCS892001R0635	0.48	1

High performance MCBs

S800N series with cage terminal, B characteristic



S803N



S804N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	6	408442	S803N-B6	2CCS893001R0065	0.72	1
	8	411664	S803N-B8	2CCS893001R0085	0.72	1
	10	204044	S803N-B10	2CCS893001R0105	0.72	1
	13	204051	S803N-B13	2CCS893001R0135	0.72	1
	16	204068	S803N-B16	2CCS893001R0165	0.72	1
	20	204075	S803N-B20	2CCS893001R0205	0.72	1
	25	204082	S803N-B25	2CCS893001R0255	0.72	1
	32	204099	S803N-B32	2CCS893001R0325	0.72	1
	40	204105	S803N-B40	2CCS893001R0405	0.72	1
	50	204112	S803N-B50	2CCS893001R0505	0.72	1
	63	204129	S803N-B63	2CCS893001R0635	0.72	1
4	6	408459	S804N-B6	2CCS894001R0065	0.96	1
	8	411671	S804N-B8	2CCS894001R0085	0.96	1
	10	204167	S804N-B10	2CCS894001R0105	0.96	1
	13	204174	S804N-B13	2CCS894001R0135	0.96	1
	16	204181	S804N-B16	2CCS894001R0165	0.96	1
	20	204198	S804N-B20	2CCS894001R0205	0.96	1
	25	204204	S804N-B25	2CCS894001R0255	0.96	1
	32	204211	S804N-B32	2CCS894001R0325	0.96	1
	40	204228	S804N-B40	2CCS894001R0405	0.96	1
	50	204235	S804N-B50	2CCS894001R0505	0.96	1
	63	204242	S804N-B63	2CCS894001R0635	0.96	1

High performance MCBs

S800N series with cage terminal, C characteristic

S800N-C characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for resistive and inductive loads with low in-rush current; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2

Icn=20 kA

Icu=36 kA



S801N



S802N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	6	408466	S801N-C6	2CCS891001R0064	0.24	1
	8	411688	S801N-C8	2CCS891001R0084	0.24	1
	10	204280	S801N-C10	2CCS891001R0104	0.24	1
	13	204297	S801N-C13	2CCS891001R0134	0.24	1
	16	204303	S801N-C16	2CCS891001R0164	0.24	1
	20	204310	S801N-C20	2CCS891001R0204	0.24	1
	25	204327	S801N-C25	2CCS891001R0254	0.24	1
	32	204334	S801N-C32	2CCS891001R0324	0.24	1
	40	204341	S801N-C40	2CCS891001R0404	0.24	1
	50	204358	S801N-C50	2CCS891001R0504	0.24	1
	63	204365	S801N-C63	2CCS891001R0634	0.24	1
2	6	408473	S802N-C6	2CCS892001R0064	0.48	1
	8	411695	S802N-C8	2CCS892001R0084	0.48	1
	10	204402	S802N-C10	2CCS892001R0104	0.48	1
	13	204419	S802N-C13	2CCS892001R0134	0.48	1
	16	204426	S802N-C16	2CCS892001R0164	0.48	1
	20	204433	S802N-C20	2CCS892001R0204	0.48	1
	25	204440	S802N-C25	2CCS892001R0254	0.48	1
	32	204457	S802N-C32	2CCS892001R0324	0.48	1
	40	204464	S802N-C40	2CCS892001R0404	0.48	1
	50	204471	S802N-C50	2CCS892001R0504	0.48	1
	63	204488	S802N-C63	2CCS892001R0634	0.48	1

High performance MCBs

S800N series with cage terminal, C characteristic



S803N



S804N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	6	408480	S803N-C6	2CCS893001R0064	0.72	1
	8	411701	S803N-C8	2CCS893001R0084	0.72	1
	10	204525	S803N-C10	2CCS893001R0104	0.72	1
	13	204532	S803N-C13	2CCS893001R0134	0.72	1
	16	204549	S803N-C16	2CCS893001R0164	0.72	1
	20	204556	S803N-C20	2CCS893001R0204	0.72	1
	25	204563	S803N-C25	2CCS893001R0254	0.72	1
	32	204570	S803N-C32	2CCS893001R0324	0.72	1
	40	204587	S803N-C40	2CCS893001R0404	0.72	1
	50	204594	S803N-C50	2CCS893001R0504	0.72	1
	63	204600	S803N-C63	2CCS893001R0634	0.72	1
4	6	408497	S804N-C6	2CCS894001R0064	0.96	1
	8	411718	S804N-C8	2CCS894001R0084	0.96	1
	10	204648	S804N-C10	2CCS894001R0104	0.96	1
	13	204655	S804N-C13	2CCS894001R0134	0.96	1
	16	204662	S804N-C16	2CCS894001R0164	0.96	1
	20	204679	S804N-C20	2CCS894001R0204	0.96	1
	25	204686	S804N-C25	2CCS894001R0254	0.96	1
	32	204693	S804N-C32	2CCS894001R0324	0.96	1
	40	204709	S804N-C40	2CCS894001R0404	0.96	1
	50	204716	S804N-C50	2CCS894001R0504	0.96	1
	63	204723	S804N-C63	2CCS894001R0634	0.96	1

High performance MCBs

S800N series with cage terminal, D characteristic

S800N-D characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for circuits which supply loads with high in-rush current at the circuit closing (motors, LV / LV transformers, breakdown lamps); very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60898, IEC/EN 60947-2

Icn=20 kA

Icu=36 kA



S801N



S802N



S803N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	6	408503	S801N-D6	2CCS891001R0061	0.24	1
	8	411725	S801N-D8	2CCS891001R0081	0.24	1
	10	204761	S801N-D10	2CCS891001R0101	0.24	1
	13	204778	S801N-D13	2CCS891001R0131	0.24	1
	16	204785	S801N-D16	2CCS891001R0161	0.24	1
	20	204792	S801N-D20	2CCS891001R0201	0.24	1
	25	204808	S801N-D25	2CCS891001R0251	0.24	1
	32	204815	S801N-D32	2CCS891001R0321	0.24	1
	40	204822	S801N-D40	2CCS891001R0401	0.24	1
	50	204839	S801N-D50	2CCS891001R0501	0.24	1
	63	204846	S801N-D63	2CCS891001R0631	0.24	1
2	6	408510	S802N-D6	2CCS892001R0061	0.49	1
	8	411732	S802N-D8	2CCS892001R0081	0.49	1
	10	204884	S802N-D10	2CCS892001R0101	0.49	1
	13	204891	S802N-D13	2CCS892001R0131	0.49	1
	16	204907	S802N-D16	2CCS892001R0161	0.49	1
	20	204914	S802N-D20	2CCS892001R0201	0.49	1
	25	204921	S802N-D25	2CCS892001R0251	0.49	1
	32	204938	S802N-D32	2CCS892001R0321	0.49	1
	40	204945	S802N-D40	2CCS892001R0401	0.49	1
	50	204952	S802N-D50	2CCS892001R0501	0.49	1
	63	204969	S802N-D63	2CCS892001R0631	0.49	1
3	6	408527	S803N-D6	2CCS893001R0061	0.74	1
	8	411749	S803N-D8	2CCS893001R0081	0.74	1
	10	205003	S803N-D10	2CCS893001R0101	0.74	1
	13	205010	S803N-D13	2CCS893001R0131	0.74	1
	16	205027	S803N-D16	2CCS893001R0161	0.74	1
	20	205034	S803N-D20	2CCS893001R0201	0.74	1
	25	205041	S803N-D25	2CCS893001R0251	0.74	1
	32	205058	S803N-D32	2CCS893001R0321	0.74	1
	40	205065	S803N-D40	2CCS893001R0401	0.74	1
	50	205072	S803N-D50	2CCS893001R0501	0.74	1
	63	205089	S803N-D63	2CCS893001R0631	0.74	1

High performance MCBs

S800N series with cage terminal, D characteristic



S804N

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
4	6	408534	S804N-D6	2CCS894001R0061	0.98	1
	8	411756	S804N-D8	2CCS894001R0081	0.98	1
	10	205126	S804N-D10	2CCS894001R0101	0.98	1
	13	205133	S804N-D13	2CCS894001R0131	0.98	1
	16	205140	S804N-D16	2CCS894001R0161	0.98	1
	20	205157	S804N-D20	2CCS894001R0201	0.98	1
	25	205164	S804N-D25	2CCS894001R0251	0.98	1
	32	205171	S804N-D32	2CCS894001R0321	0.98	1
	40	205188	S804N-D40	2CCS894001R0401	0.98	1
	50	205195	S804N-D50	2CCS894001R0501	0.98	1
	63	205201	S804N-D63	2CCS894001R0631	0.98	1

High performance MCBs

S800C series with cage terminal, B characteristic

S800C-B characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2, IEC/EN 60898, UL 1077, supplementary protector

Icn=15 kA

Icu=25 kA



S801C



S802C



S803C



S804C

Number of poles	Rated current [A]	GTIN EAN 76122712	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	10	12087	S801C-B10	2CCS881001R0105	0.25	1
	13	12247	S801C-B13	2CCS881001R0135	0.25	1
	16	12407	S801C-B16	2CCS881001R0165	0.25	1
	20	12568	S801C-B20	2CCS881001R0205	0.25	1
	25	12728	S801C-B25	2CCS881001R0255	0.25	1
	32	12889	S801C-B32	2CCS881001R0325	0.25	1
	40	13046	S801C-B40	2CCS881001R0405	0.25	1
	50	13206	S801C-B50	2CCS881001R0505	0.25	1
2	63	13367	S801C-B63	2CCS881001R0635	0.25	1
	10	12094	S802C-B10	2CCS882001R0105	0.49	1
	13	12254	S802C-B13	2CCS882001R0135	0.49	1
	16	12414	S802C-B16	2CCS882001R0165	0.49	1
	20	12575	S802C-B20	2CCS882001R0205	0.49	1
	25	12735	S802C-B25	2CCS882001R0255	0.49	1
	32	12896	S802C-B32	2CCS882001R0325	0.49	1
	40	13053	S802C-B40	2CCS882001R0405	0.49	1
3	50	13213	S802C-B50	2CCS882001R0505	0.49	1
	63	13374	S802C-B63	2CCS882001R0635	0.49	1
	10	12100	S803C-B10	2CCS883001R0105	0.74	1
	13	12261	S803C-B13	2CCS883001R0135	0.74	1
	16	12421	S803C-B16	2CCS883001R0165	0.74	1
	20	12582	S803C-B20	2CCS883001R0205	0.74	1
	25	12742	S803C-B25	2CCS883001R0255	0.74	1
	32	12902	S803C-B32	2CCS883001R0325	0.74	1
4	40	13060	S803C-B40	2CCS883001R0405	0.74	1
	50	13220	S803C-B50	2CCS883001R0505	0.74	1
	63	13381	S803C-B63	2CCS883001R0635	0.74	1
	10	12117	S804C-B10	2CCS884001R0105	0.98	1
	13	12278	S804C-B13	2CCS884001R0135	0.98	1
	16	12438	S804C-B16	2CCS884001R0165	0.98	1
	20	12599	S804C-B20	2CCS884001R0205	0.98	1
	25	12759	S804C-B25	2CCS884001R0255	0.98	1
	32	12919	S804C-B32	2CCS884001R0325	0.98	1
	40	13077	S804C-B40	2CCS884001R0405	0.98	1
	50	13237	S804C-B50	2CCS884001R0505	0.98	1
	63	13398	S804C-B63	2CCS884001R0635	0.98	1

High performance MCBs

S800C series with cage terminal, C characteristic

S800C-C characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2, IEC/EN 60898, UL 1077, supplementary protector

Icn=15 kA

Icu=25 kA



S801C



S802C



S803C



S804C

Number of poles	Rated current [A]	GTIN EAN 76122712	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	10	12124	S801C-C10	2CCS881001R0104	0.25	1
	13	12285	S801C-C13	2CCS881001R0134	0.25	1
	16	12445	S801C-C16	2CCS881001R0164	0.25	1
	20	12605	S801C-C20	2CCS881001R0204	0.25	1
	25	12766	S801C-C25	2CCS881001R0254	0.25	1
	32	12926	S801C-C32	2CCS881001R0324	0.25	1
	40	13084	S801C-C40	2CCS881001R0404	0.25	1
	50	13244	S801C-C50	2CCS881001R0504	0.25	1
2	63	13404	S801C-C63	2CCS881001R0634	0.25	1
	10	12131	S802C-C10	2CCS882001R0104	0.49	1
	13	12292	S802C-C13	2CCS882001R0134	0.49	1
	16	12452	S802C-C16	2CCS882001R0164	0.49	1
	20	12612	S802C-C20	2CCS882001R0204	0.49	1
	25	12773	S802C-C25	2CCS882001R0254	0.49	1
	32	12933	S802C-C32	2CCS882001R0324	0.49	1
	40	13091	S802C-C40	2CCS882001R0404	0.49	1
3	50	13251	S802C-C50	2CCS882001R0504	0.49	1
	63	13411	S802C-C63	2CCS882001R0634	0.49	1
	10	12148	S803C-C10	2CCS883001R0104	0.74	1
	13	12308	S803C-C13	2CCS883001R0134	0.74	1
	16	12469	S803C-C16	2CCS883001R0164	0.74	1
	20	12629	S803C-C20	2CCS883001R0204	0.74	1
	25	12780	S803C-C25	2CCS883001R0254	0.74	1
	32	12940	S803C-C32	2CCS883001R0324	0.74	1
4	40	13107	S803C-C40	2CCS883001R0404	0.74	1
	50	13268	S803C-C50	2CCS883001R0504	0.74	1
	63	13428	S803C-C63	2CCS883001R0634	0.74	1
	10	12155	S804C-C10	2CCS884001R0104	0.98	1
	13	12315	S804C-C13	2CCS884001R0134	0.98	1
	16	12476	S804C-C16	2CCS884001R0164	0.98	1
	20	12636	S804C-C20	2CCS884001R0204	0.98	1
	25	12797	S804C-C25	2CCS884001R0254	0.98	1
	32	12957	S804C-C32	2CCS884001R0324	0.98	1
	40	13114	S804C-C40	2CCS884001R0404	0.98	1
	50	13275	S804C-C50	2CCS884001R0504	0.98	1
	63	13435	S804C-C63	2CCS884001R0634	0.98	1

High performance MCBs

S800C series with cage terminal, D characteristic

S800C-D characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2, IEC/EN 60898, UL 1077, supplementary protector

I_{cn}=15kA

I_{cu}=25 kA



S801C



S802C



S803C



S804C

Number of poles	Rated current [A]	GTIN EAN 76122712	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	10	12162	S801C-D10	2CCS881001R0101	0.25	1
	13	12322	S801C-D13	2CCS881001R0131	0.25	1
	16	12483	S801C-D16	2CCS881001R0161	0.25	1
	20	12643	S801C-D20	2CCS881001R0201	0.25	1
	25	12803	S801C-D25	2CCS881001R0251	0.25	1
	32	12964	S801C-D32	2CCS881001R0321	0.25	1
	40	13121	S801C-D40	2CCS881001R0401	0.25	1
	50	13282	S801C-D50	2CCS881001R0501	0.25	1
2	63	13442	S801C-D63	2CCS881001R0631	0.25	1
	10	12179	S802C-D10	2CCS882001R0101	0.49	1
	13	12339	S802C-D13	2CCS882001R0131	0.49	1
	16	12490	S802C-D16	2CCS882001R0161	0.49	1
	20	12650	S802C-D20	2CCS882001R0201	0.49	1
	25	12810	S802C-D25	2CCS882001R0251	0.49	1
	32	12971	S802C-D32	2CCS882001R0321	0.49	1
	40	13138	S802C-D40	2CCS882001R0401	0.49	1
3	50	13299	S802C-D50	2CCS882001R0501	0.49	1
	63	13459	S802C-D63	2CCS882001R0631	0.49	1
	10	12186	S803C-D10	2CCS883001R0101	0.74	1
	13	12346	S803C-D13	2CCS883001R0131	0.74	1
	16	12506	S803C-D16	2CCS883001R0161	0.74	1
	20	12667	S803C-D20	2CCS883001R0201	0.74	1
	25	12827	S803C-D25	2CCS883001R0251	0.74	1
	32	12988	S803C-D32	2CCS883001R0321	0.74	1
4	40	13145	S803C-D40	2CCS883001R0401	0.74	1
	50	13305	S803C-D50	2CCS883001R0501	0.74	1
	63	13466	S803C-D63	2CCS883001R0631	0.74	1
	10	12193	S804C-D10	2CCS884001R0101	0.98	1
	13	12353	S804C-D13	2CCS884001R0131	0.98	1
	16	12513	S804C-D16	2CCS884001R0161	0.98	1
	20	12674	S804C-D20	2CCS884001R0201	0.98	1
	25	12834	S804C-D25	2CCS884001R0251	0.98	1
	32	12995	S804C-D32	2CCS884001R0321	0.98	1
	40	13152	S804C-D40	2CCS884001R0401	0.98	1
	50	13312	S804C-D50	2CCS884001R0501	0.98	1
	63	13473	S804C-D63	2CCS884001R0631	0.98	1

High performance MCBs

S800C series with cage terminal, K characteristic

S800C-K characteristic

Function: protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream.

Applications: commercial and industrial.

Standard: IEC/EN 60947-2, UL 1077, supplementary protector

Icu=25 kA



S801C



S802C



S803C



S804C

Number of poles	Rated current [A]	GTIN EAN 76122712	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	10	12209	S801C-K10	2CCS881001R0427	0.25	1
	13	12360	S801C-K13	2CCS881001R0447	0.25	1
	16	12520	S801C-K16	2CCS881001R0467	0.25	1
	20	12681	S801C-K20	2CCS881001R0487	0.25	1
	25	12841	S801C-K25	2CCS881001R0517	0.25	1
	32	13008	S801C-K32	2CCS881001R0537	0.25	1
	40	13169	S801C-K40	2CCS881001R0557	0.25	1
	50	13329	S801C-K50	2CCS881001R0577	0.25	1
2	63	13480	S801C-K63	2CCS881001R0597	0.25	1
	10	12216	S802C-K10	2CCS882001R0427	0.49	1
	13	12377	S802C-K13	2CCS882001R0447	0.49	1
	16	12537	S802C-K16	2CCS882001R0467	0.49	1
	20	12698	S802C-K20	2CCS882001R0487	0.49	1
	25	12858	S802C-K25	2CCS882001R0517	0.49	1
	32	13015	S802C-K32	2CCS882001R0537	0.49	1
	40	13176	S802C-K40	2CCS882001R0557	0.49	1
3	50	13336	S802C-K50	2CCS882001R0577	0.49	1
	63	13497	S802C-K63	2CCS882001R0597	0.49	1
	10	12223	S803C-K10	2CCS883001R0427	0.74	1
	13	12384	S803C-K13	2CCS883001R0447	0.74	1
	16	12544	S803C-K16	2CCS883001R0467	0.74	1
	20	12704	S803C-K20	2CCS883001R0487	0.74	1
	25	12865	S803C-K25	2CCS883001R0517	0.74	1
	32	13022	S803C-K32	2CCS883001R0537	0.74	1
4	40	13183	S803C-K40	2CCS883001R0557	0.74	1
	50	13343	S803C-K50	2CCS883001R0577	0.74	1
	63	13503	S803C-K63	2CCS883001R0597	0.74	1
	10	12230	S804C-K10	2CCS884001R0427	0.98	1
	13	12391	S804C-K13	2CCS884001R0447	0.98	1
	16	12551	S804C-K16	2CCS884001R0467	0.98	1
	20	12711	S804C-K20	2CCS884001R0487	0.98	1
	25	12872	S804C-K25	2CCS884001R0517	0.98	1
	32	13039	S804C-K32	2CCS884001R0537	0.98	1
	40	13190	S804C-K40	2CCS884001R0557	0.98	1
	50	13350	S804C-K50	2CCS884001R0577	0.98	1
	63	13510	S804C-K63	2CCS884001R0597	0.98	1

MCBs

S800S series DC technical features

S800S-UC		
General Data		
Tripping characteristics		UCB, UCK
Standards		IEC/EN 60947-2
Number of poles		1 ... 4
Rated current I_n	A	0.5 ... 125
Rated frequency f	Hz	50/60
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	DC 1500
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	kV	8
Dielectric test voltage at ind. freq. for 1 min.	kV	2.4
Overtoltage category		III
Pollution degree		2
Suitability for isolation		yes
Grid distance	mm	-
Data acc. to IEC/EN 60898-1		
Rated operational voltage U_e	V	-
Min. operating voltage	V	-
Rated short-circuit capacity I_{cn}	kA	-
Reference temperature for tripping characteristics	°C	-
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	-
Service short-circuit capacity I_{cs}	kA	-
Energy limiting class		-
Data acc. to IEC/EN 60947-2		
Rated operational voltage U_e	V	DC 250 (1-pole) DC 500 (2-pole) DC 750 (3-pole) DC 750 (4-pole) (63 ... 125 A) DC 1000 (4-pole) (up to 50 A)
Min. operating voltage	V	DC 12 V
Rated ultimate short-circuit capacity I_{cu} (Single pole / Multi pole)	kA	DC 250 V (1-pole) = 50kA DC 500 V (2-pole) = 50kA DC 750 V (3-pole) = 50kA DC 750 V (4-pole) (63...125A) = 50kA DC 1000V (4-pole)(up to 50A) = 50 kA
Rated service short-circuit capacity I_{cs} (Single pole / Multi pole)	kA	DC 250 V (1-pole): 50kA for $I_n < 125A$; 20kA $I_n = 125A$ DC 500 V (2-pole): 50kA for $I_n < 125A$; 20kA $I_n = 125A$ DC 750 V (3-pole): 50kA for $I_n < 125A$; 20kA $I_n = 125A$ DC 750 V (4-pole): 50kA for $I_n = (63...100A)$; 20kA $I_n = 125A$ DC 1000V (4-pole) (up to $I_n = 50A$): 50kA
Reference temperature for tripping characteristics	°C	UCB: 30°C UCK: 40°C
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	0.5...100 A: 1500 electrical / 10000 mechanical 125 A: 1000 electrical / 8000 mechanical

MCBs

S800S series DC technical features

S800S / S803S-KM		
Data acc. to UL 1077/ C22.2 No 235, Supplementary Protector (only for S800S)		
Alternating current:		1
int. cap.		240: 30 (0.5...63A) 277: 14 (0.5...63A) 347: 6 (0.5...63A)
		2,3,4
		240: 30 (0.5...63A) 480 Y/277: 14 (0.5...63A) 600 Y/347: 6 (0.5...63A)
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Classification for the component requirement / hazard level acc. to EN45545-2		R26 / HL3; R22 / HL2
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Shock & Vibration Resistance acc. to IEC 61373		5g / 30ms, Cat 1 / Class B
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I _e , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1	°C/RH	16 hours -40°C
Ambient temperature (with daily average ≤ +35 °C)	°C	-40...+70
Storage temperature	°C	-40 ... +70
Installation		
Terminal type		Failsafe cage or ringlug terminal
Connections (top/bottom) – C _u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
	AWG	10 - 30 A: 14 AWG – 2 AWG
	(S800S only)	40 - 63 A: 14 AWG – 2 AWG
Tightening torque	Nm	3.5
	in-lbs.	31
Wire stripping length	mm	19
Screwdriver		POZI 2
Mounting type		EN 60715
Mounting position		Any
Supply from		Top and bottom
Dimensions and weight		
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27*
Pole weight	g	ca. 240

* On multi-pole versions, rated current 125A is equipped with a lateral cover of 4.5mm on each product side. Overall product width increases of 9mm

	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	yes	yes	no	yes	yes	yes

High performance MCBs

S800S series DC range with cage terminal, UC-B characteristic

S800S-UCB characteristic

Function: Non polarized MCB for direct current applications up to 1000 VDC, providing protection and control of the circuits against overloads and short-circuits when a high breaking capacity is required; protection for people and big length cables in TN and IT systems; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream; version dedicated to application in direct current circuits.

Applications: commercial and industrial, universal current .

Standard: IEC/EN 60947-2

Icu=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Coade	Order code		
1	0.5	500351	S801S-UCB0,5	2CCF019969R0001	0.25	1
	1	500368	S801S-UCB1	2CCF019970R0001	0.25	1
	1.6	500375	S801S-UCB1,6	2CCF019971R0001	0.25	1
	2	500382	S801S-UCB2	2CCF019972R0001	0.25	1
	2.5	500399	S801S-UCB2,5	2CCF019973R0001	0.25	1
	3	500405	S801S-UCB3	2CCF019974R0001	0.25	1
	4	500412	S801S-UCB4	2CCF019975R0001	0.25	1
	5	500429	S801S-UCB5	2CCF019976R0001	0.25	1
	6	500436	S801S-UCB6	2CCF019977R0001	0.25	1
	8	500443	S801S-UCB8	2CCF019978R0001	0.25	1
	10	202842	S801S-UCB10	2CCS861001R1105	0.24	1
	13	202859	S801S-UCB13	2CCS861001R1135	0.24	1
	16	202866	S801S-UCB16	2CCS861001R1165	0.24	1
	20	202873	S801S-UCB20	2CCS861001R1205	0.24	1
	25	202880	S801S-UCB25	2CCS861001R1255	0.24	1
	32	202897	S801S-UCB32	2CCS861001R1325	0.24	1
	40	202903	S801S-UCB40	2CCS861001R1405	0.24	1
	50	202910	S801S-UCB50	2CCS861001R1505	0.24	1
	63	202927	S801S-UCB63	2CCS861001R1635	0.24	1
	80	202934	S801S-UCB80	2CCS861001R1805	0.24	1
	100	202941	S801S-UCB100	2CCS861001R1825	0.24	1
	125	202958	S801S-UCB125	2CCS861001R1845	0.24	1
2	0.5	500559	S802S-UCB0,5	2CCF019989R0001	0.49	1
	1	500566	S802S-UCB1	2CCF019990R0001	0.49	1
	1.6	500573	S802S-UCB1,6	2CCF019991R0001	0.49	1
	2	500580	S802S-UCB2	2CCF019992R0001	0.49	1
	2.5	500597	S802S-UCB2,5	2CCF019993R0001	0.49	1
	3	500603	S802S-UCB3	2CCF019994R0001	0.49	1
	4	500610	S802S-UCB4	2CCF019995R0001	0.49	1
	5	500627	S802S-UCB5	2CCF019996R0001	0.49	1
	6	500634	S802S-UCB6	2CCF019997R0001	0.49	1
	8	500641	S802S-UCB8	2CCF019998R0001	0.49	1
	10	202965	S802S-UCB10	2CCS862001R1105	0.49	1
	13	202972	S802S-UCB13	2CCS862001R1135	0.49	1
	16	202989	S802S-UCB16	2CCS862001R1165	0.49	1
	20	202996	S802S-UCB20	2CCS862001R1205	0.49	1
	25	203009	S802S-UCB25	2CCS862001R1255	0.49	1
	32	203016	S802S-UCB32	2CCS862001R1325	0.49	1
	40	203023	S802S-UCB40	2CCS862001R1405	0.49	1
	50	203030	S802S-UCB50	2CCS862001R1505	0.49	1
	63	203047	S802S-UCB63	2CCS862001R1635	0.49	1
	80	203054	S802S-UCB80	2CCS862001R1805	0.49	1
	100	203061	S802S-UCB100	2CCS862001R1825	0.49	1
	125	523343	S802S-UCB125	2CCG001894R0001	0.515	1

*For DC applications

High performance MCBs

S800S series DC range with cage terminal, UC-B characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	502713	S803S-UCB0,5	2CCF030040R0001	0.74	1
	1	502720	S803S-UCB1	2CCF030041R0001	0.74	1
	1.6	502874	S803S-UCB1,6	2CCF030056R0001	0.74	1
	2	502737	S803S-UCB2	2CCF030042R0001	0.74	1
	2.5	502744	S803S-UCB2,5	2CCF030043R0001	0.74	1
	3	502881	S803S-UCB3	2CCF030057R0001	0.74	1
	4	502751	S803S-UCB4	2CCF030044R0001	0.74	1
	5	502768	S803S-UCB5	2CCF030045R0001	0.74	1
	6	502898	S803S-UCB6	2CCF030058R0001	0.74	1
	8	500849	S803S-UCB8	2CCF020018R0001	0.74	1
	10	203085	S803S-UCB10	2CCS863001R1105	0.74	1
	13	203092	S803S-UCB13	2CCS863001R1135	0.74	1
	16	203108	S803S-UCB16	2CCS863001R1165	0.74	1
	20	203115	S803S-UCB20	2CCS863001R1205	0.74	1
	25	203122	S803S-UCB25	2CCS863001R1255	0.74	1
	32	203139	S803S-UCB32	2CCS863001R1325	0.74	1
	40	203146	S803S-UCB40	2CCS863001R1405	0.74	1
	50	203153	S803S-UCB50	2CCS863001R1505	0.74	1
	63	203160	S803S-UCB63	2CCS863001R1635	0.74	1
	80	203177	S803S-UCB80	2CCS863001R1805	0.74	1
	100	203184	S803S-UCB100	2CCS863001R1825	0.74	1
	125	523381	S803S-UCB125	2CCG001898R0001	0.765	1
4	0.5	500955	S804S-UCB0,5	2CCF020029R0001	0.98	1
	1	500962	S804S-UCB1	2CCF020030R0001	0.98	1
	1.6	500979	S804S-UCB1,6	2CCF020031R0001	0.98	1
	2	500986	S804S-UCB2	2CCF020032R0001	0.98	1
	2.5	500993	S804S-UCB2,5	2CCF020033R0001	0.98	1
	3	501006	S804S-UCB3	2CCF020034R0001	0.98	1
	4	501013	S804S-UCB4	2CCF020035R0001	0.98	1
	5	502775	S804S-UCB5	2CCF030046R0001	0.98	1
	6	502782	S804S-UCB6	2CCF030047R0001	0.98	1
	8	502904	S804S-UCB8	2CCF030059R0001	0.98	1
	10	203207	S804S-UCB10	2CCS864001R1105	0.98	1
	13	203214	S804S-UCB13	2CCS864001R1135	0.98	1
	16	203221	S804S-UCB16	2CCS864001R1165	0.98	1
	20	203238	S804S-UCB20	2CCS864001R1205	0.98	1
	25	203245	S804S-UCB25	2CCS864001R1255	0.98	1
	32	203252	S804S-UCB32	2CCS864001R1325	0.98	1
	40	203269	S804S-UCB40	2CCS864001R1405	0.98	1
	50	203276	S804S-UCB50	2CCS864001R1505	0.98	1
	63	203283	S804S-UCB63	2CCS864001R1635	0.98	1
	80	203290	S804S-UCB80	2CCS864001R1805	0.98	1
	100	203306	S804S-UCB100	2CCS864001R1825	0.98	1
	125	523428	S804S-UCB125	2CCG001902R0001	1.005	1

*For DC applications

High performance MCBs

S800S series DC range with cage terminal, UC-K characteristic

S800S-UCK characteristic

Function: Non polarized MCB for direct current applications up to 1000 VDC, providing protection and control of the circuits like motors, transformer and auxiliary circuits, against overloads and short-circuits when a high breaking capacity is required; very useful when selectivity is needed vs an MCCB or back-up vs other MCBs wired downstream; version dedicated to application in direct current circuits.

Advantages: no nuisance tripping in the case of functional peak currents up to $10 \times I_n$, depending on the series; through its highly sensitive thermostatic bimetal trip, the K-type characteristic offers protection to damageable elements in the overcurrent range; it also provides the best protection to cables and lines.

Applications: commercial and industrial, universal current.

Standard: IEC/EN 60947-2

Icu=50kA



S801S



S802S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	500450	S801S-UCK0,5	2CCF019979R0001	0.25	1
	1	500467	S801S-UCK1	2CCF019980R0001	0.25	1
	1.6	500474	S801S-UCK1,6	2CCF019981R0001	0.25	1
	2	500481	S801S-UCK2	2CCF019982R0001	0.25	1
	2.5	500498	S801S-UCK2,5	2CCF019983R0001	0.25	1
	3	500504	S801S-UCK3	2CCF019984R0001	0.25	1
	4	500511	S801S-UCK4	2CCF019985R0001	0.25	1
	5	500528	S801S-UCK5	2CCF019986R0001	0.25	1
	6	500535	S801S-UCK6	2CCF019987R0001	0.25	1
	8	500542	S801S-UCK8	2CCF019988R0001	0.25	1
	10	203320	S801S-UCK10	2CCS861001R1427	0.24	1
	13	203337	S801S-UCK13	2CCS861001R1447	0.24	1
	16	203344	S801S-UCK16	2CCS861001R1467	0.24	1
	20	203351	S801S-UCK20	2CCS861001R1487	0.24	1
	25	203368	S801S-UCK25	2CCS861001R1517	0.24	1
	32	203375	S801S-UCK32	2CCS861001R1537	0.24	1
	40	203382	S801S-UCK40	2CCS861001R1557	0.24	1
	50	203399	S801S-UCK50	2CCS861001R1577	0.24	1
	63	203405	S801S-UCK63	2CCS861001R1597	0.24	1
	80	203412	S801S-UCK80	2CCS861001R1627	0.24	1
	100	203429	S801S-UCK100	2CCS861001R1637	0.24	1
	125	203436	S801S-UCK125	2CCS861001R1647	0.24	1
2	0.5	500658	S802S-UCK0,5	2CCF019999R0001	0.49	1
	1	502652	S802S-UCK1	2CCF030034R0001	0.49	1
	1.6	502669	S802S-UCK1,6	2CCF030035R0001	0.49	1
	2	502843	S802S-UCK2	2CCF030053R0001	0.49	1
	2.5	502676	S802S-UCK2,5	2CCF030036R0001	0.49	1
	3	502683	S802S-UCK3	2CCF030037R0001	0.49	1
	4	502850	S802S-UCK4	2CCF030054R0001	0.49	1
	5	502690	S802S-UCK5	2CCF030038R0001	0.49	1
	6	502706	S802S-UCK6	2CCF030039R0001	0.49	1
	8	502867	S802S-UCK8	2CCF030055R0001	0.49	1
	10	203443	S802S-UCK10	2CCS862001R1427	0.49	1
	13	203450	S802S-UCK13	2CCS862001R1447	0.49	1
	16	203467	S802S-UCK16	2CCS862001R1467	0.49	1
	20	203474	S802S-UCK20	2CCS862001R1487	0.49	1
	25	203481	S802S-UCK25	2CCS862001R1517	0.49	1
	32	203498	S802S-UCK32	2CCS862001R1537	0.49	1
	40	203504	S802S-UCK40	2CCS862001R1557	0.49	1
	50	203511	S802S-UCK50	2CCS862001R1577	0.49	1
	63	203528	S802S-UCK63	2CCS862001R1597	0.49	1
	80	203535	S802S-UCK80	2CCS862001R1627	0.49	1
	100	203542	S802S-UCK100	2CCS862001R1637	0.49	1
	125	523336	S802S-UCK125	2CCG001893R0001	0.515	1

*For DC applications

High performance MCBs

S800S series DC range with cage terminal, UC-K characteristic



S803S



S804S

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	500856	S803S-UCK0,5	2CCF020019R0001	0.74	1
	1	500863	S803S-UCK1	2CCF020020R0001	0.74	1
	1.6	500870	S803S-UCK1,6	2CCF020021R0001	0.74	1
	2	500887	S803S-UCK2	2CCF020022R0001	0.74	1
	2.5	500894	S803S-UCK2,5	2CCF020023R0001	0.74	1
	3	500900	S803S-UCK3	2CCF020024R0001	0.74	1
	4	500917	S803S-UCK4	2CCF020025R0001	0.74	1
	5	500924	S803S-UCK5	2CCF020026R0001	0.74	1
	6	500931	S803S-UCK6	2CCF020027R0001	0.74	1
	8	500948	S803S-UCK8	2CCF020028R0001	0.74	1
	10	203566	S803S-UCK10	2CCS863001R1427	0.74	1
	13	203573	S803S-UCK13	2CCS863001R1447	0.74	1
	16	203580	S803S-UCK16	2CCS863001R1467	0.74	1
	20	203597	S803S-UCK20	2CCS863001R1487	0.74	1
	25	203603	S803S-UCK25	2CCS863001R1517	0.74	1
	32	203610	S803S-UCK32	2CCS863001R1537	0.74	1
	40	203627	S803S-UCK40	2CCS863001R1557	0.74	1
	50	203634	S803S-UCK50	2CCS863001R1577	0.74	1
	63	203641	S803S-UCK63	2CCS863001R1597	0.74	1
	80	203658	S803S-UCK80	2CCS863001R1627	0.74	1
	100	203665	S803S-UCK100	2CCS863001R1637	0.74	1
	125	523374	S803S-UCK125	2CCG001897R0001	0.765	1
4	0.5	502799	S804S-UCK0,5	2CCF030048R0001	0.98	1
	1	502805	S804S-UCK1	2CCF030049R0001	0.98	1
	1.6	502911	S804S-UCK1,6	2CCF030060R0001	0.98	1
	2	502812	S804S-UCK2	2CCF030050R0001	0.98	1
	2.5	502829	S804S-UCK2,5	2CCF030051R0001	0.98	1
	3	502928	S804S-UCK3	2CCF030061R0001	0.98	1
	4	502836	S804S-UCK4	2CCF030052R0001	0.98	1
	5	502416	S804S-UCK5	2CCF030020R0001	0.98	1
	6	502607	S804S-UCK6	2CCF030029R0001	0.98	1
	8	501143	S804S-UCK8	2CCF020048R0001	0.98	1
	10	203689	S804S-UCK10	2CCS864001R1427	0.98	1
	13	203696	S804S-UCK13	2CCS864001R1447	0.98	1
	16	203702	S804S-UCK16	2CCS864001R1467	0.98	1
	20	203719	S804S-UCK20	2CCS864001R1487	0.98	1
	25	203726	S804S-UCK25	2CCS864001R1517	0.98	1
	32	203733	S804S-UCK32	2CCS864001R1537	0.98	1
	40	203740	S804S-UCK40	2CCS864001R1557	0.98	1
	50	203757	S804S-UCK50	2CCS864001R1577	0.98	1
	63	203764	S804S-UCK63	2CCS864001R1597	0.98	1
	80	203771	S804S-UCK80	2CCS864001R1627	0.98	1
	100	203788	S804S-UCK100	2CCS864001R1637	0.98	1
	125	523411	S804S-UCK125	2CCG001901R0001	1.005	1

*For DC applications

High performance MCBs

S800PV-SP series technical features

S800PV-SP		
General Data		
Tripping characteristics		SP
Standards		IEC / EN 60947-2 and Annex P (specific for PV)
Number of poles		2 ... 4
Rated frequency I _e	A	5 ... 125
Rated frequency f	Hz	-
Rated insulation voltage U _i acc. to IEC/EN 60664-1	V	DC 1500
Rated impulse withstand voltage U _{imp} (1.2/50 μs)	kV	8
Dielectric test voltage at ind. freq. for 1 min.	kV	3
Overvoltage category		III*
Pollution degree		2
Suitability for isolation		yes
Grid distance	mm	50
Data acc. to IEC/EN 60947-2		
Rated operational voltage U _e	V	2-pole DC 800V: 5 ... 125 A 3-pole DC 1200V: 5 ... 125 A 4-pole DC 1500V: 5 ... 125 A
Min. operating voltage	V	-
Rated ultimate short-circuit capacity I _{cu}	kA	5 ... 16 A acc. IEC 60947-2 Annex P. I _{cu} = 5 kA 20 ... 125 A, acc. IEC 60947-2, I _{cu} = 5 kA 20 ... 125 A, acc. IEC 60947-2 Annex P. I _{cu} = 3 kA
Rated service short-circuit capacity I _{cs}	kA	I _{cu} = I _{cs}
Reference temperature for tripping characteristics	°C	40 °C
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	acc. to Annex P: 5 ... 16 A: 300 electrical/9700 mechanical acc. to IEC 60947-2 (general part): 20 ... 100 A: 1500 electrical/8500 mechanical 125 A: 1000 electrical/9000 mechanical
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Shock resistance acc. To IEC/EN 61373		5g / 30ms, Cat 1 / Class B
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I _e , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1	°C/RH	16 hours -40°C
Ambient temperature (with daily average ≤ +35°C)	°C	-40...+70
Storage temperature	°C	-40 ... +70
Installation		
Terminal type		Failsafe cage or ringlug terminal
Connections (top/bottom) - C _u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
Tightening torque	Nm	3.5
	in-lbs.	31
Wire stripping length	mm	19
Screwdriver		POZI 2
Mounting type		Any
Mounting position		Any
Supply from		Top and bottom
Dimensions and weight		
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27**
Pole weight	g	240

*The pollution degree of the product, as defined in standard IEC 60947-1, is related to its micro environment, to which equipment is exposed. It may be different from that of the macro-environment. According to where the equipment is located, the pollution degree of the macro environment can be considered up to category IV if protection is offered by means of such as an adequate enclosure or internal heating to prevent absorption or condensation of moisture.

**On multi-pole versions, rated current 125A is equipped with a lateral cover of 4.5mm on each product side. Overall product width increases of 9mm

High performance MCBs

S800PV series with cage terminal, SP characteristic

S800PV-SP

Function: non polarized MCB for various direct current applications up to 1500 VDC.

Particularly suitable for protection and control of photovoltaic strings against overloads, short-circuits and reverse currents.

Applications: Industrial in direct current, photovoltaic systems.

Standard: IEC/EN 60947-2 and Annex P

5 ... 16A acc. IEC 60947-2 Annex P, I_{cu} 5 kA

20 ... 125A acc. IEC 60947-2, I_{cu} 5 kA

20 ... 125A acc. IEC 60947-2 Annex P, I_{cu} 3 kA



S802PV



S803PV



S804PV

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
2	5	471170	S802PV-SP5	2CCF019596R0001	0.49	1
	6	472115	S802PV-SP6	2CCF019643R0001	0.49	1
	8	472139	S802PV-SP8	2CCF019644R0001	0.49	1
	10	471194	S802PV-SP10	2CCF019597R0001	0.49	1
	13	471217	S802PV-SP13	2CCF019598R0001	0.49	1
	16	471231	S802PV-SP16	2CCF019599R0001	0.49	1
	20	471255	S802PV-SP20	2CCF019600R0001	0.49	1
	25	471279	S802PV-SP25	2CCF019601R0001	0.49	1
	32	471293	S802PV-SP32	2CCF019602R0001	0.49	1
	40	471316	S802PV-SP40	2CCF019603R0001	0.49	1
	50	471330	S802PV-SP50	2CCF019604R0001	0.49	1
	63	471354	S802PV-SP63	2CCF019605R0001	0.49	1
	80	471378	S802PV-SP80	2CCF019606R0001	0.49	1
	100	471392	S802PV-SP100	2CCF019607R0001	0.49	1
	125	520700	S802PV-SP125	2CCG001601R0001	0.515	1
3	5	471439	S803PV-SP5	2CCF019609R0001	0.74	1
	6	472153	S803PV-SP6	2CCF019645R0001	0.74	1
	8	472177	S803PV-SP8	2CCF019646R0001	0.74	1
	10	471453	S803PV-SP10	2CCF019610R0001	0.74	1
	13	471477	S803PV-SP13	2CCF019611R0001	0.74	1
	16	471491	S803PV-SP16	2CCF019612R0001	0.74	1
	20	471514	S803PV-SP20	2CCF019613R0001	0.74	1
	25	471538	S803PV-SP25	2CCF019614R0001	0.74	1
	32	471552	S803PV-SP32	2CCF019615R0001	0.74	1
	40	471576	S803PV-SP40	2CCF019616R0001	0.74	1
	50	471590	S803PV-SP50	2CCF019617R0001	0.74	1
	63	471613	S803PV-SP63	2CCF019618R0001	0.74	1
	80	471637	S803PV-SP80	2CCF019619R0001	0.74	1
	100	471651	S803PV-SP100	2CCF019620R0001	0.74	1
	125	520717	S803PV-SP125	2CCG001602R0001	0.765	1
4	5	452124	S804PV-SP5	2CCF019586R0001	0.98	1
	6	472191	S804PV-SP6	2CCF019647R0001	0.98	1
	8	472214	S804PV-SP8	2CCF019648R0001	0.98	1
	10	471699	S804PV-SP10	2CCF019622R0001	0.98	1
	13	471712	S804PV-SP13	2CCF019623R0001	0.98	1
	16	471736	S804PV-SP16	2CCF019624R0001	0.98	1
	20	471750	S804PV-SP20	2CCF019625R0001	0.98	1
	25	471774	S804PV-SP25	2CCF019626R0001	0.98	1
	32	471798	S804PV-SP32	2CCF019627R0001	0.98	1
	40	471811	S804PV-SP40	2CCF019628R0001	0.98	1
	50	471835	S804PV-SP50	2CCF019629R0001	0.98	1
	63	471859	S804PV-SP63	2CCF019630R0001	0.98	1
	80	471873	S804PV-SP80	2CCF019631R0001	0.98	1
	100	471897	S804PV-SP100	2CCF019632R0001	0.98	1
	125	520724	S804PV-SP125	2CCG001603R0001	1.005	1

Switch Disconnectors

S802PV-M-H and S800PV-SD technical features

		S802PV-M-H	S800PV-SD
General Data			
Tripping characteristics		none	none
Standards		IEC / EN 60947-3	IEC / EN 60947-3 and Annex D
Number of poles		2 (polarized)	2 ... 4
Rated current I_n	A	32, 63, 100	32, 63, 125
Rated insulation voltage U_i acc. to IEC/EN 60664-1	V	DC 1500	DC 1500
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	kV	8	8
Dielectric test voltage at ind. freq. for 1 min.	kV	3	3
Overvoltage category		III*	III*
Pollution degree		2	2
Suitability for isolation		yes	yes
Grid distance	mm	50	50
Data acc. to IEC/EN 60947-3			
Rated operational voltage U_e	V	DC 1000V: 2-pole	DC 800V: 2-pole DC 1200V: 3-Pole DC 1500V: 4-pole
Min. operating voltage	V	-	-
Rated short-term withstand current I_{cw}	kA	1.5	1.5
Rated short-circuit making capacity I_{cm}	kA	0.5	0.5
Utilisation category		DC-21 A	DC-21 A, DC-PV2
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	1500 electrical / 10000 mechanical	32, 63 A: 1500 electrical / 10000 mechanical 125 A: 1000 electrical / 8000 mechanical
Mechanical Data			
Housing type		Material group I, RAL 7035	Material group I, RAL 7035
Toggle type		black, lockable	black, lockable
Plastic classification acc. to UL94		V0	
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)	IP20; IP40 (actuating end only)
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea	5g / 30ms, Test Ea
Shock resistance acc. To IEC/EN 61373		5g / 30ms, Cat 1 / Class B	5g / 30ms, Cat 1 / Class B
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I_n , Test Fc	5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I_n , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1		16 hours -40°C	16 hours -40°C
Ambient temperature (with daily average $\leq +35^\circ\text{C}$)	°C	-40...+70	-40...+70
Storage temperature	°C	-40 ... +70	-40 ... +70
Installation			
Terminal type		Failsafe cage or ringlug terminal	Failsafe cage or ringlug terminal
Connections (top/bottom) - C_u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
Tightening torque	Nm	3.5	3.5
	in-lbs.	31	31
Wire stripping length	mm	19	19
Screwdriver		POZI 2	POZI 2
Mounting type		Any	Any
Mounting position		Any	Any
Supply from		Top and bottom (taking into account the polarization)	Top and bottom
Dimensions and weight			
Pole dimensions (H x L x W)	mm	95 x 82.5 x 27	95 x 82.5 x 27
Pole weight	g	240	240

*The pollution degree of the product, as defined in standard IEC 60947-1, is related to its micro environment, to which equipment is exposed. It may be different from that of the macro-environment. According to where the equipment is located, the pollution degree of the macro environment can be considered up to category IV, if protection is offered by means of such as an adequate enclosure or internal heating to prevent absorption or condensation of moisture.

Switch Disconnectors

S802PV-M-H and S800PV-SD technical features


		S800PV-SP	S800PV-SD	S800PV-M-H
Combination with aux. elements	S800-AUX	yes	yes	yes
	S800-AUX/ALT	yes	no	no
	S800-RSU-H	yes	yes	yes
	S800W-RSU	yes	yes	yes
	S800-SOR	yes	yes	yes
	S800-UVR	yes	yes	yes

Switch Disconnectors

S800PV-M-H and S80PV-SD series



S802PV



S802PV-M-H

Function: this polarized disconnector is designed to meet the requirements for photovoltaic systems. Voltage up to 1000 V d.c. and rated current up to 100 A.

Applications: Photovoltaic systems

Rated short-term withstand current, I_{cw} 1,5 kA

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
2	32	419035	S802PV-M32-H	2CCP247204R0001	0.43	1
	63	419042	S802PV-M63-H	2CCP247205R0001	0.43	1
	100	419301	S802PV-M100-H	2CCP247212R0001	0.43	1

S800PV-SD

Function: Non polarized switch disconnector for DC side isolation of PV systems.

Designed for PV installations of 1500 V DC.

Applications: Photovoltaic systems

Rated short-term withstand current, I_{cw} 1,5 kA

Number of poles	Rated current [A]	GTIN EAN 76122714	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
2	32	71958	S802PV-SD32	2CCF019635R0001	0.43	1
	63	71934	S802PV-SD63	2CCF019634R0001	0.43	1
	125	71972	S802PV-SD125	2CCF019636R0001	0.43	1
3	32	71996	S803PV-SD32	2CCF019637R0001	0.65	1
	63	72016	S803PV-SD63	2CCF019638R0001	0.65	1
	125	72030	S803PV-SD125	2CCF019639R0001	0.65	1
4	32	72054	S804PV-SD32	2CCF019640R0001	0.86	1
	63	72078	S804PV-SD63	2CCF019641R0001	0.86	1
	125	72092	S804PV-SD125	2CCF019642R0001	0.86	1



S802PV



S803PV



S804PV

MCBs

S800HV series technical features

S800HV		
General Data		
Tripping characteristics		C, K
Standards		IEC/EN 60947-2, UL 1077 (only 3P, 10...32 A)
Number of poles		1 ... 3
Rated current I_n	A	0.5 ... 125
Rated frequency f	Hz	50/60
Rated Insulation Voltage U_i acc. to IEC/EN 60664-1	V	AC 1000
Rated Impulse Withstand Voltage U_{imp} , (1.2/50 μ s)	kV	8
Dielectric test voltage at ind. freq. for 1 min.	kV	2.4
Overvoltage category		III
Pollution degree		2
Suitability for isolation		yes
Grid distance	mm	50
Data acc. to IEC/EN 60947-2		
Rated operational voltage U_e	V	AC 580/1000
Min. operating voltage	V	AC 12
Rated operational current I_n	A	0.5 ... 125
Rated ultimate short-circuit capacity I_{cu}	kA	1.5 (0.5...5 A) 4 (6 ... 63 A) 3 (80 ... 125 A)
Rated service short-circuit capacity I_{cs}	kA	1.5 (0.5 ... 5 A) 2.5 (6 ... 63 A) 2 (80 ... 125 A)
Reference temperature for tripping characteristics	°C	40 °C
Electrical and Mechanical Endurance	cycle (OFF-ON-OFF)	0.5 ... 100 A: 1500 electrical/10000 mechanical 125 A: 1000 electrical/8000 mechanical
Data according to UL 1077/ C22.2 No 235, Supplementary Protector		
Interrupting rating		600 Y/347: 15 kA (3P, 10...32A)*
Mechanical Data		
Housing type		Material group I, RAL 7035
Toggle type		black, lockable
Plastic classification acc. to UL94		V0
Protection degree acc. to EN 60529		IP20; IP40 (actuating end only)
Classification acc. To NF F 126-101, NF F 16-102		I3, F2
Shock resistance acc. to IEC/EN 61373		5g / 30ms, Cat 1 / Class B
Resistance to shock acc. to IEC/EN 60068-2-27		5g / 30ms, Test Ea
Resistance to Vibrations acc. to IEC 60068-2-6		5 - 13.2Hz / 1 mm 13.2 - 100Hz / 0.7g with load 80% x I_e , Test Fc
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	°C/RH	2 cycles: 12h 55°C @98% rh; 12h 25°C @93% rh
Environmental condition (dry heat) acc. to IEC/EN 60068-2-2	°C/RH	16 hours 70°C
Environmental condition (low temp) acc. to IEC/EN 60068-2-1	°C/RH	16 hours -40°C
Ambient temperature (with daily average $\leq +35^\circ\text{C}$)	°C	-40...+70
Storage temperature	°C	-40...+70
Installation		
Terminal type		Failsafe cage terminal
Connections (top/bottom) – C_u only	mm ²	1 ... 50 flexible 1 ... 70 solid (rigid or stranded)
Tightening torque	Nm	3.5
Wire stripping length	mm	19
Screwdriver		POZI 2
Mounting type		EN 60715
Mounting position		Any
Supply from		Top and bottom
Dimensions and weight		
Pole dimensions (H x L x W)	mm	142 x 82.5 x 27**
Pole weight	kg	0.27

* 3P, 10 ... 32 A - only valid with XT2L 125 TMF 35-400

** On multi-pole versions, rated current 125A is equipped with a lateral cover of 4.5mm on each product side. Overall product width increases of 9mm

	S800-AUX	S800-AUX/ALT	S800-RSU-H	S800W-RSU	S800S-SCL-SR	S800W-SCL-SR	S800HV-SCL-SR	S800-SOR	S800-UVR	DDA800
Combination with aux. Elements	yes	yes	yes	yes	no	no	yes	yes	yes	no

High performance MCBs

S800HV series for application up to 1000V AC

S800HV-K characteristics

Function: protection and control of the circuits against overloads and short-circuits. With increased voltage level 580/1000 VAC, it is ideal for installation in AC side of high-power conversion systems (PCS) in photovoltaic and wind turbine installations.

Applications: Industrial, high-power conversion systems

Standard: IEC/EN 60947-2, UL 1077, supplementary protector (only 3P)

Icu 1.5 kA (0.5...5 A) 4 kA (6 ... 63 A); 3 kA (80 ... 125 A)



S801HV



S802HV

Number of poles	Rated current [A]	GTIN EAN 7612271	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
1	0.5	501150	S801HV-K0,5	2CCF020049R0001	0.27	1
	1	501167	S801HV-K1	2CCF020050R0001	0.27	1
	1.6	502423	S801HV-K1,6	2CCF030021R0001	0.27	1
	2	502430	S801HV-K2	2CCF030022R0001	0.27	1
	2.5	502614	S801HV-K2,5	2CCF030030R0001	0.27	1
	3	502447	S801HV-K3	2CCF030023R0001	0.27	1
	4	502454	S801HV-K4	2CCF030024R0001	0.27	1
	5	502621	S801HV-K5	2CCF030031R0001	0.27	1
	6	436445	S801HV-K6	2CCF019005R0001	0.27	1
	8	436964	S801HV-K8	2CCF019006R0001	0.27	1
	10	436452	S801HV-K10	2CCF019007R0001	0.27	1
	13	436469	S801HV-K13	2CCF019008R0001	0.27	1
	16	436476	S801HV-K16	2CCF019009R0001	0.27	1
	20	436483	S801HV-K20	2CCF019010R0001	0.27	1
	25	436490	S801HV-K25	2CCF019011R0001	0.27	1
	32	436605	S801HV-K32	2CCF019012R0001	0.27	1
	40	436612	S801HV-K40	2CCF019013R0001	0.27	1
	50	436629	S801HV-K50	2CCF019014R0001	0.27	1
	63	436636	S801HV-K63	2CCF019015R0001	0.27	1
	80	436643	S801HV-K80	2CCF019016R0001	0.27	1
	100	436650	S801HV-K100	2CCF019017R0001	0.27	1
	125	436667	S801HV-K125	2CCF019018R0001	0.27	1
2	0.5	502461	S802HV-K0,5	2CCF030025R0001	0.54	1
	1	502478	S802HV-K1	2CCF030026R0001	0.54	1
	1.6	502638	S802HV-K1,6	2CCF030032R0001	0.54	1
	2	502485	S802HV-K2	2CCF030027R0001	0.54	1
	2.5	502492	S802HV-K2,5	2CCF030028R0001	0.54	1
	3	502645	S802HV-K3	2CCF030033R0001	0.54	1
	4	501297	S802HV-K4	2CCF020063R0001	0.54	1
	5	501303	S802HV-K5	2CCF020064R0001	0.54	1
	6	436674	S802HV-K6	2CCF019019R0001	0.54	1
	8	436681	S802HV-K8	2CCF019020R0001	0.54	1
	10	436698	S802HV-K10	2CCF019021R0001	0.54	1
	13	436704	S802HV-K13	2CCF019022R0001	0.54	1
	16	436711	S802HV-K16	2CCF019023R0001	0.54	1
	20	436728	S802HV-K20	2CCF019024R0001	0.54	1
	25	436742	S802HV-K25	2CCF019025R0001	0.54	1
	32	436759	S802HV-K32	2CCF019026R0001	0.54	1
	40	436766	S802HV-K40	2CCF019027R0001	0.54	1
	50	436773	S802HV-K50	2CCF019028R0001	0.54	1
	63	436780	S802HV-K63	2CCF019029R0001	0.54	1
	80	436797	S802HV-K80	2CCF019030R0001	0.54	1
	100	436803	S802HV-K100	2CCF019031R0001	0.54	1
	125	436810	S802HV-K125	2CCF019032R0001	0.54	1

High performance MCBs

S800HV series for application up to 1000V AC



S803HV

Number of poles	Rated current [A]	GTIN EAN 76122714	Order details		Weight [kg]	Pack. unit
			Type Code	Order code		
3	0.5	501310	S803HV-K0,5	2CCF020065R0001	0.81	1
	1	501327	S803HV-K1	2CCF020066R0001	0.81	1
	1.6	501334	S803HV-K1,6	2CCF020067R0001	0.81	1
	2	501341	S803HV-K2	2CCF020068R0001	0.81	1
	2.5	501358	S803HV-K2,5	2CCF020069R0001	0.81	1
	3	501365	S803HV-K3	2CCF020070R0001	0.81	1
	4	501372	S803HV-K4	2CCF020071R0001	0.81	1
	5	501389	S803HV-K5	2CCF020072R0001	0.81	1
	6	36827	S803HV-K6	2CCF019033R0001	0.81	1
	8	36834	S803HV-K8	2CCF019034R0001	0.81	1
	10	36841	S803HV-K10	2CCF019035R0001	0.81	1
	13	36858	S803HV-K13	2CCF019036R0001	0.81	1
	16	36865	S803HV-K16	2CCF019037R0001	0.81	1
	20	36872	S803HV-K20	2CCF019038R0001	0.81	1
	25	36889	S803HV-K25	2CCF019039R0001	0.81	1
	32	36896	S803HV-K32	2CCF019040R0001	0.81	1
	40	36902	S803HV-K40	2CCF019041R0001	0.81	1
	50	36919	S803HV-K50	2CCF019042R0001	0.81	1
	63	36926	S803HV-K63	2CCF019043R0001	0.81	1
	80	36933	S803HV-K80	2CCF019044R0001	0.81	1
	100	36940	S803HV-K100	2CCF019045R0001	0.81	1
	125	36957	S803HV-K125	2CCF019046R0001	0.81	1

S800HV-C characteristics

Function: protection and control of the circuits against overloads and short-circuits. With increased voltage level 580/1000 VAC, it is ideal for installation in AC side of high-power conversion systems (PCS) in photovoltaic and wind turbine installations.

Applications: Industrial, high-power conversion systems

Standard: IEC/EN 60947-2

Icu = 4 kA



S803HV

Number of poles	Rated current [A]	Bbn 7612271 EAN	Order details		Price 1 piece	Weight 1 piece kg	Pack unit pc.
			Type code	Order code			
3	10	72221	S803HV-C10	2CCF019650R0001		0.81	1
3	32	72245	S803HV-C32	2CCF019651R0001		0.81	1