

PrimEvo RS100 & SM100

Productivity & reliability




RS100



SM100

PrimEvo RS100 & SM100

- Available at your local wholesaler
- Plug and play, maintained and non-maintained in one
- Full LED range with best price/performance ratio
- Manual and Self-test




Luminaire

Order Code	Description	Input voltage	Lamp type	Power consumption** (VA/W)	Operation duration (hrs)	Environment temperature (°C)	Weight (kg)
RS100E	PrimEvo Recessed downlite	220 - 240 Vac, 50/60Hz	2 x LED 1.5W*	10/4.8	3	0 - 25	0.425
RS100ST	PrimEvo Recessed downlite self-test	220 - 240 Vac, 50/60Hz		10/4.8	3	0 - 25	0.425
SM100E	PrimEvo Surface downlite	220 - 240 Vac, 50/60Hz		9/4.5	3	0 - 25	0.425
SM100ST	PrimEvo Surface downlite self-test	220 - 240 Vac, 50/60Hz		9/4.5	3	0 - 25	0.425

* = 3W LED



PrimEvo RS100



PrimEvo SM100

