



On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 22 tap positions, linear switching.  
 Max. effective No. of turns in pos. 1.  
 The tap-changer is delivered set in pos. 11,  
 the preceding pos. was 10.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UC DL./III, 22 lägen, linjär koppling.  
 Max. antal effektiva varv i läge 1.  
 Lindningskopplaren levereras inställd i läge 11,  
 föregående läge var 10.



Pos. Läge	Tap selector and diverter switch connect	Väljaren och lastkopplaren förbinder
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	
18	18-H-v	
19	19-V-x	
20	20-H-v	
21	21-V-x	
22	22-H-v	

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19

The tap-changer is shown in pos. 11,  
 the preceding pos. was 10.  
 The tap selector is seen from above.  
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 11,  
 föregående läge var 10.  
 Väljaren sedd uppifrån.  
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
 tap-changer. Dashed lines show leads belonging  
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
 lindningskopplaren. Streckade linjer visar  
 ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Year	Week	Cont	
	Year	Week	Cont		
	Dept				
	Rev Ind	Revision	Appd	Year	Week
	Accepted by qual control	Accepted for prod by	Description (English) CONNECTION DIAGRAM		DATA ORIGINAL
	Design checked by G.Andersson GA	Drawn by T.Larsen	Description (own language) KOPPLINGSSCHEMA		File name 0367-18
	Drawing checked by A.Hultberg M	Issued by Dept Year Week COM/FOK 07 49			Lang 1
	ABB Asea Brown Boveri		5492 0367-18		Rev Ind Cont