



PRODUCT BULLETIN

# ABB Residential Breakers carry a multi-wire rating on standard lugs



Q-line circuit breaker multi-wire is UL approved. The multiple wire rating applies to the standard lug 286A8634P2. This is available for field use.

This rating applies to the following families of 1-, 2- and 3-pole ABB breakers with ampere rating 15 A to 30 A: THQL, THHQL, THQB, THHQB, THQP, AFCI, DFCI and GFCI.

The wire ratings that can be used are as follows:

- (2) 14–10 AWG stranded Cu
- (2) 14–10 AWG solid Cu

—  
**Applicable circuit breakers**

THQL/ THHQL	THQB/ THHQB	THQP	AFCI	DFCI	GFCI	GFCI (equip)
THQL1115	THQB1115	THQP115	THQL1115AF2	THQL1115DF	THQL1115GFT	THQL1115GFEP
THQL1120	THQB1120	THQP120	THQL1120AF2	THQL1120DF	THQL1120GFT	THQL1120GFEP
THQL1125	THQB1125	THQP125	THQL1115AF2S	THQL1115DFS	THQL1125GFT	THQL1130GFEP
THQL1130	THQB1130	THQP130	THQL1120AF2S	THQL1120DFS	THQL1130GFT	THQL2115GFEP
THQL2115	THQB2115	THQP215	THHQL1115AF2	THHQL1115DF	THQL1115GFTS	THQL2120GFEP
THQL2120	THQB2120	THQP220	THHQL1120AF2	THHQL1120DF	THQL1120GFTS	THQL2130GFEP
THQL2125	THQB2125	THQP225	THQB1115AF2	THQL1115PDF	THQL2115GFT	THHQL2115GFEP
THQL2130	THQB2130	THQP230	THQB1120AF2	THQL1120PDF	THQL2120GFT	THHQL2120GFEP
THQL22015	THQB22015	—	THHQB1115AF2	THHQL1115PDF	THQL2125GFT	THQB1115GFEP
THQL22020	THQB22020	—	THHQB1120AF2	THHQL1120PDF	THQL2130GFT	THQB1120GFEP
THQL22025	THQB22025	—	THQL1120PAF2	—	THHQL1115GFT	THQB1130GFEP
THQL22030	THQB22030	—	THHQL1115PAF2	—	THHQL1120GFT	THQB2115GFEP
THQL32015	THQB32015	—	THHQL1120PAF2	—	THHQL1125GFT	THQB2120GFEP
THQL32020	THQB32020	—	—	—	THHQL1130GFT	THQB2130GFEP
THQL32025	THQB32025	—	—	—	THHQL2115GFT	THHQB2115GFEP
THQL32030	THQB32030	—	—	—	THHQL2120GFT	THHQB2120GFEP

—  
**Applicable circuit breakers**

THQL/ THHQL	THQB/ THHQB	THQP	AFCI	DFCI	GFCI	GFCI (equip)
THHQL1115	THHQB1115	-	-	-	THQL1115PGFT	THHQB2130GFEP
THHQL1120	THHQB1120	-	-	-	THQL1120PGFT	-
THHQL1125	THHQB1125	-	-	-	THQL1125PGFT	-
THHQL1130	THHQB1130	-	-	-	THQL1130PGFT	-
THHQL2115	THHQB2115	-	-	-	THHQL1115PGFT	-
THHQL2120	THHQB2120	-	-	-	THHQL1120PGFT	-
THHQL2125	THHQB2125	-	-	-	THHQL1125PGFT	-
THHQL2130	THHQB2130	-	-	-	THHQL1130PGFT	-
THHQL22015	THHQB22015	-	-	-	THQL2115PGFT	-
THHQL22020	THHQB22020	-	-	-	THQL2120PGFT	-
THHQL22025	THHQB22025	-	-	-	THQL2125PGFT	-
THHQL22030	THHQB22030	-	-	-	THQL2130PGFT	-
THHQL32015	THHQB32015	-	-	-	THHQL2115PGFT	-
THHQL32020	THHQB32020	-	-	-	THHQL2120PGFT	-
THHQL32025	THHQB32025	-	-	-	THHQL2125PGFT	-
THHQL32030	THHQB32030	-	-	-	THHQL2130PGFT	-
-	-	-	-	-	THHQL2125GFT	-
-	-	-	-	-	THHQL2130GFT	-
-	-	-	-	-	THQB1115GFT	-
-	-	-	-	-	THQB1120GFT	-
-	-	-	-	-	THQB1125GFT	-
-	-	-	-	-	THQB1130GFT	-
-	-	-	-	-	THQB2115GFT	-
-	-	-	-	-	THQB2120GFT	-
-	-	-	-	-	THQB2125GFT	-
-	-	-	-	-	THQB2130GFT	-
-	-	-	-	-	THHQB1115GFT	-
-	-	-	-	-	THHQB1120GFT	-
-	-	-	-	-	THHQB1125GFT	-
-	-	-	-	-	THHQB1130GFT	-
-	-	-	-	-	THHQB2115GFT	-
-	-	-	-	-	THHQB2120GFT	-
-	-	-	-	-	THHQB2125GFT	-
-	-	-	-	-	THHQB2130GFT	-

\*All variations of these breakers are also compatible — shunt trip (ST), low and high magnetic (LM and HM), high intensity discharge (HID) and switching neutral (WY)

—  
**ABB Inc.**  
 305 Gregson Drive  
 Cary, NC 27511  
 United States

**electrification.us.abb.com**

—  
 We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

—  
 We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2023 ABB All rights reserved.

—  
 GE is a trademark of GE. Manufactured by ABB Inc. under license from General Electric Company.