


Temp.
0 25 40 50 60C



Shift index for long-time delay only.

MULTIPLES OF CIRCUIT BREAKER CURRENT RATING



Molded Case Circuit Breaker E 100 LINE

Current Ratings
90 and 100 Amperes

Voltage Ratings
2 and 3 pole – 480 Vac (250 Vdc)

Frequency Rating
60 Hertz

Type TED, 90 and 100 Amperes Enclosure Compensated Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

K215148

Adjustments
Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.

NOTE: Limiters can only be applied to AC breakers.