


5SMY 12M1730

IGBT-Die

$V_{CE} = 1700\text{ V}$

$I_C = 150\text{ A}$

Ultra low loss thin IGBT die
 Highly rugged SPT++ design
 Large bondable emitter area
 Passivation: Silicon Nitride plus Polyimide



Maximum rated values ¹⁾

Parameter	Symbol	Conditions	min	max	Unit
Collector-emitter voltage	V_{CES}	$V_{GE} = 0\text{ V}, T_{vj} \geq 25\text{ °C}$		1700	V
DC collector current	I_C			150	A
Peak collector current	I_{CM}			300	A
Gate-emitter voltage	V_{GES}		- 20	20	V
IGBT short circuit SOA	t_{psc}	$V_{CC} = 1300\text{ V}, V_{CEM\text{ CHIP}} \leq 1700\text{ V}$ $V_{GE} \leq 15\text{ V}, T_{vj} \leq 175\text{ °C}$		10	μs
Junction temperature	$T_{vj(op)}$		-40	175	$^{\circ}\text{C}$

¹⁾ Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747

IGBT characteristic values ²⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector (-emitter) breakdown voltage ³⁾	$V_{(BR)CES}$	$V_{GE} = 0 \text{ V}$, $I_C = 1 \text{ mA}$, $T_{vj} = 25 \text{ }^\circ\text{C}$	1700			V
Collector-emitter saturation voltage	$V_{CE \text{ sat}}$	$I_C = 150 \text{ A}$, $V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	2.25	2.6	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2.55		V
			$T_{vj} = 175 \text{ }^\circ\text{C}$	2.75		V
Collector cut-off current	I_{CES}	$V_{CE} = 1700 \text{ V}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$		0.1	mA
			$T_{vj} = 125 \text{ }^\circ\text{C}$	0.2		mA
			$T_{vj} = 175 \text{ }^\circ\text{C}$	6		mA
Gate leakage current	I_{GES}	$V_{CE} = 0 \text{ V}$, $V_{GE} = \pm 20 \text{ V}$, $T_{vj} = 125 \text{ }^\circ\text{C}$	- 500		500	nA
Gate-emitter threshold voltage	$V_{GE(TO)}$	$I_C = 6 \text{ mA}$, $V_{CE} = V_{GE}$, $T_{vj} = 25 \text{ }^\circ\text{C}$	4.5		6.5	V
Gate charge	Q_{GE}	$I_C = 150 \text{ A}$, $V_{CE} = 900 \text{ V}$, $V_{GE} = 15 \text{ V} \dots 15 \text{ V}$		1.05		μC
Input capacitance	C_{ies}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$, $T_{vj} = 25 \text{ }^\circ\text{C}$		9.15		nF
Output capacitance	C_{oes}			0.52		nF
Reverse transfer capacitance	C_{res}			0.36		nF
Internal gate resistance	R_{Gint}			4.7		Ω
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $R_G = 8.2 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $L_\sigma = 200 \text{ nH}$, inductive load Aux: 5SLZ 12J1700	$T_{vj} = 25 \text{ }^\circ\text{C}$	290		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	315		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}$	330		ns
Rise time	t_r	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $R_G = 8.2 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $L_\sigma = 200 \text{ nH}$, inductive load Aux: 5SLZ 12J1700	$T_{vj} = 25 \text{ }^\circ\text{C}$	130		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	130		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}$	130		ns
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $R_G = 8.2 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $L_\sigma = 200 \text{ nH}$, inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	480		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	580		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}$	640		ns
Fall time	t_f	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $R_G = 8.2 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $L_\sigma = 200 \text{ nH}$, inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	115		ns
			$T_{vj} = 125 \text{ }^\circ\text{C}$	130		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}$	145		ns
Turn-on switching energy	E_{on}	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $V_{GE} = \pm 15 \text{ V}$, $R_G = 8.2 \text{ } \Omega$, $L_\sigma = 200 \text{ nH}$, inductive load Aux: 5SLZ 12J1700	$T_{vj} = 25 \text{ }^\circ\text{C}$	55		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	70		mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}$	80		mJ
Turn-off switching energy	E_{off}	$V_{CC} = 900 \text{ V}$, $I_C = 150 \text{ A}$, $V_{GE} = \pm 15 \text{ V}$, $R_G = 8.2 \text{ } \Omega$, $L_\sigma = 200 \text{ nH}$, inductive load	$T_{vj} = 25 \text{ }^\circ\text{C}$	29		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	42		mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}$	51		mJ
Short circuit current	I_{SC}	$t_{psc} \leq 10 \text{ } \mu\text{s}$, $V_{GE} = 15 \text{ V}$, $T_{vj} = 125 \text{ }^\circ\text{C}$, $V_{CC} = 1300 \text{ V}$, $V_{CEM \text{ CHIP}} \leq 1700 \text{ V}$	$T_{vj} = 125 \text{ }^\circ\text{C}$	470		A

²⁾ Characteristic values according to IEC 60747 - 9

³⁾ Please refer to Application Note 5SYA 2059: Applying IGBT and diode dies




Fig. 1 Typical on-state characteristics




Fig. 2 Typical transfer characteristics




Fig. 3 Typical capacitances vs collector-emitter voltage




Fig. 4 Typical gate charge characteristics




Fig. 5 Turn-off safe operating area (RBSOA)

Mechanical properties ³⁾


Parameter	Symbol	Conditions	min	Unit
Dimensions	Overall die	L x W	13.55 x 13.55	mm
	exposed front metal	L x W (except gate pad)	11.52 x 11.53	mm
	gate pad	L x W	1.73 x 1.76	mm
	thickness		190 ± 15	µm
Metallization ³⁾	front (E)	AlSi1	4	µm
	back (C)	Al / Ti / Ni / Ag	1.6	µm

³⁾ Please refer to Application Note 5SYA 2059: Applying IGBT and diode dies

Form of delivery

Description	Part number
Unsawn 6" wafer die (on blue tape)	5SMY 76M1730
Sawn 6" wafer die (on blue tape)	5SMY 86M1730

Outline drawing



Note: all dimensions are shown in millimeters

This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. VIII
This product has been designed and qualified for Industrial Level.

Related documents:

5SYA 2045 Thermal runaway during blocking
5SYA 2059 Applying IGBT & Diode Dies
5SZK 9114 Handling, packing and storage conditions for sawn wafer dies and bare die

ABB Switzerland Ltd.
Semiconductors
Fabrikstrasse 3
CH-5600 Lenzburg
Switzerland

Phone: +41 58 586 1419
Fax: +41 58 586 1306
E-Mail: abbsem@ch.abb.com

www.abb.com/semiconductors

We reserve the right to make technical changes or to modify the contents of this document without prior notice.

We reserve all rights in this document and the information contained therein. Any reproduction or utilisation of this document or parts thereof for commercial purposes without our prior written consent is forbidden.

Any liability for use of our products contrary to the instructions in this document is excluded.