Power supply CP-S.1 24/3.0

Mid-high performance switch mode power supply

CP-S.1 power supplies: high efficiency and reliability delivered in a compact footprint.

Designed for a huge variety of applications, including machine building segments, this advanced range boosts an integrated 150 % power reserve for five seconds and operates at an efficiency of up to 94 %. With overheat protection, active power factor correction, a broad certified AC and DC input range and extensive worldwide approvals including ma-rine, the all-new CP-S.1 power supplies are a preferred choice for multiple industrial applications.



2CDC271001V0021

Characteristics

- Rated supply voltage range from 100-240 V AC / 100-250 V DC
- Rated output voltage 24 V DC
- Rated output current of 3.0 A
- Rated output power 72 W
- High efficiency of 90 %
- Power reserve design of 150 % for 5 s
- Output voltage adjustable via front-face rotary potentiometer "OUTPUT Adjust", 24-28 V

- · Low power dissipation and low heating
- Free convection cooling (no forced cooling)
- Coated PCBAs
- Open-circuit, overload and short-circuit protection
- Integrated input fuse
- DC OK signaling output "13-14" (relay)
- CP-C.1-A-RU redundancy unit offers true redundancy, available as accessory
- · Various approvals and marks

Ordering details

Description	Rated input voltage	Rated output voltage	Rated output current	Output power	Order code
CP-S.1 24/3.0	100 - 240 V AC, 100 - 250 V DC	24 V DC	3.0 A	72 W	1SVR320361R1000
CP-C.1-A-RU	10 - 56 V DC	12 - 48 V DC	2 x 20 A or 1 x 40 A	-	1SVR360060R1001



Application

The new family of CP-S.1 power supplies is the right fit for OEM machine building applications. Space-saving design, a complete 24 V DC offering of up to 960 W and a metal enclosure perfectly matches the high requirements of this segment.

The CP-S.1 has a wide certified AC or DC input voltage range. Furthermore, the CP-S.1 is equipped with capacitors that ensure a hold-up time of at least 20 ms. This enables world-wide usage and permits safe operation in fluctuating networks and battery-powered applications.

The CP-S.1 power supplies with the robust metallic housing and the reliable construction are suitable for applications in industrial environments.

The power reserve of up to 150 % for five seconds enables trouble-free starting of heavy loads eliminating the need of usage of an oversized power supply.

Power reserve

The primary switch mode power supply CP-S.1 is equipped with a power reserve functionality to handle the start-up of particularly heavy loads (e.g. of a capacitive load or a motor). To ensure that heavy loads are started up, the CP-S.1 delivers additionally up to 150 % of the rated output current for up to 5 s to secure the operation of the application.

Signaling output

For the communication of the status of the power supply the CP-S.1 is equipped with a relay output to signal 'OUTPUT OK'. This signal can be used for communication to a higher level control system e.g. a PLC.

Adjustable output voltage

The CP-S.1 range power supplies feature a continuously adjustable output voltage of 24 to 28 V DC. Thus, they can be optimally adapted to the application, e.g. compensating the voltage drop caused by a long line length.

Adjustable output voltage



Output OK, relay output

Rated voltage limits of the signaling output relay: Acc. UL 61010-1: 30 V RMS, 42.4 V peak, 60 V DC

LEDs and signaling output

Output voltage	Output OK: LED green	Rated output voltage
\ge 92 % of U _{out}		Closed
< 90 % of U _{out}		Open

It is possible to use the messaging and signaling functionality with power supplies connected in parallel. The parallel operation has no influence on the function.

Operating mode

Parallel operation

There are two main reasons for a parallel connection of power supplies:

- · Increase of power
- Redundancy

Up to 3 devices of the same type can be connected in parallel. For safe and reliable operation it is important to follow the recommendations given in the following section.

Parallel connection of power supplies for increased power

If the current required by the load is higher than a single power supply can deliver, for example after the expansion of an existing installation, an increase of the output power can be obtained by connecting power supplies in parallel. The following prerequisites have to be fulfilled when connecting power supplies in parallel for the purpose of increased power:

- The paralleled devices must be of the identical type.
- Repeated voltage drops on the supply lines or at the terminals would lead to unbalanced load at the common connection point. To prevent this, you have to observe the following when connecting the power supply units:
 - Identical lengths of the load supply lines.
 - Identical conductor cross sections of the load supply lines.
 - Terminal screws have to be fastened with the same torque to guarantee equal contact resistances.
 - The output voltages of the power supplies must not differ by more than 50 mV. Otherwise, safe operation is not possible.





Correct wiring for increased power



Incorrect wiring for increased power



Important

The devices must not be connected directly to each other! This could lead to an overload of the terminals since the terminals are dimensioned for the maximum output current of a single power supply only. Always use a common connection point!

Parallel connection of power supplies for redundancy

Several power supplies are connected in parallel in order to guarantee continuous operation of the system if one power supply fails. CP-S.1 can be used in two different redundancy modes depending on what type of redundancy is required:

- Simple redundancy
- True redundancy

Simple redundancy

For simple redundancy, the power supplies are connected in parallel like for the increase of capacity. To achieve redundancy the current required by the load must not exceed the maximum output power of one single power supply (in case of "1+1 redundancy") or n power supplies (where n is max. 3).

We recommend connecting the primary sides of the power supplies to different phases of the mains in order to obtain continuous operation of the system if one phase fails.



Parallel operation, redundancy (n \leq 3)

True redundancy

True redundancy gives higher system availability compared to simple redundancy. In a true redundancy setup the power supplies are decoupled from each other with decoupling diodes. This protects the individual power supplies from affecting each other in case of failure of one unit or short cirucit on the secondary side or in the wiring.

For two inputs of up to 30 A and one output up to 60 A the ABB redundancy unit CP-C.1-A-RU (available as an accessory) can be used.

The inputs of these units are connected to the terminals L+ and L- of the power supplies. The loads are supplied directly from the outputs of the redundancy unit.



True redundancy using a CP-C.1-A-RU redundancy unit

Mounting

To mount the unit place the upper edge of the DIN rail adapter on the upper edge of the DIN rail holding the unit slightly tilted upwards as shown in the illustration. Then tilt the unit down until the latch snaps onto the DIN rail.



Mounting positions



In order to ensure a sufficient convection in mounting position 1, the minimum distance to other modules must not be less than 50 mm in vertical direction and 30 mm in horizontal direction. For the derating of the output current, see the characteristic curve of temperature. Details for other mounting positions on request.

Demounting

To release the unit pull the latching lever downwards with a screwdriver and press the upper side of the the latching lever down. The device can be unhinged from the DIN rail and removed.



Electrical connection

Connect the input terminals "L" to line and "N" to neutral conductor or to "+" and "-" with DC supply "+" to "L" and "-" to "N". The protective earth conductor PE must be connected before putting the device into operation. The installation must be executed acc. to EN 61010-1. Provide a suitable disconnecting device (e. g. line protection switch, MCB or fuse) in the supply line. The input side of the power supply is protected by an internal input fuse.

The wiring, cable choice and their protection shall comply to the local electrical standard. We recommend choosing the conductor cross-section as large as possible in order to minimize voltage drops. Check the polarity. The device is overload, short-circuit and open-circuit proof. The secondary side of the power supply is electrically isolated from the input and internally not earthed (SELV) and can be earthed for PELV.



Connection diagram

24 and 48 V DC connection

The connection diagram below shows how to setup two power supplies for +/-24 or 48 V DC output voltage.



Connection diagram for +/-24 or 48 V DC output voltage

Safety instructions and warnings



In operation pay attention to:

- Do not modify the installation (primary and secondary side)! High current!
- Risk of electric arcs and electric shock (danger to life)!
- Risk of burns: Depending on the operation conditions the housing can become hot.
- The device contains no user serviceable parts. In any case of device malfunction please send the unit back to manufacturer.

The device must be installed by qualified persons only and in accordance with the specific national regulations (e.g. VDE, etc.).



The CP-S.1 power supplies are chassis-mounted units. It is maintenance-free and does not contain any integral setting elements and should therefore not be opened.



Before any installation, maintenance or modification work:

- Read the operating and installation instructions carefully and completely!
- Disconnect the system from the supply network and protect against switching on!



CAUTION

Improper installation/operation may impair safety of personnel and cause operational difficulties or destruction of the unit.



WARNING

Before start of operation the following must be ensured:

- Connection to mains or DC supply according to the specific national regulations for class of protection I. Power supply cables and unit must be sufficiently fused. A disconnecting device has to be provided for the end product to disengage unit and supply cables from supply mains if required.
- Rate the output lines for the output current of the power supply and connect them with the correct polarity.
- In order to ensure sufficient convection the distance to the other devices has to be considered.



WARNING Danger to life!

Never carry out work when voltage is present. The power supply contains components with high stored energy and circuits with high voltage! Do not introduce any objects into the unit and do not open the unit. With some units of this range the output is capable of providing hazardous energy. Ensure that the service personnel is protected against inadvertent contact with parts carrying energy. If the internal fuse is blown most probably the device is defect. In this case an examination of the device by the manufacturer is necessary.

Technical data

Туре			CP-S.1 24/3.0	
Input circuit - Supply circuit (L(+	·). N(-))			
Rated input voltage U _{in}	//···//		100 - 240 V AC, 100 - 250 V DC	
Input voltage range			85 - 264 V AC / 90 - 277 V DC	
Input current range at 100 - 240 V AC		100 - 240 V AC		
		100 - 250 V DC		
100 230 7 20		at 115 V AC		
		at 230 V AC		
Max. power consumption		at 230 V AC	82 W	
Rated frequency			DC, 50 / 60 Hz	
Frequency range		AC	45 - 65 Hz	
Inrush current limiting, cold state	9		≤ 11 A	
Let-through energy I ² t, cold state	5	at 230 V AC	< 1.5 A ² s	
Discharge current towards PE			< 3.5 mA	
Hold-up time		at 115 V AC	> 10 ms	
		at 230 V AC		
Internal input fuse			Yes	
Recommended backup fuse for			1 pole miniature circuit breaker ABB type S 200 (for USA/CAN: use appropriate	
wire protection at 1.5 mm ²			branch circuit 20 A fuse acc. to regional and national regulations)	
		characteristic	B or C	
		max. rating	16 A	
Power Factor Correction (PFC)			no	
Transient over-voltage protection	n		yes, varistor	
User interface - Indication of op	erational state	5		
Output voltage	LED ,OUTPUT	OK' Green	> 92 % adjusted U _{out}	
	LED ,OUTPUT	OK' Flash	< 90 % adjusted U _{out}	
Output circuits - power output (L+, L-)			
Rated output voltage			24 V DC	
Tolerance of the output voltage			±1%	
Adjustment range of the output v	voltage		2428 V DC	
Rated output power			72 W	
Rated output current I _R		$-25^{\circ}C \leq T_a \leq 60 \ ^{\circ}C$		
Dynamic Boost output current		$-25^{\circ}C \leq T_a \leq 60 \ ^{\circ}C$		
Short-circuit current limiting			< 5.2 A	
Derating of the output current		$60 \text{ °C} \leq T_a \leq 70 \text{ °C}$		
Deviation width	Load effect/ load	static load	< 1 %	
of output voltage	regulation	change: 25 - 100 %		
	Transient	dynamic load	0%-100%:<3%	
	response of	change:		
	voltage to	recovery	< 1 ms	
	load current changes	time T _R		
	Change of	within the rated	< 0.5%	
	input voltage	input voltage		
Starting time after applying the supply voltage			< 1,500 ms	
Residual ripple and switching per	aks	BW = 20 MHz	< 75 mV _{pp} , class A	
Parallel connection			yes, up to 3	
Series connection			yes, 2	
No-load, overload and short-circ	cuit behavior			
Characteristic curve of output			U/I characteristic curve	
Short-circuit protection			continuous short-circuit stability	
Short-circuit behavior			current limiting	
Resistance to reverse feed			\leq 35 V DC	
Overvoltage protection			yes, < 35 V	
Overload protection			constant current limitation	
Overtemperature protection			protection by switch off in case of overtemperature (thermal)	
No-load protection			continuous no-load stability	
Starting of capacitive loads			Yes	

POWER SUPPLY CP-S.1 24/3.0 MID-HIGH PERFORMANCE POWER SUPPLY

Type Signaling outputs - OUTPUT OK si	analing output	CP-S.1 24/3.0		
		velev a la sente et		
Type of output	13 - 14	relay, n/o contact		
ON (contact closed)		92 % adjusted U _{out}		
OFF (contact open)		90 % adjusted U _{out}		
Contact ratings max. switching voltage / current min. switching voltage / current		30 V AC - 0.5 A / 24 V DC - 1 A (resistive load)		
		5 V DC / 1 mA		
General data	current			
Efficiency	at rated load	> 89 %		
Power losses	at rated load	< 10 W		
	at 50 % of rated load			
	at no load	<2.8 W		
Duty time		100 %		
MTBF	acc. to MIL 217 HDBK GB 25	on request		
Dimensions (W x H x D)		see dimensional drawings		
Material of housing	cover	zinc-coated sheet-steel		
Haterial of Housing	housing shell			
	front			
Mounting		plastic, PC GE8B35, V0 DIN rail (IEC/EN 60715), snap-on mounting		
Mounting position		position 1 (standard orientation); other mounting positions possible with		
mounting position		derating / deratings are available on demand		
Minimum distance to other units	horizontal	30 mm		
	vertical	50 mm		
Degree of protection	housing / terminals	IP20 / IP20		
(IEC/EN 60529)				
Protection class (IEC/EN 61140)		1		
Electrical connection - Input circu	its (L(+), N(-), PE)			
Connecting capacity	rigid	0.5-2.5 mm² (20-14 AWG)		
	fine-strand with(out) wire end	0.5-2.5 mm² (20-14 AWG)		
	ferrule			
Stripping length		9 mm		
Tightening torque		0.5 Nm		
		4.43 lb.in		
Recommended screw driver		PH0 / Ø 3.5 x 0.6 mm		
Output circuits (L+, L+, L-, L-)				
Stripping length		9 mm		
Tightening torque		0.5 Nm		
Recommended screw driver		4.43 lb.in		
Signalling output (13-14)		PH0 / Ø 3.5 x 0.6 mm		
Connecting capacity	rigid	0.15 - 0.8 mm² (26 - 18 AWG)		
		0.15 - 0.8 mm ² (26 - 18 AWG)		
	trand with(out) wire end ferrule			
Stripping length Connection terminals		7 mm		
		push-in		
Environmental data	ו			
Ambient temperature range	operation	-25+70 °C (-13+158 °F)		
	rated output power	-25+60 °C (-13+140 °F)		
	storage	-40+85 °C (-40+185 °F)		
Climatic class (IEC/EN-COZO1-2-1)	transportation	-40+85 °C (-40 +185 °F)		
Climatic class (IEC/EN 60721-3-1)	storage	1K2		
Climatic class (IEC/EN 60721-3-2)	transportation	2K2		
Climatic class (IEC/EN 60721-3-3)	operation	3K3		
Damp heat, cyclic (IEC/EN 60068-2-30)		test Db: 55 °C, 2 cycles		
Vibration (IEC/EN 60068-2-6)		test Fc: 10-58 Hz, amplitude ±0.15 mm, 58-150 Hz, 2 g, 10 sweep cycles each axis		
Shock, half-sine (IEC/EN 60068-2-2 Location classes (according DNVGI		test Ea: 30 g, 6 ms, 3 pulses each axis; bump 20 g, 11 ms, 100 pulses each axis		
LOCATION CLASSES (according DNVG)	-)	temperature: B / humidity: B / vibration: A / enclosure: A		
		yes		
Coated PCBA				
Coated PCBA Isolation data Rated impulse withstand voltage	input circuit / output circuit	4 kV (1.2/50 μs)		
Coated PCBA Isolation data	· · ·			
Coated PCBA Isolation data Rated impulse withstand voltage	input circuit / PE	4 kV (1.2/50 μs)		
Coated PCBA Isolation data Rated impulse withstand voltage	input circuit / PE input circuit / relay contact	4 kV (1.2/50 μs) 4 kV (1.2/50 μs)		
Coated PCBA Isolation data Rated impulse withstand voltage	input circuit / PE	4 kV (1.2/50 μs)		

Туре		CP-S.1 24/3.0	
Rated insulation voltage U _i	input circuit / output circuit		
(IEC/EN 62477-1)			
	input circuit / PE		
_	input circuit / relay contact		
-	output circuit / relay contact		
-	relay contact / PE	50 V	
	output circuit / PE	50 V	
Overvoltage category	< 2000 m		
(IEC/EN 62477-1)	20005000 m		
Overvoltage category	< 2000 m		
(IEC/EN 61010-1/IEC/ EN 61010-2-201)	20005000 m	П	
Pollution degree	input circuit / ground	2	
Protective separation	input circuit / output circuit		
IEC/EN 61010-1, 61010-2-201	input circuit / relay output		
Standards / Directives	input circuit / relay output	ycs	
Low Voltage Directive		2014/35/EU, IEC/EN 61204	
EMC directive		2014/30/EU	
RoHS directive			
WEEE directive		2011/65/EU incl. 2015/863/EU 2012/19/EU	
Electrical safety		IEC/EN 61010-1. IEC/EN 61010-2-201	
Process control equipment		UL 61010-1, UL 61010-2-201/ CAN/CSA C22.2 No. 61010-1-12, CAN/CSA-IEC 61010-2-201:18	
Protective extra low voltage		PELV IEC/EN 61010-2-201	
Safety extra low voltage		SELV_IEC/EN 61010-2-201	
Limitation of harmonic line currents		IEC/EN 61010-2-201	
Electromagnetic compatibility	· · · · · · · · · · · · · · · · · · ·		
	tout Dart 2.	IEC/EN 61204-3	
Low-voltage power supplies, d.c. output – Part 3:		12C/EN 01204-5	
Electromagnetic compatibility (EM	-)	IEC/EN 61000-6-2	
Interference immunity to		contact discharge air discharge, level 4, 8 kV / 15 kV (criterion A)	
electrostatic discharge (ESD) IEC/EN 61000-4-2		80 to 1000 MHz, 10 V/m (criterion A), 1.4 to 6 GHz, 3 V/m (criterion A)	
radiated, radio-frequency, IEC/EN 61000-4-3 electromagnetic field			
electrical fast transient / IEC/EN 61000-4-4 burst		level 4, 4 kV / 2 kV (criterion A)	
surge	IEC/EN 61000-4-5	level 4, L/N 3 kV (criterion A); level 4, L, N / PE 4 kV (criterion A)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V (criterion A)	
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3	
harmonics and interharmonics	IEC/EN 61000-4-13	class 3 (criterion A)	
conducted, common mode disturbances in the frequency range 0 Hz to 150 kHz	IEC/EN 61000-4-1	level 3, 10 V	
Interference emission		IEC/EN 61000-6-3; IEC/EN 61000-6-4	
limits for harmonic current emissions	IEC/EN 61000-3-2	class A	
limitation of voltage changes e	tc. IEC/EN 61000-3-3	compliant	
information technology equipn	•	•	
radio disturbance characteristics EN 55032 limits and methods of measurement			
limits and methods of measure		class B	
limits and methods of measure industrial scientific and medica	al EC/CISPR 11,		
industrial scientific and medica (ISM) radio-frequency equipme electromagnetic disturbance characteristics	ent EN 55011 EN 50204		
industrial scientific and medica (ISM) radio-frequency equipme electromagnetic disturbance characteristics limits and methods of measure	ent EN 55011 EN 50204 ement	nassad	
industrial scientific and medica (ISM) radio-frequency equipme electromagnetic disturbance characteristics limits and methods of measure Voltage sags	ent EN 55011 EN 50204 ement SEMI F47-0706	-	
industrial scientific and medica (ISM) radio-frequency equipme electromagnetic disturbance characteristics limits and methods of measure	ent EN 55011 EN 50204 ement SEMI F47-0706	-	

Technical diagrams

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

U/I characteristic curves of output at $T_a = 25 \text{ °C}$



CP-S.124/3.0

Characteristic curves of temperature $T_{\rm out}$ = 24 V DC





The switch mode power supply CP-S.1 is able to supply at 24 V DC output voltage and at an ambient temperature of

+ \leq 60 °C the rated current of 3 A

+ \leq 60 °C a continuous output current of typ. \leq 4.5 A for 5 s

With mounting position 1 (standard) and at ambient temperatures of > +60 °C the output power has to be reduced by 2.5 % per Celsius degree temperature increase. Deratings for other mounting positions on request.

At thermal overload the device will switch-off as soon as the internal temperature exceeds the acceptable level. The exact ambient temperature threshold depends on the mounting position and load of the power supply.

The device is equipped with an overtemperature protection function. It will switch-off as soon as the internal overtemperature protection function is activated.

Dimensions

in mm and inch



CP-S.124/3.0

Further documentation

Document title	Document type	Document number
Electronic relays and controls	Catalog	2CDC110004C0210
Operating and installation instructions CP-S.1	Instruction manual	1SVC320360M0000
CP-S.1 power supply range	Leaflet	1SAC200134W0001

You can find the documentation at www.abb.com/lowvoltage > Automation, Control and Protection > Power supplies.

CAD system files

You can find the CAD files for CAS systems at http:/abb-control-products.partcommunity.com > Low voltage Products & Systems > Control Products > Electronic Relays and Controls.



ABB STOTZ-KONTAKT GmbH Eppelheimer Straße 82 69123 Heidelberg, Germany

abb.com/lowvoltage



Further information:

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG. Copyright© 2022 ABB AG. All rights reserved 1SAC200137H0001 Rev. A (08/2021)