


On-load tap-changer type (V)UCGR./F, (V)UCLR./F, UCCR./F,
 19 tap positions, plus/minus switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 10,
 the preceding pos. was 9.

Lindningskopplare typ (V)UCGR./F, (V)UCLR./F, UCCR./F,
 19 lägen, plus/minus koppling.
 Max antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 10,
 föregående läge var 9.



Pos. Läge	R connects in direction R förbinder i riktning		Tap selector and diverter switch connect Väljaren och lastkopplaren förbinder
1		▲	1-V-x
2	↓	▲	2-H-v
3	↓	▲	3-V-x
4	↓	▲	4-H-v
5	20-21 ↓	20-21 ▲	5-V-x
6	↓	▲	6-H-v
7	↓	▲	7-V-x
8	↓	▲	8-H-v
9	↓	▲	9-V-x
10	↓	▲	10-H-v
11	↓	▲	1-V-x
12	↓	▲	2-H-v
13	↓	▲	3-V-x
14	↓	▲	4-H-v
15	20-22 ↓	20-22 ▲	5-V-x
16	↓	▲	6-H-v
17	↓	▲	7-V-x
18	↓	▲	8-H-v
19	↓	▲	9-V-x

30

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

The tap-changer is shown in pos. 10,
 the preceding pos. was 9.
 The tap selector and the change-over selector
 are seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 10,
 föregående läge var 9.
 Väljaren och plus/minus-omkopplaren sedda uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Cont		
	Year	Week	Cont	
	Dept			
	Rev Ind	Revision	Appd	Year Week
Rev Ind	Accepted by qual control L.Oberg	Accepted for prod by M.Haggmar	Description (English) CONNECTION DIAGRAM	DATAORIGINAL
Design checked by	Design checked by H.Sundberg	Drawn by A.Wang	Description (own language) KOPPLINGSSHEMA	File name
	Drawing checked by N.Gustavsson	Issued by Dept CO/TK		Year 14
			1ZSC004309-AAF	Lang 1
				Rev Ind Cont