


FurseWELD

Cable to cable CC11

Cable to cable CC11 - FurseWELD

	Stranded/solid circular conductor size A (mm ²)	Stranded/solid circular conductor size B (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	50	50	CC11-7-5050	7TCA083910R1156	150P10	HCPK7
	70	70	CC11-7-7070	7TCA083910R1157	200P10	HCPK7
	95	95	CC11-7-9595	7TCA083910R1160	250P10	HCPK7
	120	120	CC11-7-120120	7TCA014980R0056	2 x 150P10	HCPK7
	150	150	CC11-8-150150	7TCA083910R1161	2 x 200P10	HCPK8
	185	185	CC11-8-185185	7TCA083910R1166	2 x 250P10	HCPK8
	240	240	CC11-8-240240	7TCA083910R1167	3 x 200P10	HCPK8
	300	300	CC11-8-300300	7TCA083910R1169	3 x 250P10	HCPK8

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection