

# Ferrule hand tools



—  
01

—  
02

—  
01 FER9500  
—  
02 FER9501

The ABB 950X series of ergonomic crimping tools feature convenient integrated range-taking dies for crimping wire ferrules within the range of 0.14–10.00 mm<sup>2</sup>/26–8 AWG.

These tools provide UL listed crimps to many of our Sta-Kon® ferrules, and do so without the need for carrying or changing dies.

Enhanced comfort — thanks to ergonomic handles, light weight, relatively low handle force and optimal handle opening.


- Provides UL listed crimps on a wide range of bare and insulated Sta-Kon ferrules (see reverse)
- Will crimp any ABB ferrules within 0.14–10.00 mm<sup>2</sup>/26–8 AWG range without changing dies
- Compact design for easy access to wires in confined spaces
- Ergonomic design helps reduce operator strain and fatigue
- Full-cycle Shure-Stake™ crimp mechanism ensures a consistent, reliable crimp when used according to instructions
- Features ratchet-release mechanism for clearing obstructions
- Non-slip handle features hole for attachment of safety strap
- Range-taking design does not require a user to identify the proper die or nest to use, minimizing the risk of mistakes or improper crimps



01

01 FER9500


02 FER9501



**Square crimp  
(FER9500)**



02



**Hex crimp  
(FER9501)**

**Ferrule hand tools for 0.14–10 mm<sup>2</sup> (26–8 AWG)**

| Part no. | Description       | UPC no.      |
|----------|-------------------|--------------|
| FER9500  | With square crimp | 786210-08872 |
| FER9501  | With hex crimp    | 786210-08938 |

**Sta-Kon ferrules with UL listing**



|                           | 20 AWG<br>(0.5 mm <sup>2</sup> ) | 18 AWG<br>(0.75 mm <sup>2</sup> ) | 18 AWG<br>(1 mm <sup>2</sup> )   | 16 AWG<br>(1.5 mm <sup>2</sup> ) | 14 AWG<br>(2.5 mm <sup>2</sup> ) | 12 AWG<br>(4 mm <sup>2</sup> )   | 10 AWG<br>(6 mm <sup>2</sup> ) | 8 AWG<br>(10 mm <sup>2</sup> ) |
|---------------------------|----------------------------------|-----------------------------------|----------------------------------|----------------------------------|----------------------------------|----------------------------------|--------------------------------|--------------------------------|
| <b>Bare ferrules</b>      | F9001<br>F9002                   | F9003<br>F9004                    | F9005<br>F9006                   | F9007<br>F9008<br>F9009<br>F9010 | F9011<br>F9012<br>F9013<br>F9014 | F9015<br>F9016<br>F9017<br>F9018 | F9019<br>F9020<br>F9021        | F9022<br>F9023<br>F9024        |
| <b>Insulated ferrules</b> | F2022                            | F2023<br>F2024<br>F2025<br>F2026  | F2027<br>F2028<br>F2029<br>F2030 | F2031<br>F2032<br>F2033<br>F2034 | F2035<br>F2036<br>F2037          | F2038<br>F2039<br>F2040          | F2041<br>F2042                 | F2043<br>F2044                 |

All ferrules above are UL listed with the FER9500, FER9501 and ERG4 installation tools.  
For more information on Sta-Kon ferrules, visit our website or see our full-line Sta-Kon wire termination catalog.

**ABB Installation Products Inc.**  
Electrification business  
860 Ridge Lake Blvd.  
Memphis, TN 38120

[tnb.abb.com](http://tnb.abb.com)

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Installation Products Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved