


On-load tap-changer type UCGL./C, VUCGL./C, 14 tap positions, linear switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 7,
 the preceding pos. was 6.

Lindningskopplare typ UCGL./C, VUCGL./C, 14 lägen,
 linjär koppling.
 Max antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 7,
 föregående läge var 6.

Pos. Läge	Tap selector and diverter switch connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	



The tap-changer is shown in pos. 7,
 the preceding pos. was 6.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 7,
 föregående läge var 6.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19

Sheet	Cont								
	Year	Week							
Dept			1	VUCG Added.	SUKN	07	47		
	Rev Ind	Revision	Appd	Year	Week				
RevInd	Accepted by qual control		Accepted for prod by		Description (English)			DATAORIGINAL	
	R.Yngvesson				CONNECTION DIAGRAM				
Design checked by	Design checked by		Drawn by		Description (own language)			File name	
	B-O.Stenestam		L.Bergman		KOPPLINGSSHEMA			0373-10	
Lang	Drawing checked by		Issued by Dept		Year		Week		Sheet
	M.Hedlund		COM/TKO		97		17		1
RevInd	Cont				5492 0373-10				
Asea Brown Boveri									