


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.  
© ABB '19

On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UC DL./III,  
13 tap positions, linear switching.  
Max. effective No. of turns in pos. 1.  
The tap-changer is delivered set in pos. 7,  
the preceding pos. was 6.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UC DL./III,  
13 lägen, linjär koppling.  
Max antal effektiva varv i läge 1.  
Lindningskopplaren levereras inställd i läge 7,  
föregående läge var 6.



Pos. Läge	Tap selector and diverter switch connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	

The tap-changer is shown in pos. 7,  
the preceding pos. was 6.  
The tap selector is seen from above.  
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 7,  
föregående läge var 6.  
Väljaren sedd uppifrån.  
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the  
tap-changer. Dashed lines show leads belonging  
to the cleats and leads.

Heldragna linjer visar ledare som ingår i  
lindningskopplaren. Streckade linjer visar  
ledare som tillhör anslutningsdonet.

3	Tap selector figure changed.	THLA	17	07
2	VUCL Added	CA	12	37
1	VUCG Added	CE	07	47
Rev Ind	Revision	Appd	Year	Week

Sheet	Cont	Year	Week	Dept	Rev Ind	Accepted by qual control	Accepted for prod by	Description (English)	DATA ORIGINAL	
							CONNECTION DIAGRAM			
Form No.	Design checked by	M.Hedlund	Year	Week	COM/TKO 97 16	Design checked by	Drawn by	Description (own language)	File name	
						B-O.Stenestam	L.Bergman	KOPPLINGSSHEMA	0367-5	
									Lang	Sheet
									1	
									Rev Ind	Cont
									-	



Asea Brown Boveri

5492 0367-5