

TX

Thermal Dispersion Switch

Thermal Dispersion flow/level/
temperature switch
K-TEK Products



Features

- For Liquids, Gases & Small Granular Solids
- One Switch for Gas or Liquid Flow, Liquid Level, Interface Level or Temperature
- 316L Stainless Steel All Welded Construction Standard
- Explosion Proof, No Moving Parts
- Temperature Range -50 to 350°F / -46 to 177°C Standard
- Pressure to 4000 psig / 275 bar Standard

Options

- Exotic Alloys for Corrosive Applications
- Temperatures from -320 to 900°F / -195 to 482°C
- Pressure to 10,000 psig / 689 bar
- Extended Sensor
- Remote Mounting
- Flange Mounting
- Ceramic Glass To Metal Feedthrough Provides Secondary Pressure Boundry

Accessory

- Stainless steel flow tube adapter for small diameter pipe

SPECIFICATIONS

Sensor

Materials of Construction	316L Stainless Steel Standard, Exotic Alloys Optional
Response Time	No Flow to Flow: From 3 Seconds; Flow to No Flow: From 8 Seconds
Operating Temperature	Level: +/- 1/8"; Temperature: From 1 second -50 to 350°F / -46 to 177°C Standard Options: -320 to 500°F / -196 to 260°C -100 to 900°F / -73 to 482°C
Operating Pressure	Full Vacuum to 4000 psig / 275 bar Standard Option: 10,000 psig / 689 bar maximum
Repeatability	Flow: 0.5% of maximum flow rating at Constant Conditions Standard ; Level: +/- 1/8"; Temperature: +/- 1°C
Process Connection	3/4" MNPT Standard Options: 1", 1-1/4", 1-1/2", 2" MNPT, Flanges, Retractable Probes
Insertion Length	1.8" / 45.7mm Standard Option: 1.2" / 30.5mm; Custom Lengths Available

Electronics

Housing	Powder Coated Aluminum Standard Optional: Dual Compartment Aluminum; Dual Compartment 316L SS
Operating Temperature	-50 to 140°F/-46 to 60°C Ambient Option: Remote Mounting of Electronics Up to 2000 ft. / 609 meters
Power Input	90-132 VAC, 50/60 Hz, 5.5 watts max Options: 24 VDC, 24 VAC, 208-240 VAC
Relay Output	DPDT 8 amps @ 250 VAC
Conduit Entry	3/4" FNPT Standard
Approvals	CL I, Div I, GP A,B,C,D; CL I, Div II, GP E,F,G; Div III, DIP, NEMA or Type 4X FM: T3A @ Ta = 60C CSA: T3C @ Ta = 60C (For A, A1 and S housing options) GOST Russia, GOST Kazakhstan: 1ExdIICT3
Shipping Weight	5 lbs standard



ORDERING INFORMATION:

TX/a/b/c/d/e/f/g/h:

/a Housing

A1	Single Compartment Aluminum Housing Standard
A1W	Single Compartment Aluminum Housing with glass window cover
A	Dual Compartment Aluminum Housing
AW	Dual Compartment Aluminum Housing with Glass Viewing Window
S	Dual Compartment 316L Stainless Steel Housing
SW	Dual Compartment 316L Stainless Steel Housing with Glass Viewing Window

/b Material Type

S6	316L Stainless Steel Standard
HB	Hastelloy B-3
HC	Hastelloy C-276
AM	Monel
T2	Titanium GR. 2
T7	Titanium GR. 7
A20	Carpenter 20

/c A) Process Connection – Threaded

0750	3/4" MNPT Standard
1000	1" MNPT
1250	1-1/4" MNPT
1500	1-1/2" MNPT
2000	2" MNPT

B) Process Connection – Flanged

/AABC	AA	B	C
	10 1" Flange	1 150#	1 Raised Face, 316L SS
	15 1-1/2" Flange	2 300#	2 Raised Face, Carbon Steel
	20 2" Flange	3 600#	3 Flat Face, 316L SS
	30 3" Flange	4 900#	4 Flat Face, Carbon Steel
	40 4" Flange	5 1500#	6 Special
	60 6" Flange		

/d Insertion Length

1.8	1.8" / 45.7 mm Insertion Length Standard
1.2	1.2" / 30.5 mm Insertion Length
Length	Customer Specified Length in Inches or Millimeters (1.2" / 30.5 mm minimum)

/e Power Input

1	90-132 VAC Standard
2	24 VDC or VAC (22.8 - 28.8 VDC; 20 VAC - 25 VAC)
3	200-240 VAC

/f Process Temperature

H0	-50 to 350°F / -46 to 177°C Standard
H1	-320 to 500°F / -196 to 260°C (Requires remote mounting of electronics)
H2	-100 to 900°F / -73 to 482°C (Requires remote mounting of electronics)

/g Approvals


X	Not FM or CSA Approved
FMX	Factory Mutual Research Corp (FMRC) Standard
CSX	CSA Canadian Standard Association
GR	GOST Russia
GK	GOST Kazakhstan

/h Options (leave blank if no options required)


DS	Dual Switch Point Electronics with Millivolt Output
RJxxxx	Remote Electronics with PVC Cable (200°F / 93.3°C) Specify cable length "xxxx" ft. (Max. Length 2000 ft. / 609 m)
RFxxxx	Remote Electronics with Teflon Cable (500°F / 260°C) Specify cable length "xxxx" ft. (Max. Length 2000 ft. / 609 m)
HF	High Flow Option (Requires 1" MNPT or 1-1/2" Flange or larger; for clean liquids only)
HP	High Pressure Option (10,000 psig / 689 bar)
G1	Packing Gland for Retractable Probe, 50 psig / 3.4 bar Maximum
G2	Packing Gland for Retractable Probe, 500 psig / 34.5 bar Maximum
HS	5 Pin Hermetic Feed-through (not offered with Titanium)

Accessory: 316 Stainless Flow Tube part# MEC 2796 (to adapt standard TX to small diameter pipe sizes)

***Note: For available set points / flow calibration & conversion charts see MKT-0189-1**



TX Dimensions with Standard Housing



Contact us

ABB Inc.

18321 Swamp Road
Prairieville, LA 70769 USA
Phone: +1 225 673 6100
Service: +1 225 677 5836
Fax: +1 225 673 2525
Service e-mail: service@us.abb.com

www.abb.com/level

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2012 ABB
All rights reserved

DS/TX-EN Rev. M 06.2012