

NOTES:

1. RADIO KEY DELAY MUST BE SET BETWEEN 200 & 250 MS. APPROPRIATE SOFTWARE CONTAINING PROM RAD DELAY MUST BE USED.

2

SWITCH SETTING FOR BAUD RATE

SWITCH 4	SWITCH 5	BAUD RATE
OFF	OFF	9600
OFF	ON	4800
ON	OFF	2400
ON	ON	1200

3

ON FOR 60 SECOND TIME-OUT TIMER

REVISIONS

REV	ACTION	DRAWN	CHECKED	APPROVED	DATE
AA	L4742	KASTNER	KASTNER	HOLLAND	97/10/01
AB	D4975	KASTNER	KASTNER	HOLLAND	97/11/20
AC	D12447	KASTNER	KASTNER	HOLLAND	01/12/14

ASSEMBLY/QUANTITY	ITEM NO.	PART NUMBER	DESCRIPTION	REF/ZONE DESIG MATERIAL	UNIT MEAS
PARTS LIST					
DO NOT SCALE DRAWING	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMAL .XX ± -- ANGULAR ± -- .XXX ± -- BREAK ALL SHARP CORNERS AND EDGES DIMENSIONS APPLY BEFORE FINISH		<b>PRODUCT LINE</b> TOTALFLOW® <b>DESIGN</b> G. HOLLAND <b>DRAWN</b> A. KASTNER <b>CHECKED</b> A. KASTNER <b>APPROVED</b> HOLLAND	<b>LEVEL</b> 3 <b>DATE</b> 97/9 <b>DATE</b> 97/9/25 <b>DATE</b> 97/9/30 <b>DATE</b> 97/10/1	<b>AB</b> <b>TITLE</b> WIRING INTERCONNECT RNET W/MODEM TO 68XX WI <b>SCALE</b> NONE <b>SIZE</b> B <b>REV</b> WI <b>DRAWING NO.</b> 2017447 <b>REV</b> AC <b>SHEET</b> 1 OF 3

MODEL

6613  
6614  
6615



