




**Product selection:**

Part no.	Profile	Conduit size		rec. fitting thread size		Dimensions in mm (nom.)				Weight	Packing unit
		NW	metric	PG	metric	d1	d2	stat. R	dyn. R.		
black/blue	T/G	NW	metric	PG	metric	d1	d2	stat. R	dyn. R.	kg/100 m	metre
XTPCG-17BB.50	G	17	20	16	M20x1.5	15.2	21.1	30	75	8.5	50
XTPCG-23BB.50	G	23	25	21	M25x1.5	21.2	28.4	40	100	13.0	50
XTPCG-29BB.50	G	29	32	29	M32x1.5	26.8	34.5	50	120	17.0	50
XTPCG-36BB.30	G	36	40	36	M40x1.5	35.5	42.4	60	150	20.5	30
XTPCG-48BB.30	G	48	50	48	M50x1.5	46.5	54.5	80	190	29.0	30
XTPCG-56BB.30	G	56	68	-	-	56.2	67.5	105	235	39.0	30
XTPCG-70BB.30	G	70	80	-	-	67.3	79.6	120	280	54.0	30

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



stat. R. = min. bending radius for static (fixed) installation

dyn. R. = min. bending radius for dynamic (flexible) installation

Mechanical Properties:	Value:	Test parameters:	Test method:
Impact strength	> 4.5 J		PMA DO 9.21-4330
Compression strength	> 160 N	(50 x 50 mm)	PMA DO 9.21-4320
	> 320 N	(100 x 100 mm)	
Resistance to fatigue	> 5'000'000 cycles		PMA DO 9.21-4420
	> 10'000'000 cycles		PMA DO 9.21-4425
Pull-out resistance conduit - fitting series			
PMAFIX Pro	> 280 N		PMA DO 9.21-4610
PMAFIX IP68	> 260 N		PMA DO 9.21-4610
PMAFIX IP66	> 220 N		PMA DO 9.21-4610

Note: Testing at 23°C, 50% r.h., conduit nominal width 17, unless otherwise stated

Additional sealing may be required to archive IP performance in combination with the fitting series PMAFIX, PMAFIXpro and PMAGRIP due to higher material shrinkage of the corrugated conduit

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	-40 ... +105°C		PMA DO 9.21-4510
Upper application temperature	+120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+150°C	(168 h)	PMA DO 9.21-4360

ABB Switzerland Ltd,  
PMA Cable Protection  
Aathalstrasse 90  
8610 Uster, Switzerland  
Phone: +41 58 585 00 11  
pma-info@ch.abb.com  
www.pma.ch

Let's write the future.  
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

