

ABB MEASUREMENT & ANALYTICS | DATA SHEET

**8037**

Sodium monitor



---

## **Measurement made easy**

Rugged and reliable performance in a wide range of harsh environments

### **Wide measuring range**

- covers all power plant applications

### **Automatic sample temperature compensation**

- maximizes measurement accuracy

### **'Pumpless' liquid handling section**

- ensures low maintenance

### **Comprehensive diagnostics facility with built-in software protection**

- provides security and confidence in operation

### **Detachable cable electrode option**

- simplifies maintenance

### **Reagent entrainment system**

- sample flow controls addition of reagent; no diffusion tubing required

## Introduction

The prevention of damage to the boilers on modern power stations becomes more and more critical as the cost of repairs and out-of-service plant continues to rise. To reduce the effect of boiler tube corrosion and the formation of scale on the inside of the tubes, the levels of impurities in the various parts of the steam/water cycle must be monitored carefully.

Sodium ions are normally the most abundant element found in solution in boiler plant, therefore the measurement of sodium provides a valuable indication of the overall purity of the solution. While on-line conductivity can give useful information concerning the total concentration of the ionic element, it is far less sensitive than a specific measurement for sodium.

The points where on-line sampling for sodium would be required are:

- Water treatment plant
  - Sodium measurement, at the outlet of cation and mixed resin exchange beds, gives an early indication of resin exhaustion and treated water quality.
- Condensate monitoring at the extraction pump discharge
  - As condensers are operated under vacuum, leaks result in the ingress of cooling water into the process water. If the cooling water contains relatively high levels of sodium (as is usually the case), monitoring of sodium in the process water can provide an early indication of condenser leaks.
- Saturated steam in drum boilers
  - The monitoring of sodium in the saturated steam between the boiler drum and the superheater detects carryover and, in conjunction with sodium monitoring in the condensate (the sodium balance), can indicate problems caused by sodium deposits on superheated tubes and turbine blades.
- Once-through boilers
  - Since the purity of the boiler water is more stringent in these boilers, sodium monitoring, after the condensate polishing plant, boiler feed and superheated steam, can assist in maintaining water/ steam purity within limits.

## General information

The ABB 8037 Sodium Monitor uses an ABB sodium ion-selective electrode and reference electrode to measure the sodium ion concentration in power station waters.

The model 8037 is an accurate, reliable instrument which requires very little maintenance and measures sodium ion concentrations within the ranges of  $0.10 \mu\text{g kg}^{-1}$  to  $10\text{mg.kg}^{-1}$ .

The basic monitor is supplied with a panel- or wall-mount unit and cable-attached electrodes. Optional facilities are available as detailed below:

- Detachable cable electrodes
- Serial data interface
- Second current output
- Second current output
- Reservoir-fed reference electrode
- Environmental cover kit

---

## Transmitter

The 8037 Series transmitter provides the operator interface and communications to other devices. The signal from the sensing system is converted by the transmitter and information is displayed as a  $\mu\text{g}/\text{l}$ ,  $\mu\text{g}/\text{kg}$ , ppb,  $\text{mg}/\text{l}$ ,  $\text{mg}/\text{kg}$  or ppm value.

A process retransmission signal and two alarm relay outputs are provided as standard. A second current output or RS485 serial interface, which allows the transmitter to be easily incorporated into an ABB PC30 or other Modbus-compatible supervisory systems, are available as options.

Available in wall-mount or  $\frac{1}{4}$  DIN panel-mount versions, the transmitter is protected to IP66, ensuring reliable operation in the most demanding situations. The same level of protection is maintained during programming and calibration.

The large, easy-to-read, customized liquid crystal display (LCD) is used in conjunction with the four tactile membrane key pads to prompt the user through the programming procedures. Included, as standard, is a four-language software package, to display information in English, French, Spanish or German.

---

## Sensing panel

A flow schematic is shown opposite. The sample enters the monitor via the compression fitting on the 3-way changeover valve. It then passes through the changeover valve to the constant head unit which removes the effect of changes in sample pressure and flow-rate. A small tube, overflowing into the constant head on one side, ensures self-starting when the sample is lost and enables the monitor to function over a wide sample flow range.


The sample is then delivered to the entrainment 'T' piece and stainless steel entrainment tube, where an alkaline vapor reagent is added to raise the pH value, before flowing past the sodium and reference electrodes mounted in the flowcell. Finally, the sample leaves the flowcell and exits to drain.

The potential developed between the sodium ion-responsive electrode and silver/silver chloride reference electrode is logarithmic with respect to changes in sodium ion concentration. The signal from the electrode pair is connected to the 8037 Transmitter.


A temperature sensor, fitted into the flowcell, detects the temperature of the sample. The sensor is connected to the transmitter unit which compensates for changes in output from the electrode pair over a range of 5 to 55 °C (41 to 131 °F).

Calibration is carried out manually after connection of the calibration tube to the standard solution container. The 3-way changeover valve on the liquid handling panel is changed-over manually from sample to standard solution. The calibration is initiated from the transmitter unit, where it is controlled by the microprocessor. The standard solution takes the same path as the sample through the liquid handling panel.

## Schematic flow diagram



## Components of 8037 sodium monitor



## Specification

### General

#### Display

Measured value	5-digit, 7-segment back-lit LCD
Information	16-character, single-line, dot matrix back-lit LCD

#### Display range

0.01  $\mu\text{g kg}^{-1}$  to 10  $\text{mg kg}^{-1}$

#### Units of measure

- ppb / ppm
- $\mu\text{g/l}$  /  $\text{mg/l}$
- $\mu\text{g kg}^{-1}$  /  $\text{mg kg}^{-1}$

#### Current output expansion

- Scale expansion between 2 and 4 decades logarithmic or the equivalent linearized
- Programmable in the range 0.10  $\mu\text{g kg}^{-1}$  to 10  $\text{mg kg}^{-1}$
- Maximum load resistance 500  $\Omega$  (20 mA)

#### Display resolution

- 0.01  $\mu\text{g kg}^{-1}$  in range 0.01  $\mu\text{g kg}^{-1}$  to 9.99  $\mu\text{g kg}^{-1}$
- 0.1  $\mu\text{g kg}^{-1}$  in range 10.0  $\mu\text{g kg}^{-1}$  to 99.9  $\mu\text{g kg}^{-1}$
- 1  $\mu\text{g kg}^{-1}$  in range 100  $\mu\text{g kg}^{-1}$  to 999  $\mu\text{g kg}^{-1}$
- 0.01  $\text{mg kg}^{-1}$  in range 1.00  $\text{mg kg}^{-1}$  to 9.99  $\text{mg kg}^{-1}$

#### Accuracy

$\pm 10\%$  of concentration or  $\pm 0.1 \mu\text{g kg}^{-1}$  whichever is the greater (when sample temperature is within  $\pm 5^\circ\text{C}$  ( $\pm 9^\circ\text{F}$ ) of calibration temperature)

#### Reproducibility

$\pm 5\%$  of concentration or 0.1  $\mu\text{g kg}^{-1}$  (whichever is the greater) at constant temperature

#### Response time

- 1 to 100  $\mu\text{g kg}^{-1}$  less than 4 minutes for 90 % step change
- 100 to 1  $\mu\text{g kg}^{-1}$  less than 6 minutes for 90 % step change

#### Temperature compensation

Automatic within  $\pm 5^\circ\text{C}$  ( $\pm 9^\circ\text{F}$ ) of calibration temperature

#### Current outputs

- One, fully isolated
- Two, fully isolated (optional)
- 0 to 10, 0 to 20 or 4 to 20 mA, programmable

#### Serial communication

- RS422/RS485 (optional)
- Modbus compatible

#### Alarms

- Two fail-safe, high and low concentration alarms
- Hysteresis  $\pm 1\%$  of FSD (fixed)
- Relay contacts (single pole changeover):
  - Rating 250 V AC 250 V DC max.  
3 A AC 3 A DC max.
  - Loading (non-inductive) 750 VA 30 W max.  
(inductive) 75 VA 3 W max.
- Insulation, contacts to earth: 2 kV RMS

#### Calibration

- Manual initiation of calibration sequence
- Calibration frequency (typically) weekly for 1-point, and 4-weekly for 2-point calibration

### Installation Information

#### Sample temperature

5 to 55  $^\circ\text{C}$  (41 to 131  $^\circ\text{F}$ )

#### Sample flow

50  $\text{ml/min}^{-1}$  to 500  $\text{ml/min}^{-1}$

#### Sample pressure (gauge)

- Maximum 0.14 bar (2 psi)
- Outlet from sensing panel must go to atmospheric drain

#### Ambient temperature

0 to 55  $^\circ\text{C}$  (32 to 131  $^\circ\text{F}$ )

#### Dimensions of sensing panel

250 mm (9.84 in.) wide x 440 mm (17.32 in.) high (690 mm [27.16 in.] high to clear bottle assemblies) x 160 mm (6.29 in.) deep

#### Mounting for sensing panel

Four holes: 8.5 mm (0.33 in.) diameter  
200 mm (7.87 in.) horizontal  
325 mm (12.79 in.) vertical

#### Weight of sensing panel

11 kg (24.3 lb.) (including optional environmental cover)

#### Connections to sensing panel

- Sample inlet  $\frac{3}{4}$  in OD compression fitting (6.3 mm)
- Sample drains 10 mm (0.39 in.) ID flexible, atmospheric drain

#### Dimensions of transmitter unit

- Wall-mount unit
  - 160 x 214 x 68 mm (6.29 x 8.42 x 2.67 in.)
- Panel-mount unit
  - 96 x 96 x 191 mm (3.78 x 3.78 x 7.52 in.) (cut-out 92 x 92 mm [3.62 x 3.62 in.]

#### Weight of transmitter unit

- Wall-mount: 2 kg (4.41 lb.)
- Panel-mount: 1.5 kg (3.31 lb.)

#### Power supply requirements

- 115 V nom.  $\pm 15$  V, 50/60 Hz or
- 230 V nom.  $\pm 30$  V, 50/60 Hz

#### Power consumption

<10 VA

#### Insulation, mains to earth

2 kV RMS

#### Max. cable core sizes

- Mains supply 32/0.2 mm
- Signal 24/0.2 mm

#### Maximum distance between sensor & transmitter unit

10 m (32.8 ft.)

### Environmental data

#### Storage temperature limits

0 to 55  $^\circ\text{C}$  (32 to 131  $^\circ\text{F}$ )

#### Operating humidity limits

Up to 95 % RH non-condensing

#### Environmental protection



Wall-mount transmitter	IP66/NEMA4X
Panel-mount transmitter	P66/NEMA4X (front)

## Installation

It is recommended that the sample supply line is fitted with a needle valve and flow indicator (not supplied) and the sample is discharged from the monitor to an atmospheric drain.

Maximum distance between sensing panel and transmitter 10 m (32.8 ft.) (with detachable-cable electrode option).

### Sensing panel installation details




**Note.** 160 mm (6.29 in.) space required below the sensor panel to allow for the opening of the optional environmental cover.

## Overall dimensions


### 8037 wall-mount version

Dimensions in mm (in.)




### 8037 panel-mount version

Dimensions in mm (in.)




# Electrical connections

## 8037 wall-mount version



## 8037 panel-mount version



## Ordering information

Model 8037 sodium monitor	8037/00	X	X	X	X	X	X	X
<b>Standard</b>								
Standard	0							
Special	9							
<b>Enclosure</b>								
Wall-mount transmitter	0							
Panel-mount transmitter	1							
<b>Output</b>								
Current output only				0				
Current output and serial data interface (Modbus optional)				1				
2 current outputs				2				
<b>Electrode type</b>								
Cable attached electrodes (1 m [39 in.] only)					0			
Cable detached electrodes					1			
Cable detached electrodes (reservoir-fed reference)					2			
<b>Cable assemblies</b>								
Cable attached electrodes						0		
1 m (39 in.) cable assemblies						1		
3 m (9.75 ft.) cable assemblies						2		
5 m (16.25 ft.) cable assemblies						3		
10 m (32.5 ft.) cable assemblies						4		
<b>Optional items</b>								
Without environmental cover kit							0	
With environmental cover kit							1	
<b>Language</b>								
English								0
German								1
French								2
Spanish								3

### Reservoir-fed reference electrode kit

A kit to upgrade model 8037 from using a refillable reference electrode to one using a reservoir-fed reference electrode is available – part no. 8037-150.

Service



---

**ABB Limited****Measurement & Analytics**

Oldends Lane, Stonehouse  
Gloucestershire, GL10 3TA  
UK

Tel: +44 (0)1453 826 661

Fax: +44 (0)1453 829 671

**ABB Inc.****Measurement & Analytics**

125 E. County Line Road  
Warminster, PA 18974

USA

Tel: +1 215 674 6000

Fax: +1 215 674 7183

**[abb.com/measurement](http://abb.com/measurement)**

---

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.