



Test Report				Date of issue: 25.5.2015							
Customer:				Serial No.:							
Customer ref.:				Order No.:							
				Type: M3GP 180MLA 4							
				Product Code: 3GGP182410-ADK							
				Protection type: Ex tc IIIB/C T125C Dc							
				Cert. No.: LCIE 13 ATEX 1034 X / IECEx LCIE 13.0047 X							
Rating:											
		V	Hz	kW	r/min	A	cos φ	Duty			
3-Motor		690	Y 50	18,5	1481	20,2	0,82	S1			
Insul.cl.F		400	D 50	18,5	1481	34,9	0,82	S1			
		660	Y 50	18,5	1478	21,1	0,83	S1			
		380	D 50	18,5	1478	36,4	0,83	S1			
		415	D 50	18,5	1482	34,0	0,81	S1			
		460	D 60	18,5	1482	30,6	0,81	S1			
Eff class IE3		50Hz : IE3-93,3(100%)-94,0(75%)-93,8(50%) 60Hz : IE3-93,6(100%)									
Resistance Line				Ambient: 22,4 °C			Insulation resistance at 23 °C		Overload		
U ₁ - V ₁				0,2211 Ω			R > 2000 Mohm 1000 V		Current 150 % 120s		
U ₁ - W ₁				0,2202 Ω					Torque 160 % 15s		
V ₁ - W ₁				0,2202 Ω					Speed 120 % 120s		
High-voltage test winding						2400 V		60 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]		
No load test		400 D	50	14,0	0,42		1500	0,04			
Locked rotor test		76 D	50	34,0	1,30		0	0,3			
Thermal test (100% load)	119,1	400 D	50	34,9	19,76	18,50	1483	0,82	93,62		
Partial load points:											
~75% load	89,9	400 D	50	27,8	14,90	14,01	1488	0,77	94,02		
~50% load	59,6	400 D	50	21,4	9,95	9,31	1492	0,67	93,62		
~25% load	29,2	400 D	50	16,4	5,06	4,58	1497	0,45	90,47		
Temperature rise at rated load.				°C	[K]	Method		Measurement method			
Stator winding :				46,7	46,7	1		1 Resistance			
Frame :				31,5	31,5	2		2 Thermometer			
Bearing D-end :				32,2	32,2	2		3 Thermocouples			
Ambient Temperature :				23	23	2					
<p>These tests have been carried out on motor no. 3GV1110779332001, on date 2011-09-28 which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p>											
On behalf of customer											
On behalf of manufacturer				Date of test							
Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden						Telephone +46 (0)21 32 90 00		Telefax +46 (0)21 32 90 22			

Computer print-out valid without signature.