

$V_{RRM} = 1200 \text{ V}$

$I_F = 100 \text{ A}$

Diode-Die

5SLY 12G1200



Die size: 8.4 x 8.4 mm

Doc. No. 5SYA 1683-03 12 14

- Ultra low losses
- Fast and soft reverse-recovery
- Highly rugged SPT+ design
- Passivation: Silicon Nitride plus Polyimide

Maximum rated values ¹⁾

Parameter	Symbol	Conditions	min	max	Unit
Repetitive peak reverse voltage	V_{RRM}			1200	V
Continuous forward current	I_F			100	A
Repetitive peak forward current	I_{FRM}	Limited by T_{vjmax}		200	A
Junction temperature	T_{vj}			175	°C
	$T_{vj(op)}$		-40	150	

¹⁾ Maximum rated values indicate limits beyond which damage to the device may occur per IEC 60747 - 2

Diode characteristic values ²⁾

Parameter	Symbol	Conditions	min	typ	max	Unit	
Continuous forward voltage	V_F	$I_F = 100 \text{ A}$	$T_{vj} = 25 \text{ °C}$		1.8	2.1	V
			$T_{vj} = 125 \text{ °C}$		1.85		V
Continuous reverse current	I_R	$V_R = 1200 \text{ V}$	$T_{vj} = 25 \text{ °C}$			100	µA
			$T_{vj} = 125 \text{ °C}$		1		mA
Peak reverse recovery current	I_{rr}	$I_F = 100 \text{ A},$ $V_R = 600 \text{ V},$ $di/dt = 2100 \text{ A}/\mu\text{s},$ $L_\sigma = 60 \text{ nH},$ Inductive load, Switch: 1x 5SMY 12K1280	$T_{vj} = 25 \text{ °C}$		83		A
			$T_{vj} = 125 \text{ °C}$		110		A
Recovered charge	Q_{rr}	$I_F = 100 \text{ A},$ $V_R = 600 \text{ V},$ $di/dt = 2100 \text{ A}/\mu\text{s},$ $L_\sigma = 60 \text{ nH},$ Inductive load, Switch: 1x 5SMY 12K1280	$T_{vj} = 25 \text{ °C}$		13		µC
			$T_{vj} = 125 \text{ °C}$		25		µC
Reverse recovery time	t_{rr}	$I_F = 100 \text{ A},$ $V_R = 600 \text{ V},$ $di/dt = 2100 \text{ A}/\mu\text{s},$ $L_\sigma = 60 \text{ nH},$ Inductive load, Switch: 1x 5SMY 12K1280	$T_{vj} = 25 \text{ °C}$		250		ns
			$T_{vj} = 125 \text{ °C}$		380		ns
Reverse recovery energy	E_{rec}	$I_F = 100 \text{ A},$ $V_R = 600 \text{ V},$ $di/dt = 2100 \text{ A}/\mu\text{s},$ $L_\sigma = 60 \text{ nH},$ Inductive load, Switch: 1x 5SMY 12K1280	$T_{vj} = 25 \text{ °C}$		4.8		mJ
			$T_{vj} = 125 \text{ °C}$		10		mJ

²⁾ Characteristic values according to IEC 60747 - 2

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.






Fig. 1 Typical diode forward characteristics




Fig. 2 Typical reverse recovery characteristics vs. forward current




Fig. 3 Typical reverse recovery vs. di/dt




Fig. 4 Safe operating area (FBSOA)

Mechanical properties


Parameter				Unit
Dimensions	Overall die	L x W	8.4 x 8.4	mm
	exposed front metal	L x W	6.7 x 6.7	mm
	thickness		350 ± 15	μm
Metallization ³⁾	front (A)	AlSi1	4	μm
	back (K)	Al / Ti / Ni / Ag	1.2	μm

³⁾ For assembly instructions refer to: IGBT and Diode chips from ABB Switzerland Ltd, Semiconductors, Doc. No. 5SYA 2033.

Form of delivery

Description	Part number
Unsawn 6" wafer die	5SLY 76G1200
Sawn 6" wafer die (on blue tape)	5SLY 86G1200

Outline Drawing



This is an electrostatic sensitive device, please observe the international standard IEC 60747-1, chap. IX.
This product has been designed and qualified for Industrial Level.

Related documents:

5SYA 2045 Thermal runaway during blocking
5SYA 2059 Applying IGBT and Diode dies
5SYA 2093-00 Thermal design of IGBT Modules

We reserve the right to make technical changes or to modify the contents of this document without prior notice. We reserve all rights in this document and the information contained therein. Any reproduction or utilisation of this document or parts thereof for commercial purposes without our prior written consent is forbidden. Any liability for use of our products contrary to the instructions in this document is excluded.

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



ABB Switzerland Ltd
Semiconductors
Fabrikstrasse 3
CH-5600 Lenzburg, Switzerland

Doc. No. 5SYA 1683-03 12 14

Telephone +41 (0)58 586 1419
Fax +41 (0)58 586 1306
Email abbsem@ch.abb.com
Internet www.abb.com/semiconductors