


FurseWELD

Cable to bar CB5

Cable to bar CB5 - FurseWELD



	Stranded/solid circular conductor size A (mm ²)	Flat tape conductor size B (mm)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16 *	25 x 3	CB5-4-16253	7TCA083910R0981	45P10	HCPK4
	25	25 x 3	CB5-4-25253	7TCA083910R0991	65P10	HCPK4
	35	25 x 3	CB5-4-35253	7TCA083910R0992	65P10	HCPK4
	50	25 x 3	CB5-4-50253	7TCA083910R0995	65P10	HCPK4
	Ø 8	25 x 3	CB5-4-8SC253	7TCA083910R2843	65P10	HCPK4
	70	25 x 3	CB5-4-70253	7TCA083910R0997	90P10	HCPK4
	70	25 x 4	CB5-4-70254	7TCA083910R0998	115P10	HCPK4
	70	25 x 6	CB5-4-70256	7TCA083910R0999	115P10	HCPK4
	Ø 10	25 x 3	CB5-4-10SC253	7TCA083910R0960	115P10	HCPK4
	Ø 10	25 x 4	CB5-4-10SC254	7TCA083910R0961	150P10	HCPK4
	Ø 10	25 x 6	CB5-4-10SC256	7TCA083910R2954	150P10	HCPK4
	95	25 x 4	CB5-4-95254	7TCA083910R1007	150P10	HCPK4
	95	25 x 6	CB5-4-95256	7TCA083910R1008	150P10	HCPK4
	120	25 x 6	CB5-4-120256	7TCA083910R0965	150P10	HCPK4
	120	30 x 5	CB5-4-120305	7TCA083910R0967	200P10	HCPK4
	150	25 x 6	CB5-4-150256	7TCA083910R0976	200P10	HCPK4
	150	30 x 5	CB5-4-150305	7TCA083910R0977	200P10	HCPK4
	150	40 x 5	CB5-4-150405	7TCA083910R0979	250P10	HCPK4
	185	31 x 6	CB5-4-185316	7TCA083910R2955	250P10	HCPK4
	185	40 x 5	CB5-4-185405	7TCA083910R0988	240P10	HCPK4
	185	50 x 5	CB5-5-185505	7TCA083910R1023	2 x 150P10	HCPK5
	240	50 x 6	CB5-5-240505	7TCA083910R1027	2 x 200P10	HCPK5
	240	50 x 6	CB5-5-240506	7TCA083910R1028	2 x 250P10	HCPK5
	300	50 x 6	CB5-5-300506	7TCA083910R1031	2 x 250P10	HCPK5

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*2 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection