


Temp.
0 25 40 50 60



Shift index for long-time delay only.

MULTIPLES OF CURRENT RATING



Molded Case Circuit Breaker E 100 LINE

GES6122

Current Ratings

15, 20, 25, 30, 35, 40, 45 and 50 Amperes

Voltage Ratings

1 pole – 120 Vac (125 Vdc)
2 and 3 pole – 240 Vac (250 Vdc)

Frequency Rating

60 Hertz

Type TEB, 15-50 Amperes
Enclosure Compensated
Long-time Delay and Instantaneous

Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use shift index at top of sheet.

Adjustments

Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.