



# 中国国家强制性产品认证证书

证书编号: 2006010304213519

委托人名称、地址

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

生产者(制造商)名称、地址

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

生产企业名称、地址

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

产品名称和系列、规格、型号

交流接触器  
AF1250-30-\*. 详见参数附件

产品标准和技术要求

GB/T14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求,  
特发此证。

发证日期: 2018 年 04 月 28 日 有效期至: 2022 年 06 月 20 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2006 年 12 月 06 日

本证书的相关信息可通过国家认监委网站 [www.cnca.gov.cn](http://www.cnca.gov.cn) 查询



主 任:



## 中国质量认证中心





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO.: 2006010304213519**

## **NAME AND ADDRESS OF THE APPLICANT**

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

## **NAME AND ADDRESS OF THE MANUFACTURER**

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

## **NAME AND ADDRESS OF THE FACTORY**

ABB AB, Control Products  
Motorgrand 20, 72161 Vasteras, Sweden

## **PRODUCT NAME, MODEL AND SPECIFICATION**

AC Contactor  
AF1250-30-\*, See the Appendix

## **THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

**Valid from:** Apr.28,2018

**Valid until:** Jun.20,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Dec.06,2006

The certificate information is available through CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



President:

Wang Kejiao



**CHINA QUALITY CERTIFICATION CENTRE**

<http://www.cqc.com.cn>

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666

Q 1932240





# 中国国家强制性产品认证证书

附 录

第 1 页 共 3 页

证书编号: 2006010304213519

纸 号: 1932240

AF1250-30-\*\*-\*

Ui: 1000V;

Uimp: 8kV;

Ith: 1260A;

AC-1: Ue/Ie: 1000V/1260A;

AC-3: Ue/Ie: 380-400V/800A;

Us: 48-130V AC/DC, 100-250V AC/DC, 250-500V AC/DC (50Hz/60Hz),  
24-60V DC;

极数: 3P;

配用辅助触头:

CAL18-11, CAL18-11B, CAL18-11RT: 1N01NC, 2N02NC; Ith: 16A;

AC-15: Ue/Ie: 24-127V/6A, 220-240V/4A, 280-440V/3A, 500-690V/2A;

DC-13: Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 125V/0.55A, 250V/0.3A

CEL18-10, CEL18-01: 1N0, 1NC; Ith: 0.1A;

AC-14: Ue/Ie: 24-125V/0.1A, DC-12: Ue/Ie: 24-110V/0.1A

注: 此附录与证书同时使用时有效。



主 任:



## 中国质量认证中心





# 中国国家强制性产品认证证书

附 录

证书编号: 2006010304213519

第 2 页 共 3 页

纸 号: 1932240

型号解释:

注: 此附录与证书同时使用时有效。



主 任:



## 中国质量认证中心





# 中国国家强制性产品认证证书

附 录

证书编号: 2006010304213519

第 3 页 共 3 页

纸 号: 1932240

| Full type |               | AF1250-30-11-68 |        |        |        |
|-----------|---------------|-----------------|--------|--------|--------|
|           |               | 1 (AF1250)      | 2 (30) | 3 (11) | 4 (68) |
| Position  | product       | √               | √      |        |        |
|           | package label | √               | √      | √      | √      |

AF1250 -30 -11 -70  
-1 -2 -3 -4

1 = Name of series and size of contactor  
AF1250 = Basic model

2: Number of main contacts  
30 = 3 NO- and 0 NC-contacts

3: Number of NO and NC auxiliary contacts (CAL18-11, CEL18-01 or CEL18-10)  
00 = without auxiliary contact  
11 = 1 NO- and 1 NC-contacts (side mounted CAL18-11)  
22 = 2 NO- and 2 NC-contacts (side mounted, 2 pieces CAL18-11)  
01 = 0 NO- and 1 NC-contacts (side-mounted CEL18-01)  
10 = 1 NO- and 0 NC-contacts (side-mounted CEL18-10)

4: Control supply voltage code  
68: Us = 24-60V d.c. with PLC-control  
69: Us = 48-130V a.c./d.c. with PLC-control  
70: Us = 100-250V a.c./d.c. with PLC-control  
71: Us = 250-500V a.c./d.c. with PLC-control

注: 此附录与证书同时使用时有效。



主 任:



## 中国质量认证中心