







35mm EN/IEC 60715



| Products reference   | Dimensions |        |        |
|----------------------|------------|--------|--------|
|                      | R (mm)     | P (mm) | Q (mm) |
| AF09..16(Z)-xx-xx-xx | 65.5       | 38     | 87     |
| AF09..16Z-xx-xx-30   | 85.5       | 58     | 107    |

(\*) : Minimum distance to grounded component

|              |            |                                           |                 |                |                     |              |
|--------------|------------|-------------------------------------------|-----------------|----------------|---------------------|--------------|
| Code article |            | Material                                  |                 | Heat treatment | Surface treatment   | Finish       |
| Created by   |            | Andre Imperato                            |                 | Checked by     | Approved by         | Hugo Guilhem |
| Created on   |            | 2018-02-07                                |                 | Checked on     | Approved on         | 2018-02-07   |
|              | Comments   |                                           |                 |                |                     | Folio: 1/1   |
|              | ECN number | Approuvé                                  | Language: FR/EN | Format: A3     | Scale: 1:1          | PRUFRFRA_EPP |
| Title        |            | AF09....16 + LF16-4 DIMENSIONS + DRILLING |                 | PRT            | 1SBB910501R3501 B.2 |              |
| Title (en)   |            | AF09....16 + LF16-4 DIMENSIONS + DRILLING |                 | DRW            | 1SBB910501D3501 B   |              |