


NOTES:

1. RADIO KEY DELAY MUST BE SET BETWEEN 200 & 250 MS. APPROPRIATE SOFTWARE CONTAINING PROM RAD DELAY MUST BE USED.


REVISIONS					
REV	ACTION	DRAWN	CHECKED	APPROVED	DATE
AA	L6294	TIERNEY	TIERNEY	HOLLAND	99/02/05
AB	D12502	KASTNER	KASTNER	HOLLAND	02/01/16



ASSEMBLY/QUANTITY		ITEM NO.	PART NUMBER	DESCRIPTION	REF /ZONE DESIG MATERIAL	UNIT MEAS
PARTS LIST						
DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMAL                      ANGULAR .XX ±    —                      ±    — .XXX ±    — BREAK ALL SHARP CORNERS AND EDGES DIMENSIONS APPLY BEFORE FINISH		PRODUCT LINE <b>TOTALFLOW®</b>	LEVEL <b>3</b>	 <b>TOTALFLOW Products</b>
				DESIGN G. HOLLAND	DATE 99/2/5	
				DRAWN TIERNEY	99/2/5	TITLE <b>WIRING INTERCONNECT JOHNSON RNET (9600S) W/MODEM TO 6400 PCBA WI</b>
				CHECKED TIERNEY	99/2/5	
				APPROVED G. HOLLAND	99/2/5	SCALE <b>NONE</b>
						SIZE <b>B</b>
						DOC TYPE <b>WI</b>
						DRAWING NO. <b>2018350</b>
						REV <b>AB</b>
						SHEET <b>1 OF 2</b>

JOHNSON RNET (9600S)  
W/MODEM

DE-15S	SOC	PIN
	J1	W1P1
	1	1
RXD	2	2
TXD	3	3
+VDC	5	5
GND	6	6
RTS	8	8



6400 PCBA  
2015333-XXX  
2015189-XXX

P4	J4	
6	6	RXD+
4	4	TXD+
3	3	SW VBATT
1	1	GND
8	8	RTS