



Test Report				Date of issue: 5.6.2014						
				Serial No.: 3GP11019357						
				Type: M3JP 355SMA 6 B3						
				Product Code: 3GJP353210-ADG						
				Protection type: Ex d IIB T4 Gb						
				Cert. No.: LCIE 10 ATEX 3089X / IECEX LCI 04.0008X						
Rating:				V	Hz	kW	r/min	A	cos φ	Duty
3-Motor				400	D 50	160	993	291	0,83	S1
Insul.cl.F				415	D 50	160	994	284	0,82	S1
IP55				690	Y 50	160	993	169	0,83	S1
Eff class IE2				400 V 50Hz : IE2 - 95.4(100%) - 95.4(75%) - 94,8(50%)						
Resistance				Ambient: 20,0 °C		Insulation resistance at 32,0 °C				
Line						14000 MΩ		1000 V		
U ₁ - V ₁				0,01260 Ω						
U ₁ - W ₁				0,01261 Ω						
V ₁ - W ₁				0,01260 Ω						
						High-voltage test winding		1900 V		60 s
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]	
No load test		400,0 D	50	95,5	2,85		1000	0,04		
Locked rotor test		83,0 D	50	292,8	11,4		0	0,27		
Thermal test (100% load)	1539,0	401,3 D	50	292,0	167,7	160,0	993	0,83	95,4	
Partial load points:										
~75% load	1152,9	401,5 D	50	225,7	125,6	120,0	995	0,80	95,6	
~50% load	767,2	401,7 D	50	166,8	84,1	80,0	997	0,73	95,2	
~25% load	392,1	402,0 D	50	119,0	43,2	40,0	998	0,52	92,7	
Temperature rise at rated load.				[°C]	[K]	Method		Measurement method		
Stator winding :				54,5	1			1 Resistance		
Frame :				29,7	2			2 Thermometer		
Bearing D-end :				40,3	2			3 Thermocouples		
Ambient Temperature :				25,0	2					
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.										
On behalf of customer										
On behalf of manufacturer			Date of test		27.10.2011					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland								Telephone		+358 10 2211
								Telefax		+358 10 22 47372

Computer print-out valid without signature.