


The reproduction, transmission or use of this document or its contents is not permitted without express written authority. Offenders will be liable for damages. All rights, including rights created by patent grant or registration of a utility model or design, are reserved.

Die Weitergabe und Vervielfältigung dieser Unterlage, sowie die Verwertung und Mitteilung ihres Inhaltes ist nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte vorbehalten, besonders für den Fall der Patenterteilung oder OEM-Eintragung.



Tripping characteristic with three pole load and two pole load based at cold state at any setting. With three pole load and two pole load and currents higher than 3 times of current setting the tolerance of the tripping time is +-20%. DIN VDE 0165, IEC 60079-14, EN 50019+A1...A5.

The tripping time of the short-circuit release and the damage curve of the overload release are based on the max. rated operational current.

Maximum permissible fuse if the rated short-circuit breaking capacity is exceeded