

# Current monitoring relays CM-SRS.M1

## For single-phase AC/DC currents

The CM-SRS.M1 is an electronic current monitoring relay that monitors single-phase mains (DC or AC) for over- and undercurrent from 3 mA to 1 A. All devices are available with two different terminal versions. You can choose between the proven screw connection technology (double-chamber cage connecting terminals) and the completely tool-free Easy Connect Technology (push-in terminals).

### Characteristics

- Monitoring of DC and AC currents (3 mA to 1 A)
- TRMS measuring principle
- One device includes 3 measuring ranges
- Over- or undercurrent monitoring configurable
- Open- or closed-circuit principle configurable
- Latching function configurable
- Hysteresis adjustable (3-30 %)
- Precise adjustment by front-face operating controls
- Screw connection technology or Easy Connect Technology available
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting on DIN rail as well as demounting
- Start-up delay  $T_S$  adjustable (0 s; 0.1-30 s)
- Tripping delay  $T_V$  adjustable (0 s; 0.1-30 s)
- 2 c/o (SPDT) contacts
- 22.5 mm (0.89 in) width
- 3 LEDs for status indication



### Approvals

- UL LISTED UL 508, CAN/CSA C22.2 No. 14
- GL GL
- EAC EAC
- CCC CCC
- RMRS RMRS

### Marks

- CE CE
- RCM RCM

### Order data

#### Current monitoring relays

Type	Rated control supply voltage	Connection technology	Measuring ranges	Order code
CM-SRS.M1P	24-240 V AC/DC	Push-in terminals	3-30 mA, 10-100 mA, 0.1-1 A	1SVR740840R0600
CM-SRS.M1S		Screw type terminals		1SVR730840R0600


#### Accessories

Type	Description	Order code
ADP.01	Adapter for screw mounting	1SVR430029R0100
MAR.12	Marker label for devices with DIP switches	1SVR730006R0000
COV.11	Sealable transparent cover	1SVR730005R0100

## Connection technology

Maintenance free Easy Connect Technology with push-in terminals

Type designation CM-xxS.yyP




### Push-in terminals

- Tool-free connection of rigid and flexible wires with wire end ferrule
- Easy connection of flexible wires without wire end ferrule by opening the terminals
- No retightening necessary
- One operation lever for opening both connecting terminals
- For triggering the lever and disconnecting of wires you can use the same tool (Screwdriver according to DIN ISO 2380-1 Form A 0.8 x 4 mm (0.0315 x 0.157 in), DIN ISO 8764-1 PZ1  $\varnothing$  4.5 mm (0.177 in))
- Constant spring force on terminal point independent of the applied wire type, wire size or ambient conditions (e. g. vibrations or temperature changes)
- Opening for testing the electrical contacting
- Gas-tight

Approved screw connection technology with double-chamber cage connecting terminals

Type designation CM-xxS.yyS




### Double-chamber cage connecting terminals

- Terminal spaces for different wire sizes
- One screw for opening and closing of both cages
- Pozidrive screws for pan- or crosshead screwdrivers according to DIN ISO 2380-1 Form A 0.8 x 4 mm (0.0315 x 0.157 in), DIN ISO 8764-1 PZ1  $\varnothing$  4.5 mm (0.177 in)

Both the Easy Connect Technology with push-in terminals and screw connection technology with double-chamber cage connecting terminals have the same connection geometry as well as terminal position.

## Functions

### Operating controls



- 1** Adjustment of the hysteresis (MIN = Default)
- 2** Adjustment of the threshold value (MIN = Default)
- 3** Indication of operational states  
U/T: green LED – control supply voltage/timing  
R: yellow LED – relay status  
I: red LED – over- / undercurrent
- 4** Adjustment of the tripping delay  $T_v$
- 5** Adjustment of the start-up delay  $T_s$
- 6** DIP switches (see DIP switch functions)

### Application

The multifunctional current monitoring relays CM-SRS.M2 are designed for use in single-phase AC and/or DC systems for over- or undercurrent monitoring. The devices operate over an universal range of supply voltages, provide an adjustable start-up as well as tripping delay and work according to the open- or closed-circuit principle.


### Operating mode


The CM-SRS.M1 with 2 c/o (SPDT) contacts offer the following 3 selectable measuring ranges: 3-30 mA, 10-100 mA, 0.1-1 A. The measuring range is selected by connecting the monitored wire to the corresponding terminal B1/B2/B3-C. The units are adjusted with front-face operating controls. The selection of over-  or undercurrent monitoring , open-  or closed-circuit principle  and latching function ON  or OFF  is made with DIP switches. Potentiometers, with direct reading scale, allow the adjustment of the threshold value I, the hysteresis %, the tripping delay  $T_v$  and the start-up delay  $T_s$ . The hysteresis % is adjustable within a range of 3 to 30 % of the threshold value and the tripping delay  $T_v$  and the start-up delay  $T_s$  are adjustable over a range of instantaneous to a 30 s delay. Timing is displayed by a flashing green LED labelled U/T.

**Function diagrams**


**Overcurrent monitoring  without latching **


**Open-circuit principle **


The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  overcurrent is only displayed by glowing of the red LED.

If the measured value exceeds the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED glows. Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value still exceeds the threshold value minus the adjusted hysteresis, the output relays energize and the yellow LED (relay energized) glows.


If the measured value decreases below the threshold value minus the hysteresis, the output relays de-energize and the red and yellow LEDs turn off. If control supply voltage is interrupted, the green LED turns off.

**Closed-circuit principle **


The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins, the output relays energize and the yellow LED (relays energized) glows. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  overcurrent is only displayed by glowing of the red LED.



If the measured value exceeds the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED glows. Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value still exceeds the threshold value minus the adjusted hysteresis, the output relays de-energize and the yellow LED turns off.



If the measured value decreases below the threshold value minus the hysteresis, the output relays re-energize, the yellow LED glows and the red LED turns off. If control supply voltage is interrupted, the output relays de-energize and the green and yellow LEDs turn off.



Undercurrent monitoring  without latching 



Open-circuit principle 



The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  undercurrent is only displayed by flashing  of the red LED.

If the measured value decreases below the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED flashes . Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value is still below the threshold value plus the adjusted hysteresis, the output relays energize and the yellow LED (relays energized) turns off.


If the measured value exceeds the threshold value plus the hysteresis, the output relays de-energize and the red and yellow LEDs turn off. If control supply voltage is interrupted, the green LED turns off.

Closed-circuit principle 

The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins, the output relays energize and the yellow LED (relays energized) glows. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  undercurrent is only displayed by flashing  of the red LED.

If the measured value decreases below the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED flashes . Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value is still below the threshold value plus the adjusted hysteresis, the output relays de-energize and the yellow LED turns off.


If the measured value exceeds the threshold value plus the hysteresis, the output relays re-energize, the yellow LEDs glows and the red LED turns off. If control supply voltage is interrupted, the output relays de-energize and the green and yellow LEDs turn off.





2CDC 252 213 F0205

Overcurrent monitoring  with latching 


Open-circuit principle 



The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  overcurrent is only displayed by glowing of the red LED.

If the measured value exceeds the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED glows. Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value still exceeds the threshold value minus the adjusted hysteresis, the output relays energize and the yellow LED (relay energized) flashes .


If the measured value decreases below the threshold value minus the hysteresis, the red LED turns off. The output relays remain energized (latching function). If control supply voltage is interrupted (reset), the output relays de-energize and the green and yellow LEDs turn off.

Closed-circuit principle 

The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins, the output relays energize and the yellow LED (relays energized) glows. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  overcurrent is only displayed by glowing of the red LED.


If the measured value exceeds the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED glows. Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value still exceeds the threshold value minus the adjusted hysteresis, the output relays de-energize and the yellow LED flashes .



If the measured value decreases below the threshold value minus the hysteresis, the red LED turns off. The output relays remain de-energized (latching function). If control supply voltage is interrupted (reset), the green and yellow LEDs turn off. The output relays energize again when control supply voltage is re-applied.






200C 252 214 F0205

Undercurrent monitoring  with latching 



Open-circuit principle 




The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  undercurrent is only displayed by flashing  of the red LED.

If the measured value decreases below the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED flashes . Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value is still below the threshold value plus the adjusted hysteresis, the output relays energize and the yellow LED (relays energized) flashes .


If the measured value exceeds the threshold value plus the hysteresis, the red LED turns off. The output relays remain energized (latching function). If control supply voltage is interrupted (reset), the output relays de-energize and the green and yellow LEDs turn off.

Closed-circuit principle 

The current to be monitored (measured value) is applied to terminals B1/B2/B3-C. When control supply voltage is applied to terminals A1-A2, the start-up delay  $T_S$  begins, the output relays energize and the yellow LED (relays energized) glows. The green LED flashes  during the start-up delay  $T_S$  and then turns steady. During the start-up delay  $T_S$  undercurrent is only displayed by flashing  of the red LED.


If the measured value decreases below the adjusted threshold value, when  $T_S$  is complete, the tripping delay  $T_V$  starts and the red LED flashes . Timing of  $T_V$  is displayed by the flashing  green LED. When  $T_V$  is complete and the measured value is still below the threshold value plus the adjusted hysteresis, the output relays de-energize and the yellow LED flashes .

If the measured value exceeds the threshold value plus the hysteresis, the red LED turns off. The output relays remain de-energized (latching function). If control supply voltage is interrupted (reset), the green and yellow LEDs turn off. The output relays energize again when control supply voltage is re-applied.



200C 252 215 F0205


## Electrical connection



A1-A2 Rated control supply voltage  
 B1-C Measuring range 1: 3-30 mA  
 B2-C Measuring range 2: 10-100 mA  
 B3-C Measuring range 3: 0.1-1 A  
 11<sub>15</sub>-12<sub>16</sub>/14<sub>18</sub>  
 21<sub>25</sub>-22<sub>26</sub>/24<sub>28</sub> Output contacts – open- or closed-circuit principle

Connection diagram

## DIP switches



1 ON Undercurrent monitoring  
 OFF Overcurrent monitoring  
 2 ON Closed-circuit principle  
 OFF Open-circuit principle  
 3 ON Latching function activated  
 OFF Latching function not activated

OFF = Default











## Technical data

Data at  $T_a = 25\text{ °C}$  and rated values, unless otherwise indicated

### Input circuits

Supply circuit		A1-A2		
Rated control supply voltage $U_s$		24-240 V AC/DC		
Rated control supply voltage $U_s$ tolerance		-15...+10 %		
Rated frequency		50/60 Hz or DC		
Typical current / power consumption	24 V DC	30 mA / 0.75 W		
	115 V AC	17 mA / 1.9 VA		
	230 V AC	11 mA / 2.6 VA		
Power failure buffering time		20 ms		
Transient overvoltage protection		varistors		
Measuring circuit		B1/B2/B3-C		
Monitoring function		over- or undercurrent monitoring configurable		
Measuring method		TRMS measuring principle		
Measuring inputs	terminal connection	B1-C	B2-C	B3-C
	measuring range	3-30 mA	10-100 mA	0.1-1 A
	input resistance	3.3 $\Omega$	1 $\Omega$	0.1 $\Omega$
	pulse overload capacity $t < 1\text{ s}$	500 mA	1 A	10 A
	continuous capacity	50 mA	150 mA	1.5 A
Threshold value		adjustable within the indicated measuring range		
Tolerance of the adjusted threshold value		10 % of the range end value		
Hysteresis related to the threshold value		3-30 % adjustable		
Measuring signal frequency range		DC / 15 Hz - 2 kHz		
Rated measuring signal frequency range		DC / 50-60 Hz		
Maximum response time	AC	80 ms		
	DC	120 ms		
Accuracy within the rated control supply voltage tolerance		$\Delta U \leq 0.5\%$		
Accuracy within the temperature range		$\Delta U \leq 0.06\% / \text{°C}$		
Timing circuit				
Start-up time $T_S$		0 s or 0.1-30 s adjustable		
Time delay $T_V$		0 or 0.1-30 s adjustable		
Repeat accuracy (constant parameters)		$\pm 0.07\%$ of full scale		
Tolerance of the adjusted time delay		-		
Accuracy within the rated control supply voltage tolerance		$\Delta t \leq 0.5\%$		
Accuracy within temperature range		$\Delta t \leq 0.06\% / \text{°C}$		

### User interface

Indication of operational states		
Control supply voltage	U/T: green LED	 : control supply voltage applied  : start-up delay $T_S$ active  : tripping delay $T_V$ active
Measured value	I: red LED	 : overcurrent  : undercurrent
Relay status	R: yellow LED	 : output relay energized, no latching function  : output relay energized, active latching function  : output relay de-energized, active latching function

## Output circuits

Kind of output	11 <sub>15</sub> -12 <sub>16</sub> /14 <sub>18</sub>	relay, 1st c/o (SPDT) contact
	21 <sub>25</sub> -22 <sub>26</sub> /24 <sub>28</sub>	relay, 2nd c/o (SPDT) contact
Operating principle		open- or closed-circuit principle configurable (open-circuit principle: output relays energize if the measured value exceeds $\square_{\uparrow}$ / falls below $\square_{\downarrow}$ the adjusted threshold value, closed-circuit principle: output relays de-energize if measured value exceeds $\square_{\uparrow}$ / falls below $\square_{\downarrow}$ the adjusted threshold value)
Contact material		AgNi
Rated operational voltage $U_e$		250 V
Minimum switching voltage / Minimum switching current		24 V / 10 mA
Maximum switching voltage / Maximum switching current		250 V AC / 4 A AC
Rated operational current $I_e$	AC-12 (resistive) at 230 V	4 A
	AC-15 (inductive) at 230 V	3 A
	DC-12 (resistive) at 24 V	4 A
	DC-13 (inductive) at 24 V	2 A
AC rating (UL 508)	utilization category (Control Circuit Rating Code)	B 300
	max. rated operational voltage	300 V AC
	max. continuous thermal current at B 300	5 A
	max. making/breaking apparent power at B 300	3600/360 VA
Mechanical lifetime		30 x 10 <sup>6</sup> switching cycles
Electrical lifetime	AC-12, 230 V, 4 A	0.1 x 10 <sup>6</sup> switching cycles
Maximum fuse rating to achieve short-circuit protection	n/c contact	10 A fast-acting
	n/o contact	10 A fast-acting

## General data

MTBF		on request	
Duty time		100 %	
Dimensions (W x H x D)	product dimensions	22.5 x 85.6 x 103.7 mm (0.89 x 3.37 x 4.08 in)	
	packaging dimensions	97 x 109 x 30 mm (3.82 x 4.29 x 1.18 in)	
Weight		<b>Screw connection technology</b>	<b>Easy Connect Technology (Push-in)</b>
	net weight	0.153 kg (0.337 lb)	0.142 kg (0.313 lb)
	gross weight	0.175 kg (0.386 lb)	0.164 kg (0.362 lb)
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position		any	
Material of housing		UL 94 V-0	
Degree of protection	housing	IP50	
	terminals	IP20	

## Electrical connection

		Screw connection technology	Easy Connect Technology (Push-in)
Connecting capacity	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm <sup>2</sup> (1 x 18-14 AWG) 2 x 0.5-1.5 mm <sup>2</sup> (2 x 18-16 AWG)	2 x 0.5-1.5 mm <sup>2</sup> (2 x 18-16 AWG)
	rigid	1 x 0.5-4 mm <sup>2</sup> (1 x 20-12 AWG) 2 x 0.5-2.5 mm <sup>2</sup> (2 x 20-14 AWG)	2 x 0.5-1.5 mm <sup>2</sup> (2 x 20-16 AWG)
Stripping length		8 mm (0.32 in)	
Tightening torque		0.6 - 0.8 Nm (7.08 lb.in)	-

## Environmental data

Ambient temperature ranges	operation	-25...+60 °C (-13...+140 °F)
	storage	-40...+85 °C (-40...+185 °F)
Damp heat, cyclic (IEC/EN 60068-2-30)		55 °C, 6 cycles
Vibration, sinusoidal		Class 2
Shock		Class 2

## Isolation data

Rated insulation voltage U <sub>i</sub>	supply / measuring circuit / output	600 V
	output 1 / output 2	250 V
Rated impulse withstand voltage U <sub>imp</sub>	supply / measuring circuit / output	6 kV 1.2/50 µs
	output 1 / output 2	4 kV 1.2/50 µs
Pollution degree		3
Overvoltage category		III

## Standards / Directives


Standards	IEC/EN 60947-5-1, IEC/EN 60255-27, EN 50178
Low Voltage Directive	2014/35/EU
EMC Directive	2014/30/EU
RoHS Directive	2011/65/EU

## Electromagnetic compatibility


Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	Level 3
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3
surge	IEC/EN 61000-4-5	Level 3
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B

## Technical diagrams


### Load limit curves




AC load (resistive)



DC load (resistive)




Derating factor F for inductive AC load



Contact lifetime


## Dimensions

in **mm** and inches




## Accessories


in **mm** and inches



ADP.01 - Adapter for screw mounting



MAR.12 - Marker label for devices with DIP switches



COV.11 - Sealable transparent cover

## Further documentation

Document title	Document type	Document number
Electronic products and relays	Technical catalogue	2CDC 110 004 C02xx
CM-SRS.M	Instruction manual	1SVC 730 620 M0000

You can find the documentation on the internet at [www.abb.com/lowvoltage](http://www.abb.com/lowvoltage)  
 -> Automation, control and protection -> Electronic relays and controls -> Measuring and monitoring relays.

## CAD system files

You can find the CAD files for CAD systems at <http://abb-control-products.partcommunity.com>  
 -> Low Voltage Products & Systems -> Control Products -> Electronic Relays and Controls.

# Contact us

## **ABB STOTZ-KONTAKT GmbH**

P. O. Box 10 16 80  
69006 Heidelberg, Germany  
Phone: +49 (0) 6221 7 01-0  
Fax: +49 (0) 6221 7 01-13 25  
E-mail: info.desto@de.abb.com

You can find the address of your  
local sales organisation on the  
ABB home page  
<http://www.abb.com/contacts>  
-> Low Voltage Products and Systems

### **Note:**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.

Copyright© 2016 ABB  
All rights reserved