



| MVI Fault Interrupter | CO-11-1 Relay | 30-900 Ampere |
|--|---|---|
| MINIMUM TRIPPING AND TOTAL CLEARING TIME-CURRENT CHARACTERISTIC CURVES | | |
| <p>Notes:</p> <ol style="list-style-type: none"> 1. Tested per C37.60 2. Accuracy is equal to +/- 10% of the current or time which ever is greater. 3. Minimum power up current: 15 Amperes 4. Curves are applicable to the operating range of -40°C to +65°C. | <ol style="list-style-type: none"> 5. CT current sensing capability range: 10 -10,000 amperes RMS 6. Curves and trips are set using a personal computer or a control panel 7. The total clearing time-current characteristics curves represent the total time required to detect and interrupt the fault current 8. This curve in its entirety, including the title block, should be printed on a 11"x 17" sheet in order to conform with the C37.41 curve presentation standard (5.6 cm/decade). | <p>CO-11-1 Relay 30-900 Ampere</p> |
|  |  497 Schooley's Mountain Road Hackettstown NJ, 07840 | |
| | | Issue Date: December 13, 2022 Reference number: MVI-TCC-08 |