



Ref. Certif. No.

**SE-94569**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product	Control circuit device and switching element
Name and address of the applicant	ABB France 3 Rue Jean Perrin, CS 90009 69687 Chassieu Cedex FRANCE
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Linaset a. s. Ceskoslovenské armády 362, 747 87 Budisov Nad, Budisovkou CZECH REPUBLIC
Ratings and principal characteristics	AC-15: 24-240V 2A; DC-12: 24V 2A / 48V 1A / 72V 0,3A / 125V 0,2A / 250V 0,1A AC-14: 125V 0,1A; DC-12: 110V 0,1A
Trademark (if any)	<b>ABB</b>
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	CE5-***
Additional information (if necessary may also be reported on page 2)	See also page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-5-1:2016
As shown in the Test Report Ref. No. which forms part of this Certificate	1906643STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB  
Box 1103  
SE-164 22 Kista, Sweden  
Int +46 8 750 00 00

Date: 24 June 2019

**intertek**

Signature:

Fredrik Wennersten

**Additional information**

Type key for product:

CE5 - 10 W 0,1  
1 2 3 4

- 1 = Main designation  
CE5 1 pole, 2nd stack mounted contact block
- 2 = Number of auxiliary contacts  
01 = 0 NO and 1 NC  
10 = 1 NO and 0 NC
- 3 = Connection type  
W = IP67  
D = IP40
- 4 = Rated current  
0,1 = 0,1A  
2 = 2A

Date: 24 June 2019

Signature: 