
Data Sheet DS/NAB-EN Rev. G

# Model NAB Differential pressure transmitter

Deltapi N Series A complete range of pneumatic pressure transmitters



#### Introduction

The blind type differential pressure transmitter mod. NAB is used to measure and convert a differential pressure value into a proportional pneumatic signal.

#### DESCRIPTION

The instrument works on the force-balance principle and consists of two main units.

The measuring unit which detects the differential pressure variation and consists of two forged bodies and a measuring capsule.

The capsule is available in a single version of 5 in diameter diaphragms, filled with a special liquid which can withstand the maximum rated static pressure on either side without damaging itself.

The transmission unit converts the differential force applied to the measuring element into a proportional output pneumatic signal.

The output pressure, generated by a flapper nozzle relay, feeds the feedback bellows with a rising pressure until the bellows force balances that of the measuring element.

**Span value** continuously adjustable by an internal micrometric screw.

**Zero value** adjustable by an external screw.

**Mounting** in a vertical position on 2in diameter pipe by a special bracket.

#### **OPTIONAL EXTRA FEATURES**

**Special feedback bellows** allow to reduce the standard calibration span to a lower value (see table)

A zero elevation or suppression device allows to set as a zero of the transmitter a measured variable value different from zero.

The sum of the zero suppression value (S) plus the calibrated span cannot exceed the upper range limit (M) suitable for the diaphragm capsule:  $S + \text{span} \le M$  (see table).

**Air filter regulator** can be directly mounted on the transmitter, with or without pressure gauge, and connected with piping and fittings either in stainless steel or copper.

Special versions of air filter regulator and gauges, in stainless steel, are available on request.

**Manifold.** The transmitter can be supplied with a 3-valve manifold block integrally mounted to simplify maintenance and calibration procedures.

**Oxygen measurements**, special degreasing and final test operations can be required on the oxygen measuring transmitter

### **SPECIFICATIONS**

The data were obtained from laboratory tests on standard instruments with: carbon steel or AISI 316L bodies; AISI 316L measuring element with silicone oil filling; gasket: PTFE; calibration span: 4 kPa - 40 mbar.

| MEASURING        | SPAN                              | RANGE                                 | MAXIMUM            | MAXIMUM            | STATIC PRESSURE |  |
|------------------|-----------------------------------|---------------------------------------|--------------------|--------------------|-----------------|--|
| CAPSULE          | LIMITS                            | LIMITS                                | ZERO               | ZERO               | LIMITS          |  |
| (DIAPHRAGM DIA.) | min. and max.                     | lover and upper (M)                   | SUPPRESSION (S)    | ELEVATION          | Full vacuum and |  |
| 5 in             | 1.2 and 7.5 kPa<br>12 and 75 mbar | -7.5 and +7.5 kPa<br>-75 and +75 mbar | 6.3 kPa<br>63 mbar | 7.5 kPa<br>75 mbar | 7,5 MPa (•)     |  |
| with special     | 0.6 and 1.2 kPa                   | -7.5 and +7.5 kPa                     | 6.9 kPa            | 7.5 kPa            | 75 bar (•)      |  |
| feedback bellows | 6 and 12 mbar                     | -75 and +75 mbar                      | 69 mbar            | 75 mbar            |                 |  |

<sup>(•)</sup> Equal to Maximum Working pressure as well as overrange limit (on either side).

## Air supply

nom. 140 kPa (1.4 bar, 20 psi); min. 125 kPa (1.25 bar, 18 psi); max. 175 kPa (1.75 bar, 25 psi)

#### **Output signal**

20 to 100 kPa/0.2 to 1 bar, 3 to 15 psi or 0.2 to 1 kg/cm<sup>2</sup>

#### Static air consumption

350 NI/h

#### **Maximum output flow**

with rising output pressure: 30 Nl/min.with falling output pressure: 40 Nl/min.

#### **Accuracy**

± 0.5% F.S.D. (typical)

# **Thermal drift** (for ambient temperature variation between -20° C and + 65° C)

span 1.2 to 2 kPa (12 to 20 mbar): 0.6%/10°C
 span 2 to 7.5 kPa (20 to 75 mbar): 0.4%/10°C

#### Static pressure effect

for variation of 2.5 MPa (25 bar):  $\leq \pm 0.25\%$ 

#### Maximum displacement

2.5 cm<sup>3</sup>

# Degree of protection in accordance with IEC 529 IP55

#### **Ambient temperature limits**

-40 and + 120°C

#### **Bodies material**

Carbon steel, AISI 316L

#### Body bolts and nuts material

High tensile carbon steel; AISI 316 Class A4-80 per ISO3506; AISI 316 Class A4-50 (\*) per ISO3506, in compliance

with NACE MR0175;

high tensile stainless steel, in compliance with NACE MR0175.

(\*) Maximum static pressure reduced to 4 MPa (40 bar)

#### **Cover material**

thermoplastic resin

#### Diaphragm material

AISI 316L, Monel (\*)

(\*) Maximum overrange pressure reduced to 5 MPa (50 bar)

#### **Gaskets material**

PTFE, Viton

#### Capsule filling

Silicone oil, Perfluorinated polyethers (Galden) (\*)

(\*) When used for oxygen measurements the operating temperature limits are -20°C and + 40°C.

#### **Surface protections**

- carbon steel body and flange: zinc plating and chrome passivation,
- AISI 316L body and flange: no protection

#### **Process connections** (see figure ref. D and E)

on flanges: 1/2 in NPT-F
on adapters: 1/4 in NPT-F
center distance: 54 mm.

#### **Pneumatic connections**

- Air supply (in figure ref. A): 1/4 in NPT-F- Output (in figure ref. B): 1/4 in NPT-F

#### Pressure gauge

Brass with stainless steel case (all stainless steel on request) external diameter 51 mm; 0-200 kPa, 0-2 bar and 0-30 psi indication on 82 mm/260° scale.

# Air filter regulator

with copper or stainless steel piping, as specified. Die cast aluminium alloy with light grey epoxy finish.

## Net weight (maximum)

16 kg approx

#### **Packing**

expanded polythene box

# **ORDERING INFORMATION**

Select one character or set of characters from each category and specify complete catalog number.

| PRODUCT CODE  abc de fg hi j k lm  |          |
|--|----------|
| BASE MODEL VERSION BODY MEASURING ELEMENT GASKETS OUTPUT EXTRAS  |          |
|  | Code     |
|  | NAB      |
| de VERSION   |          |
| Standard With Sody Soile and Hate in high tenene carson closi  | 01       |
| The of with integrally incurred marinola (to be quoted coparately)   | 07       |
| Standard with body bolts and nuts in AISI 316  | 11       |
| The TT with integrally incurried marinela (to be queted deparately)  | 17       |
| Chartener than cody contract and the contract chartener  | 21<br>27 |
|  | 51       |
| 51   | 57       |
| 1.6.0.1. Included included the story desired department of the story desired to 4 intra department of the story department | السند    |
| fg BODY  |          |
| Carbon steel   | 01       |

#### **MEASURING ELEMENT**

| hi | Diaphragm<br>material | Core<br>material   | Capsule<br>filling | Capsule diameter | Span limits<br>kPa (inH <sub>2</sub> O) - (Note 1) |    |
|----|-----------------------|--------------------|--------------------|------------------|--|----|
|    | AISI 316L             | AISI 316L (Note 2) | Inert fill (*)     | 5 in             | 1.2 and 7.5 (4.8 and 30)                           | 04 |
|    | AISI 316L             | AISI 316L (Note 2) | Inert fill (*)     | 5 in             | 0.6 and 1.2 (2.4 and 4.8)                          | 06 |
|    | Monel                 | Monel (**)         | Silicone oil       | 5 in             | 1.2 and 7.5 (4.8 and 30)                           | 21 |
|    | Monel                 | Monel (**)         | Silicone oil       | 5 in             | 0.6 and 1.2 (2.4 and 4.8)                          | 23 |
|    | AISI 316L             | AISI 316L (Note 2) | Silicone oil       | 5 in             | 1.2 and 7.5 (4.8 and 30)                           | 41 |
|    | AISI 316L             | AISI 316L (Note 2) | Silicone oil       | 5 in             | 0.6 and 1.2 (2.4 and 4.8)                          | 43 |

Note 1: Multiply by 10 the value in kPa (MPa) to obtain mbar (bar). Note 2: Hastelloy C for some wetted parts.

Suitable for oxygen service (operating temperature limits reduced: -20°C to + 40°C; -4°F to 104°F)

Maximum overrange reduced to 5 MPa (725 psi)


| _ |   | GASKETS       | Fulcrum        |                  |   |  |
|---|---|---------------|----------------|------------------|---|--|
| ı | j | Flange gasket | Capsule gasket | diaphragm gasket |   |  |
|   |   | Viton         | Viton          | Viton            | 4 |  |
|   |   | PTFE (*)      | PTFE (*)       | PTFE (*)         | 5 |  |


(\*) Suitable for oxygen service

| k | OUTPUT   |                      |   |
|---|--|----------------------|---|
|   | 3 to 15 psi  |                      | 1 |
|   | 3 to 15 psi with zero elevation device                     |                      | 2 |
|   | 3 to 15 psi with zero suppression device                   |                      | 3 |
|   | 0.2 to 1.0 kg/cm <sup>2</sup>                              | According to         | 4 |
|   | 0.2 to 1.0 kg/cm <sup>2</sup> with zero elevation device   | ANSI/ISA S 51.1-1979 | 5 |
|   | 0.2 to 1.0 kg/cm <sup>2</sup> with zero suppression device | standard terminology | 6 |
|   | 20 to 100 kPa / 0.2 to 1 bar                               |                      | 7 |
|   | 20 to 100 kPa / 0.2 to 1 bar with zero elevation device    |                      | 8 |
|   | 20 to 100 kPa / 0.2 to 1 bar with zero suppression device  |                      | 9 |

| -v  |    |    | _ |
|-----|----|----|---|
| EX. | ΙП | iA | J |

| lm | Identification tag material | Piping<br>material | Air filter regulator | Pressure<br>gauge |    |
|----|-----------------------------|--------------------|----------------------|-------------------|----|
|    | Stainless Steel             |                    |                      |                   | 02 |
|    | Stainless Steel             | Stainless Steel    | with                 |                   | 10 |
|    | Stainless Steel             | Copper             | with                 |                   | 11 |
|    | Stainless Steel             | Stainless Steel    | with                 | with              | 13 |
|    | Stainless Steel             | Copper             | with                 | with              | 14 |





# Contact us

#### ABB Ltd.

#### **Process Automation**

Howard Road St. Neots Cambridgeshire PE19 8EU UK

Tel: +44 (0)1480 475321 Fax: +44 (0)1480 217948

#### ABB Inc.

#### **Process Automation**

125 E. County Line Road Warminster PA 18974 USA

Tel: +1 215 674 6000 Fax: +1 215 674 7183

# ABB Automation Products GmbH

# **Process Automation**

Schillerstr. 72 32425 Minden Germany

Tel: +49 551 905 534 Fax: +49 551 905 555

### ABB S.p.A.

## **Process Automation**

Via Statale 113 22016 Lenno (CO) Italy

Tel: +39 0344 58111 Fax: +39 0344 56278

www.abb.com

#### Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2011 ABB All rights reserved

3KXP900202R1001

