



# OVR DIN Rail SPD OVRT21N40150PTSU UL 1449 3rd Edition



## Electrical Characteristics

Protection mode		L-N / L-G / N-G
Number of poles / Type of current		2 / AC
Type / Test class		UL 1449 3rd Ed. - Type 4 for Type 2 apps IEC 61 643-1 2nd Ed - T2 / II
Nominal voltage ( $U_n$ ) (L-N)	V	120 +/- 15%
Frequency	Hz	50-60
Maximum continuous operating voltage ( $U_c$ ) (L-N)	V	175
Voltage protection level ( $U_{res}$ ) - 3kA (L-N / L-G)	kV	0.6 / 0.6
Voltage protection level ( $U_{res}$ ) - 5kA (L-N / L-G)	kV	0.7 / 0.7
Voltage protection level ( $U_{res}$ ) - 10kA (L-N / L-G)	kV	0.8 / 0.8
Voltage Protection Rating (VPR - UL 3rd Ed.) (L-N / L-G)	kV	0.6 / 0.7
Nominal discharge current ( $I_n @ 8/20$ )	kA	20
Maximum discharge current ( $I_{max} @ 8/20$ )	kA	40
Follow current interrupt rating ( $I_f$ ) (L-N / N-G)	A	None / 100
Response time	ns	<25
Operating current ( $I_o$ )	mA	<0.1
Short circuit withstand current ( $I_{sc}$ )	kA	200
Integrated thermal disconnecter		Yes
State indicator		Yes
Safety reserve		No
Remote indicator		Yes
Disconnecter	Circuit breaker - B or C curve	A
	Class J fuse	A
		≤125
		≤100

## Mechanical Characteristics

Wire range - solid wire	AWG	4-14
Wire range - stranded wire	AWG	6-14
Stripping length	in	0.5
Tightening torque	in-lbs	24.5
Degree of protection		NEMA 1

## Remote Indicator

Type of contact		1 NO / 1 NC
Minimum load		12 VDC / 10 mA
Maximum load		250 VAC / 1 A
Connection cross section	AWG	16

## Miscellaneous Characteristics

Operating temperature	F	-40° to 176°
Maximum altitude	ft	6562
Weight	lb	0.5
Color of housing / Fire resistance according to UL 94		Gray RAL 7035 / V-0
Reference standards		UL 1449 3rd Ed, IEC 61 643-1 2nd Ed

## Replacement Cartridges

Phase		OVRT240150CU
Neutral		OVRT270NCU

# Contact Us

## **ABB Inc.**

Low Voltage Control Products  
16250 W. Glendale Drive  
New Berlin, WI 53151  
Phone: 888-385-1221  
Fax: 800-726-1441

USA Technical Support & Customer Service:  
888-385-1221, Option 4  
7:30AM to 5:30PM, CST,  
Monday - Friday  
[lvps.support@us.abb.com](mailto:lvps.support@us.abb.com)

Web: [www.abb.us/lowvoltage](http://www.abb.us/lowvoltage)