



Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 400LKC 6																																																																																												
				Product Code: 3GJM403830 - _DG																																																																																												
				Protection type: Ex d I Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3004 X / IECEx LCI 04.0032X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> <th colspan="3"></th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>500</td> <td>993</td> <td>516</td> <td>0,83</td> <td>S1</td> <td colspan="3"></td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>500</td> <td>993</td> <td>891</td> <td>0,83</td> <td>S1</td> <td colspan="3"></td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>500</td> <td>994</td> <td>872</td> <td>0,83</td> <td>S1</td> <td colspan="3"></td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty				3-Motor	690	Y 50	500	993	516	0,83	S1				Insul.cl.F	400	D 50	500	993	891	0,83	S1				IP66	415	D 50	500	994	872	0,83	S1																																													
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	500	993	516	0,83	S1																																																																																									
Insul.cl.F	400	D 50	500	993	891	0,83	S1																																																																																									
IP66	415	D 50	500	994	872	0,83	S1																																																																																									
Cold resistance				Insulation resistance at 74 °C				Overload																																																																																								
Line Ambient: 22 °C				4000 MΩ 1000 V				Torque 160% 15s																																																																																								
U ₁ - V ₁ 0,00277 Ω																																																																																																
U ₁ - W ₁ 0,00278 Ω																																																																																																
V ₁ - W ₁ 0,00278 Ω																																																																																																
				High-voltage test winding 1800 V				60 s																																																																																								
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>400,0</td> <td>D 50</td> <td>285,0</td> <td>6,79</td> <td></td> <td>1000</td> <td>0,03</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>64,1</td> <td>D 50</td> <td>604,0</td> <td>18,1</td> <td></td> <td>0</td> <td>0,19</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>4809</td> <td>400,1</td> <td>D 50</td> <td>892,6</td> <td>519,9</td> <td>500,0</td> <td>993</td> <td>0,84</td> <td>96,2</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>3606</td> <td>400,5</td> <td>D 50</td> <td>689,1</td> <td>389,0</td> <td>375,0</td> <td>995</td> <td>0,82</td> <td>96,4</td> </tr> <tr> <td>~50% load</td> <td>2397</td> <td>400,7</td> <td>D 50</td> <td>506,9</td> <td>259,9</td> <td>250,0</td> <td>997</td> <td>0,74</td> <td>96,2</td> </tr> <tr> <td>~25% load</td> <td>1203</td> <td>401,0</td> <td>D 50</td> <td>259,9</td> <td>132,6</td> <td>125,0</td> <td>999</td> <td>0,53</td> <td>94,3</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		400,0	D 50	285,0	6,79		1000	0,03		Locked rotor test		64,1	D 50	604,0	18,1		0	0,19		Thermal test (100% load)	4809	400,1	D 50	892,6	519,9	500,0	993	0,84	96,2	Partial load points:										~75% load	3606	400,5	D 50	689,1	389,0	375,0	995	0,82	96,4	~50% load	2397	400,7	D 50	506,9	259,9	250,0	997	0,74	96,2	~25% load	1203	401,0	D 50	259,9	132,6	125,0	999	0,53	94,3
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		400,0	D 50	285,0	6,79		1000	0,03																																																																																								
Locked rotor test		64,1	D 50	604,0	18,1		0	0,19																																																																																								
Thermal test (100% load)	4809	400,1	D 50	892,6	519,9	500,0	993	0,84	96,2																																																																																							
Partial load points:																																																																																																
~75% load	3606	400,5	D 50	689,1	389,0	375,0	995	0,82	96,4																																																																																							
~50% load	2397	400,7	D 50	506,9	259,9	250,0	997	0,74	96,2																																																																																							
~25% load	1203	401,0	D 50	259,9	132,6	125,0	999	0,53	94,3																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>78</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>44</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>57</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		78	1	1 Resistance	Frame :		44	2	2 Thermocouples	Bearing D-end :		57	2	3 Thermometer	Ambient Temperature :	25		2																																																														
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		78	1	1 Resistance																																																																																												
Frame :		44	2	2 Thermocouples																																																																																												
Bearing D-end :		57	2	3 Thermometer																																																																																												
Ambient Temperature :	25		2																																																																																													
<p>These tests have been carried out on motor no. 0902-010684594A, on date 2009-03-30, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.